

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Masonary Dry Rot Treatment

Revision Date 24.01.2019

Version 0.0

Print Date 24.01.2019



BUILDING TRUST



SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : Everbuild Masonary Dry Rot Treatment

1.2 Relevant identified uses of the substance or mixture and uses advised against

1.3 Details of the supplier of the safety data sheet

Company : Everbuild – A Sika Company
Site 41
Knowsthorpe Way
Cross Green Industrial Estate
Leeds
West Yorkshire LS9 0SW
United Kingdom

Telephone : 0113 240 3456

E-mail address : everbuild.sds@uk.sika.com

1.4 Emergency telephone number

Emergency telephone number : 0044 113 240 3456 (office hours only)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)

Serious eye damage, Category 1 H318: Causes serious eye damage.

Long-term (chronic) aquatic hazard, Category 2 H411: Toxic to aquatic life with long lasting effects.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :



Signal word : Danger

Hazard statements : H318 Causes serious eye damage.
H411 Toxic to aquatic life with long lasting effects.

Precautionary statements : P101 If medical advice is needed, have product

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Masonary Dry Rot Treatment

Revision Date 24.01.2019



BUILDING TRUST



Version 0.0

Print Date 24.01.2019

P102 container or label at hand.
Keep out of reach of children.

Prevention:

P273 Avoid release to the environment.
P280 Wear protective gloves/ eye protection/ face protection.

Response:

P305 + P351 + P338 + P310 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER/doctor.

Disposal:

P501 Dispose of contents/container in accordance with local regulation.

Hazardous components which must be listed on the label:

- Alcohols, C6-12, ethoxylated

Additional Labelling

EUH208 Contains 3-iodo-2-propynyl butylcarbamate (IPBC). May produce an allergic reaction.

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

Contains a biocide in order to protect the product. Active ingredient: 3-iodo-2-propynyl butylcarbamate (IPBC), 55406-53-6. Please use treated articles responsibly.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Components

Chemical name	CAS-No. EC-No. Registration number	Classification	Concentration (% w/w)
3-iodo-2-propynyl butylcarbamate (IPBC)	55406-53-6 259-627-5	Acute Tox. 4; H302 Acute Tox. 3; H331 Eye Dam. 1; H318 Skin Sens. 1; H317 STOT RE 1; H372 Aquatic Acute 1; H400 Aquatic Chronic 1; H410	>= 0,25 - < 1

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Masonary Dry Rot Treatment

Revision Date 24.01.2019

Version 0.0

Print Date 24.01.2019



BUILDING TRUST



SECTION 4: First aid measures

4.1 Description of first aid measures

- | | | |
|-------------------------|---|---|
| General advice | : | Move out of dangerous area.
Consult a physician.
Show this safety data sheet to the doctor in attendance. |
| If inhaled | : | Move to fresh air.
Consult a physician after significant exposure. |
| In case of skin contact | : | Take off contaminated clothing and shoes immediately.
Wash off with soap and plenty of water.
If symptoms persist, call a physician. |
| In case of eye contact | : | Small amounts splashed into eyes can cause irreversible tissue damage and blindness.
In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
Continue rinsing eyes during transport to hospital.
Remove contact lenses.
Keep eye wide open while rinsing. |
| If swallowed | : | Do not induce vomiting without medical advice.
Rinse mouth with water.
Do not give milk or alcoholic beverages.
Never give anything by mouth to an unconscious person. |

4.2 Most important symptoms and effects, both acute and delayed

- | | | |
|----------|---|--|
| Symptoms | : | Excessive lachrymation
See Section 11 for more detailed information on health effects and symptoms. |
| Risks | : | No known significant effects or hazards.

Causes serious eye damage. |

4.3 Indication of any immediate medical attention and special treatment needed

- | | | |
|-----------|---|------------------------|
| Treatment | : | Treat symptomatically. |
|-----------|---|------------------------|

SECTION 5: Firefighting measures

5.1 Extinguishing media

- | | | |
|------------------------------|---|---|
| Suitable extinguishing media | : | Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. |
|------------------------------|---|---|

5.2 Special hazards arising from the substance or mixture

- | | | |
|---------------------------------------|---|---|
| Specific hazards during fire-fighting | : | Do not allow run-off from fire fighting to enter drains or water courses. |
| Hazardous combustion prod- | : | No hazardous combustion products are known |

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Masonry Dry Rot Treatment

Revision Date 24.01.2019

Version 0.0

Print Date 24.01.2019



BUILDING TRUST



ucts

5.3 Advice for firefighters

Special protective equipment : In the event of fire, wear self-contained breathing apparatus.
for firefighters

Further information : Collect contaminated fire extinguishing water separately. This must not be discharged into drains.
Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Use personal protective equipment.
Deny access to unprotected persons.

6.2 Environmental precautions

Environmental precautions : Do not flush into surface water or sanitary sewer system.
If the product contaminates rivers and lakes or drains inform respective authorities.

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : Avoid exceeding the given occupational exposure limits (see section 8).
Do not get in eyes, on skin, or on clothing.
For personal protection see section 8.
Smoking, eating and drinking should be prohibited in the application area.
Follow standard hygiene measures when handling chemical products

Advice on protection against fire and explosion : Normal measures for preventive fire protection.

Hygiene measures : Handle in accordance with good industrial hygiene and safety practice. When using do not eat or drink. When using do not

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Masonary Dry Rot Treatment

Revision Date 24.01.2019



BUILDING TRUST



Version 0.0

Print Date 24.01.2019

smoke. Wash hands before breaks and at the end of workday.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully re-sealed and kept upright to prevent leakage. Store in accordance with local regulations.

Further information on storage stability : No decomposition if stored and applied as directed.

7.3 Specific end use(s)

Specific use(s) : Consult most current local Product Data Sheet prior to any use.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Contains no substances with occupational exposure limit values.

8.2 Exposure controls

Personal protective equipment

Eye protection : Safety glasses with side-shields
Eye wash bottle with pure water

Hand protection : Chemical-resistant, impervious gloves complying with an approved standard must be worn at all times when handling chemical products. Reference number EN 374. Follow manufacturer specifications.

Suitable for short time use or protection against splashes:
Butyl rubber/nitrile rubber gloves (0,4 mm)
Contaminated gloves should be removed.
Suitable for permanent exposure:
Viton gloves (0.4 mm),
breakthrough time >30 min.

Skin and body protection : Protective clothing (e.g. Safety shoes acc. to EN ISO 20345, long-sleeved working clothing, long trousers). Rubber aprons and protective boots are additionally recommended for mixing and stirring work.

Respiratory protection : No special measures required.

Environmental exposure controls

General advice : Do not flush into surface water or sanitary sewer system. If the product contaminates rivers and lakes or drains inform respective authorities.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Masonry Dry Rot Treatment

Revision Date 24.01.2019

Version 0.0

Print Date 24.01.2019



BUILDING TRUST



SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance	: liquid
Colour	: light yellow
Odour	: characteristic
Odour Threshold	: No data available
pH	: 7,5
Melting point/range / Freezing point	: No data available
Boiling point/boiling range	: No data available
Flash point	: Not applicable
Evaporation rate	: No data available
Flammability (solid, gas)	: No data available
Upper explosion limit / Upper flammability limit	: No data available
Lower explosion limit / Lower flammability limit	: No data available
Vapour pressure	: No data available
Relative vapour density	: No data available
Density	: 1 g/cm ³ (20 °C)
Solubility(ies)	
Water solubility	: soluble
Solubility in other solvents	: No data available
Partition coefficient: n-octanol/water	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Viscosity	
Viscosity, dynamic	: No data available
Viscosity, kinematic	: > 7 mm ² /s (40 °C)

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Masonary Dry Rot Treatment

Revision Date 24.01.2019

Version 0.0

Print Date 24.01.2019



BUILDING TRUST



Explosive properties : No data available

Oxidizing properties : No data available

9.2 Other information

No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

No dangerous reaction known under conditions of normal use.

10.2 Chemical stability

The product is chemically stable.

10.3 Possibility of hazardous reactions

Hazardous reactions : Stable under recommended storage conditions.

10.4 Conditions to avoid

Conditions to avoid : No data available

10.5 Incompatible materials

Materials to avoid : No data available

10.6 Hazardous decomposition products

:
No decomposition if stored and applied as directed.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Not classified based on available information.

Components:

3-iodo-2-propynyl butylcarbamate (IPBC):

Acute oral toxicity : Acute toxicity estimate: 500,0 mg/kg
Method: Converted acute toxicity point estimate

Skin corrosion/irritation

Not classified based on available information.

Serious eye damage/eye irritation

Causes serious eye damage.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Masonary Dry Rot Treatment

Revision Date 24.01.2019



BUILDING TRUST



Version 0.0

Print Date 24.01.2019

Respiratory or skin sensitisation

Skin sensitisation

Not classified based on available information.

Respiratory sensitisation

Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

SECTION 12: Ecological information

12.1 Toxicity

Components:

3-iodo-2-propynyl butylcarbamate (IPBC):

M-Factor (Acute aquatic toxicity) : 10

: 10

M-Factor (Chronic aquatic toxicity) : 1

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Masonary Dry Rot Treatment

Revision Date 24.01.2019



BUILDING TRUST



Version 0.0

Print Date 24.01.2019

to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher..

12.6 Other adverse effects

Product:

Additional ecological information : An environmental hazard cannot be excluded in the event of unprofessional handling or disposal.
Toxic to aquatic life with long lasting effects.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : The generation of waste should be avoided or minimized wherever possible.
Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe way.
Dispose of surplus and non-recyclable products via a licensed waste disposal contractor.
Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.
Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

European Waste Catalogue : 20 01 19* pesticides

Contaminated packaging : 15 01 10* packaging containing residues of or contaminated by dangerous substances

SECTION 14: Transport information

14.1 UN number

Not regulated as a dangerous good

14.2 UN proper shipping name

Not regulated as a dangerous good

14.3 Transport hazard class(es)

Not regulated as a dangerous good

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Masonary Dry Rot Treatment

Revision Date 24.01.2019

Version 0.0

Print Date 24.01.2019



BUILDING TRUST



14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

International Chemical Weapons Convention (CWC) : Not applicable
Schedules of Toxic Chemicals and Precursors

Regulation (EC) No 649/2012 of the European Parliament and the Council concerning the export and import of dangerous chemicals : Not applicable

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : None of the components are listed
(=> 0.1 %).

REACH - List of substances subject to authorisation (Annex XIV) : Not applicable

Regulation (EC) No 1005/2009 on substances that deplete the ozone layer : Not applicable

Regulation (EC) No 850/2004 on persistent organic pollutants : Not applicable

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, preparations and articles (Annex XVII) : Not applicable

REACH Information: All substances contained in our Products are
- registered by our upstream suppliers, and/or
- registered by us, and/or
- excluded from the regulation, and/or
- exempted from the registration.

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.

E2 ENVIRONMENTAL HAZARDS

Volatile organic compounds : Law on the incentive tax for volatile organic compounds (VOCV)
no VOC duties

Directive 2010/75/EU of 24 November 2010 on industrial emissions (integrated pollution prevention and control)
Not applicable

If other regulatory information applies that is not already provided elsewhere in the Safety Data Sheet, then it is described in this subsection.

Health, safety and environmental regulation/legislation : Environmental Protection Act 1990 & Subsidiary Regulations
Health and Safety at Work Act 1974 & Subsidiary Regulations

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Masonary Dry Rot Treatment

Revision Date 24.01.2019

Version 0.0

Print Date 24.01.2019



BUILDING TRUST



specific for the substance or mixture:

Control of Substances Hazardous to Health Regulations (COSHH)
May be subject to the Control of Major Accident Hazards Regulations (COMAH), and amendments.

15.2 Chemical safety assessment

No Chemical Safety Assessment has been carried out for this mixture by the supplier.

SECTION 16: Other information

Full text of H-Statements

H302	: Harmful if swallowed.
H317	: May cause an allergic skin reaction.
H318	: Causes serious eye damage.
H331	: Toxic if inhaled.
H372	: Causes damage to organs through prolonged or repeated exposure if inhaled.
H400	: Very toxic to aquatic life.
H410	: Very toxic to aquatic life with long lasting effects.

Full text of other abbreviations

Acute Tox.	: Acute toxicity
Aquatic Acute	: Short-term (acute) aquatic hazard
Aquatic Chronic	: Long-term (chronic) aquatic hazard
Eye Dam.	: Serious eye damage
Skin Sens.	: Skin sensitisation
STOT RE	: Specific target organ toxicity - repeated exposure
ADR	: European Agreement concerning the International Carriage of Dangerous Goods by Road
CAS	: Chemical Abstracts Service
DNEL	: Derived no-effect level
EC50	: Half maximal effective concentration
GHS	: Globally Harmonized System
IATA	: International Air Transport Association
IMDG	: International Maritime Code for Dangerous Goods
LD50	: Median lethal dosis (the amount of a material, given all at once, which causes the death of 50% (one half) of a group of test animals)
LC50	: Median lethal concentration (concentrations of the chemical in air that kills 50% of the test animals during the observation period)
MARPOL	: International Convention for the Prevention of Pollution from Ships, 1973 as modified by the Protocol of 1978
OEL	: Occupational Exposure Limit
PBT	: Persistent, bioaccumulative and toxic
PNEC	: Predicted no effect concentration
REACH	: Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency
SVHC	: Substances of Very High Concern
vPvB	: Very persistent and very bioaccumulative

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Masonary Dry Rot Treatment

Revision Date 24.01.2019

Version 0.0

Print Date 24.01.2019



BUILDING TRUST



Further information

Classification of the mixture:

Eye Dam. 1	H318
Aquatic Chronic 2	H411

Classification procedure:

Calculation method
Calculation method

The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.

|| Changes as compared to previous version !

GB / EN