


1. Identification

Product identifier	Propylene
Other means of identification	
SDS number	WC001
Product code	MAP-Pro™, PRO-Max™
CAS number	115-07-1
Recommended use	Hand Torch Fuel
Recommended restrictions	None known.
Manufacturer/Importer/Supplier/Distributor information	
Manufacturer/Supplier	Faithfull Tools
Address	Phoenix House, 3 White Lodge Business Estate, Hall Road, Norwich, NR4 6DG
Contact person	Martin Smith
E-mail address	msmith@faithfulltools.com
Telephone number	01603 671653
Emergency telephone number	01603 671653

2. Hazard(s) identification

Physical hazards	Flammable gases Gases under pressure	Category 1 Liquefied gas
Health hazards	Not classified.	
OSHA defined hazards	Simple asphyxiant	
Label elements		
Signal word	Danger	
Hazard statement	Extremely flammable gas. Contains gas under pressure; may explode if heated. May displace oxygen and cause rapid suffocation.	
Precautionary statement		
Prevention	Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Keep container tightly closed. Use only outdoors or in a well-ventilated area. Wear respiratory protection.	
Response	Leaking gas fire: Do not extinguish, unless leak can be stopped safely. Eliminate all ignition sources if safe to do so.	
Storage	Protect from sunlight. Store in a well-ventilated place.	
Disposal	Dispose of waste and residues in accordance with local authority requirements.	
Hazard(s) not otherwise classified (HNOC)	None known.	
Supplemental information	None.	

3. Composition/information on ingredients

Substances

Chemical name	Common name and synonyms	CAS number	%
Propylene		115-07-1	99.5 - 100

Impurities

Chemical name	CAS number	%
Propane	74-98-6	0 - 0.5

Composition comments Gas concentrations are in percent by volume.

4. First-aid measures**Inhalation**

Remove from further exposure. For those providing assistance, avoid exposure to yourself or others. Use adequate respiratory protection. If respiratory tract irritation, dizziness, nausea, or unconsciousness occurs, seek immediate medical assistance. If breathing has stopped, assist ventilation with a mechanical device or use mouth-to-mouth resuscitation.

Skin contact

Not likely, due to the form of the product. If frostbite occurs, immerse affected area in warm water (not exceeding 105°F/41°C). Keep immersed for 20 to 40 minutes. Get medical attention immediately.

Eye contact

Not likely, due to the form of the product. If frostbite occurs, immediately flush eyes with plenty of warm water (not exceeding 105°F/41°C) for at least 15 minutes. If easy to do, remove contact lenses. Get medical attention promptly if symptoms persist or occur after washing.

Ingestion

This material is a gas under normal atmospheric conditions and ingestion is unlikely.

Most important symptoms/effects, acute and delayed

Exposure to rapidly expanding gas or vaporizing liquid may cause frostbite ("cold burn"). Very high exposure can cause suffocation from lack of oxygen. Symptoms may include loss of mobility/consciousness. Victim may not be aware of asphyxiation. Asphyxiation may bring about unconsciousness without warning and so rapidly that victim may be unable to protect themselves.

Indication of immediate medical attention and special treatment needed

Exposure may aggravate pre-existing respiratory disorders. Provide general supportive measures and treat symptomatically.

General information

If you feel unwell, seek medical advice (show the label where possible). Ensure that medical personnel are aware of the material(s) involved, and take precautions to protect themselves.

5. Fire-fighting measures**Suitable extinguishing media**

Dry chemical powder. Carbon dioxide (CO₂). Water fog. Foam.

Unsuitable extinguishing media

Do not use water jet as an extinguisher, as this will spread the fire.

Specific hazards arising from the chemical

Extremely flammable gas. During fire, gases hazardous to health may be formed.

Special protective equipment and precautions for firefighters

Self-contained breathing apparatus and full protective clothing must be worn in case of fire.

Fire fighting equipment/instructions

Do not extinguish fires unless gas flow can be stopped safely; explosive re-ignition may occur. Promptly isolate the scene by removing all persons from the vicinity of the incident. No action shall be taken involving any personal risk or without suitable training. For fires involving this material, do not enter any enclosed or confined fire space without proper protective equipment, including self-contained breathing apparatus. Stop flow of material. Use water to keep fire exposed containers cool and to protect personnel effecting shutoff. If a leak or spill has not ignited, use water spray to disperse the vapors and to protect personnel attempting to stop leak. Prevent runoff from fire control or dilution from entering streams, sewers or drinking water supply.

Specific methods

Use standard firefighting procedures and consider the hazards of other involved materials. Cool containers with flooding quantities of water until well after fire is out.

General fire hazards

Extremely flammable gas. Contents under pressure. Pressurized container may explode when exposed to heat or flame.

6. Accidental release measures**Personal precautions, protective equipment and emergency procedures**

Evacuate the area promptly. No action shall be taken involving any personal risk or without suitable training. In the event of a leak evacuate all personnel until ventilation can restore oxygen concentrations to safe levels. Keep unnecessary personnel away. Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Do not touch damaged containers or spilled material unless wearing appropriate protective clothing. Ventilate closed spaces before entering them. Wear appropriate personal protective equipment (See Section 8).

Methods and materials for containment and cleaning up

Eliminate all ignition sources (no smoking, flares, sparks, or flames in immediate area). Keep combustibles (wood, paper, oil, etc.) away from spilled material. Stop leak if you can do so without risk. If possible, turn leaking containers so that gas escapes rather than liquid. Isolate area until gas has dispersed. For waste disposal, see section 13 of the SDS.

Environmental precautions

Should not be released into the environment. Prevent further leakage or spillage if safe to do so.

7. Handling and storage

Precautions for safe handling

Keep away from heat/sparks/open flames/hot surfaces. - No smoking. Do not handle, store or open near an open flame, sources of heat or sources of ignition. Protect material from direct sunlight. All equipment used when handling the product must be grounded. Do not breathe gas. Avoid prolonged exposure. Do not enter storage areas or confined spaces unless adequately ventilated. Use only outdoors or in a well-ventilated area. Oxygen concentration should not fall below 19.5 % at sea level (pO₂ = 135 mmHg). Mechanical ventilation or local exhaust ventilation may be required. Wear appropriate personal protective equipment. Observe good industrial hygiene practices.

Conditions for safe storage, including any incompatibilities

Store at temperatures not exceeding 49°C/120°F. Keep away from heat, sparks and open flame. Prevent electrostatic charge build-up by using common bonding and grounding techniques. Store in a cool, dry place out of direct sunlight. Cylinders should be stored upright, with valve protection cap in place, and firmly secured to prevent falling or being knocked over. Protect cylinders from damage. Stored containers should be periodically checked for general condition and leakage. Store in original tightly closed container. Keep container tightly closed. Store in a well-ventilated place. Use care in handling/storage. Store away from incompatible materials (see Section 10 of the SDS).

8. Exposure controls/personal protection

Occupational exposure limits

US. OSHA Table Z-1 Limits for Air Contaminants (29 CFR 1910.1000)

Impurities	Type	Value
Propane (CAS 74-98-6)	PEL	1800 mg/m ³ 1000 ppm

US. ACGIH Threshold Limit Values

Components	Type	Value
Propylene (CAS 115-07-1)	TWA	500 ppm

US. NIOSH: Pocket Guide to Chemical Hazards

Impurities	Type	Value
Propane (CAS 74-98-6)	TWA	1800 mg/m ³ 1000 ppm

Biological limit values

No biological exposure limits noted for the ingredient(s).

Appropriate engineering controls

Provide adequate ventilation and minimize the risk of inhalation of gas. Use process enclosures, local exhaust ventilation, or other engineering controls to control airborne levels below recommended exposure limits.

Individual protection measures, such as personal protective equipment

Eye/face protection

Wear approved safety glasses or goggles.

Skin protection

Hand protection

Wear appropriate chemical resistant gloves. Nitrile, butyl rubber or neoprene gloves are recommended.

Skin protection

Other

Wear protective clothing appropriate for the risk of exposure.

Respiratory protection

If engineering controls do not maintain airborne concentrations below recommended exposure limits (where applicable) or to an acceptable level (in countries where exposure limits have not been established), an approved respirator must be worn. Wear air supplied respiratory protection.

Thermal hazards

Contact with liquefied gas might cause frostbites, in some cases with tissue damage. Wear appropriate thermal protective clothing, when necessary.

General hygiene considerations

Do not eat, drink or smoke when using the product. Wash thoroughly after handling. Provide eyewash station and safety shower. Handle in accordance with good industrial hygiene and safety practices.

9. Physical and chemical properties

Appearance

Physical state

Gas.

Form

Compressed liquefied gas.

Color

Colorless.

Odor	Hydrocarbon or mercaptan if odorized.
Odor threshold	Not available.
pH	Not applicable.
Melting point/freezing point	-301 °F (-185 °C)
Initial boiling point and boiling range	-54.4 °F (-48 °C)
Boiling point pressure	101.33 kPa
Flash point	-162.0 °F (-107.8 °C)
Evaporation rate	Not applicable.
Flammability (solid, gas)	Extremely flammable gas.
Upper/lower flammability or explosive limits	
Flammability limit - lower (%)	2 % v/v
Flammability limit - upper (%)	11 % v/v
Vapor pressure	109.73 PSIG
Vapor pressure temp.	69.8 °F (21 °C)
Vapor density	1.5 (Air=1)
Vapor density temp.	32 °F (0 °C) (gas)
Relative density	0.52 (liquid) (H ₂ O=1)
Solubility(ies)	
Solubility (water)	384 mg/l - Slightly soluble in water.
Partition coefficient (n-octanol/water)	1.77
Auto-ignition temperature	927 °F (497.22 °C)
Decomposition temperature	Not available.
Viscosity	Not available.
Other information	
Explosive properties	Not explosive.
Molecular weight	42 g/mol
Oxidizing properties	Not oxidizing.
Percent volatile	100 %
Surface tension	16.7 mN/m (194 °F (90 °C))
VOC	100 % EPA estimated

10. Stability and reactivity

Reactivity	The product is stable and non-reactive under normal conditions of use, storage and transport.
Chemical stability	Stable under normal temperature conditions and recommended use.
Possibility of hazardous reactions	Polymerization will not occur. May form explosive mixture with air. This product may react with oxidizing agents.
Conditions to avoid	Avoid heat, sparks, open flames and other ignition sources. Avoid temperatures exceeding the flash point. Contact with incompatible materials.
Incompatible materials	Strong oxidizing agents. Strong acids. Halogens.
Hazardous decomposition products	Thermal decomposition of this product can generate carbon monoxide and carbon dioxide. Hydrocarbons.

11. Toxicological information

Information on likely routes of exposure

Inhalation	High concentrations: Suffocation (asphyxiant) hazard - if allowed to accumulate to concentrations that reduce oxygen below safe breathing levels. Breathing of high concentrations may cause dizziness, light-headedness, headache, nausea and loss of coordination. Continued inhalation may result in unconsciousness.
Skin contact	Contact with liquefied gas may cause frostbite.
Eye contact	Contact with liquefied gas may cause frostbite.

Ingestion	This material is a gas under normal atmospheric conditions and ingestion is unlikely.	
Symptoms related to the physical, chemical and toxicological characteristics	Exposure to rapidly expanding gas or vaporizing liquid may cause frostbite ("cold burn"). Very high exposure can cause suffocation from lack of oxygen. Victim may not be aware of asphyxiation. Asphyxiation may bring about unconsciousness without warning and so rapidly that victim may be unable to protect themself.	
Information on toxicological effects		
Acute toxicity	Not expected to be acutely toxic.	
Components	Species	Test Results
Propylene (CAS 115-07-1)		
Acute Inhalation Gas		
LC50	Rat	> 65000 ppm, 4 Hours
Skin corrosion/irritation	Not classified.	
Serious eye damage/eye irritation	Not classified.	
Respiratory or skin sensitization		
Respiratory sensitization	Not a respiratory sensitizer.	
Skin sensitization	This product is not expected to cause skin sensitization.	
Germ cell mutagenicity	No data available to indicate product or any components present at greater than 0.1% are mutagenic or genotoxic.	
Carcinogenicity	This product is not considered to be a carcinogen by IARC, ACGIH, NTP, or OSHA.	
IARC Monographs. Overall Evaluation of Carcinogenicity		
Propylene (CAS 115-07-1)	3 Not classifiable as to carcinogenicity to humans.	
NTP Report on Carcinogens		
Not listed.		
OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)		
Not regulated.		
Reproductive toxicity	This product is not expected to cause reproductive or developmental effects.	
Specific target organ toxicity - single exposure	Not classified.	
Specific target organ toxicity - repeated exposure	Not classified.	
Aspiration hazard	Not likely, due to the form of the product.	
Chronic effects	Exposure over a long period of time may cause central nervous system effects.	
12. Ecological information		
Ecotoxicity	The product is not expected to be hazardous to the environment.	
Persistence and degradability	The product is readily biodegradable.	
Bioaccumulative potential	The product is not expected to bioaccumulate.	
Partition coefficient n-octanol / water (log Kow)		
Propylene (CAS 115-07-1)	1.77	
Propane (CAS 74-98-6)	2.36	
Mobility in soil	Not relevant, due to the form of the product.	
Other adverse effects	The product contains volatile organic compounds which have a photochemical ozone creation potential.	
13. Disposal considerations		
Disposal instructions	Use the container until empty. Do not dispose of any non-empty container. Empty containers have residual vapor that is flammable and explosive. Cylinders should be emptied and returned to a hazardous waste collection point. Do not puncture or incinerate even when empty. Dispose in accordance with all applicable regulations.	
Local disposal regulations	Dispose of in accordance with local regulations.	
Hazardous waste code	D001: Waste Flammable material with a flash point <140 °F The waste code should be assigned in discussion between the user, the producer and the waste disposal company.	

Waste from residues / unused products	Dispose in accordance with all applicable regulations.
Contaminated packaging	Empty containers should be taken to an approved waste handling site for recycling or disposal.

14. Transport information

DOT

UN number	UN1077
UN proper shipping name	Propylene
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	-
Environmental hazards	
Marine pollutant	No
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.
Special provisions	19, T50
Packaging exceptions	306
Packaging non bulk	304
Packaging bulk	314, 315

IATA

UN number	UN1077
UN proper shipping name	Propylene
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Label(s)	2.1
Packing group	-
Environmental hazards	No
ERG Code	10L
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

IMDG

UN number	UN1077
UN proper shipping name	PROPYLENE
Transport hazard class(es)	
Class	2.1
Subsidiary risk	-
Packing group	-
Environmental hazards	
Marine pollutant	No
EmS	F-D, S-U
Special precautions for user	Read safety instructions, SDS and emergency procedures before handling.

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not established.

General information Avoid transport on vehicles where the load space is not separated from the driver's compartment. Ensure vehicle driver is aware of the potential hazards of the load and knows what to do in the event of an accident or an emergency. Before transporting product containers: Ensure that containers are firmly secured. Ensure cylinder valve is closed and not leaking. Ensure valve outlet cap nut or plug (where provided) is correctly fitted. Ensure valve protection device (where provided) is correctly fitted. Ensure adequate ventilation. Ensure compliance with applicable regulations.

15. Regulatory information

US federal regulations This product is a "Hazardous Chemical" as defined by the OSHA Hazard Communication Standard, 29 CFR 1910.1200.

TSCA Section 12(b) Export Notification (40 CFR 707, Subpt. D)

Not regulated.

OSHA Specifically Regulated Substances (29 CFR 1910.1001-1050)

Not regulated.

CERCLA Hazardous Substance List (40 CFR 302.4)

Propane (CAS 74-98-6)	LISTED
Propylene (CAS 115-07-1)	LISTED

Superfund Amendments and Reauthorization Act of 1986 (SARA)

Hazard categories

Immediate Hazard - Yes
Delayed Hazard - No
Fire Hazard - Yes
Pressure Hazard - Yes
Reactivity Hazard - No

SARA 302 Extremely hazardous substance

Not listed.

SARA 311/312 Hazardous chemical Yes

SARA 313 (TRI reporting)

Chemical name	CAS number	% by wt.
Propylene	115-07-1	99.5 - 100

Other federal regulations**Clean Air Act (CAA) Section 112 Hazardous Air Pollutants (HAPs) List**

Not regulated.

Clean Air Act (CAA) Section 112(r) Accidental Release Prevention (40 CFR 68.130)

Propane (CAS 74-98-6)
Propylene (CAS 115-07-1)

Safe Drinking Water Act (SDWA) Not regulated.

US state regulations California Safe Drinking Water and Toxic Enforcement Act of 1986 (Proposition 65): This material is not known to contain any chemicals currently listed as carcinogens or reproductive toxins.

US. Massachusetts RTK - Substance List

Propane (CAS 74-98-6)
Propylene (CAS 115-07-1)

US. New Jersey Worker and Community Right-to-Know Act

Propane (CAS 74-98-6)
Propylene (CAS 115-07-1)

US. Pennsylvania Worker and Community Right-to-Know Law

Propane (CAS 74-98-6)
Propylene (CAS 115-07-1)

US. Rhode Island RTK

Propane (CAS 74-98-6)
Propylene (CAS 115-07-1)

International Inventories

Country(s) or region	Inventory name	On inventory (yes/no)*
Australia	Australian Inventory of Chemical Substances (AICS)	Yes
Canada	Domestic Substances List (DSL)	Yes
Canada	Non-Domestic Substances List (NDSL)	No
China	Inventory of Existing Chemical Substances in China (IECSC)	Yes
Europe	European Inventory of Existing Commercial Chemical Substances (EINECS)	Yes
Europe	European List of Notified Chemical Substances (ELINCS)	No
Japan	Inventory of Existing and New Chemical Substances (ENCS)	Yes
Korea	Existing Chemicals List (ECL)	Yes
New Zealand	New Zealand Inventory	Yes
Philippines	Philippine Inventory of Chemicals and Chemical Substances (PICCS)	Yes
United States & Puerto Rico	Toxic Substances Control Act (TSCA) Inventory	Yes

*A "Yes" indicates this product complies with the inventory requirements administered by the governing country(s).

A "No" indicates that one or more components of the product are not listed or exempt from listing on the inventory administered by the governing country(s).

16. Other information, including date of preparation or last revision

Issue date 26-February-2017
Revision date -
Version # 01
Further information The classification for health and environmental hazards is derived by a combination of calculation methods and test data, if available.
HMIS® ratings Health: 1
Flammability: 4
Physical hazard: 1

NFPA ratings



References

HSDB® - Hazardous Substances Data Bank
IARC Monographs. Overall Evaluation of Carcinogenicity
National Toxicology Program (NTP) Report on Carcinogens
ACGIH Documentation of the Threshold Limit Values and Biological Exposure Indices
EPA: AQUIRE database
NLM: Hazardous Substances Data Base

Disclaimer

All information in this Safety Data Sheet is believed to be accurate and reliable. However, no guarantee or warranty of any kind is made with regard to the accuracy of information or the suitability of the recommendations contained herein. It is the user's responsibility to assess the safety and toxicity of this product under their own conditions of use and to comply with all applicable laws and regulations.