



HG laminate protector

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878
Issue date: 06/12/2022 Revision date: 06/12/2022 Version: 1.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : HG laminate protector
Product code : 136 ART
Type of product : Detergent
Product group : Trade product

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Intended for general public
Main use category : Consumer use

1.2.2. Uses advised against

Restrictions on use : All other uses not recommended above

1.3. Details of the supplier of the safety data sheet

Manufacturer

HG International B.V.
P.J. Oudweg 41
NL- 1314 CJ Almere
The Netherlands
T +31 (0)36 54 94 700
safety@hg.eu - www.hg.eu

Distributor

HG UKI LTD
Weston Business Centre
Parsonage Road
UK- CM22 6PU Takeley – Essex
United Kingdom
T +44 (0) 1206 822 744
www.hg.eu

1.4. Emergency telephone number

Emergency number : +31 (0)36 54 94 777
Only for medical personnel
Mon-Fri 09:00 AM - 05:00 PM (CEST)

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	Only for healthcare professionals
United Kingdom	Guy's & St Thomas' Poisons Unit Medical Toxicology Unit, Guy's & St Thomas' Hospital Trust	Avonley Road SE14 5ER London	+44 20 7188 7188	

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

Adverse physicochemical, human health and environmental effects

To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Precautionary statements (CLP) : P102 - Keep out of reach of children.

HG laminate protector

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

EUH-statements : EUH208 - Contains triisobutyl phosphate (126-71-6) (00086), Rosin, fumarated, polymer with glycerol, ammonium salt (68554-18-7) (00305). May produce an allergic reaction.

2.3. Other hazards

Contains no PBT/vPvB substances $\geq 0,1\%$ assessed in accordance with REACH Annex XIII

The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or is not identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at a concentration equal to or greater than 0,1 %

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	Conc. (% w/w)	Classification according to Regulation (EC) No. 1272/2008 [CLP]
PPG-2 METHYL ETHER substance with national workplace exposure limit(s) (AT, BE, BG, CY, CZ, DK, EE, ES, FI, FR, GB, GI, GR, HR, HU, IE, IT, LT, LU, LV, MT, NL, PL, PT, RO, SE, SI, SK); substance with a Community workplace exposure limit	CAS-No.: 34590-94-8 EC-No.: 252-104-2 REACH-no: 01-2119450011-60	$\geq 1 - < 2$	Not classified
Rosin, fumarated, polymer with glycerol, ammonium salt	CAS-No.: 68554-18-7 EC-No.: 812-691-3	$\geq 0,1 - < 1$	Eye Irrit. 2, H319 Skin Sens. 1B, H317 Aquatic Chronic 4, H413
triisobutyl phosphate substance with national workplace exposure limit(s) (AT, DE, SI)	CAS-No.: 126-71-6 EC-No.: 204-798-3 REACH-no: 01-2119957118-32	$\geq 0,1 - < 1$	Skin Sens. 1, H317 Aquatic Chronic 3, H412

Full text of H- and EUH-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact : Wash skin with plenty of water.
First-aid measures after eye contact : Rinse eyes with water as a precaution.
First-aid measures after ingestion : Call a poison center or a doctor if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

No additional information available

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.

HG laminate protector

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released.

5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Protective equipment : See Section 8 for information on personal protection equipment.
Emergency procedures : Ventilate spillage area.

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

For containment : Stop leak if safe to do so. Contain any spills with dikes or absorbents to prevent migration and entry into sewers or streams. Do not touch or walk on the spilled product.
Methods for cleaning up : Take up liquid spill into absorbent material.
Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Wear personal protective equipment. Wash contaminated clothes.
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in a well-ventilated place. Keep cool.
Storage temperature : 20 °C
Storage area : Keep out of frost.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

HG laminate protector

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

PPG-2 METHYL ETHER (34590-94-8)	
EU - Indicative Occupational Exposure Limit (IOEL)	
Local name	(2-Methoxymethylethoxy)-propanol
IOEL TWA	308 mg/m ³
IOEL TWA [ppm]	50 ppm
Remark	Skin
Regulatory reference	COMMISSION DIRECTIVE 2000/39/EC
United Kingdom - Occupational Exposure Limits	
Local name	(2-methoxymethylethoxy) propanol
WEL TWA (OEL TWA) [1]	308 mg/m ³
WEL TWA (OEL TWA) [2]	50 ppm
Remark	Sk (Can be absorbed through the skin. The assigned substances are those for which there are concerns that dermal absorption will lead to systemic toxicity)
Regulatory reference	EH40/2005 (Fourth edition, 2020). HSE

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

8.2.2. Personal protection equipment

Personal protective equipment symbol(s):



8.2.2.1. Eye and face protection

Eye protection:

Safety glasses with side shields

Eye protection			
Type	Field of application	Characteristics	Standard
Safety glasses with side shields	Normal use conditions		EN 166

8.2.2.2. Skin protection

Skin and body protection:

Long sleeved protective clothing. Chemical resistant safety shoes

HG laminate protector

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Skin and body protection	
Type	Standard
Long sleeved protective clothing	
Chemical resistant safety shoes	EN ISO 20345

Hand protection:

Protective gloves

Hand protection					
Type	Material	Permeation	Thickness (mm)	Penetration	Standard
Disposable gloves	Nitrile rubber (NBR)	6 (> 480 minutes)	0,35		EN ISO 374
Disposable gloves	Butyl rubber	6 (> 480 minutes)	0,5		EN ISO 374

8.2.2.3. Respiratory protection

Respiratory protection:

No respiratory protection needed under normal use conditions

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Environmental exposure controls:

Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: white.
Odour	: characteristic.
Odour threshold	: Not available
Melting point	: Not applicable
Freezing point	: 5 °C
Boiling point	: 100 °C
Flammability	: Not applicable
Explosive limits	: Not available
Lower explosion limit	: Not available
Upper explosion limit	: Not available
Flash point	: > 100 °C
Auto-ignition temperature	: Not available
Decomposition temperature	: Not available
pH	: 8.8
Viscosity, kinematic	: Not available
Solubility	: Not available
Partition coefficient n-octanol/water (Log Kow)	: Not available
Vapour pressure	: Not available
Vapour pressure at 50°C	: Not available
Density	: Not available
Relative density	: 1.013
Relative vapour density at 20°C	: Not available
Particle characteristics	: Not applicable

9.2. Other information

9.2.1. Information with regard to physical hazard classes

No additional information available

HG laminate protector

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

9.2.2. Other safety characteristics

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity (oral) : Not classified
Acute toxicity (dermal) : Not classified
Acute toxicity (inhalation) : Not classified

triisobutyl phosphite (126-71-6)	
LD50 oral	> 5000 mg/kg bodyweight
LD50 dermal	> 5000 mg/kg bodyweight
LC50 Inhalation - Rat (Dust/Mist)	> 5140 mg/l

Skin corrosion/irritation : Not classified
pH: 8.8
Serious eye damage/irritation : Not classified
pH: 8.8
Respiratory or skin sensitisation : Not classified
Germ cell mutagenicity : Not classified
Carcinogenicity : Not classified
Reproductive toxicity : Not classified
STOT-single exposure : Not classified
STOT-repeated exposure : Not classified
Aspiration hazard : Not classified

11.2. Information on other hazards

No additional information available

HG laminate protector

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.

Hazardous to the aquatic environment, short-term (acute) : Not classified

Hazardous to the aquatic environment, long-term (chronic) : Not classified

Not rapidly degradable

triisobutyl phosphate (126-71-6)	
EC50 - Other aquatic organisms [1]	11 mg/l waterflea
EC50 - Other aquatic organisms [2]	34.1 mg/l

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

triisobutyl phosphate (126-71-6)	
Partition coefficient n-octanol/water (Log Pow)	3.7

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Endocrine disrupting properties

No additional information available

12.7. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Regional legislation (waste) : Disposal must be done according to official regulations.

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number or ID number				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.2. UN proper shipping name				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated

HG laminate protector

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

ADR	IMDG	IATA	ADN	RID
14.4. Packing group				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

14.6. Special precautions for user

Overland transport

Not regulated

Transport by sea

Not regulated

Air transport

Not regulated

Inland waterway transport

Not regulated

Rail transport

Not regulated

14.7. Maritime transport in bulk according to IMO instruments

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

REACH Annex XVII (Restriction List)

Contains no substance(s) listed on REACH Annex XVII (Restriction Conditions)

REACH Annex XIV (Authorisation List)

Contains no substance(s) listed on REACH Annex XIV (Authorisation List)

REACH Candidate List (SVHC)

Contains no substance(s) listed on the REACH Candidate List

PIC Regulation (Prior Informed Consent)

Contains no substance(s) listed on the PIC list (Regulation EU 649/2012 concerning the export and import of hazardous chemicals)

POP Regulation (Persistent Organic Pollutants)

Contains no substance(s) listed on the POP list (Regulation EU 2019/1021 on persistent organic pollutants)

Ozone Regulation (1005/2009)

Contains no substance(s) listed on the Ozone Depletion list (Regulation EU 1005/2009 on substances that deplete the ozone layer)

Detergent Regulation (648/2004)

Labelling of contents	
Component	%
phosphates	<5%
BENZISOTHIAZOLINONE	

HG laminate protector

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Explosives Precursors Regulation (2019/1148)

Contains no substance(s) listed on the Explosives Precursors list (Regulation EU 2019/1148 on the marketing and use of explosives precursors)

Drug Precursors Regulation (273/2004)

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on the manufacture and the placing on market of certain substances used in the illicit manufacture of narcotic drugs and psychotropic substances)

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Abbreviations and acronyms:

ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant

HG laminate protector

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Abbreviations and acronyms:	
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified
vPvB	Very Persistent and Very Bioaccumulative
ED	Endocrine disrupting properties

Full text of H- and EUH-statements:	
Aquatic Chronic 3	Hazardous to the aquatic environment – Chronic Hazard, Category 3
Aquatic Chronic 4	Hazardous to the aquatic environment – Chronic Hazard, Category 4
EUH208	Contains triisobutyl phosphate (126-71-6) (00086), Rosin, fumarated, polymer with glycerol, ammonium salt (68554-18-7) (00305). May produce an allergic reaction.
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H412	Harmful to aquatic life with long lasting effects.
H413	May cause long lasting harmful effects to aquatic life.
Skin Sens. 1	Skin sensitisation, Category 1
Skin Sens. 1B	Skin sensitisation, category 1B

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.