

SECTION 1: Identification of the substance/mixture and of the company/undertaking**1.1. Product identifier**

Product form : Mixture
Product name : Rhino Non-Acid Drain Unblocker
Type of product : Detergent

1.2. Relevant identified uses of the substance or mixture and uses advised against**1.2.1. Relevant identified uses**

Intended for general public
Main use category : Professional use, Consumer use
Use of the substance/mixture : Cleaning agent

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Kilrock Products Ltd
Units 1b/2b
Alma Road ind Est
HP5 3HB Chesham - United Kingdom
T +44 (0)1494 793900
velda@kilrock.co.uk

1.4. Emergency telephone number

Emergency number : +44 (0)1494 793900

SECTION 2: Hazards identification**2.1. Classification of the substance or mixture****Classification according to Regulation (EC) No. 1272/2008 [CLP]**

Skin corrosion/irritation, Category 1A H314

Full text of hazard classes and H-statements : see section 16

Adverse physicochemical, human health and environmental effects

Causes severe skin burns and eye damage.

2.2. Label elements**Labelling according to Regulation (EC) No. 1272/2008 [CLP]**

Hazard pictograms (CLP) :



GHS05

Signal word (CLP) : Danger
Hazardous ingredients : Sodium Hydroxide
Hazard statements (CLP) : H314 - Causes severe skin burns and eye damage.
Precautionary statements (CLP) : P102 - Keep out of reach of children.
P260 - Do not breathe fume, mist, spray, vapours.
P280 - Wear eye protection, protective clothing, protective gloves.
P301+P330+P331 - IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P303+P361+P353 - IF ON SKIN (or hair): Remove/Take off immediately all contaminated clothing. Rinse skin with water/shower.
P304+P340 - IF INHALED: remove victim to fresh air and keep at rest in a position comfortable for breathing.
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P310 - Immediately call a POISON CENTER or doctor/physician.
P501 - Dispose of contents/container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.

Security closing plug for children : Applicable
Tactile warning : Applicable

Rhino Non-Acid Drain Unblocker

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Sodium Hydroxide	(CAS-No.) 1310-73-2 (EC-No.) 215-185-5 (EC Index-No.) 011-002-00-6 (REACH-no) 01-2119457892-27	20 - 40	Skin Corr. 1A, H314
Reaction products of C12-18-(even numbered)-alkylamines and acrylic acid and sodium hydroxide	(EC-No.) 939-647-7	1 - 10	Skin Irrit. 2, H315 Eye Dam. 1, H318

Specific concentration limits:

Name	Product identifier	Specific concentration limits
Sodium Hydroxide	(CAS-No.) 1310-73-2 (EC-No.) 215-185-5 (EC Index-No.) 011-002-00-6 (REACH-no) 01-2119457892-27	(0.5 =<C < 2) Eye Irrit. 2, H319 (0.5 =<C < 2) Skin Irrit. 2, H315 (2 =<C < 5) Skin Corr. 1B, H314 (C >= 5) Skin Corr. 1A, H314

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Call a physician immediately.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Rinse skin with water/shower. Remove/Take off immediately all contaminated clothing. Call a physician immediately.
First-aid measures after eye contact	: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Call a physician immediately.
First-aid measures after ingestion	: Rinse mouth. Do not induce vomiting. Call a physician immediately.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after skin contact	: Burns.
Symptoms/effects after eye contact	: Serious damage to eyes.
Symptoms/effects after ingestion	: Burns.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Use extinguishing media appropriate for surrounding fire.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released.

5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area. Avoid contact with skin and eyes. Do not breathe fume, mist, spray, vapours.

Rhino Non-Acid Drain Unblocker

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Take up liquid spill into absorbent material.
Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Avoid contact with skin and eyes. Do not breathe fume, mist, spray, vapours. Wear personal protective equipment.
Hygiene measures : Wash contaminated clothing before reuse. Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store locked up. Store in a well-ventilated place. Keep cool.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Sodium Hydroxide (1310-73-2)		
United Kingdom	Local name	Sodium hydroxide
United Kingdom	WEL STEL (mg/m ³)	2 mg/m ³

8.2. Exposure controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

Personal protective equipment:

Avoid all unnecessary exposure. Safety glasses. Gloves. Protective clothing.

Hand protection:

Protective gloves

Eye protection:

Safety glasses

Skin and body protection:

Wear suitable protective clothing

Respiratory protection:

Wear respiratory protection



Environmental exposure controls:

Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Liquid
Colour : No data available
Odour : No data available

Rhino Non-Acid Drain Unblocker

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Not applicable
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: No data available
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity	: Not classified
Skin corrosion/irritation	: Causes severe skin burns and eye damage.
Serious eye damage/irritation	: Serious eye damage, category 1, implicit
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
STOT-single exposure	: Not classified
STOT-repeated exposure	: Not classified
Aspiration hazard	: Not classified

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : Before neutralisation, the product may represent a danger to aquatic organisms.

Rhino Non-Acid Drain Unblocker

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Sodium Hydroxide (1310-73-2)	
LC50 fish 1	> 35 mg/l
EC50 other aquatic organisms 1	> 33 mg/l waterflea

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

Sodium Hydroxide (1310-73-2)	
Log Pow	-3.88

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.
Ecology - waste materials : Avoid release to the environment.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
1824	1824	1824	1824	1824
14.2. UN proper shipping name				
SODIUM HYDROXIDE SOLUTION	SODIUM HYDROXIDE SOLUTION	Sodium hydroxide solution	SODIUM HYDROXIDE SOLUTION	SODIUM HYDROXIDE SOLUTION
Transport document description				
UN 1824 SODIUM HYDROXIDE SOLUTION, 8, II, (E)	UN 1824 SODIUM HYDROXIDE SOLUTION, 8, II	UN 1824 Sodium hydroxide solution, 8, II	UN 1824 SODIUM HYDROXIDE SOLUTION, 8, II	UN 1824 SODIUM HYDROXIDE SOLUTION, 8, II
14.3. Transport hazard class(es)				
8	8	8	8	8
				
14.4. Packing group				
II	II	II	II	II
14.5. Environmental hazards				
Dangerous for the environment : No	Dangerous for the environment : No Marine pollutant : No	Dangerous for the environment : No	Dangerous for the environment : No	Dangerous for the environment : No
No supplementary information available				

14.6. Special precautions for user

- Overland transport

Classification code (ADR) : C5
Limited quantities (ADR) : 11
Excepted quantities (ADR) : E2
Packing instructions (ADR) : P001, IBC02
Mixed packing provisions (ADR) : MP15
Portable tank and bulk container instructions (ADR) : T7
Portable tank and bulk container special provisions (ADR) : TP2

Rhino Non-Acid Drain Unblocker

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Tank code (ADR) : L4BN
Vehicle for tank carriage : AT
Transport category (ADR) : 2
Hazard identification number (Kemler No.) : 80
Orange plates :



Tunnel restriction code (ADR) : E
EAC code : 2R

- Transport by sea

Limited quantities (IMDG) : 1 L
Excepted quantities (IMDG) : E2
Packing instructions (IMDG) : P001
IBC packing instructions (IMDG) : IBC02
Tank instructions (IMDG) : T7
Tank special provisions (IMDG) : TP2
EmS-No. (Fire) : F-A
EmS-No. (Spillage) : S-B
Stowage category (IMDG) : A
Segregation (IMDG) : SG35
Properties and observations (IMDG) : Colourless liquid. Colourless liquid. Reacts with ammonium salts, evolving ammonia gas. Causes burns to skin, eyes and mucous membranes. Reacts violently with acids.

- Air transport

PCA Excepted quantities (IATA) : E2
PCA Limited quantities (IATA) : Y840
PCA limited quantity max net quantity (IATA) : 0.5L
PCA packing instructions (IATA) : 851
PCA max net quantity (IATA) : 1L
CAO packing instructions (IATA) : 855
CAO max net quantity (IATA) : 30L
Special provisions (IATA) : A3
ERG code (IATA) : 8L

- Inland waterway transport

Classification code (ADN) : C5
Limited quantities (ADN) : 1 L
Excepted quantities (ADN) : E2
Carriage permitted (ADN) : T
Equipment required (ADN) : PP, EP
Number of blue cones/lights (ADN) : 0

- Rail transport

Classification code (RID) : C5
Limited quantities (RID) : 1L
Excepted quantities (RID) : E2
Packing instructions (RID) : P001, IBC02
Mixed packing provisions (RID) : MP15
Portable tank and bulk container instructions (RID) : T7
Portable tank and bulk container special provisions (RID) : TP2
Tank codes for RID tanks (RID) : L4BN
Transport category (RID) : 2
Colis express (express parcels) (RID) : CE6
Hazard identification number (RID) : 80

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

Rhino Non-Acid Drain Unblocker

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

The following restrictions are applicable according to Annex XVII of the REACH Regulation (EC) No 1907/2006:

3(b) Substances or mixtures fulfilling the criteria for any of the following hazard classes or categories set out in Annex I to Regulation (EC) No 1272/2008: Hazard classes 3.1 to 3.6, 3.7 adverse effects on sexual function and fertility or on development, 3.8 effects other than narcotic effects, 3.9 and 3.10	Rhino Non-Acid Drain Unblocker - Reaction products of C12-18-(even numbered)-alkylamines and acrylic acid and sodium hydroxide
--	--

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Detergent Regulation : Ingredient data sheet:

Component	CAS-No.	%
AQUA	7732-18-5	>=10%
Sodium hydroxide	1310-73-2	>=10%
Reaction products of C12-18-(even numbered)-alkylamines and acrylic acid and sodium hydroxide		1 - 10%

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Full text of H- and EUH-statements:

Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Skin Corr. 1A	Skin corrosion/irritation, Category 1A
Skin Irrit. 2	Skin corrosion/irritation, Category 2
H314	Causes severe skin burns and eye damage
H315	Causes skin irritation
H318	Causes serious eye damage

SDS EU (REACH Annex II) - Llewellyn

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product