

# SAFETY DATA SHEET



HG carpet & upholstery cleaner

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

**Product name** : HG carpet & upholstery cleaner  
**Product code** : 151 ART  
**Product description** : Cleaner.  
**Product type** : Liquid.  
**Other means of identification** : HG product 95

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Specially developed for cleaning carpet and furniture upholstery with either (spray-extraction) carpet cleaning machine or by hand.

### 1.3 Details of the supplier of the safety data sheet

HG International BV  
Damsluisweg 70 - NL-1332 EJ - Almere - The Netherlands  
Tel.: +31 (0)36 54 94 700 - Fax: +31 (0)36 54 94 744  
Email: info@hg.eu - Internet: www.hg.eu

**e-mail address of person responsible for this SDS** : safety@hg.eu

#### National contact

HG Hagesan UK Ltd.  
Unit 2  
Lanswood Park  
Broomfield Road  
Elmstead Market  
Colchester  
Essex  
CO7 7FD  
Tel.: 0044 (0)1206 822744  
Fax: 0044 (0)1206 827019

### 1.4 Emergency telephone number

#### National advisory body/Poison Centre

**Telephone number** : **England and Wales**  
NHS Direct: 0845 4647

**Scotland**  
NHS 24: 08454 24 24 24

**Republic of Ireland**  
01 809 2166

#### Supplier

**Telephone number** : +31 (0)36 54 94 777  
**Hours of operation** : Mo-Fr 9.00-17.00  
**Information limitations** : Only for medical personnel.

## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

**Product definition** : Mixture

**Classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]**

Eye Dam. 1, H318

The product is classified as hazardous according to Regulation (EC) 1272/2008 as amended.

**Ingredients of unknown toxicity** : 4.2 percent of the mixture consists of component(s) of unknown toxicity

See Section 16 for the full text of the H statements declared above.

See Section 11 for more detailed information on health effects and symptoms.

### 2.2 Label elements

**Hazard pictograms** :



**Signal word** : Danger

**Hazard statements** : Causes serious eye damage.

#### **Precautionary statements**

**General** : If medical advice is needed: Have product container or label at hand. Keep out of reach of children.

**Prevention** : Wear eye protection.

**Response** : IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

**Storage** : Not applicable

**Disposal** : Not applicable

**Hazardous ingredients** : sodium etasulfate

**Supplemental label elements** : Contains 2-methyl-2H-isothiazol-3-one. May produce an allergic reaction.

**Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles** : Not applicable.

#### **Special packaging requirements**

**Containers to be fitted with child-resistant fastenings** : Not applicable.

**Tactile warning of danger** : Not applicable.

### 2.3 Other hazards

**Other hazards which do not result in classification** : None known.

## SECTION 3: Composition/information on ingredients

**3.2 Mixtures** : Mixture

HG carpet & upholstery cleaner

## SECTION 3: Composition/information on ingredients

Product/ingredient name	Identifiers	%	Regulation (EC) No. 1272/2008 [CLP]	Type
sodium etasulfate	EC: 204-812-8 CAS: 126-92-1	≥3 - <5	Skin Irrit. 2, H315 Eye Dam. 1, H318 <b>See Section 16 for the full text of the H statements declared above.</b>	[1]

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs, vPvBs or Substances of equivalent concern, or have been assigned a workplace exposure limit and hence require reporting in this section.

### Type

[1] Substance classified with a health or environmental hazard

[2] Substance with a workplace exposure limit

[3] Substance meets the criteria for PBT according to Regulation (EC) No. 1907/2006, Annex XIII

[4] Substance meets the criteria for vPvB according to Regulation (EC) No. 1907/2006, Annex XIII

[5] Substance of equivalent concern

Occupational exposure limits, if available, are listed in Section 8.

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

- Eye contact** : Get medical attention immediately. Call a poison center or physician. Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 10 minutes. Chemical burns must be treated promptly by a physician.
- Inhalation** : Get medical attention if symptoms occur. Remove victim to fresh air and keep at rest in a position comfortable for breathing.
- Skin contact** : Get medical attention immediately. Call a poison center or physician. Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Wash contaminated clothing thoroughly with water before removing it, or wear gloves. Continue to rinse for at least 10 minutes. Chemical burns must be treated promptly by a physician. Wash clothing before reuse. Clean shoes thoroughly before reuse.
- Ingestion** : Get medical attention immediately. Call a poison center or physician. Chemical burns must be treated promptly by a physician.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training. If it is suspected that fumes are still present, the rescuer should wear an appropriate mask or self-contained breathing apparatus. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Wash contaminated clothing thoroughly with water before removing it, or wear gloves.

### 4.2 Most important symptoms and effects, both acute and delayed

#### Over-exposure signs/symptoms

- Eye contact** : Adverse symptoms may include the following:  
pain  
watering  
redness
- Inhalation** : No specific data.
- Skin contact** : Adverse symptoms may include the following:  
pain or irritation  
redness  
blistering may occur
- Ingestion** : Adverse symptoms may include the following:  
stomach pains

### 4.3 Indication of any immediate medical attention and special treatment needed

## SECTION 4: First aid measures

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

- Suitable extinguishing media** : Not applicable
- Unsuitable extinguishing media** : Not applicable

### 5.2 Special hazards arising from the substance or mixture

- Hazards from the substance or mixture** : In a fire or if heated, a pressure increase will occur and the container may burst.
- Hazardous combustion products** : Decomposition products may include the following materials:  
carbon dioxide  
carbon monoxide  
sulfur oxides  
metal oxide/oxides

### 5.3 Advice for firefighters

- Special protective actions for fire-fighters** : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.
- Special protective equipment for fire-fighters** : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilt material. Do not breathe vapour or mist. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment.
- For emergency responders** : If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

### 6.2 Environmental precautions

- : Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

### 6.3 Methods and material for containment and cleaning up

- Small spill** : Stop leak if without risk. Move containers from spill area. Dilute with water and mop up if water-soluble. Alternatively, or if water-insoluble, absorb with an inert dry material and place in an appropriate waste disposal container. Dispose of via a licensed waste disposal contractor.

## SECTION 6: Accidental release measures

- Large spill** : Stop leak if without risk. Move containers from spill area. Approach the release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Wash spillages into an effluent treatment plant or proceed as follows. Contain and collect spillage with non-combustible, absorbent material e.g. sand, earth, vermiculite or diatomaceous earth and place in container for disposal according to local regulations. Dispose of via a licensed waste disposal contractor. Contaminated absorbent material may pose the same hazard as the spilt product.
- 6.4 Reference to other sections** : See Section 1 for emergency contact information.  
See Section 8 for information on appropriate personal protective equipment.  
See Section 13 for additional waste treatment information.

## SECTION 7: Handling and storage

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

### 7.1 Precautions for safe handling

- Protective measures** : Put on appropriate personal protective equipment (see Section 8). Do not get in eyes or on skin or clothing. Do not breathe vapour or mist. Do not ingest. If during normal use the material presents a respiratory hazard, use only with adequate ventilation or wear appropriate respirator. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Empty containers retain product residue and can be hazardous. Do not reuse container.
- Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

### 7.2 Conditions for safe storage, including any incompatibilities

Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Store locked up. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabelled containers. Use appropriate containment to avoid environmental contamination.

### 7.3 Specific end use(s)

- Recommendations** :
- Industrial sector specific solutions** : Not available.

## SECTION 8: Exposure controls/personal protection

The information in this section contains generic advice and guidance. Information is provided based on typical anticipated uses of the product. Additional measures might be required for bulk handling or other uses that could significantly increase worker exposure or environmental releases.

### 8.1 Control parameters

#### Occupational exposure limits

No exposure limit value known.

- Recommended monitoring procedures** : If this product contains ingredients with exposure limits, personal, workplace atmosphere or biological monitoring may be required to determine the effectiveness of the ventilation or other control measures and/or the necessity to use respiratory protective equipment. Reference should be made to monitoring standards, such as the following: European Standard EN 689 (Workplace atmospheres - Guidance for the assessment of exposure by inhalation to chemical agents for comparison with limit values and measurement strategy) European Standard EN 14042 (Workplace atmospheres - Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents) European Standard EN 482

## SECTION 8: Exposure controls/personal protection

(Workplace atmospheres - General requirements for the performance of procedures for the measurement of chemical agents) Reference to national guidance documents for methods for the determination of hazardous substances will also be required.

### DNELs/DMELs

No DNELs/DMELs available.

### PNECs

No PNECs available

## 8.2 Exposure controls

**Appropriate engineering controls** : If user operations generate dust, fumes, gas, vapour or mist, use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure to airborne contaminants below any recommended or statutory limits.

### Individual protection measures

**Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

**Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: chemical splash goggles and/or face shield. If inhalation hazards exist, a full-face respirator may be required instead. Recommended: chemical splash goggles.

### Skin protection

**Hand protection** : Not applicable

**Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

**Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

**Respiratory protection** : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

**Thermal hazards** :

**Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

#### Appearance

**Physical state** : Liquid.  
**Colour** : Colourless to light yellow. [Light]  
**Odour** : Characteristic.  
**Odour threshold** : Not available.  
**pH** : 9,2  
**Melting point/freezing point** : 0°C  
**Initial boiling point and boiling range** : 100°C

HG carpet & upholstery cleaner

## SECTION 9: Physical and chemical properties

Flash point	: Not available.
Evaporation rate	: Not available.
Flammability (solid, gas)	: Not available.
Upper/lower flammability or explosive limits	: Not available.
Vapour pressure	: Not available.
Vapour density	: Not available.
Relative density	: 1,03
Solubility(ies)	: Easily soluble in the following materials: cold water and hot water.
Partition coefficient: n-octanol/ water	: Not available.
Auto-ignition temperature	: Not available.
Decomposition temperature	: Not available.
Viscosity	: Not available.
Explosive properties	: Not available.
Oxidising properties	: Not available.

### 9.2 Other information

Solubility in water : Not available.

No additional information.

## SECTION 10: Stability and reactivity

10.1 Reactivity	: No specific test data related to reactivity available for this product or its ingredients.
10.2 Chemical stability	: The product is stable.
10.3 Possibility of hazardous reactions	: Under normal conditions of storage and use, hazardous reactions will not occur.
10.4 Conditions to avoid	: Not applicable
10.5 Incompatible materials	: No specific data.
10.6 Hazardous decomposition products	: Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
sodium etasulfate	LD50 Oral	Rat	4 g/kg	-

Conclusion/Summary : Not available.

#### Acute toxicity estimates

Not available.

#### Irritation/Corrosion



## SECTION 11: Toxicological information

Product/ingredient name	Result	Species	Score	Exposure	Observation
sodium etasulfate	Eyes - Mild irritant	Rabbit	-	250 Micrograms	-
	Skin - Moderate irritant	Rabbit	-	500 milligrams	-

**Conclusion/Summary** : Not available.

### Sensitisation

**Conclusion/Summary** : Not available.

### Mutagenicity

**Conclusion/Summary** : Not available.

### Carcinogenicity

**Conclusion/Summary** : Not available.

### Reproductive toxicity

**Conclusion/Summary** : Not available.

### Teratogenicity

**Conclusion/Summary** : Not available.

### Specific target organ toxicity (single exposure)

Not available.

### Specific target organ toxicity (repeated exposure)

Not available.

### Aspiration hazard

Not available.

**Information on likely routes of exposure** : Not available.

### Potential acute health effects

**Eye contact** : Causes serious eye damage.

**Inhalation** : No known significant effects or critical hazards.

**Skin contact** : No known significant effects or critical hazards.

**Ingestion** : No known significant effects or critical hazards.

### Symptoms related to the physical, chemical and toxicological characteristics

**Eye contact** : Adverse symptoms may include the following:  
pain  
watering  
redness

**Inhalation** : No specific data.

**Skin contact** : Adverse symptoms may include the following:  
pain or irritation  
redness  
blistering may occur

**Ingestion** : Adverse symptoms may include the following:  
stomach pains

### Delayed and immediate effects as well as chronic effects from short and long-term exposure

#### Short term exposure

**Potential immediate effects** : Not available.

**Potential delayed effects** : Not available.



HG carpet & upholstery cleaner

## SECTION 11: Toxicological information

### Long term exposure

**Potential immediate effects** : Not available.

**Potential delayed effects** : Not available.

### Potential chronic health effects

Not available.

**Conclusion/Summary** : Not available.

**General** : No known significant effects or critical hazards.

**Carcinogenicity** : No known significant effects or critical hazards.

**Mutagenicity** : No known significant effects or critical hazards.

**Teratogenicity** : No known significant effects or critical hazards.

**Developmental effects** : No known significant effects or critical hazards.

**Fertility effects** : No known significant effects or critical hazards.

**Other information** : Not available.

## SECTION 12: Ecological information

### 12.1 Toxicity

**Conclusion/Summary** : Readily biodegradable

### 12.2 Persistence and degradability

**Conclusion/Summary** : Readily biodegradable

Product/ingredient name	Aquatic half-life	Photolysis	Biodegradability
HG carpet & upholstery cleaner	-	-	Readily

### 12.3 Bioaccumulative potential

Not available.

### 12.4 Mobility in soil

**Soil/water partition coefficient (K<sub>oc</sub>)** : Not available.

**Mobility** : Not available.

### 12.5 Results of PBT and vPvB assessment

**PBT** : Not applicable.

**vPvB** : Not applicable.

**12.6 Other adverse effects** : No known significant effects or critical hazards.

## SECTION 13: Disposal considerations

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

### 13.1 Waste treatment methods

#### Product

## SECTION 13: Disposal considerations

- Methods of disposal** : The generation of waste should be avoided or minimised wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction.
- Hazardous waste** : The classification of the product may meet the criteria for a hazardous waste.
- Packaging**
- Methods of disposal** : The generation of waste should be avoided or minimised wherever possible. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible.
- Special precautions** : This material and its container must be disposed of in a safe way. Care should be taken when handling emptied containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers.

## SECTION 14: Transport information

	ADR/RID	ADN	IMDG	IATA
<b>14.1 UN number</b>	Not regulated.	Not regulated.	Not regulated.	Not regulated.
<b>14.2 UN proper shipping name</b>	-	-	-	-
<b>14.3 Transport hazard class(es)</b>	-	-	-	-
<b>14.4 Packing group</b>	-	-	-	-
<b>14.5 Environmental hazards</b>	No.	No.	No.	No.
<b>Additional information</b>	-	-	-	-

- 14.6 Special precautions for user** : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

- 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code** : Not applicable.

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

#### EU Regulation (EC) No. 1907/2006 (REACH)

#### Annex XIV - List of substances subject to authorisation

#### Annex XIV

None of the components are listed.

#### Substances of very high concern

None of the components are listed.

HG carpet & upholstery cleaner

## SECTION 15: Regulatory information

**Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles** : Not applicable.

### Other EU regulations

**Europe inventory** : Not determined.

### Ozone depleting substances (1005/2009/EU)

Not listed.

### Prior Informed Consent (PIC) (649/2012/EU)

Not listed.

### Seveso Directive

This product is not controlled under the Seveso Directive.

**Contains (Regulation (EC) No 648/2004)** :

anionic surfactants	5-15%
preservation agents: methylisothiazolinone, benzisothiazolinone	

**References** :

### International regulations

#### Chemical Weapon Convention List Schedules I, II & III Chemicals

Not listed.

#### Montreal Protocol (Annexes A, B, C, E)

Not listed.

#### Stockholm Convention on Persistent Organic Pollutants

Not listed.

#### Rotterdam Convention on Prior Informed Consent (PIC)

Not listed.

#### UNECE Aarhus Protocol on POPs and Heavy Metals

Not listed.

### International lists

#### National inventory

**Australia** : Not determined.  
**Canada** : Not determined.  
**China** : Not determined.  
**Turkey** : Not determined.  
**United States** : Not determined.  
**Taiwan** : Not determined.  
**Philippines** : Not determined.  
**New Zealand** : Not determined.  
**Malaysia** : Not determined.  
**Republic of Korea** : Not determined.  
**Japan** : **Japan inventory (ENCS)**: Not determined.  
**Japan inventory (ISHL)**: Not determined.

**15.2 Chemical safety assessment** : This product contains substances for which Chemical Safety Assessments are still required.

## SECTION 16: Other information

Indicates information that has changed from previously issued version.

### Abbreviations and acronyms

: ATE = Acute Toxicity Estimate  
CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]  
DMEL = Derived Minimal Effect Level  
DNEL = Derived No Effect Level  
EUH statement = CLP-specific Hazard statement  
PBT = Persistent, Bioaccumulative and Toxic  
PNEC = Predicted No Effect Concentration  
RRN = REACH Registration Number  
vPvB = Very Persistent and Very Bioaccumulative

### Procedure used to derive the classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Classification	Justification
Eye Dam. 1, H318	Expert judgment

### Full text of abbreviated H statements

H315	Causes skin irritation.
H318	Causes serious eye damage.

### Full text of classifications [CLP/GHS]

Eye Dam. 1, H318 Skin Irrit. 2, H315	SERIOUS EYE DAMAGE/EYE IRRITATION - Category 1 SKIN CORROSION/IRRITATION - Category 2
---	--

**Date of printing** : 16-1-2020

**Date of issue/ Date of revision** : 15-1-2020

**Date of previous issue** : 19-7-2019

**Version** : 2.06

### Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.