

# Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878 Issue date: 09/10/2023 Version: 1.0

# SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixture

Product name : HG natural stone cleaner streak free

Product code : 382 ART
Type of product : Detergent
Product group : Trade product

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

#### 1.2.1. Relevant identified uses

Intended for general public

Main use category : Consumer use Function or use category : Floor cleaning products

1.2.2. Uses advised against

Restrictions on use : All other uses not recommended above

# 1.3. Details of the supplier of the safety data sheet

ManufacturerImporterHG International B.V.HG UKI LTD

P.J. Oudweg 41 Weston Business Centre NL- 1314 CJ Almere Parsonage Road

The Netherlands UK- CM22 6PU Takeley - Essex

T +31 (0)36 54 94 700 United Kingdom

safety@hg.eu - www.hg.eu T +44 (0) 1206 822 744

www.hg.eu

# 1.4. Emergency telephone number

Emergency number : +31 (0)36 54 94 777

Only for medical personnel

Mon-Fri 09:00 AM - 05:00 PM (CEST)

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH	0344 892 0111	Only for healthcare professionals
United Kingdom	Guy's & St Thomas' Poisons Unit Medical Toxicology Unit, Guy's & St Thomas' Hospital Trust	Avonley Road SE14 5ER	+44 20 7188 7188	

### **SECTION 2: Hazards identification**

# 2.1. Classification of the substance or mixture

#### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

### Adverse physicochemical, human health and environmental effects

To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.

# Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

#### 2.2. Label elements

### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Precautionary statements (CLP) : P101 - If medical advice is needed, have product container or label at hand.

P102 - Keep out of reach of children.

EUH-statements : EUH208 - Contains 2-methylisothiazol-3(2H)-one (2682-20-4) (00180). May produce an

allergic reaction.

Child-resistant fastening : Not applicable Tactile warning : Not applicable

# 2.3. Other hazards

Contains no PBT/vPvB substances ≥ 0.1% assessed in accordance with REACH Annex XIII

The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or substances identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at a concentration equal to or greater than 0,1 %

# **SECTION 3: Composition/information on ingredients**

#### 3.1. Substances

Not applicable

#### 3.2. Mixtures

Name	Product identifier	Conc. (% w/w)	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Alcohols, C12-14, ethoxylated, sulfates, sodium salts	CAS-No.: 68891-38-3 EC-No.: 500-234-8 REACH-no: 01-2119488639- 16	≥ 2 - < 5	Skin Irrit. 2, H315 Eye Dam. 1, H318 Aquatic Chronic 3, H412
2-methylisothiazol-3(2H)-one	CAS-No.: 2682-20-4 EC-No.: 220-239-6 EC Index-No.: 613-326-00-9 REACH-no: 01-2120764690- 50	≥ 0.001 – < 0.01	Acute Tox. 3 (Oral), H301 Acute Tox. 2 (Dermal), H310 Acute Tox. 2 (Inhalation), H330 Acute Tox. 2 (Inhalation:dust,mist), H330 Skin Corr. 1B, H314 Eye Dam. 1, H318 Skin Sens. 1A, H317 Aquatic Acute 1, H400 (M=10) Aquatic Chronic 1, H410

Specific concentration limits:		
Name	Product identifier	Specific concentration limits (Conc. (% w/w))
Alcohols, C12-14, ethoxylated, sulfates, sodium salts	CAS-No.: 68891-38-3 EC-No.: 500-234-8 REACH-no: 01-2119488639- 16	(5 ≤ C < 10) Eye Irrit. 2, H319 (10 ≤ C < 100) Eye Dam. 1, H318
2-methylisothiazol-3(2H)-one	CAS-No.: 2682-20-4 EC-No.: 220-239-6 EC Index-No.: 613-326-00-9 REACH-no: 01-2120764690- 50	(0.0015 ≤ C ≤ 100) Skin Sens. 1A, H317

Full text of H- and EUH-statements: see section 16

# Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

#### **SECTION 4: First aid measures**

#### 4.1. Description of first aid measures

First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing.

First-aid measures after skin contact : Wash skin with plenty of water.
First-aid measures after eye contact : Rinse eyes with water as a precaution.

First-aid measures after ingestion : Call a poison center or a doctor if you feel unwell.

#### 4.2. Most important symptoms and effects, both acute and delayed

No additional information available

#### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

### **SECTION 5: Firefighting measures**

### 5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.

### 5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released.

#### 5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained

breathing apparatus. Complete protective clothing.

### **SECTION 6: Accidental release measures**

### 6.1. Personal precautions, protective equipment and emergency procedures

### 6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area.

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information

refer to section 8: "Exposure controls/personal protection".

# 6.2. Environmental precautions

Avoid release to the environment.

#### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Take up liquid spill into absorbent material.

Other information : Dispose of materials or solid residues at an authorized site.

#### 6.4. Reference to other sections

For further information refer to section 13.

# **SECTION 7: Handling and storage**

# 7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Wear personal protective equipment.

Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product. Wash contaminated clothing before reuse.

09/10/2023 (Issue date) GB - en 3/11

# Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in a well-ventilated place. Keep cool.

Storage temperature :  $0 - 30 \, ^{\circ}\text{C}$ 

### 7.3. Specific end use(s)

No additional information available

### SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### 8.1.1 National occupational exposure and biological limit values

No additional information available

#### 8.1.2. Recommended monitoring procedures

No additional information available

#### 8.1.3. Air contaminants formed

No additional information available

### 8.1.4. DNEL and PNEC

No additional information available

#### 8.1.5. Control banding

No additional information available

#### 8.2. Exposure controls

# 8.2.1. Appropriate engineering controls

# Appropriate engineering controls:

Ensure good ventilation of the work station.

#### 8.2.2. Personal protection equipment

### Personal protective equipment symbol(s):









### 8.2.2.1. Eye and face protection

### Eye protection:

Safety glasses with side shields

Eye protection			
Туре	Field of application	Characteristics Standard	Standard
Safety glasses with side shields			EN 166

#### 8.2.2.2. Skin protection

#### Skin and body protection:

Chemical resistant safety shoes. Long sleeved protective clothing

Skin and body protection		
Туре	Standard	
Safety shoes	EN ISO 20345	
Long sleeved protective clothing		

# Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

#### Hand protection:

Nitrile rubber gloves

Hand protection					
Туре	Material	Permeation	Thickness (mm)	Penetration	Standard
Gloves	Nitrile rubber (NBR)	6 (> 480 minutes)	0.35		EN ISO 374
Gloves	Butyl rubber	6 (> 480 minutes)	0.5		EN ISO 374

#### 8.2.2.3. Respiratory protection

#### Respiratory protection:

No respiratory protection needed under normal use conditions

#### 8.2.2.4. Thermal hazards

No additional information available

#### 8.2.3. Environmental exposure controls

#### **Environmental exposure controls:**

Avoid release to the environment.

# **SECTION 9: Physical and chemical properties**

### 9.1. Information on basic physical and chemical properties

Physical state : Liquid Colour : light yellow. Appearance : Clear to cloudy. Odour : perfumed. Odour threshold : Not available Melting point : Not applicable Freezing point : Not available **Boiling point** : Not available Flammability : Not applicable : Not available Lower explosion limit : Not available Upper explosion limit : Not available Flash point Auto-ignition temperature : Not available Decomposition temperature : Not available : 6.7 **–** 7.7 рΗ Viscosity, kinematic : Not available Solubility : Not available Partition coefficient n-octanol/water (Log Kow) : Not available : Not available Vapour pressure Vapour pressure at 50°C : Not available Density : Not available Relative density : Not available Relative vapour density at 20°C 1.004 - 1.014Particle characteristics : Not applicable

#### 9.2. Other information

#### 9.2.1. Information with regard to physical hazard classes

No additional information available

#### 9.2.2. Other safety characteristics

No additional information available

# Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

### **SECTION 10: Stability and reactivity**

#### 10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

# 10.2. Chemical stability

Stable under normal conditions.

#### 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

### 10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

### 10.5. Incompatible materials

No additional information available

### 10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

# **SECTION 11: Toxicological information**

### 11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity (oral) : Not classified
Acute toxicity (dermal) : Not classified
Acute toxicity (inhalation) : Not classified

Alcohols, C12-14, ethoxylated, sulfates, sodium salts (68891-38-3)		
LD50 oral rat > 2000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 401 (Acute Oral Toxicity)		
LD50 dermal rat	≥ 2000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 402 (Acute Dermal Toxicity), Remarks on results: other:	
2-methylisothiazol-3(2H)-one (2682-20-4)		
LD50 oral rat	66 – 105 mg/kg	
LD50 dermal rabbit	200 mg/kg	
LC50 Inhalation - Rat (Dust/Mist)	0.33 mg/l	

Skin corrosion/irritation : Not classified pH: 6.7 – 7.7

2-methylisothiazol-3(2H)-one (2682-20-4)	
рН	2.58 Temp.: 25 °C Concentration: 50 g/L

Serious eye damage/irritation : Not classified pH: 6.7 – 7.7

STOT-single exposure STOT-repeated exposure

2-methylisothiazol-3(2H)-one (2682-20-4)		
рН	2.58 Temp.: 25 °C Concentration: 50 g/L	
Respiratory or skin sensitisation	Not classified	
Germ cell mutagenicity	Not classified	
Carcinogenicity	Not classified	
Reproductive toxicity	Not classified	

: Not classified

: Not classified

09/10/2023 (Issue date) GB - en 6/11

# Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Alcohols, C12-14, ethoxylated, sulfates, sodium salts (68891-38-3)		
LOAEL (oral, rat, 90 days)	25 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity Study in Rodents), Remarks on results: other:	
NOAEL (oral, rat, 90 days)	> 225 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity Study in Rodents), Remarks on results: other:	
2-methylisothiazol-3(2H)-one (2682-20-4)		
LOAEL (oral, rat, 90 days)	71.2 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 407 (Repeated Dose 28-Day Oral Toxicity Study in Rodents), Guideline: other:	
Aspiration hazard	: Not classified	

# 11.2. Information on other hazards

No additional information available

# **SECTION 12: Ecological information**

# 12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms nor to cause long-term adverse

effects in the environment.

: Not classified

Hazardous to the aquatic environment, short–term

acute)

Hazardous to the aquatic environment, long-term : Not classified

(chronic)

Alcohols, C12-14, ethoxylated, sulfates, sodium salts (68891-38-3)		
LC50 - Fish [1]	7.1 mg/l Test organisms (species): Danio rerio (previous name: Brachydanio rerio)	
EC50 - Crustacea [1]	7.4 mg/l Test organisms (species): Daphnia magna	
EC50 72h - Algae [1]	27.7 mg/l Test organisms (species): Desmodesmus subspicatus (previous name: Scenedesmus subspicatus)	
NOEC (chronic)	0.27 mg/l Test organisms (species): Daphnia magna Duration: '21 d'	
NOEC chronic fish	0.14 mg/l Test organisms (species): Oncorhynchus mykiss (previous name: Salmo gairdneri) Duration: '28 d'	
NOEC chronic algae	0.95 mg/l Scenedesmus subspicatus	
2-methylisothiazol-3(2H)-one (2682-20-4)		
LC50 - Fish [1]  4.77 mg/l Test organisms (species): Oncorhynchus mykiss (previous name: Salmo gairdneri)		
EC50 - Crustacea [1]	1.6 mg/l Test organisms (species): Daphnia magna	

# 12.2. Persistence and degradability

HG natural stone cleaner streak free		
Persistence and degradability	The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No.648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.	
Alcohols, C12-14, ethoxylated, sulfates, sodium salts (68891-38-3)		
Chemical oxygen demand (COD)	0.51 g O <sub>2</sub> /g substance	
Biodegradation	80 % (OECD 302B method)	
Additional information	95 % biodegradation (OECD 301E method)	

# Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

### 12.3. Bioaccumulative potential

Alcohols, C12-14, ethoxylated, sulfates, sodium salts (68891-38-3)	
Partition coefficient n-octanol/water (Log Pow)	0.3
2-methylisothiazol-3(2H)-one (2682-20-4)	
Partition coefficient n-octanol/water (Log Pow) -0.49	

# 12.4. Mobility in soil

No additional information available

### 12.5. Results of PBT and vPvB assessment

No additional information available

# 12.6. Endocrine disrupting properties

No additional information available

### 12.7. Other adverse effects

No additional information available

### **SECTION 13: Disposal considerations**

### 13.1. Waste treatment methods

Regional legislation (waste) : Dispose of in accordance with relevant local regulations.

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

Sewage disposal recommendations : Do not flush down sewers.

Product/Packaging disposal recommendations : Clean using water and a detergent. Recycling is preferred to disposal or incineration.

European List of Waste (LoW) code : 15 01 02 - plastic packaging

# **SECTION 14: Transport information**

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID	
14.1. UN number or ID number					
Not regulated for transport	Not regulated for transport				
14.2. UN proper shipping name					
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated	
14.3. Transport hazard class(es)					
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated	
14.4. Packing group					
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated	
14.5. Environmental hazards					
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated	
No supplementary information available					

### 14.6. Special precautions for user

#### **Overland transport**

Not regulated

# Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

#### Transport by sea

Not regulated

#### Air transport

Not regulated

#### **Inland waterway transport**

Not regulated

#### Rail transport

Not regulated

#### 14.7. Maritime transport in bulk according to IMO instruments

Not applicable

# **SECTION 15: Regulatory information**

# 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

#### **REACH Annex XVII (Restriction List)**

Contains no substance(s) listed on REACH Annex XVII (Restriction Conditions)

#### **REACH Annex XIV (Authorisation List)**

Contains no substance(s) listed on REACH Annex XIV (Authorisation List)

#### **REACH Candidate List (SVHC)**

Contains no substance(s) listed on the REACH Candidate List

#### **PIC Regulation (Prior Informed Consent)**

Contains no substance(s) listed on the PIC list (Regulation EU 649/2012 concerning the export and import of hazardous chemicals)

#### **POP Regulation (Persistent Organic Pollutants)**

Contains no substance(s) listed on the POP list (Regulation EU 2019/1021 on persistent organic pollutants)

#### Ozone Regulation (1005/2009)

Contains no substance(s) listed on the Ozone Depletion list (Regulation EU 1005/2009 on substances that deplete the ozone layer)

### Detergent Regulation (648/2004)

#### Allergenic fragrances > 0.01 %:

HEXYL CINNAMAL

ALPHA-ISOMETHYL IONONE

Labelling of contents	
Component	%
anionic surfactants, phosphonates	<5%
2-BROMO-2-NITROPROPANE-1,3-DIOL	
METHYLISOTHIAZOLINONE	
BENZISOTHIAZOLINONE	
perfumes	
HEXYL CINNAMAL	
ALPHA-ISOMETHYL IONONE	

#### **Explosives Precursors Regulation (2019/1148)**

Contains no substance(s) listed on the Explosives Precursors list (Regulation EU 2019/1148 on the marketing and use of explosives precursors)

# Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

### **Drug Precursors Regulation (273/2004)**

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on the manufacture and the placing on market of certain substances used in the illicit manufacture of narcotic drugs and psychotropic substances)

### 15.1.2. National regulations

No additional information available

# 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

# **SECTION 16: Other information**

Abbreviations and acronyms:		
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways	
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road	
ATE	Acute Toxicity Estimate	
BCF	Bioconcentration factor	
BLV	Biological limit value	
BOD	Biochemical oxygen demand (BOD)	
COD	Chemical oxygen demand (COD)	
DMEL	Derived Minimal Effect level	
DNEL	Derived-No Effect Level	
EC-No.	European Community number	
EC50	Median effective concentration	
EN	European Standard	
IARC	International Agency for Research on Cancer	
IATA	International Air Transport Association	
IMDG	International Maritime Dangerous Goods	
LC50	Median lethal concentration	
LD50	Median lethal dose	
LOAEL	Lowest Observed Adverse Effect Level	
NOAEC	No-Observed Adverse Effect Concentration	
NOAEL	No-Observed Adverse Effect Level	
NOEC	No-Observed Effect Concentration	
OECD	Organisation for Economic Co-operation and Development	
OEL	Occupational Exposure Limit	
PBT	Persistent Bioaccumulative Toxic	
PNEC	Predicted No-Effect Concentration	
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail	
SDS	Safety Data Sheet	
STP	Sewage treatment plant	
ThOD	Theoretical oxygen demand (ThOD)	
TLM	Median Tolerance Limit	

# Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Abbreviations and acronyms:	
VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified
vPvB	Very Persistent and Very Bioaccumulative
ED	Endocrine disrupting properties

Full text of H- and EUH-statements:	
Acute Tox. 2 (Dermal)	Acute toxicity (dermal), Category 2
Acute Tox. 2 (Inhalation)	Acute toxicity (inhal.), Category 2
Acute Tox. 2 (Inhalation:dust,mist)	Acute toxicity (inhalation:dust,mist) Category 2
Acute Tox. 3 (Oral)	Acute toxicity (oral), Category 3
Aquatic Acute 1	Hazardous to the aquatic environment – Acute Hazard, Category 1
Aquatic Chronic 1	Hazardous to the aquatic environment – Chronic Hazard, Category 1
Aquatic Chronic 3	Hazardous to the aquatic environment – Chronic Hazard, Category 3
EUH208	Contains 2-methylisothiazol-3(2H)-one (2682-20-4) (00180). May produce an allergic reaction.
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
H301	Toxic if swallowed.
H310	Fatal in contact with skin.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H330	Fatal if inhaled.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.
Skin Corr. 1B	Skin corrosion/irritation, Category 1, Sub-Category 1B
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1A	Skin sensitisation, category 1A

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.