

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form	: Mixture
Product name	: HG drain and plug hair unblocker - component 2
Product code	: 670 ART (667 ART)
Type of product	: Detergent
Product group	: Trade product

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Intended for general public	
Main use category	: Consumer use

1.2.2. Uses advised against

Restrictions on use	: All other uses not recommended above
---------------------	--

1.3. Details of the supplier of the safety data sheet

Manufacturer

HG International B.V.
P.J. Oudweg 41
NL- 1314 CJ Almere
The Netherlands
T +31 (0)36 54 94 700
safety@hg.eu - www.hg.eu

Distributor

HG UKI LTD
Weston Business Centre
Parsonage Road
UK- CM22 6PU Takeley – Essex
United Kingdom
T +44 (0) 1206 822 744
www.hg.eu

1.4. Emergency telephone number

Emergency number	: +31 (0)36 54 94 777
	Only for medical personnel
	Mon-Fri 09:00 AM - 05:00 PM (CEST)

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH	0344 892 0111	Only for healthcare professionals
United Kingdom	Guy's & St Thomas' Poisons Unit Medical Toxicology Unit, Guy's & St Thomas' Hospital Trust	Avonley Road SE14 5ER	+44 20 7188 7188	

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Acute toxicity (oral), Category 4	H302
Skin corrosion/irritation, Category 1	H314
Serious eye damage/eye irritation, Category 1	H318
Full text of H- and EUH-statements: see section 16	

Adverse physicochemical, human health and environmental effects

Harmful if swallowed. Causes severe skin burns and eye damage. Causes serious eye damage.

HG drain and plug hair unblocker - component 2


Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP)



Signal word (CLP)

Contains

Hazard statements (CLP)

Precautionary statements (CLP)

- : Danger
- : potassium hydroxide; caustic potash
- : H302 - Harmful if swallowed.
- H314 - Causes severe skin burns and eye damage.
- : P101 - If medical advice is needed, have product container or label at hand.
- P102 - Keep out of reach of children.
- P280 - Wear protective gloves, eye protection.
- P301+P312 - IF SWALLOWED: Call a POISON CENTER, doctor if you feel unwell.
- P301+P330+P331 - IF SWALLOWED: Rinse mouth. Do NOT induce vomiting.
- P303+P361+P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water or shower.
- P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P501 - Dispose of contents and container to a hazardous or special waste collection point.
- : Applicable
- : Applicable

Child-resistant fastening

Tactile warning

2.3. Other hazards

Contains no PBT/vPvB substances $\geq 0.1\%$ assessed in accordance with REACH Annex XIII

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	Conc. (% w/w)	Classification according to Regulation (EC) No. 1272/2008 [CLP]
potassium hydroxide; caustic potash	CAS-No.: 1310-58-3 EC-No.: 215-181-3 EC Index-No.: 019-002-00-8 REACH-no: 01-2119487136-33	$\geq 50 - < 75$	Met. Corr. 1, H290 Acute Tox. 4 (Oral), H302 Skin Corr. 1A, H314 Eye Dam. 1, H318

Specific concentration limits:

Name	Product identifier	Specific concentration limits
potassium hydroxide; caustic potash	CAS-No.: 1310-58-3 EC-No.: 215-181-3 EC Index-No.: 019-002-00-8 REACH-no: 01-2119487136-33	(0.5 $\leq$ C < 2) Skin Irrit. 2, H315 (0.5 $\leq$ C < 2) Eye Irrit. 2, H319 (2 $\leq$ C < 5) Skin Corr. 1B, H314 (5 $\leq$ C $\leq$ 100) Skin Corr. 1A, H314

Full text of H- and EUH-statements: see section 16

HG drain and plug hair unblocker - component 2

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Call a physician immediately.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Rinse skin with water/shower. Take off immediately all contaminated clothing. Call a physician immediately.
First-aid measures after eye contact	: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Call a physician immediately.
First-aid measures after ingestion	: Rinse mouth. Do not induce vomiting. Call a physician immediately.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after skin contact	: Burns.
Symptoms/effects after eye contact	: Serious damage to eyes.
Symptoms/effects after ingestion	: Burns.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Water spray. Dry powder. Foam. Carbon dioxide.
------------------------------	--

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire	: Toxic fumes may be released.
--	--------------------------------

5.3. Advice for firefighters

Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.
--------------------------------	--

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures	: Ventilate spillage area. Avoid contact with skin and eyes. Do not breathe mist, spray, vapours. Do not touch or walk on the spilled product. Evacuate unnecessary personnel.
----------------------	--

6.1.2. For emergency responders

Protective equipment	: Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".
----------------------	---

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up	: Take up liquid spill into absorbent material.
Other information	: Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13. For further information refer to section 8: "Exposure controls/personal protection".

HG drain and plug hair unblocker - component 2

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

- Precautions for safe handling : Ensure good ventilation of the work station. Avoid contact with skin and eyes. Do not breathe spray, vapours. Wear personal protective equipment.
- Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product. Take off immediately all contaminated clothing and wash it before reuse.

7.2. Conditions for safe storage, including any incompatibilities

- Storage conditions : Store locked up. Store in a well-ventilated place. Keep cool.
- Incompatible materials : Acid.
- Storage temperature : 0 – 30 °C

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

potassium hydroxide; caustic potash (1310-58-3)

United Kingdom - Occupational Exposure Limits

Local name	Potassium hydroxide
WEL STEL (OEL STEL)	2 mg/m ³
Regulatory reference	EH40/2005 (Fourth edition, 2020). HSE

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

HG drain and plug hair unblocker - component 2

DNEL/DMEL (Workers)

Long-term - local effects, inhalation	1 mg/m ³
---------------------------------------	---------------------

DNEL/DMEL (General population)

Long-term - local effects, inhalation	1 mg/m ³
---------------------------------------	---------------------

DNEL : 1 mg/m³

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Ensure good ventilation of the work station. Emergency eye wash fountains and safety showers should be available in the immediate vicinity of any potential exposure.

HG drain and plug hair unblocker - component 2

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

8.2.2. Personal protection equipment

Personal protective equipment symbol(s):



8.2.2.1. Eye and face protection

Eye protection:

Safety glasses with side shields

Eye protection			
Type	Field of application	Characteristics	Standard
Safety glasses	Normal use conditions		EN 166

8.2.2.2. Skin protection

Skin and body protection:

Wear suitable protective clothing

Skin and body protection	
Type	Standard
Use chemically protective clothing	EN 13034
Long sleeved protective clothing	
Chemical resistant safety shoes	

Hand protection:

Protective gloves

Hand protection					
Type	Material	Permeation	Thickness (mm)	Penetration	Standard
Disposable gloves	Nitrile rubber (NBR)	6 (> 480 minutes)	0.35 mm		EN ISO 374
Disposable gloves	Butyl rubber	6 (> 480 minutes)	0.5 mm		EN ISO 374

8.2.2.3. Respiratory protection

Respiratory protection:

No respiratory protection needed under normal use conditions. In case of insufficient ventilation, wear suitable respiratory equipment

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Environmental exposure controls:

Avoid release to the environment.

Other information:

Do not eat, drink or smoke when using this product.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Colourless.
Odour	: Odourless.

HG drain and plug hair unblocker - component 2

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

Odour threshold	: No data available
pH	: 14
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Not applicable
Vapour pressure	: No data available
Relative vapour density at 20°C	: No data available
Relative density	: 1.5
Solubility	: No data available
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

Acids.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity (oral)	: Harmful if swallowed.
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified

HG drain and plug hair unblocker - component 2

ATE CLP (oral)	1000 mg/kg bodyweight
Skin corrosion/irritation	: Causes severe skin burns. pH: 14

HG drain and plug hair unblocker - component 2

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

potassium hydroxide; caustic potash (1310-58-3)

pH	≈ 13.5 Temp.: 25 °C Concentration: 5,611 g/L Remarks on result: 'other:'
----	--

Serious eye damage/irritation : Causes serious eye damage.
pH: 14

potassium hydroxide; caustic potash (1310-58-3)

pH	≈ 13.5 Temp.: 25 °C Concentration: 5,611 g/L Remarks on result: 'other:'
----	--

Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
STOT-single exposure	: Not classified
STOT-repeated exposure	: Not classified
Aspiration hazard	: Not classified

potassium hydroxide; caustic potash (1310-58-3)

Viscosity, kinematic	1.252 mm²/s
----------------------	-------------

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	: Before neutralisation, the product may represent a danger to aquatic organisms.
Hazardous to the aquatic environment, short-term (acute)	: Not classified
Hazardous to the aquatic environment, long-term (chronic)	: Not classified

potassium hydroxide; caustic potash (1310-58-3)

LC50 - Fish [1]	80 mg/l
-----------------	---------

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

potassium hydroxide; caustic potash (1310-58-3)

Partition coefficient n-octanol/water (Log Pow)	0.75
---	------

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods	: Dispose of contents/container in accordance with licensed collector's sorting instructions.
Ecology - waste materials	: Avoid release to the environment.

HG drain and plug hair unblocker - component 2

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

SECTION 14: Transport information


In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
UN 1814	UN 1814	UN 1814	UN 1814	UN 1814
14.2. UN proper shipping name				
POTASSIUM HYDROXIDE SOLUTION	POTASSIUM HYDROXIDE SOLUTION	Potassium hydroxide solution	POTASSIUM HYDROXIDE SOLUTION	POTASSIUM HYDROXIDE SOLUTION
Transport document description				
UN 1814 POTASSIUM HYDROXIDE SOLUTION, 8, II, (E)	UN 1814 POTASSIUM HYDROXIDE SOLUTION, 8, II	UN 1814 Potassium hydroxide solution, 8, II	UN 1814 POTASSIUM HYDROXIDE SOLUTION, 8, II	UN 1814 POTASSIUM HYDROXIDE SOLUTION, 8, II
14.3. Transport hazard class(es)				
8	8	8	8	8
				
14.4. Packing group				
II	II	II	II	II
14.5. Environmental hazards				
Dangerous for the environment: No	Dangerous for the environment: No Marine pollutant: No	Dangerous for the environment: No	Dangerous for the environment: No	Dangerous for the environment: No
No supplementary information available				

14.6. Special precautions for user

Overland transport

Classification code (ADR)	: C5
Limited quantities (ADR)	: 1I
Excepted quantities (ADR)	: E2
Packing instructions (ADR)	: P001, IBC02
Mixed packing provisions (ADR)	: MP15
Portable tank and bulk container instructions (ADR)	: T7
Portable tank and bulk container special provisions (ADR)	: TP2
Tank code (ADR)	: L4BN
Tank special provisions (ADR)	: TU42
Vehicle for tank carriage	: AT
Transport category (ADR)	: 2
Hazard identification number (Kemler No.)	: 80
Orange plates	:



Tunnel restriction code (ADR)	: E
EAC code	: 2R

Transport by sea

Limited quantities (IMDG)	: 1 L
Excepted quantities (IMDG)	: E2

HG drain and plug hair unblocker - component 2

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

Packing instructions (IMDG)	: P001
IBC packing instructions (IMDG)	: IBC02
Tank instructions (IMDG)	: T7
Tank special provisions (IMDG)	: TP2
EmS-No. (Fire)	: F-A
EmS-No. (Spillage)	: S-B
Stowage category (IMDG)	: A
Segregation (IMDG)	: SGG18, SG35
Properties and observations (IMDG)	: Colourless liquid. Reacts with ammonium salts, evolving ammonia gas. Reacts with ammonium salts, evolving ammonia gas. Causes burns to skin, eyes and mucous membranes. Reacts violently with acids.

Air transport

PCA Excepted quantities (IATA)	: E2
PCA Limited quantities (IATA)	: Y840
PCA limited quantity max net quantity (IATA)	: 0.5L
PCA packing instructions (IATA)	: 851
PCA max net quantity (IATA)	: 1L
CAO packing instructions (IATA)	: 855
CAO max net quantity (IATA)	: 30L
Special provisions (IATA)	: A3, A803
ERG code (IATA)	: 8L

Inland waterway transport

Classification code (ADN)	: C5
Limited quantities (ADN)	: 1 L
Excepted quantities (ADN)	: E2
Carriage permitted (ADN)	: T
Equipment required (ADN)	: PP, EP
Number of blue cones/lights (ADN)	: 0

Rail transport

Classification code (RID)	: C5
Limited quantities (RID)	: 1L
Excepted quantities (RID)	: E2
Packing instructions (RID)	: P001, IBC02
Mixed packing provisions (RID)	: MP15
Portable tank and bulk container instructions (RID)	: T7
Portable tank and bulk container special provisions (RID)	: TP2
Tank codes for RID tanks (RID)	: L4BN
Special provisions for RID tanks (RID)	: TU42
Transport category (RID)	: 2
Colis express (express parcels) (RID)	: CE6
Hazard identification number (RID)	: 80

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

REACH Annex XVII (Restriction List)

Contains no substance(s) listed on REACH Annex XVII (Restriction Conditions)

REACH Annex XIV (Authorisation List)

Contains no substance(s) listed on REACH Annex XIV (Authorisation List)

HG drain and plug hair unblocker - component 2

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

REACH Candidate List (SVHC)

Contains no substance(s) listed on the REACH Candidate List

PIC Regulation (Prior Informed Consent)

Contains no substance(s) listed on the PIC list (Regulation EU 649/2012 concerning the export and import of hazardous chemicals)

POP Regulation (Persistent Organic Pollutants)

Contains no substance(s) listed on the POP list (Regulation EU 2019/1021 on persistent organic pollutants)

Ozone Regulation (1005/2009)

Contains no substance(s) listed on the Ozone Depletion list (Regulation EU 1005/2009 on substances that deplete the ozone layer)

Detergent Regulation (648/2004)

Explosives Precursors Regulation (2019/1148)

Contains no substance(s) listed on the Explosives Precursors list (Regulation EU 2019/1148 on the marketing and use of explosives precursors)

Drug Precursors Regulation (273/2004)

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on the manufacture and the placing on market of certain substances used in the illicit manufacture of narcotic drugs and psychotropic substances)

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Abbreviations and acronyms:	
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level

HG drain and plug hair unblocker - component 2

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

Abbreviations and acronyms:	
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified
vPvB	Very Persistent and Very Bioaccumulative
ED	Endocrine disrupting properties

Other information

: **DISCLAIMER OF LIABILITY** The information in this SDS was obtained from sources which we believe are reliable. However, the information is provided without any warranty, express or implied, regarding its correctness. The conditions or methods of handling, storage, use or disposal of the product are beyond our control and may be beyond our knowledge. For this and other reasons, we do not assume responsibility and expressly disclaim liability for loss, damage or expense arising out of or in any way connected with the handling, storage, use or disposal of the product. This SDS was prepared and is to be used only for this product. If the product is used as a component in another product, this SDS information may not be applicable.

Full text of H- and EUH-statements:	
Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
H290	May be corrosive to metals.
H302	Harmful if swallowed.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
Met. Corr. 1	Corrosive to metals, Category 1
Skin Corr. 1A	Skin corrosion/irritation, Category 1, Sub-Category 1A
Skin Corr. 1B	Skin corrosion/irritation, Category 1, Sub-Category 1B
Skin Irrit. 2	Skin corrosion/irritation, Category 2

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.