

SAFETY DATA SHEET



White Silicone

Section 1. Identification

GHS product identifier : White Silicone
Product code : 31312
Chemical name : silicone acetoxyl
Other means of identification : Not available.
Product type : Solid.

Relevant identified uses of the substance or mixture and uses advised against

Identified uses

Specialized adhesive and sealant products for cabinet making and furniture manufacturing, including putty. Does not include wood glues primarily for home use, see 'Adhesives and sealants - household, office or school use'.

Uses advised against

Not applicable.

Supplier's details : J-B Weld Company
400 CMH Road
Sulphur Springs, TX 75482 USA
info@jbweld.com
Tel: +1 (903) 885-7696
Website: www.jbweld.com

Emergency telephone number : US: +1 (800) 535-5053 (INFOTRAC®)
Outside USA: +1 (352) 323-3500 (INFOTRAC® INTL)


Section 2. Hazards identification

OSHA/HCS status : This material is considered hazardous by the OSHA Hazard Communication Standard (29 CFR 1910.1200).

Classification of the substance or mixture : SERIOUS EYE DAMAGE - Category 1

GHS label elements

Hazard pictograms



Signal word : Danger

Hazard statements : Causes serious eye damage.

Precautionary statements

Prevention : Wear eye or face protection.

Response : IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Immediately call a POISON CENTER or doctor.

Storage : Not applicable.

Disposal : Not applicable.

Hazards not otherwise classified : None known.

Section 3. Composition/information on ingredients

Substance/mixture	: Mixture
Chemical name	: silicone acetoxyl
Other means of identification	: Not available.

Ingredient name	%	CAS number
Distillates (petroleum), hydrotreated middle	≥5 - ≤10	64742-46-7
triacetoxylethylsilane	≥5 - ≤10	17689-77-9
methylsilanetriyl triacetate	≥1 - ≤5	4253-34-3
silicon dioxide	≥1 - ≤5	7631-86-9

The exact percentage (concentration) of composition has been withheld as a trade secret in accordance with § 1910.1200 (i)

There are no additional ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified and hence require reporting in this section.

Occupational exposure limits, if available, are listed in Section 8.

Section 4. First aid measures

Description of necessary first aid measures

- Eye contact** : Get medical attention immediately. Call a poison center or physician. Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Continue to rinse for at least 10 minutes. Chemical burns must be treated promptly by a physician.
- Inhalation** : Get medical attention immediately. Call a poison center or physician. Remove victim to fresh air and keep at rest in a position comfortable for breathing. If it is suspected that fumes are still present, the rescuer should wear an appropriate mask or self-contained breathing apparatus. If not breathing, if breathing is irregular or if respiratory arrest occurs, provide artificial respiration or oxygen by trained personnel. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.
- Skin contact** : Get medical attention immediately. Call a poison center or physician. Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Wash contaminated clothing thoroughly with water before removing it, or wear gloves. Continue to rinse for at least 10 minutes. Chemical burns must be treated promptly by a physician. Wash clothing before reuse. Clean shoes thoroughly before reuse.
- Ingestion** : Get medical attention immediately. Call a poison center or physician. Wash out mouth with water. Remove dentures if any. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Stop if the exposed person feels sick as vomiting may be dangerous. Do not induce vomiting unless directed to do so by medical personnel. If vomiting occurs, the head should be kept low so that vomit does not enter the lungs. Chemical burns must be treated promptly by a physician. Never give anything by mouth to an unconscious person. If unconscious, place in recovery position and get medical attention immediately. Maintain an open airway. Loosen tight clothing such as a collar, tie, belt or waistband.

Most important symptoms/effects, acute and delayed

Potential acute health effects

- Eye contact** : Causes serious eye damage.
- Inhalation** : No known significant effects or critical hazards.
- Skin contact** : No known significant effects or critical hazards.
- Ingestion** : No known significant effects or critical hazards.

Section 4. First aid measures

Over-exposure signs/symptoms

- Eye contact** : Adverse symptoms may include the following:
pain
watering
redness
- Inhalation** : No specific data.
- Skin contact** : Adverse symptoms may include the following:
pain or irritation
redness
blistering may occur
- Ingestion** : Adverse symptoms may include the following:
stomach pains

Indication of immediate medical attention and special treatment needed, if necessary

- Notes to physician** : Treat symptomatically. Contact poison treatment specialist immediately if large quantities have been ingested or inhaled.
- Specific treatments** : No specific treatment.
- Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training. If it is suspected that fumes are still present, the rescuer should wear an appropriate mask or self-contained breathing apparatus. It may be dangerous to the person providing aid to give mouth-to-mouth resuscitation. Wash contaminated clothing thoroughly with water before removing it, or wear gloves.

See toxicological information (Section 11)

Section 5. Fire-fighting measures

Extinguishing media

- Suitable extinguishing media** : Use an extinguishing agent suitable for the surrounding fire.
- Unsuitable extinguishing media** : None known.

Specific hazards arising from the chemical : No specific fire or explosion hazard.

- Hazardous thermal decomposition products** : Decomposition products may include the following materials:
carbon dioxide
carbon monoxide
metal oxide/oxides

Special protective actions for fire-fighters : Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.

Special protective equipment for fire-fighters : Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode.

Section 6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

- For non-emergency personnel** : No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilled material. Provide adequate ventilation. Wear appropriate respirator when ventilation is inadequate. Put on appropriate personal protective equipment.
- For emergency responders** : If specialized clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

Section 6. Accidental release measures

Environmental precautions : Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).

Methods and materials for containment and cleaning up

- Small spill** : Move containers from spill area. Avoid dust generation. Using a vacuum with HEPA filter will reduce dust dispersal. Place spilled material in a designated, labeled waste container. Dispose of via a licensed waste disposal contractor.
- Large spill** : Move containers from spill area. Approach release from upwind. Prevent entry into sewers, water courses, basements or confined areas. Avoid dust generation. Do not dry sweep. Vacuum dust with equipment fitted with a HEPA filter and place in a closed, labeled waste container. Dispose of via a licensed waste disposal contractor. Note: see Section 1 for emergency contact information and Section 13 for waste disposal.

Section 7. Handling and storage

Precautions for safe handling

Protective measures : Put on appropriate personal protective equipment (see Section 8). Do not get in eyes or on skin or clothing. Do not ingest. If during normal use the material presents a respiratory hazard, use only with adequate ventilation or wear appropriate respirator. Keep in the original container or an approved alternative made from a compatible material, kept tightly closed when not in use. Empty containers retain product residue and can be hazardous. Do not reuse container.

Advice on general occupational hygiene : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

Conditions for safe storage, including any incompatibilities : Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Store locked up. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabeled containers. Use appropriate containment to avoid environmental contamination. See Section 10 for incompatible materials before handling or use.

Section 8. Exposure controls/personal protection

Control parameters

Occupational exposure limits

Ingredient name	Exposure limits
Distillates (petroleum), hydrotreated middle	NIOSH REL (United States, 10/2020). [OIL MIST MINERAL] TWA: 5 mg/m ³ 10 hours. Form: Mist STEL: 10 mg/m ³ 15 minutes. Form: Mist
triacetoxymethylsilane	None.
methylsilanetriyl triacetate	None.
silicon dioxide	NIOSH REL (United States, 10/2020). [SILICA, AMORPHOUS] TWA: 6 mg/m ³ 10 hours.

Biological exposure indices

No exposure indices known.

Appropriate engineering controls : If user operations generate dust, fumes, gas, vapor or mist, use process enclosures, local exhaust ventilation or other engineering controls to keep worker exposure to airborne contaminants below any recommended or statutory limits.

Section 8. Exposure controls/personal protection

Environmental exposure controls : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

Individual protection measures

- Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.
- Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: chemical splash goggles and/or face shield. If inhalation hazards exist, a full-face respirator may be required instead.
- Skin protection**
- Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary. Considering the parameters specified by the glove manufacturer, check during use that the gloves are still retaining their protective properties. It should be noted that the time to breakthrough for any glove material may be different for different glove manufacturers. In the case of mixtures, consisting of several substances, the protection time of the gloves cannot be accurately estimated.
- Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.
- Respiratory protection** : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

Section 9. Physical and chemical properties and safety characteristics

The conditions of measurement of all properties are at standard temperature and pressure unless otherwise indicated.

Appearance

- Physical state** : Solid.
- Color** : White.
- Odor** : Acetic acid.
- Odor threshold** : Not available.
- pH** : Not available.
- Melting point/freezing point** : Not available.
- Boiling point, initial boiling point, and boiling range** : >200°C
- Flash point** : Closed cup: >93.3°C (>199.9°F)
- Flammability** : Not available.
- Lower and upper explosion limit/flammability limit** : Not applicable.
- Vapor pressure** : 1.3 to 1.5 kPa (10 to 11 mm Hg)
- Relative vapor density** : >1 [Air = 1]
- Relative density** : 1 to 1.02

Section 9. Physical and chemical properties and safety characteristics

Solubility in water	: Not available.
Miscible with water	: No.
Partition coefficient: n-octanol/water	: Not applicable.
Auto-ignition temperature	: Not applicable.
Decomposition temperature	: <input checked="" type="checkbox"/> Not available.
Viscosity	: <input checked="" type="checkbox"/> Not applicable.

Particle characteristics

Median particle size	: Not available.
-----------------------------	------------------

Section 10. Stability and reactivity

Reactivity	: <input checked="" type="checkbox"/> No specific test data related to reactivity available for this product or its ingredients.
Chemical stability	: <input checked="" type="checkbox"/> The product is stable.
Possibility of hazardous reactions	: <input checked="" type="checkbox"/> Under normal conditions of storage and use, hazardous reactions will not occur.
Conditions to avoid	: <input checked="" type="checkbox"/> No specific data.
Incompatible materials	: <input checked="" type="checkbox"/> No specific data.
Hazardous decomposition products	: <input checked="" type="checkbox"/> Under normal conditions of storage and use, hazardous decomposition products should not be produced.

Section 11. Toxicological information

Information on toxicological effects

Acute toxicity

Product/ingredient name	Result	Species	Dose	Exposure
<input checked="" type="checkbox"/> methylsilanetriyl triacetate	LD50 Oral	Rat	2060 mg/kg	-

Irritation/Corrosion

Product/ingredient name	Result	Species	Score	Exposure	Observation
<input checked="" type="checkbox"/> silicon dioxide	Eyes - Mild irritant	Rabbit	-	24 hours 25 mg	-

Sensitization

Not available.

Mutagenicity

Not available.

Carcinogenicity

Not available.

Classification

Product/ingredient name	OSHA	IARC	NTP
<input checked="" type="checkbox"/> silicon dioxide	-	3	-

Reproductive toxicity

Not available.

Teratogenicity

Section 11. Toxicological information

Not available.

Specific target organ toxicity (single exposure)

Not available.

Specific target organ toxicity (repeated exposure)

Not available.

Aspiration hazard

Product/ingredient name	Result
Distillates (petroleum), hydrotreated middle	ASPIRATION HAZARD - Category 1

Information on the likely routes of exposure : Not available.

Potential acute health effects

- Eye contact** : Causes serious eye damage.
Inhalation : No known significant effects or critical hazards.
Skin contact : No known significant effects or critical hazards.
Ingestion : No known significant effects or critical hazards.

Symptoms related to the physical, chemical and toxicological characteristics

- Eye contact** : Adverse symptoms may include the following:
 pain
 watering
 redness
- Inhalation** : No specific data.
- Skin contact** : Adverse symptoms may include the following:
 pain or irritation
 redness
 blistering may occur
- Ingestion** : Adverse symptoms may include the following:
 stomach pains

Delayed and immediate effects and also chronic effects from short and long term exposure

Short term exposure

Potential immediate effects : Not available.

Potential delayed effects : Not available.

Long term exposure

Potential immediate effects : Not available.

Potential delayed effects : Not available.

Potential chronic health effects

Not available.

- General** : No known significant effects or critical hazards.
Carcinogenicity : No known significant effects or critical hazards.
Mutagenicity : No known significant effects or critical hazards.
Reproductive toxicity : No known significant effects or critical hazards.

Numerical measures of toxicity

Acute toxicity estimates

Section 11. Toxicological information

Product/ingredient name	Oral (mg/kg)	Dermal (mg/kg)	Inhalation (gases) (ppm)	Inhalation (vapors) (mg/l)	Inhalation (dusts and mists) (mg/l)
Distillates (petroleum), hydrotreated middle methylsilanetriyl triacetate	N/A 2060	N/A N/A	N/A N/A	N/A N/A	1.5 N/A

Section 12. Ecological information

Toxicity

Product/ingredient name	Result	Species	Exposure
Silicon dioxide	Acute EC50 2.2 g/L Fresh water	Daphnia - <i>Daphnia magna</i> - Neonate	48 hours
	Chronic NOEC 12.5 mg/l Fresh water	Daphnia - <i>Daphnia magna</i> - Neonate	21 days

Persistence and degradability

Not available.

Bioaccumulative potential

Not available.

Mobility in soil

Soil/water partition coefficient (K_{oc}) : Not available.

Other adverse effects : No known significant effects or critical hazards.

Section 13. Disposal considerations

Disposal methods : The generation of waste should be avoided or minimized wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible. This material and its container must be disposed of in a safe way. Care should be taken when handling emptied containers that have not been cleaned or rinsed out. Empty containers or liners may retain some product residues. Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

Section 14. Transport information

	DOT Classification	TDG Classification	Mexico Classification	IMDG	IATA
UN number	<input checked="" type="checkbox"/> Not regulated.	<input checked="" type="checkbox"/> Not regulated.	<input checked="" type="checkbox"/> Not regulated.	Not regulated.	Not regulated.
UN proper shipping name	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	<input checked="" type="checkbox"/>	-	-

Section 14. Transport information

Transport hazard class(es)				-	-
Packing group				-	-
Environmental hazards	No.	No.	No.	No.	No.

Special precautions for user : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

Transport in bulk according to IMO instruments : Not available.

Section 15. Regulatory information

U.S. Federal regulations : **TSCA 8(a) PAIR:** Siloxanes and Silicones, di-Me, hydroxy-terminated
 TSCA 8(a) CDR Exempt/Partial exemption: Not determined

Clean Air Act Section 112 (b) Hazardous Air Pollutants (HAPs) : Not listed

Clean Air Act Section 602 Class I Substances : Not listed

Clean Air Act Section 602 Class II Substances : Not listed

DEA List I Chemicals (Precursor Chemicals) : Not listed

DEA List II Chemicals (Essential Chemicals) : Not listed

SARA 302/304

Composition/information on ingredients

No products were found.

SARA 304 RQ : Not applicable.

SARA 311/312

Classification : **SERIOUS EYE DAMAGE - Category 1**

Composition/information on ingredients

Name	%	Classification
Distillates (petroleum), hydrotreated middle	≥5 - ≤10	FLAMMABLE LIQUIDS - Category 4 ACUTE TOXICITY (inhalation) - Category 4 SKIN IRRITATION - Category 2
triacetoxymethylsilane	≥5 - ≤10	ASPIRATION HAZARD - Category 1
methylsilanetriyl triacetate	≥1 - ≤5	SERIOUS EYE DAMAGE - Category 1
silicon dioxide	≥1 - ≤5	SERIOUS EYE DAMAGE - Category 1 EYE IRRITATION - Category 2B

State regulations

Massachusetts : The following components are listed: OIL MIST, MINERAL; DIATOMACEOUS EARTH

New York : None of the components are listed.

New Jersey : The following components are listed: MINERAL OIL (UNTREATED and MILDLY TREATED)

Pennsylvania : The following components are listed: SILICA

Section 15. Regulatory information

California Prop. 65

This product does not require a Safe Harbor warning under California Prop. 65.

International regulations

Chemical Weapon Convention List Schedules I, II & III Chemicals

Not listed.

Montreal Protocol

Not listed.

Stockholm Convention on Persistent Organic Pollutants

Not listed.

Rotterdam Convention on Prior Informed Consent (PIC)

Not listed.

UNECE Aarhus Protocol on POPs and Heavy Metals

Not listed.

Inventory list

Australia	: All components are listed or exempted.
Canada	: All components are listed or exempted.
China	: All components are listed or exempted.
Eurasian Economic Union	: Russian Federation inventory : All components are listed or exempted.
Japan	: Japan inventory (CSCL) : All components are listed or exempted. Japan inventory (ISHL) : Not determined.
New Zealand	: All components are listed or exempted.
Philippines	: All components are listed or exempted.
Republic of Korea	: All components are listed or exempted.
Taiwan	: All components are listed or exempted.
Thailand	: All components are listed or exempted.
Turkey	: Not determined.
United States	: All components are active or exempted.
Viet Nam	: All components are listed or exempted.

Section 16. Other information

Hazardous Material Information System (U.S.A.)

Health	1	3
Flammability	1	
Physical hazards	0	

Caution: HMIS® ratings are based on a 0-4 rating scale, with 0 representing minimal hazards or risks, and 4 representing significant hazards or risks. Although HMIS® ratings and the associated label are not required on SDSs or products leaving a facility under 29 CFR 1910.1200, the preparer may choose to provide them. HMIS® ratings are to be used with a fully implemented HMIS® program. HMIS® is a registered trademark and service mark of the American Coatings Association, Inc.

The customer is responsible for determining the PPE code for this material. For more information on HMIS® Personal Protective Equipment (PPE) codes, consult the HMIS® Implementation Manual.

National Fire Protection Association (U.S.A.)



Section 16. Other information

Procedure used to derive the classification

Classification	Justification
☒ SERIOUS EYE DAMAGE - Category 1	Calculation method

History

Date of printing : 5/29/2024

Date of issue/Date of revision : 5/29/2024

Date of previous issue : 4/24/2024

Version : 2

Key to abbreviations

: ATE = Acute Toxicity Estimate
 BCF = Bioconcentration Factor
 GHS = Globally Harmonized System of Classification and Labelling of Chemicals
 IATA = International Air Transport Association
 IBC = Intermediate Bulk Container
 IMDG = International Maritime Dangerous Goods
 LogPow = logarithm of the octanol/water partition coefficient
 MARPOL = International Convention for the Prevention of Pollution From Ships, 1973 as modified by the Protocol of 1978. ("Marpol" = marine pollution)
 N/A = Not available
 SGG = Segregation Group
 UN = United Nations

References : ☒ Not available.

☑ Indicates information that has changed from previously issued version.

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.

Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.