

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 13

Revision: 16.09.2019

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** MOTIP® CYCLING CHAIN OIL WET ULTRA 1200 100 ML
- **Article number:** 000279
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
- **Sector of Use**
SU21 Consumer uses: Private households / general public / consumers
SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Product category** PC24 Lubricants, greases, release products
- **Process category**
PROC7 Industrial spraying
PROC11 Non industrial spraying
- **Application of the substance / the mixture** Preparation
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
MOTIP DUPLI B.V.
Wolfraamweg 2
NL- 8471 XC Wolvega
The Netherlands
Tel: +31 (0)561 694400
Fax: +31 (0)561 694411
e-mail: msds@nl.motipdupli.com
- **Further information obtainable from:** Department Product Safety
- **1.4 Emergency telephone number:**
+31 (0)561-694400 (09:00h - 17:00h)

UK: NPIS National Poisons Information Centre Tel: +44 0344 892 0111

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
The product is not classified, according to the CLP regulation.
- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008** Void
- **Hazard pictograms** Void
- **Signal word** Void
- **Hazard statements** Void
- **Precautionary statements**
P101 If medical advice is needed, have product container or label at hand.
P102 Keep out of reach of children.
P405 Store locked up.
P501 Dispose of contents / container in accordance with regional regulations.
- **2.3 Other hazards**
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 13

Revision: 16.09.2019

Trade name: **MOTIP® CYCLING CHAIN OIL WET ULTRA 1200 100 ML**

(Contd. of page 1)

· **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

· 3.2 Chemical characterisation: Mixtures

· **Description:** Mixture of substances listed below with nonhazardous additions.

· **Dangerous components:**


CAS: 64742-55-8

EINECS: 265-158-7

Index number: 649-468-00-3

Reg.nr.: 01-2119487077-29

Distillates (petroleum), hydrotreated light paraffinic

 Asp. Tox. 1, H304

25-<50%

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

· 4.1 Description of first aid measures

· **General information:** No special measures required.· **After inhalation:** Supply fresh air; consult doctor in case of complaints.· **After skin contact:** Generally the product does not irritate the skin.· **After eye contact:** Rinse opened eye for several minutes under running water.· **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.· **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.· **4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

SECTION 5: Firefighting measures

· 5.1 Extinguishing media

· **Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.

· 5.2 Special hazards arising from the substance or mixture

No further relevant information available.

No further relevant information available.

· 5.3 Advice for firefighters -

· **Protective equipment:** No special measures required.

SECTION 6: Accidental release measures

· **6.1 Personal precautions, protective equipment and emergency procedures** Not required.· **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.

· 6.3 Methods and material for containment and cleaning up:

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Dispose contaminated material as waste according to item 13.

· 6.4 Reference to other sections

No dangerous substances are released.

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

· **7.1 Precautions for safe handling** No special measures required.· **Information about fire - and explosion protection:** No special measures required.

(Contd. on page 3)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 13

Revision: 16.09.2019

Trade name: MOTIP® CYCLING CHAIN OIL WET ULTRA 1200 100 ML

(Contd. of page 2)

- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep container tightly sealed.
- **Storage class:** 10
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
The usual precautionary measures are to be adhered to when handling chemicals.
- **Respiratory protection:** Not required.
- **Protection of hands:**
Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.
The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.
Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**
Butyl rubber gloves with a thickness of 0.4 mm are resistant to:
Acetone: 480 min
Butyl acetate: 60 min
Ethyl acetate: 170 min
Xylene: 42 min
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Goggles recommended during refilling

SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**
- **Form:** Fluid
- **Colour:** Brown
- **Odour:** Mineral-oil-like
- **Odour threshold:** Not determined.
- **pH-value:** Not determined.
- **Change in condition**
- **Melting point/freezing point:** Undetermined.

(Contd. on page 4)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 13

Revision: 16.09.2019

Trade name: **MOTIP® CYCLING CHAIN OIL WET ULTRA 1200 100 ML**

(Contd. of page 3)

Initial boiling point and boiling range: 999 °C (1830.2 °F)	
· Flash point:	174 °C (345.2 °F)
· Flammability (solid, gas):	Not applicable.
· Ignition temperature:	240 °C (464 °F)
· Decomposition temperature:	Not determined.
· Explosive properties:	Product does not present an explosion hazard.
· Explosion limits:	
Lower:	Not determined.
Upper:	Not determined.
· Density at 20 °C (68 °F):	0.9 g/cm ³ (7.5 lbs/gal)
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not determined.
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient: n-octanol/water:	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic at 40 °C (104 °F):	21 mm ² /s
· Solvent content:	
Organic solvents:	0.4 %
VOC (EC)	---
	3.3 g/l
· VOC-EU%	0.38 %
· Solids content:	1.0 %
· 9.2 Other information	No further relevant information available.

*

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

*

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.

(Contd. on page 5)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 13

Revision: 16.09.2019

Trade name: MOTIP® CYCLING CHAIN OIL WET ULTRA 1200 100 ML

(Contd. of page 4)

- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation** Smaller quantities can be disposed of with household waste.

· European waste catalogue

20 01 13*	solvents
15 01 02	plastic packaging

- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

SECTION 14: Transport information

- | | |
|--|-----------------|
| · 14.1 UN-Number | |
| · ADR, ADN, IMDG, IATA | not regulated |
| · 14.2 UN proper shipping name | |
| · ADR, ADN, IMDG, IATA | not regulated |
| · 14.3 Transport hazard class(es) | |
| · ADR, ADN, IMDG, IATA | |
| · Class | not regulated |
| · 14.4 Packing group | |
| · ADR, IMDG, IATA | not regulated |
| · 14.5 Environmental hazards: | Not applicable. |
| · 14.6 Special precautions for user | Not applicable. |
| · 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code | Not applicable. |
| · UN "Model Regulation": | not regulated |

GB

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 13

Revision: 16.09.2019

Trade name: **MOTIP® CYCLING CHAIN OIL WET ULTRA 1200 100 ML**

(Contd. of page 5)

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **National regulations:**
- **Other regulations, limitations and prohibitive regulations**
- **Substances of very high concern (SVHC) according to REACH, Article 57**
- None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
H304 May be fatal if swallowed and enters airways.
- **Department issuing SDS:** R&D legislation and regulatory advisor
- **Contact:** msds@nl.motipdupli.com
- **Abbreviations and acronyms:**
 RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)
 ICAO: International Civil Aviation Organisation
 ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
 IMDG: International Maritime Code for Dangerous Goods
 IATA: International Air Transport Association
 GHS: Globally Harmonised System of Classification and Labelling of Chemicals
 EINECS: European Inventory of Existing Commercial Chemical Substances
 ELINCS: European List of Notified Chemical Substances
 CAS: Chemical Abstracts Service (division of the American Chemical Society)
 VOC: Volatile Organic Compounds (USA, EU)
 PBT: Persistent, Bioaccumulative and Toxic
 SVHC: Substances of Very High Concern
 vPvB: very Persistent and very Bioaccumulative
 Asp. Tox. 1: Aspiration hazard – Category 1
- *** Data compared to the previous version altered.**

GB