SAFETY DATA SHEET

(REACH regulation (EC) n° 1907/2006 - n° 2020/878)

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name: LIBERON - SHELLAC FILLER STICKS (3-pack) - MEDIUM - 3 × 10mL

Product code: 126841

1.2. Relevant identified uses of the substance or mixture and uses advised against

Wax

Use descriptor system (REACH):

Paints, varnishes and related products coating with layered application.

1.3. Details of the supplier of the safety data sheet

Registered company name: LIBERON Ltd

Address: .Mountfield Industrial Estate KENT TN28 8XU NEW ROMNEY GB Telephone: + (44) 1797 367 555. Fax: + (44) 1797 367 575. Telex: .

fds.produits@v33.com www.liberon.co.uk

1.4. Emergency telephone number: .

Association/Organisation: .

Other emergency numbers

UK/NI: 111 - Emergency Action: In the event of a medical enquiry involving this product, please contact your doctor or local hospital accident and emergency department.

Republic of Ireland: +353 (0)1 809

2166 - Emergency medical information: 8am-10pm (seven days) contact NPIC, Beaumont Hospital, Dublin 9 DOV2NO, Ireland.

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

In compliance with EC regulation No. 1272/2008 and its amendments.

This mixture does not present a physical hazard. Refer to the recommendations regarding the other products present on the site.

This mixture does not present an environmental hazard. No known or foreseeable environmental damage under standard conditions of use.

2.2. Label elements

In compliance with EC regulation No. 1272/2008 and its amendments.

Additional labeling:

EUH212 Warning! Hazardous respirable dust may be formed when used. Do not breathe dust.

Hazard statements:

Precautionary statements - General :

P102 Keep out of reach of children.

Precautionary statements - Disposal:

P501 Dispose of contents/container to a waste collection center (contact the local authority)

2.3. Other hazards

The mixture does not contain substances classified as 'Substances of Very High Concern' (SVHC) >= 0.1% published by the European CHemicals Agency (ECHA) under article 57 of REACH: http://echa.europa.eu/fr/candidate-list-table

The mixture fulfils neither the PBT nor the vPvB criteria for mixtures in accordance with annexe XIII of the REACH regulations EC 1907/2006.

The mixture does not contain substances> = 0.1% with endocrine disrupting properties in accordance with the criteria of the Delegated Regulation (EU) 2017/2100 of the Commission or Regulation (EU) 2018/605 of the Commission.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

Composition:

Identification	(EC) 1272/2008	Note	%
INDEX: Z636		[1]	2.5 <= x % < 10
CAS: 1317-65-3			
EC: 215-279-6			
CARBONATE DE CALCIUM NATUREL			
INDEX: 022-006-00-2	GHS08	[1]	0 <= x % < 2.5

SAFETY DATA SHEET (REGULATION (EC) n° 1907/2006 - REACH) LIBERON - SHELLAC FILLER STICKS (3-pack) - MEDIUM - 3 × 10mL - 126841			(19-12-2022) - Page 2/7
CAS: 13463-67-7 EC: 236-675-5	Wng Carc. 2, H351	[10]	
TITANIUM DIOXIDE [IN F FORM CONTAINING 1 % PARTICLES WITH AERO DIAMETER <= 10 µM]	OR MORE OF		
INDEX: Z858 CAS: 1333-86-4 EC: 215-609-9 REACH: 01-2119384822-	32	[1] [nano]	0 <= x % < 2.5

Nanoform

Identification	Nanoform
INDEX: Z858	Number based particle size distribution:
CAS: 1333-86-4	d10:20-43 nm
EC: 215-609-9	d50 : 30 - 87 nm
REACH: 01-2119384822-32	d90 : 54 - 178 nm
	Specific surface area: 35 - 600 m²/g
NOIR DE CARBONE, AMORPHE	

Information on ingredients:

(Full text of H-phrases: see section 16)

NOIR DE CARBONE, AMORPHE

[Nano] Nanoform.

[1] Substance for which maximum workplace exposure limits are available.

Note 10: The classification as a carcinogen by inhalation applies only to mixtures in powder form containing 1 % or more of titanium dioxide which is in the form of or incorporated in particles with aerodynamic diameter <= 10 µm.

SECTION 4: FIRST AID MEASURES

As a general rule, in case of doubt or if symptoms persist, always call a doctor.

NEVER induce swallowing by an unconscious person.

4.1. description of first aid measures

In the event of splashes or contact with eyes :

Wash thoroughly with fresh, clean water for 15 minutes holding the eyelids open.

In the event of swallowing:

In the event of swallowing, if the quantity is small (no more than one mouthful), rinse the mouth with water and consult a doctor.

Keep the person exposed at rest. Do not force vomiting.

Seek medical attention, showing the label.

If swallowed accidentally, call a doctor to ascertain whether observation and hospital care will be necessary. Show the label.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

$\textbf{4.3.} \ \textbf{Indication of any immediate medical attention and special treatment needed}$

No data available.

SECTION 5: FIREFIGHTING MEASURES

Non-flammable.

5.1. Extinguishing media

Suitable methods of extinction

In the event of a fire, use:

- sprayed water or water mist
- foam
- multipurpose ABC powder
- BC powder
- carbon dioxide (CO2)

Unsuitable methods of extinction

In the event of a fire, do not use:

- water iet

5.2. Special hazards arising from the substance or mixture

A fire will often produce a thick black smoke. Exposure to decomposition products may be hazardous to health.

LIBERON - SHELLAC FILLER STICKS (3-pack) - MEDIUM - 3×10 mL - 126841

Do not breathe in smoke.

In the event of a fire, the following may be formed :

- carbon monoxide (CO)
- carbon dioxide (CO2)

5.3. Advice for firefighters

No data available.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Consult the safety measures listed under headings 7 and 8.

For first aid worker

First aid workers will be equipped with suitable personal protective equipment (See section 8).

6.2. Environmental precautions

Contain and control the leaks or spills with non-combustible absorbent materials such as sand, earth, vermiculite, diatomaceous earth in drums for waste disposal.

Prevent any material from entering drains or waterways.

6.3. Methods and material for containment and cleaning up

No data available.

6.4. Reference to other sections

No data available.

SECTION 7: HANDLING AND STORAGE

Requirements relating to storage premises apply to all facilities where the mixture is handled.

7.1. Precautions for safe handling

Always wash hands after handling.

Remove and wash contaminated clothing before re-using.

Fire prevention:

Handle in well-ventilated areas.

Prevent access by unauthorised personnel.

Recommended equipment and procedures :

For personal protection, see section 8.

Observe precautions stated on label and also industrial safety regulations.

Packages which have been opened must be reclosed carefully and stored in an upright position.

Prohibited equipment and procedures :

No smoking, eating or drinking in areas where the mixture is used.

7.2. Conditions for safe storage, including any incompatibilities

No data available.

Storage

Keep out of reach of children.

Keep the container tightly closed in a dry, well-ventilated place.

Packaging

Always keep in packaging made of an identical material to the original.

7.3. Specific end use(s)

No data available.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Occupational exposure limits :

- France (INRS - Outils 65 / 2021-1849, 2021-1763, decree of 09/12/2021):

· · · · · · · · · · · · · · · · · · ·							
CAS	VME-ppm:	VME-mg/m3:	VLE-ppm:	VLE-mg/m3:	Notes:	TMP No:	
1317-65-3	-	10	-	-	-	-	
13463-67-7	-	10	-	-	-	-	
1333-86-4	-	3.5	-	-	-	-	

- UK / WEL (Workplace exposure limits, EH40/2005, Fourth Edition 2020):

	· · ·	·	<u>'</u>	,	
CAS	TWA:	STEL:	Ceiling:	Definition:	Criteria :
1317-65-3	4 mg/m³				
13463-67-7	4 mg/m³				

SAFETY DATA SHEET (REGULATION (EC) n° 1907/2006 - REACH) LIBERON - SHELLAC FILLER STICKS (3-pack) - MEDIUM - 3 × 10mL - 126841

Version 1.1 (19-12-2022) - Page 4/7

1333-86-4	3.5 mg/m ³	7 mg/m ³		

- ACGIH TLV (American Conference of Governmental Industrial Hygienists, Threshold Limit Values, 2010):					
CAS	TWA:	STEL:	Ceiling :	Definition :	Criteria :
13463-67-7	10 mg/m3			A4	
1333-86-4	3 (I) mg/m3			A3	

8.2. Exposure controls

Personal protection measures, such as personal protective equipment

Use personal protective equipment that is clean and has been properly maintained.

Store personal protective equipment in a clean place, away from the work area.

Never eat, drink or smoke during use. Remove and wash contaminated clothing before re-using. Ensure that there is adequate ventilation, especially in confined areas.

- Eye / face protection

Avoid contact with eyes.

Before handling powders or dust emission, wear mask goggles in accordance with standard EN166.

- Hand protection

Wear suitable protective gloves in the event of prolonged or repeated skin contact.

Use suitable protective gloves that are resistant to chemical agents in accordance with standard EN ISO 374-1.

Gloves must be selected according to the application and duration of use at the workstation.

Protective gloves need to be selected according to their suitability for the workstation in question: other chemical products that may be handled, necessary physical protections (cutting, pricking, heat protection), level of dexterity required.

Type of gloves recommended:

- Natural latex
- Nitrile rubber (butadiene-acrylonitrile copolymer rubber (NBR))
- PVC (polyvinyl chloride)
- PVA (Polyvinyl alcohol)
- Butyl Rubber (Isobutylene-isoprene copolymer)

- Body protection

Work clothing worn by personnel shall be laundered regularly.

After contact with the product, all parts of the body that have been soiled must be washed.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

9.1. Information on basic physical and chemical property	ties
Physical state	
Physical state :	Paste.
Colour	
wood dye	
Odour	
Odour threshold :	Not stated.
Melting point	
Melting point/melting range :	Not relevant.
Freezing point	
Freezing point / Freezing range :	Not stated.
Boiling point or initial boiling point and boiling range	
Boiling point/boiling range :	Not relevant.
Flammability	
Flammability (solid, gas) :	Not stated.
Lower and upper explosion limit	
Explosive properties, lower explosivity limit (%):	Not stated.
Explosive properties, upper explosivity limit (%):	Not stated.
Flash point	
Flash point interval :	Not relevant.
Auto-ignition temperature	
Self-ignition temperature :	Not relevant.
Decomposition temperature	
Decomposition point/decomposition range :	Not relevant.
рН	
pH (aqueous solution) :	Not stated.
pH:	Not stated.

SAFETY DATA SHEET (REGULATION (EC) n° 1907/2006 - REACH) LIBERON - SHELLAC FILLER STICKS (3-pack) - MEDIUM - 3 × 10mL - 126841

Version 1.1 (19-12-2022) - Page 5/7

	Slightly basic.
	Olightity basic.
Kinematic viscosity	
Viscosity:	Not stated.
Solubility	
Water solubility:	Insoluble.
Fat solubility :	Not stated.
Partition coefficient n-octanol/water (log value)	
Partition coefficient: n-octanol/water :	Not stated.
Vapour pressure	
Vapour pressure (50°C) :	Below 110 kPa (1.10 bar).
Density and/or relative density	
Density:	<1
Relative vapour density	
Vapour density :	Not stated.

9.2. Other information

No data available.

9.2.1. Information with regard to physical hazard classes

No data available.

9.2.2. Other safety characteristics

No data available.

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

No data available.

10.2. Chemical stability

This mixture is stable under the recommended handling and storage conditions in section 7.

10.3. Possibility of hazardous reactions

When exposed to high temperatures, the mixture can release hazardous decomposition products, such as carbon monoxide and dioxide, fumes and nitrogen oxide.

10.4. Conditions to avoid

Avoid:

- frost

10.5. Incompatible materials

No data available.

10.6. Hazardous decomposition products

The thermal decomposition may release/form :

- carbon monoxide (CO)
- carbon dioxide (CO2)

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Splashes in the eyes may cause irritation and reversible damage

11.1.1. Substances

Acute toxicity:

NOIR DE CARBONE, AMORPHE (CAS: 1333-86-4)

Oral route : LD50 > 8000 mg/kg Species : Rat

Skin corrosion/skin irritation:

NOIR DE CARBONE, AMORPHE (CAS: 1333-86-4)

Irritation: No observed effect.

Average score < 1.5 Species : Rabbit

11.1.2. Mixture

No toxicological data available for the mixture.

LIBERON - SHELLAC FILLER STICKS (3-pack) - MEDIUM - 3 × 10mL - 126841

11.2. Information on other hazards

Monograph(s) from the IARC (International Agency for Research on Cancer):

CAS 108-05-4 : IARC Group 2B : The agent is possibly carcinogenic to humans.

CAS 1333-86-4: IARC Group 2B: The agent is possibly carcinogenic to humans.

CAS 1309-37-1: IARC Group 3: The agent is not classifiable as to its carcinogenicity to humans.

CAS 13463-67-7: IARC Group 2B: The agent is possibly carcinogenic to humans.

SECTION 12: ECOLOGICAL INFORMATION

12.1. Toxicity

12.1.2. Mixtures

No aquatic toxicity data available for the mixture.

12.2. Persistence and degradability

No data available.

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Endocrine disrupting properties

No data available.

12.7. Other adverse effects

No data available

SECTION 13: DISPOSAL CONSIDERATIONS

Proper waste management of the mixture and/or its container must be determined in accordance with Directive 2008/98/EC.

13.1. Waste treatment methods

Do not pour into drains or waterways.

Waste:

Waste management is carried out without endangering human health, without harming the environment and, in particular without risk to water, air, soil, plants or animals.

Recycle or dispose of waste in compliance with current legislation, preferably via a certified collector or company.

Do not contaminate the ground or water with waste, do not dispose of waste into the environment.

Soiled packaging:

Empty container completely. Keep label(s) on container.

Give to a certified disposal contractor.

SECTION 14: TRANSPORT INFORMATION

Exempt from transport classification and labelling.

14.1. UN number or ID number

14.2. UN proper shipping name

=

14.3. Transport hazard class(es)

14.4. Packing group

-

14.5. Environmental hazards

14.6. Special precautions for user

14.7. Maritime transport in bulk according to IMO instruments

14.7. Martine transport in bulk according to IMO instruments

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

- Classification and labelling information included in section 2:

The following regulations have been used:

- EU Regulation No. 1272/2008 amended by EU Regulation No. 2022/692 (ATP 18)

- Container information:

The mixture does not contain any substance restricted under Annex XVII of Regulation (EC) No. 1907/2006 (REACH): https://echa.europa.eu/substances-restricted-under-reach.

- Particular provisions :

No data available.

15.2. Chemical safety assessment

No data available.

SECTION 16: OTHER INFORMATION

Since the user's working conditions are not known by us, the information supplied on this safety data sheet is based on our current level of knowledge and on national and community regulations.

The mixture must not be used for other uses than those specified in section 1 without having first obtained written handling instructions.

It is at all times the responsibility of the user to take all necessary measures to comply with legal requirements and local regulations.

The information in this safety data sheet must be regarded as a description of the safety requirements relating to the mixture and not as a guarantee of the properties thereof.

Wording of the phrases mentioned in section 3:

H351 Suspected of causing cancer

Abbreviations:

LD50: The dose of a test substance resulting in 50% lethality in a given time period.

REACH: Registration, Evaluation, Authorization and Restriction of Chemical Substances.

STEL: Short-term exposure limit
TWA: Time Weighted Averages
TMP: French Occupational Illness table
TLV: Threshold Limit Value (exposure)

AEV : Average Exposure Value.

ADR: European agreement concerning the international carriage of dangerous goods by Road.

IMDG: International Maritime Dangerous Goods. IATA: International Air Transport Association. ICAO: International Civil Aviation Organisation

RID: Regulations concerning the International carriage of Dangerous goods by rail.

WGK : Wassergefahrdungsklasse (Water Hazard Class).

PBT: Persistent, bioaccumulable and toxic. vPvB: Very persistent, very bioaccumulable. SVHC: Substances of very high concern.