

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 27.06.2017

Version number 4

Revision: 27.06.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** PLASTI-KOTE® Hydro Spray glz. dunkelblau 350ml
- **Article number:** 440.0111010.076
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
- **Sector of Use**
 - SU21 Consumer uses: Private households / general public / consumers
 - SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
 - SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Product category** PC9a Coatings and paints, thinners, paint removers
- **Process category**
 - PROC11 Non industrial spraying
 - PROC7 Industrial spraying
 - PROC11 Non industrial spraying
- **Environmental release category**
 - ERC8f Widespread use leading to inclusion into/onto article (outdoor)
 - ERC8a Widespread use of non-reactive processing aid (no inclusion into or onto article, indoor)
 - ERC8d Widespread use of non-reactive processing aid (no inclusion into or onto article, outdoor)
- **Application of the substance / the mixture** Lacquer
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
 - MOTIP DUPLI GmbH
 - Kurt Vogelsang Strasse 6
 - D-74855 Haßmersheim
 - Tel.: +49/6266/75-0
 - msds@dupli-color.de
- **Further information obtainable from:** Department Product Safety
- **1.4 Emergency telephone number:**
 - Tel.: +49 6266-75-310
 - Fax +49 6266-75-362
 - (Mo - Th 08:00 am - 04:00 pm, Fr 08:00 am - 00:30 pm)

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
 - The product is classified and labelled according to the CLP regulation.

(Contd. on page 2)

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 27.06.2017

Version number 4

Revision: 27.06.2017

Trade name: **PLASTI-KOTE® Hydro Spray glz. dunkelblau 350ml**

(Contd. of page 1)

· **Hazard pictograms**

GHS02

· **Signal word** Danger· **Hazard statements**

H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

· **Precautionary statements**

P101 If medical advice is needed, have product container or label at hand.

P102 Keep out of reach of children.

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P211 Do not spray on an open flame or other ignition source.

P251 Do not pierce or burn, even after use.

P260 Do not breathe spray.

P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.

P501 Dispose of contents / container in accordance with regional regulations.

· **Additional information:**

Buildup of explosive mixtures possible without sufficient ventilation.

· **2.3 Other hazards**· **Results of PBT and vPvB assessment**· **PBT:** Not applicable.· **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

· **3.2 Chemical characterisation: Mixtures**· **Description:** Mixture of substances listed below with nonhazardous additions.· **Dangerous components:**

CAS: 115-10-6 EINECS: 204-065-8 Index number: 603-019-00-8 Reg.nr.: 01-2119472128-37	dimethyl ether	Flam. Gas 1, H220 Press. Gas C, H280	25-<50%
CAS: 123-86-4 EINECS: 204-658-1 Index number: 607-025-00-1 Reg.nr.: 01-2119485493-29	n-butyl acetate	Flam. Liq. 3, H226 STOT SE 3, H336	2.5-<5.0%

· **Additional information:**

The content of Benzene (EINECS-Nr. 200-753-7) in the ingredients is less than 0,1% (Note P Annex 1A 1272/2008 EU), so the classification as carcinogen need not to apply.

For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

· **4.1 Description of first aid measures**· **After inhalation:** Supply fresh air; consult doctor in case of complaints.· **After skin contact:** Generally the product does not irritate the skin.· **After eye contact:** Rinse opened eye for several minutes under running water.· **After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.· **4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.

(Contd. on page 3)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 27.06.2017

Version number 4

Revision: 27.06.2017

Trade name: PLASTI-KOTE® Hydro Spray glz. dunkelblau 350ml

(Contd. of page 2)

- **4.3 Indication of any immediate medical attention and special treatment needed**
No further relevant information available.

SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:** Use fire extinguishing methods suitable to surrounding conditions.
- **5.2 Special hazards arising from the substance or mixture**
During heating or in case of fire poisonous gases are produced.
- **5.3 Advice for firefighters -**
- **Protective equipment:** Mouth respiratory protective device.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**
Mount respiratory protective device.
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**
Ensure good ventilation/exhaustion at the workplace.
No special measures required.
- **Information about fire - and explosion protection:**
Keep ignition sources away - Do not smoke.
Keep respiratory protective device available.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**
Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep container tightly sealed.
- **Storage class:** 2 B
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**

- **Ingredients with limit values that require monitoring at the workplace:**

115-10-6 dimethyl ether

WEL	Short-term value: 958 mg/m ³ , 500 ppm
	Long-term value: 766 mg/m ³ , 400 ppm

(Contd. on page 4)

GB

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 27.06.2017

Version number 4

Revision: 27.06.2017

Trade name: **PLASTI-KOTE® Hydro Spray glz. dunkelblau 350ml**

(Contd. of page 3)

123-86-4 n-butyl acetate

WEL	Short-term value: 966 mg/m ³ , 200 ppm Long-term value: 724 mg/m ³ , 150 ppm
-----	---

- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.
- **Respiratory protection:**
In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.
- **Protection of hands:**
In case of contact with spray dust protective gloves made of butyl should be used (min. 0.4 mm thick), e.g. KCL Camatril, article no. 898 or similar products
Solvent resistant gloves
The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.
Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.
Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**
Natural rubber, NR
Butyl rubber, BR
The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**
Butyl rubber gloves with a thickness of 0.4 mm are resistant to:
Acetone: 480 min
Butyl acetate: 60 min
Ethyl acetate: 170 min
Xylene: 42 min
The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **For the permanent contact in work areas without heightened risk of injury (e.g. Laboratory) gloves made of the following material are suitable:**
Natural rubber, NR
- **Eye protection:** Not required.

SECTION 9: Physical and chemical properties

- **9.1 Information on basic physical and chemical properties**
- **General Information**
- **Appearance:**

Form:	Aerosol
Colour:	According to product specification
- **Odour:** Characteristic
- **Odour threshold:** Not determined.
- **pH-value at 20 °C (68 °F):** >8
- **Change in condition**

Melting point/freezing point:	Undetermined.
Initial boiling point and boiling range:	Not applicable, as aerosol.

(Contd. on page 5)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 27.06.2017

Version number 4

Revision: 27.06.2017

Trade name: **PLASTI-KOTE® Hydro Spray glz. dunkelblau 350ml**

(Contd. of page 4)

· Flash point:	Not applicable, as aerosol.
· Flammability (solid, gas):	Not applicable.
· Ignition temperature:	240 °C (464 °F)
· Decomposition temperature:	Not determined.
· Auto-ignition temperature:	Product is not selfigniting.
· Explosive properties:	Not determined.
· Explosion limits:	
Lower:	3.3 Vol %
Upper:	26.2 Vol %
· Vapour pressure at 20 °C (68 °F):	4000 hPa (3000 mm Hg)
· Density at 20 °C (68 °F):	0.88 g/cm ³ (7.344 lbs/gal)
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not applicable.
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient: n-octanol/water:	Not determined.
· Viscosity:	
Dynamic:	Not determined.
Kinematic:	Not determined.
· Solvent content:	
Organic solvents:	52.5 %
VOC (EC)	---
	461.6 g/l
· VOC-EU%	52.51 %
· Solids content:	47.5 %
· 9.2 Other information	No further relevant information available.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.

· LD/LC50 values relevant for classification:		
115-10-6 dimethyl ether		
Inhalative	LC50	309 mg/l (rat)
123-86-4 n-butyl acetate		
Oral	LD50	10770 mg/kg (rat)

(Contd. on page 6)

GB

Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 27.06.2017

Version number 4

Revision: 27.06.2017

Trade name: **PLASTI-KOTE® Hydro Spray glz. dunkelblau 350ml**

(Contd. of page 5)

Dermal	LD50	>17600 mg/kg (rabbit)
Inhalative	LC50 / 4 h	>21.0 mg/m ³ (rat)

- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

· 12.1 Toxicity

· Aquatic toxicity:

115-10-6 dimethyl ether

EC50 / 48 h >4000 mg/l (daphnia magna)

123-86-4 n-butyl acetate

EC50 / 48 h 44 mg/l (daphnia magna)

EC50 / 96 h 320 mg/l (algae)

LC50 / 24 h 205 mg/l (daphnia magna)

LC50 / 96 h 18 mg/l (Pimephales promelas)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

· 13.1 Waste treatment methods

· Recommendation

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

· European waste catalogue

08 01 11*	waste paint and varnish containing organic solvents or other hazardous substances
15 01 04	metallic packaging
15 01 11*	metallic packaging containing a hazardous solid porous matrix (for example asbestos), including empty pressure containers

(Contd. on page 7)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 27.06.2017

Version number 4

Revision: 27.06.2017

Trade name: **PLASTI-KOTE® Hydro Spray glz. dunkelblau 350ml**

(Contd. of page 6)

- **Uncleaned packaging:**
- **Recommendation:** Non contaminated packagings may be recycled.

SECTION 14: Transport information

- **14.1 UN-Number**
- **ADR, IMDG, IATA** UN1950

- **14.2 UN proper shipping name**
- **ADR** 1950 AEROSOLS
- **IMDG** AEROSOLS
- **IATA** AEROSOLS, flammable

- **14.3 Transport hazard class(es)**
- **ADR**



- **Class** 2 5F Gases.
- **Label** 2.1

- **IMDG, IATA**



- **Class** 2.1
- **Label** 2.1

- **14.4 Packing group**
- **ADR, IMDG, IATA** not regulated

- **14.5 Environmental hazards:** Not applicable.

- **14.6 Special precautions for user** Warning: Gases.
- **Danger code (Kemler):** -
- **EMS Number:** F-D,S-U
- **Stowage Code** SW1 Protected from sources of heat.
SW22 For AEROSOLS with a maximum capacity of 1 litre:
Category A. For AEROSOLS with a capacity above 1 litre:
Category B. For WASTE AEROSOLS: Category C, Clear
of living quarters.
- **Segregation Code** SG69 For AEROSOLS with a maximum capacity of 1 litre:
Segregation as for class 9. Stow "separated from" class 1
except for division 1.4. For AEROSOLS with a capacity
above 1 litre: Segregation as for the appropriate
subdivision of class 2. For WASTE AEROSOLS:
Segregation as for the appropriate subdivision of class 2.

- **14.7 Transport in bulk according to Annex II of
Marpol and the IBC Code** Not applicable.

- **Transport/Additional information:**

- **ADR**
- **Limited quantities (LQ)** 1L
- **Excepted quantities (EQ)** Code: E0
Not permitted as Excepted Quantity

(Contd. on page 8)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 27.06.2017

Version number 4

Revision: 27.06.2017

Trade name: PLASTI-KOTE® Hydro Spray glz. dunkelblau 350ml

(Contd. of page 7)

· Transport category	2
· Tunnel restriction code	D
<hr/>	
· IMDG	
· Limited quantities (LQ)	1L
· Excepted quantities (EQ)	Code: E0 Not permitted as Excepted Quantity
· UN "Model Regulation":	UN 1950 AEROSOLS, 2.1

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 150 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
H220 Extremely flammable gas.
H226 Flammable liquid and vapour.
H280 Contains gas under pressure; may explode if heated.
H336 May cause drowsiness or dizziness.
- **Abbreviations and acronyms:**
RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)
IATA-DGR: Dangerous Goods Regulations by the "International Air Transport Association" (IATA)
ICAO: International Civil Aviation Organisation
ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)
IMDG: International Maritime Code for Dangerous Goods
IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
EINECS: European Inventory of Existing Commercial Chemical Substances
ELINCS: European List of Notified Chemical Substances
CAS: Chemical Abstracts Service (division of the American Chemical Society)
VOC: Volatile Organic Compounds (USA, EU)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
PBT: Persistent, Bioaccumulative and Toxic
vPvB: very Persistent and very Bioaccumulative
Flam. Gas 1: Flammable gases – Category 1
Aerosol 1: Aerosols – Category 1
Press. Gas C: Gases under pressure – Compressed gas
Flam. Liq. 3: Flammable liquids – Category 3
STOT SE 3: Specific target organ toxicity (single exposure) – Category 3
- *** Data compared to the previous version altered.**

GB