

# SAFETY DATA SHEET

(REACH regulation (EC) n° 1907/2006 - n° 2020/878)

## SECTION 1 : IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

### 1.1. Product identifier

Product name : LIBERON - WAX FILLER STICK - 8 - Medium Oak - 50 g BP

Product code : 126846

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Wax

### Use descriptor system (REACH) :

Paints, varnishes and related products coating with layered application.

### 1.3. Details of the supplier of the safety data sheet

Registered company name : LIBERON Ltd

Address : .Mountfield Industrial Estate KENT TN28 8XU NEW ROMNEY GB

Telephone : + (44) 1797 367 555. Fax: + (44) 1797 367 575. Telex: .

fds.produits@v33.com

www.liberon.co.uk

### 1.4. Emergency telephone number : .

Association/Organisation : .

### Other emergency numbers

UK/NL: 111 - Emergency Action: In the event of a medical enquiry involving this product, please contact your doctor or local hospital accident and emergency department.

Republic of Ireland : +353 (0)1 809

2166 - Emergency medical information: 8am-10pm (seven days) contact NPIC, Beaumont Hospital, Dublin 9 DOV2NO, Ireland.

## SECTION 2 : HAZARDS IDENTIFICATION

### 2.1. Classification of the substance or mixture

#### In compliance with EC regulation No. 1272/2008 and its amendments.

This mixture does not present a physical hazard. Refer to the recommendations regarding the other products present on the site.

This mixture does not present a health hazard with the exception of possible occupational exposure thresholds (see paragraphs 3 and 8).

This mixture does not present an environmental hazard. No known or foreseeable environmental damage under standard conditions of use.

### 2.2. Label elements

#### In compliance with EC regulation No. 1272/2008 and its amendments.

Precautionary statements - General :

P102 Keep out of reach of children.

Precautionary statements - Prevention :

P271 Use only outdoors or in a well-ventilated area.

Precautionary statements - Disposal :

P501 Dispose of contents/container to a waste collection center (contact the local authority)

### 2.3. Other hazards

The mixture does not contain substances classified as 'Substances of Very High Concern' (SVHC)  $\geq 0.1\%$  published by the European CHemicals Agency (ECHA) under article 57 of REACH: <http://echa.europa.eu/fr/candidate-list-table>

The mixture fulfils neither the PBT nor the vPvB criteria for mixtures in accordance with annexe XIII of the REACH regulations EC 1907/2006.

The mixture does not contain substances  $\geq 0.1\%$  with endocrine disrupting properties in accordance with the criteria of the Delegated Regulation (EU) 2017/2100 of the Commission or Regulation (EU) 2018/605 of the Commission.

## SECTION 3 : COMPOSITION/INFORMATION ON INGREDIENTS

### 3.2. Mixtures

#### Composition :

| Identification                                                                                               | (EC) 1272/2008 | Note | %                  |
|--------------------------------------------------------------------------------------------------------------|----------------|------|--------------------|
| INDEX: Z365<br>CAS: 8002-74-2<br>EC: 232-315-6<br>REACH: 01-2119488076-30<br><br>CIRES DE PARAFFINE ET CIRES |                | [1]  | 10 $\leq$ x % < 25 |

|                                                                                    |                                   |  |                |
|------------------------------------------------------------------------------------|-----------------------------------|--|----------------|
| D'HYDROCARBURES                                                                    |                                   |  |                |
| INDEX: 649_474_00_6<br>CAS: 64742-65-0<br>EC: 265-169-7<br>REACH: 01-2119487077-29 | GHS08<br>Dgr<br>Asp. Tox. 1, H304 |  | 0 <= x % < 2.5 |
| DISTILLATES (PETROLEUM),<br>SOLVENT-DEWAXED HEAVY<br>PARAFFINIC                    |                                   |  |                |

**Information on ingredients :**

(Full text of H-phrases: see section 16)

[1] Substance for which maximum workplace exposure limits are available.

**SECTION 4 : FIRST AID MEASURES**

As a general rule, in case of doubt or if symptoms persist, always call a doctor.

NEVER induce swallowing by an unconscious person.

**4.1. description of first aid measures****In the event of swallowing :**

Seek medical attention, showing the label.

**4.2. Most important symptoms and effects, both acute and delayed**

No data available.

**4.3. Indication of any immediate medical attention and special treatment needed**

No data available.

**SECTION 5 : FIREFIGHTING MEASURES**

Non-flammable.

**5.1. Extinguishing media****Suitable methods of extinction**

In the event of a fire, use :

- sprayed water or water mist
- foam
- multipurpose ABC powder
- BC powder
- carbon dioxide (CO<sub>2</sub>)

**Unsuitable methods of extinction**

In the event of a fire, do not use :

- water jet

**5.2. Special hazards arising from the substance or mixture**

A fire will often produce a thick black smoke. Exposure to decomposition products may be hazardous to health.

Do not breathe in smoke.

In the event of a fire, the following may be formed :

- carbon monoxide (CO)
- carbon dioxide (CO<sub>2</sub>)

**5.3. Advice for firefighters**

No data available.

**SECTION 6 : ACCIDENTAL RELEASE MEASURES****6.1. Personal precautions, protective equipment and emergency procedures**

Consult the safety measures listed under headings 7 and 8.

**For first aid worker**

First aid workers will be equipped with suitable personal protective equipment (See section 8).

**6.2. Environmental precautions**

Prevent any material from entering drains or waterways.

**6.3. Methods and material for containment and cleaning up**

No data available.

**6.4. Reference to other sections**

No data available.

**SECTION 7 : HANDLING AND STORAGE**

Requirements relating to storage premises apply to all facilities where the mixture is handled.

**7.1. Precautions for safe handling**

Always wash hands after handling.

**Fire prevention :**

Prevent access by unauthorised personnel.

**Recommended equipment and procedures :**

For personal protection, see section 8.

Observe precautions stated on label and also industrial safety regulations.

**Prohibited equipment and procedures :**

No smoking, eating or drinking in areas where the mixture is used.

**7.2. Conditions for safe storage, including any incompatibilities**

No data available.

**Storage**

Keep out of reach of children.

**Packaging**

Always keep in packaging made of an identical material to the original.

**7.3. Specific end use(s)**

No data available.

**SECTION 8 : EXPOSURE CONTROLS/PERSONAL PROTECTION****8.1. Control parameters****Occupational exposure limits :**

- France (INRS - Outils 65 / 2021-1849, 2021-1763, decree of 09/12/2021) :

| CAS       | VME-ppm : | VME-mg/m3 : | VLE-ppm : | VLE-mg/m3 : | Notes : | TMP No : |
|-----------|-----------|-------------|-----------|-------------|---------|----------|
| 8002-74-2 | -         | 2           | -         | -           | -       | 36       |

- ACGIH TLV (American Conference of Governmental Industrial Hygienists, Threshold Limit Values, 2010) :

| CAS       | TWA :   | STEL : | Ceiling : | Definition : | Criteria : |
|-----------|---------|--------|-----------|--------------|------------|
| 8002-74-2 | 2 mg/m3 |        |           |              |            |

- UK / WEL (Workplace exposure limits, EH40/2005, Fourth Edition 2020) :

| CAS       | TWA :               | STEL :              | Ceiling : | Definition : | Criteria : |
|-----------|---------------------|---------------------|-----------|--------------|------------|
| 8002-74-2 | 2 mg/m <sup>3</sup> | 6 mg/m <sup>3</sup> |           |              |            |

**8.2. Exposure controls****Personal protection measures, such as personal protective equipment**

Use personal protective equipment that is clean and has been properly maintained.

Store personal protective equipment in a clean place, away from the work area.

Never eat, drink or smoke during use. Remove and wash contaminated clothing before re-using. Ensure that there is adequate ventilation, especially in confined areas.

**- Eye / face protection**

Avoid contact with eyes.

Before handling powders or dust emission, wear mask goggles in accordance with standard EN166.

**- Hand protection**

Wear suitable protective gloves in the event of prolonged or repeated skin contact.

Type of gloves recommended :

- Natural latex
- Nitrile rubber (butadiene-acrylonitrile copolymer rubber (NBR))
- PVC (polyvinyl chloride)
- Butyl Rubber (Isobutylene-isoprene copolymer)

**- Body protection**

Work clothing worn by personnel shall be laundered regularly.

After contact with the product, all parts of the body that have been soiled must be washed.

**SECTION 9 : PHYSICAL AND CHEMICAL PROPERTIES****9.1. Information on basic physical and chemical properties****Physical state**

|                                                                 |                 |
|-----------------------------------------------------------------|-----------------|
| Physical state :                                                | Paste.          |
| <b>Colour</b><br>wood dye                                       |                 |
| <b>Odour</b>                                                    |                 |
| Odour threshold :                                               | Not stated.     |
| <b>Melting point</b>                                            |                 |
| Melting point/melting range :                                   | Not relevant.   |
| <b>Freezing point</b>                                           |                 |
| Freezing point / Freezing range :                               | Not stated.     |
| <b>Boiling point or initial boiling point and boiling range</b> |                 |
| Boiling point/boiling range :                                   | Not relevant.   |
| <b>Flammability</b>                                             |                 |
| Flammability (solid, gas) :                                     | Not stated.     |
| <b>Lower and upper explosion limit</b>                          |                 |
| Explosive properties, lower explosivity limit (%) :             | Not stated.     |
| Explosive properties, upper explosivity limit (%) :             | Not stated.     |
| <b>Flash point</b>                                              |                 |
| Flash point interval :                                          | Not relevant.   |
| <b>Auto-ignition temperature</b>                                |                 |
| Self-ignition temperature :                                     | Not relevant.   |
| <b>Decomposition temperature</b>                                |                 |
| Decomposition point/decomposition range :                       | Not relevant.   |
| <b>pH</b>                                                       |                 |
| pH (aqueous solution) :                                         | Not stated.     |
| pH :                                                            | 8.00 .          |
|                                                                 | Slightly basic. |
| <b>Kinematic viscosity</b>                                      |                 |
| Viscosity :                                                     | Not stated.     |
| <b>Solubility</b>                                               |                 |
| Water solubility :                                              | Insoluble.      |
| Fat solubility :                                                | Not stated.     |
| <b>Partition coefficient n-octanol/water (log value)</b>        |                 |
| Partition coefficient: n-octanol/water :                        | Not stated.     |
| <b>Vapour pressure</b>                                          |                 |
| Vapour pressure (50°C) :                                        | Not relevant.   |
| <b>Density and/or relative density</b>                          |                 |
| Density :                                                       | < 1             |
| <b>Relative vapour density</b>                                  |                 |
| Vapour density :                                                | Not stated.     |

**9.2. Other information**

No data available.

**9.2.1. Information with regard to physical hazard classes**

No data available.

**9.2.2. Other safety characteristics**

No data available.

**SECTION 10 : STABILITY AND REACTIVITY****10.1. Reactivity**

No data available.

**10.2. Chemical stability**

This mixture is stable under the recommended handling and storage conditions in section 7.

**10.3. Possibility of hazardous reactions**

No data available.

**10.4. Conditions to avoid**

Avoid :

- frost

#### 10.5. Incompatible materials

No data available.

#### 10.6. Hazardous decomposition products

The thermal decomposition may release/form :

- carbon monoxide (CO)
- carbon dioxide (CO<sub>2</sub>)

### SECTION 11 : TOXICOLOGICAL INFORMATION

#### 11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

No data available.

##### 11.1.1. Substances

No toxicological data available for the substances.

##### 11.1.2. Mixture

No toxicological data available for the mixture.

#### 11.2. Information on other hazards

##### Monograph(s) from the IARC (International Agency for Research on Cancer) :

- CAS 108-05-4 : IARC Group 2B : The agent is possibly carcinogenic to humans.  
CAS 13463-67-7 : IARC Group 2B : The agent is possibly carcinogenic to humans.

### SECTION 12 : ECOLOGICAL INFORMATION

#### 12.1. Toxicity

##### 12.1.2. Mixtures

No aquatic toxicity data available for the mixture.

#### 12.2. Persistence and degradability

No data available.

#### 12.3. Bioaccumulative potential

No data available.

#### 12.4. Mobility in soil

No data available.

#### 12.5. Results of PBT and vPvB assessment

No data available.

#### 12.6. Endocrine disrupting properties

No data available.

#### 12.7. Other adverse effects

No data available.

### SECTION 13 : DISPOSAL CONSIDERATIONS

Proper waste management of the mixture and/or its container must be determined in accordance with Directive 2008/98/EC.

#### 13.1. Waste treatment methods

Do not pour into drains or waterways.

##### Waste :

Waste management is carried out without endangering human health, without harming the environment and, in particular without risk to water, air, soil, plants or animals.

Recycle or dispose of waste in compliance with current legislation, preferably via a certified collector or company.

Do not contaminate the ground or water with waste, do not dispose of waste into the environment.

##### Soiled packaging :

Empty container completely. Keep label(s) on container.

Give to a certified disposal contractor.

### SECTION 14 : TRANSPORT INFORMATION

Exempt from transport classification and labelling.

#### 14.1. UN number or ID number

-

#### 14.2. UN proper shipping name

-

**14.3. Transport hazard class(es)**

-

**14.4. Packing group**

-

**14.5. Environmental hazards**

-

**14.6. Special precautions for user**

-

**14.7. Maritime transport in bulk according to IMO instruments**

-

## SECTION 15: Regulatory information

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

**- Classification and labelling information included in section 2:**

The following regulations have been used:

- EU Regulation No. 1272/2008 amended by EU Regulation No. 2022/692 (ATP 18)

**- Container information:**

The mixture does not contain any substance restricted under Annex XVII of Regulation (EC) No. 1907/2006 (REACH):

<https://echa.europa.eu/substances-restricted-under-reach>.

**- Particular provisions :**

No data available.

**15.2. Chemical safety assessment**

No data available.

## SECTION 16 : OTHER INFORMATION

Since the user's working conditions are not known by us, the information supplied on this safety data sheet is based on our current level of knowledge and on national and community regulations.

The mixture must not be used for other uses than those specified in section 1 without having first obtained written handling instructions.

It is at all times the responsibility of the user to take all necessary measures to comply with legal requirements and local regulations.

The information in this safety data sheet must be regarded as a description of the safety requirements relating to the mixture and not as a guarantee of the properties thereof.

**Wording of the phrases mentioned in section 3 :**

|      |                                               |
|------|-----------------------------------------------|
| H304 | May be fatal if swallowed and enters airways. |
|------|-----------------------------------------------|

**Abbreviations :**

REACH : Registration, Evaluation, Authorization and Restriction of Chemical Substances.

STEL : Short-term exposure limit

TWA : Time Weighted Averages

TMP : French Occupational Illness table

TLV : Threshold Limit Value (exposure)

AEV : Average Exposure Value.

ADR : European agreement concerning the international carriage of dangerous goods by Road.

IMDG : International Maritime Dangerous Goods.

IATA : International Air Transport Association.

ICAO : International Civil Aviation Organisation

RID : Regulations concerning the International carriage of Dangerous goods by rail.

WGK : Wassergefährdungsklasse (Water Hazard Class).

PBT: Persistent, bioaccumulable and toxic.

vPvB : Very persistent, very bioaccumulable.

SVHC : Substances of very high concern.