



Rustins QD ASAP Range

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2015/830
Issue date: 9/3/2015 Revision date: 7/24/2023 Supersedes version of: 7/13/2023 Version: 7.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Trade name : Rustins QD ASAP Range
UFI : 0UG7-H0HW-N002-C2HE
Product code : ASAP
Type of product : Paint
Product group : End product

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Intended for general public
Main use category : Consumer use, Professional use
Use of the substance/mixture : Colouring agents
Function or use category : Colouring agents

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Manufacturer

Rustins Ltd
Waterloo road
NW2 7TX London
United Kingdom
T +44 (0)208 450 4666 - F +44 (0)208 452 2008
rustins@rustins.co.uk - rustins.ltd

Distributor

Excellence Ltd
43 Grange Parade,
Unit 43 Baldoyle Industrial Estate,
D13 Y860 Dublin
Ireland
T 00353 (0)1 8323300 - F 00353 (0)1 8323584
Orders@excellence.ie - www.excellence.ie

1.4. Emergency telephone number

Emergency number : +44 (0)208 450 4666
OFFICE HOURS ONLY MON. - FRI. 08:00 - 16:30

Country	Organisation/Company	Address	Emergency number	Comment
Ireland	National Poisons Information Centre Beaumont Hospital	PO Box 1297 Beaumont Road 9	+353 1 809 2566 (Healthcare professionals- 24/7) +353 1 809 2166 (public, 8am - 10pm, 7/7)	
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH	0344 892 0111	Only for healthcare professionals

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

Adverse physicochemical, human health and environmental effects

To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.

Rustins QD ASAP Range

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2015/830

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Precautionary statements (CLP)	: P102 - Keep out of reach of children. P234 - Keep only in original packaging. P314 - Get medical advice/attention if you feel unwell. P301+P310 - IF SWALLOWED: Immediately call a POISON CENTER. P501 - Dispose of contents and container to hazardous or special waste collection point, in accordance with local, regional, national and/or international regulation.
EUH-statements	: EUH211 - Warning! Hazardous respirable droplets may be formed when sprayed. Do not breathe spray or mist. EUH208 - Contains Mixture of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1). May produce an allergic reaction.

2.3. Other hazards

Other hazards which do not result in classification : The classification for titanium dioxide as a carcinogen by inhalation applies only to mixtures in powder form containing 1% or more of titanium dioxide which is in the form of or incorporated into particles with an aerodynamic diameter of less than or equal to 10µm.

Contains no PBT/vPvB substances $\geq 0.1\%$ assessed in accordance with REACH Annex XIII

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Titanium Dioxide	CAS-No.: 12026-28-7 EC-No.: 236-675-5 REACH-no: 01-2119489379-17	$\geq 10 - < 15$	Carc. 2, H351
5-CHLORO-2-METHYL-2H-ISOTHIAZOL-3-ONE	CAS-No.: 55965-84-9 EC Index-No.: 613-167-00-5	< 0.1	Acute Tox. 3 (Oral), H301 Acute Tox. 2 (Dermal), H310 Acute Tox. 2 (Inhalation), H330 Skin Corr. 1C, H314 Eye Dam. 1, H318 Skin Sens. 1A, H317 Aquatic Acute 1, H400 Aquatic Chronic 1, H410

Specific concentration limits:

Name	Product identifier	Specific concentration limits
5-CHLORO-2-METHYL-2H-ISOTHIAZOL-3-ONE	CAS-No.: 55965-84-9 EC Index-No.: 613-167-00-5	(0.0015 \leq C \leq 100) Skin Sens. 1A, H317 (0.06 \leq C $<$ 0.6) Skin Irrit. 2, H315 (0.06 \leq C $<$ 0.6) Eye Irrit. 2, H319 (0.6 \leq C \leq 100) Skin Corr. 1C, H314 (0.6 \leq C \leq 100) Eye Dam. 1, H318

Full text of H- and EUH-statements: see section 16

Rustins QD ASAP Range

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2015/830

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures general	: Call a poison center or a doctor if you feel unwell.
First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash skin with plenty of water.
First-aid measures after eye contact	: Rinse eyes with water as a precaution.
First-aid measures after ingestion	: Call a poison center or a doctor if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects	: Not expected to present a significant hazard under anticipated conditions of normal use.
Symptoms/effects after inhalation	: None under normal use.
Symptoms/effects after skin contact	: Slight irritation.
Symptoms/effects after eye contact	: May cause slight irritation.
Symptoms/effects after ingestion	: None under normal conditions.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Water spray. Dry powder. Foam. Carbon dioxide.
------------------------------	--

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire	: Toxic fumes may be released.
--	--------------------------------

5.3. Advice for firefighters

Precautionary measures fire	: Keep container tightly closed and away from heat, sparks and flame.
Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures	: Absorb spillage to prevent material damage.
------------------	---

6.1.1. For non-emergency personnel

Protective equipment	: Wear recommended personal protective equipment.
Emergency procedures	: Ventilate spillage area.

6.1.2. For emergency responders

Protective equipment	: Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".
----------------------	---

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

For containment	: Absorb spilled material with sand or earth.
Methods for cleaning up	: Take up liquid spill into absorbent material.
Other information	: Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

Rustins QD ASAP Range

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2015/830

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Additional hazards when processed	: Not expected to present a significant hazard under anticipated conditions of normal use.
Precautions for safe handling	: Ensure good ventilation of the work station. Wear personal protective equipment.
Hygiene measures	: Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Technical measures	: Keep in a cool, well-ventilated place away from heat.
Storage conditions	: Store in a well-ventilated place. Keep cool.
Incompatible products	: Oxidizing agent. Strong acids. Strong bases.
Incompatible materials	: Heat sources.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

Rustins QD ASAP Range	
Austria - Occupational Exposure Limits	
Local name	5-Chlor-2-methyl-2,3-dihydroisothiazol-3-on und 2-Methyl-2,3-di-hydroisothiazol-3-on (Gemisch im Verhältnis 3:1)
MAK (OEL TWA)	0.05 mg/m ³
Remark	Sh
Regulatory reference	BGBl. II Nr. 156/2021
Switzerland - Occupational Exposure Limits	
Local name	2,3-Dihydro-isothiazol-3-one de 5-chloro-2-méthyle et 2,3-dihydro-isothiazol-3-one de 2-méthyle [2,3-Dihydro-isothiazol-3-one de 5-chloro-2-méthyle, 2,3-Dihydro-isothiazol-3-one de 2-méthyle] / 5-Chlor-2-methyl-2,3-dihydro-isothiazol-3-on und 2-Methyl-2,3-dihydroisothiazol-3-on [2-Methyl-2,3-dihydroisothiazol-3-on, 5-Chlor-2-methyl-2,3-dihydroisothiazol-3-on]
MAK (OEL TWA) [1]	0.2 mg/m ³ (i) / (e)
KZGW (OEL STEL)	0.4 mg/m ³ (i) / (e)
Critical toxicity	VRS, Peau, Yeux / OAW, Haut, Auge
Notation	S, SS _C / S, SS _C
Regulatory reference	www.suva.ch, 01.01.2023

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

Rustins QD ASAP Range

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2015/830

8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

8.2.2. Personal protection equipment

Personal protective equipment:

Gloves.

Personal protective equipment symbol(s):



8.2.2.1. Eye and face protection

Eye protection:

Safety glasses

8.2.2.2. Skin protection

Skin and body protection:

Wear suitable protective clothing

Hand protection:

Protective gloves

8.2.2.3. Respiratory protection

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Environmental exposure controls:

Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: white.
Odour	: Low.
Odour threshold	: No data available
pH	: 7 – 8
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available.
Freezing point	: No data available
Boiling point	: 100 °C
Flash point	: > 93 °C
Auto-ignition temperature	: No data available.
Decomposition temperature	: No data available
Flammability (solid, gas)	: Not applicable
Vapour pressure	: No data available
Relative vapour density at 20°C	: No data available.
Relative density	: 1.24-1.25 @ 20 C
Solubility	: Material highly soluble in water.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available

Rustins QD ASAP Range

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2015/830

Explosive properties : No data available
Oxidising properties : No data available
Explosive limits : No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity (oral) : Not classified
Acute toxicity (dermal) : Not classified
Acute toxicity (inhalation) : Not classified

Titanium Dioxide (12026-28-7)	
LD50 oral rat	> 5000 mg/kg bodyweight Animal: rat, Animal sex: female, Guideline: OECD Guideline 425 (Acute Oral Toxicity: Up-and-Down Procedure), Guideline: EPA OPPTS 870.1100 (Acute Oral Toxicity)

Skin corrosion/irritation : Not classified
pH: 7 – 8
Serious eye damage/irritation : Not classified
pH: 7 – 8
Respiratory or skin sensitisation : Not classified
Germ cell mutagenicity : Not classified
Carcinogenicity : Not classified
Reproductive toxicity : Not classified
STOT-single exposure : Not classified
STOT-repeated exposure : Not classified
Aspiration hazard : Not classified

Titanium Dioxide (12026-28-7)	
Viscosity, kinematic	Not applicable

Rustins QD ASAP Range

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2015/830

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general : The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.

Hazardous to the aquatic environment, short-term (acute) : Not classified

Hazardous to the aquatic environment, long-term (chronic) : Not classified

Not rapidly degradable

Titanium Dioxide (12026-28-7)	
EC50 - Other aquatic organisms [1]	> 100 mg/l Test organisms (species):
EC50 72h - Algae [1]	> 100 mg/l Test organisms (species): Pseudokirchneriella subcapitata (previous names: Raphidocelis subcapitata, Selenastrum capricornutum)
LOEC (chronic)	5 mg/l Test organisms (species): Daphnia magna Duration: '21 d'

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.2. UN proper shipping name				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated

Rustins QD ASAP Range

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2015/830

ADR	IMDG	IATA	ADN	RID
14.5. Environmental hazards				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				

14.6. Special precautions for user

Overland transport

Not regulated

Transport by sea

Not regulated

Air transport

Not regulated

Inland waterway transport

Not regulated

Rail transport

Not regulated

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

REACH Annex XVII (Restriction List)

Contains no substance(s) listed on REACH Annex XVII (Restriction Conditions)

REACH Annex XIV (Authorisation List)

Contains no substance(s) listed on REACH Annex XIV (Authorisation List)

REACH Candidate List (SVHC)

Contains no substance(s) listed on the REACH Candidate List

PIC Regulation (Prior Informed Consent)

Contains no substance(s) listed on the PIC list (Regulation EU 649/2012 concerning the export and import of hazardous chemicals)

POP Regulation (Persistent Organic Pollutants)

Contains no substance(s) listed on the POP list (Regulation EU 2019/1021 on persistent organic pollutants)

Ozone Regulation (1005/2009)

Contains no substance(s) listed on the Ozone Depletion list (Regulation EU 1005/2009 on substances that deplete the ozone layer)

VOC Directive (2004/42)

Organic solvent : Yes

Explosives Precursors Regulation (2019/1148)

Contains no substance(s) listed on the Explosives Precursors list (Regulation EU 2019/1148 on the marketing and use of explosives precursors)

Drug Precursors Regulation (273/2004)

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on the manufacture and the placing on market of certain substances used in the illicit manufacture of narcotic drugs and psychotropic substances)

Rustins QD ASAP Range

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2015/830

15.1.2. National regulations

France

Occupational diseases	
Code	Description
RG 84	Conditions caused by liquid organic solvents for professional use: saturated or unsaturated aliphatic or cyclic liquid hydrocarbons and mixtures thereof; liquid halogenated hydrocarbons; nitrated derivatives of aliphatic hydrocarbons; alcohols; glycols, glycol ethers; ketones; aldehydes; aliphatic and cyclic ethers, including tetrahydrofuran; esters; dimethylformamide and dimethylacetamine; acetonitrile and propionitrile; pyridine; dimethylsulfone and dimethylsulfoxide

Germany

Employment restrictions	: Observe restrictions according Act on the Protection of Working Mothers (MuSchG). Observe restrictions according Act on the Protection of Young People in Employment (JArbSchG).
Water hazard class (WGK)	: WGK 2, Significantly hazardous to water (Classification according to AwSV, Annex 1).
Hazardous Incident Ordinance (12. BImSchV)	: Is not subject of the Hazardous Incident Ordinance (12. BImSchV)

Netherlands

ABM category	: A(4) - low hazard for aquatic organisms, may have longterm hazardous effects in aquatic environment
SZW-lijst van kankerwekkende stoffen	: None of the components are listed
SZW-lijst van mutagene stoffen	: None of the components are listed
SZW-lijst van reprotoxische stoffen – Borstvoeding	: None of the components are listed
SZW-lijst van reprotoxische stoffen – Vruchtbaarheid	: None of the components are listed
SZW-lijst van reprotoxische stoffen – Ontwikkeling	: None of the components are listed

Denmark

Classification remarks	: Emergency management guidelines for the storage of flammable liquids must be followed
Danish National Regulations	: Young people below the age of 18 years are not allowed to use the product Pregnant/breastfeeding women working with the product must not be in direct contact with the product The requirements from the Danish Working Environment Authorities regarding work with carcinogens must be followed during use and disposal

Switzerland

Storage class (LK)	: LK 10/12 - Liquids
--------------------	----------------------

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Abbreviations and acronyms:	
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level

Rustins QD ASAP Range

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2015/830

Abbreviations and acronyms:	
EC-No.	European Community number
EC50	Median effective concentration
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified
vPvB	Very Persistent and Very Bioaccumulative
ED	Endocrine disrupting properties

Full text of H- and EUH-statements:	
Acute Tox. 2 (Dermal)	Acute toxicity (dermal), Category 2
Acute Tox. 2 (Inhalation)	Acute toxicity (inhal.), Category 2
Acute Tox. 3 (Oral)	Acute toxicity (oral), Category 3
Aquatic Acute 1	Hazardous to the aquatic environment – Acute Hazard, Category 1
Aquatic Chronic 1	Hazardous to the aquatic environment – Chronic Hazard, Category 1
Carc. 2	Carcinogenicity, Category 2
EUH208	Contains Mixture of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1). May produce an allergic reaction.
EUH211	Warning! Hazardous respirable droplets may be formed when sprayed. Do not breathe spray or mist.
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2

Rustins QD ASAP Range

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2015/830

Full text of H- and EUH-statements:	
H301	Toxic if swallowed.
H310	Fatal in contact with skin.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H330	Fatal if inhaled.
H351	Suspected of causing cancer.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
Skin Corr. 1C	Skin corrosion/irritation, Category 1, Sub-Category 1C
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1A	Skin sensitisation, category 1A

The classification complies with : ATP 12

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.