



Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 10

Unibond Aero 360° Lavender Garden

SDS No. : 676728
V001.3

Revision: 14.07.2022
printing date: 01.08.2023

Replaces version from: 24.03.2022

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Unibond Aero 360° Lavender Garden

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Air dryer

1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Adhesives

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

ua-productsafety.uk@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 0 8701 906777 - For further general health & safety, technical and practical advice on this product, please call +44 (0) 1606 593933 or write to: Technical Services; Henkel Limited; Road 5; Winsford Industrial Estate; Winsford; Cheshire; CW7 3QY- Email: technical.services@henkel.co.uk

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Serious eye irritation

H319 Causes serious eye irritation.

Category 2

2.2. Label elements

Label elements (CLP):

Hazard pictogram:



Signal word:

Warning

Hazard statement: H319 Causes serious eye irritation.

Precautionary statement: P101 If medical advice is needed, have product container or label at hand.
 P102 Keep out of reach of children.
 P280 Wear eye protection/face protection.
 P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
 P337+P313 If eye irritation persists: Get medical advice/attention.

2.3. Other hazards

None if used properly.
 Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

Following substances are present in a concentration >= 0,1% and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

This mixture does not contain any substances in concentration ≥ the concentration limit that are assessed to be a PBT, vPvB or ED.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No. EC Number REACH-Reg No.	Concentration	Classification	Specific Conc. Limits, M-factors and ATEs	Add. Information
calcium chloride 10043-52-4 233-140-8 01-2119494219-28	60- 80 %	Eye Irrit. 2, H319		

**For full text of the H - statements and other abbreviations see section 16 "Other information".
 Substances without classification may have community workplace exposure limits available.**

SECTION 4: First aid measures

4.1. Description of first aid measures

General information:
 In case of adverse health effects seek medical advice.

Inhalation:
 Move to fresh air, consult doctor if complaint persists.

Skin contact:
 Rinse with running water and soap. Skin care. Remove contaminated clothes immediately.

Eye contact:
 Immediately flush eyes with soft jet of water or eye rinse solution for at least 5 minutes. If pains remain (intensive smarting, sensitivity to light, visual disturbance) continue flushing and contact/seek doctor or hospital.

Ingestion:
 Rinse mouth and throat. Drink 1-2 glasses of water. Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

Causes serious eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**5.1. Extinguishing media****Suitable extinguishing media:**

carbon dioxide, foam, powder, water spray jet, fine water spray

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of fire, chlorine gas may be formed.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Wear protective equipment.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Wear protective equipment.

Avoid contact with skin and eyes.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Dispose of contaminated material as waste according to Section 13.

Remove mechanically.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Open and handle container with care.

Avoid skin and eye contact.

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, dry place.

Avoid strictly temperatures below 0 °C and above + 50 °C.

Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

7.3. Specific end use(s)

Air dryer

SECTION 8: Exposure controls/personal protection

8.1. Control parameters**Occupational Exposure Limits**

Valid for
Great Britain

None

Occupational Exposure Limits

Valid for
Ireland

None

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Calcium chloride 10043-52-4	Workers	inhalation	Acute/short term exposure - local effects		10 mg/m ³	
Calcium chloride 10043-52-4	Workers	inhalation	Long term exposure - local effects		5 mg/m ³	
Calcium chloride 10043-52-4	General population	inhalation	Long term exposure - local effects		2,5 mg/m ³	
Calcium chloride 10043-52-4	General population	inhalation	Acute/short term exposure - local effects		5 mg/m ³	

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:
Not needed.

Hand protection:

In the case of longer contact protective gloves made from nitrile rubber are recommended according to EN 374.

material thickness > 0.1 mm

Perforation time > 480 minutes

In the case of longer and repeated contact please note that in practice the penetration times may be considerably shorter than those determined according to EN 374. The protective gloves must always be checked for their suitability for use at the specific workplace (e.g. mechanical and thermal stress, product compatibility, antistatic effects, etc.). The gloves must be replaced immediately at the first signs of wear and tear. The information provided by the manufacturers and given in the relevant trade association regulations for industrial safety must always be observed. We recommend that a hand care plan is drawn up in cooperation with a glove manufacturer and the trade association in accordance with the local operating conditions.

Eye protection:

Goggles which can be tightly sealed.

Protective eye equipment should conform to EN166.

Skin protection:

Suitable protective clothing

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	solid
Delivery form	tablet
Colour	blue, white
Odor	lavender
Melting point	772 °C (1421.6 °F)
Solidification temperature	Not applicable, Product is a solid.
Initial boiling point	> 1.600 °C (> 2912 °F)
Flammability	The product is not flammable.
Explosive limits	Not applicable, Product is a solid.
Flash point	Not applicable, Product is a solid.
Auto-ignition temperature	Not applicable, Product is a solid.
Decomposition temperature	176 °C (348.8 °F);
pH	8 - 10
(20 °C (68 °F); Conc.: 40 % product; Solvent: Water)	
Viscosity (kinematic)	Not applicable, Product is a solid.
Solubility (qualitative)	Soluble
(23 °C (73.4 °F); Solvent: Water)	
Partition coefficient: n-octanol/water	Not applicable
	Mixture
Vapour pressure	< 0,1 hPa
(20 °C (68 °F))	
Density	2,15 g/cm ³
(20 °C (68 °F))	
Bulk density	Not applicable, The product is a tablet.
Relative vapour density:	Not applicable, Product is a solid.
Particle characteristics	Not applicable
	Product is not powder.

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity

10.1. Reactivity

None if used for intended purpose.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

None if used properly.

10.6. Hazardous decomposition products

None known.

SECTION 11: Toxicological information

1.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
calcium chloride 10043-52-4	LD50	2.301 mg/kg	rat	OECD Guideline 401 (Acute Oral Toxicity)

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
calcium chloride 10043-52-4	LD50	> 5.000 mg/kg	rabbit	not specified

Acute inhalative toxicity:

No data available.

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
calcium chloride 10043-52-4	not irritating		rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
calcium chloride 10043-52-4	moderately irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

No data available.

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
calcium chloride 10043-52-4	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
calcium chloride 10043-52-4	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)

Carcinogenicity

No data available.

Reproductive toxicity:

No data available.

STOT-single exposure:

No data available.

STOT-repeated exposure::

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
calcium chloride 10043-52-4	NOAEL > 1.000 mg/kg	oral: feed	12 w daily	rat	not specified

Aspiration hazard:

No data available.

11.2 Information on other hazards

not applicable

SECTION 12: Ecological information**General ecological information:**

Do not empty into drains, soil or bodies of water.

12.1. Toxicity**Toxicity (Fish):**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
calcium chloride 10043-52-4	LC50	> 10.000 mg/l	96 h	Gambusia affinis	OECD Guideline 203 (Fish, Acute Toxicity Test)

Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
calcium chloride 10043-52-4	EC50	3.005 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

Chronic toxicity to aquatic invertebrates

No data available.

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
calcium chloride 10043-52-4	EC50	3.130 mg/l	96 h	Nitscheria linearis	OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
calcium chloride 10043-52-4	EC0	> 2.500 mg/l			OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)

12.2. Persistence and degradability

No data available.

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
calcium chloride 10043-52-4	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Endocrine disrupting properties

not applicable

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of waste and residues in accordance with local authority requirements.

Disposal of uncleaned packages:

Use packages for recycling only when totally empty.

Waste code

060314

SECTION 14: Transport information

- 14.1. UN number**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packing group**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Maritime transport in bulk according to IMO instruments**
not applicable

SECTION 15: Regulatory information

No information available:

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Ozone Depleting Substance (ODS) (Regulation (EC) No 1005/2009):	Not applicable
Prior Informed Consent (PIC) (Regulation (EU) No 649/2012):	Not applicable
Persistent organic pollutants (Regulation (EU) 2019/1021):	Not applicable

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H319 Causes serious eye irritation.

ED:	Substance identified as having endocrine disrupting properties
EU OEL:	Substance with a Union workplace exposure limit
EU EXPLD 1:	Substance listed in Annex I, Reg (EC) No. 2019/1148
EU EXPLD 2:	Substance listed in Annex II, Reg (EC) No. 2019/1148
SVHC:	Substance of very high concern (REACH Candidate List)
PBT:	Substance fulfilling persistent, bioaccumulative and toxic criteria
PBT/vPvB:	Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very bioaccumulative criteria
vPvB:	Substance fulfilling very persistent and very bioaccumulative criteria

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.