Report Date : 06/02/2006 1 / 5

REVISION DATE: 25-11-2005 SDS No.: 10088



SAFETY DATA SHEET THOMPSON'S uPVC RESTORER

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND COMPANY/ UNDERTAKING

PRODUCT NAME THOMPSON'S uPVC RESTORER

PRODUCT NO. 33180/jb

INTERNAL ID (Commodity Code 340220 90 00)

APPLICATION Cleaning agent
SUPPLIER Ronseal Ltd
Thorncliffe Park

Chapeltown
Sheffield S35 2YP
enquiry@ronseal.co.uk

EMERGENCY TELEPHONE Tel +44 (0) 114 246 7171

Fax +44 (0) 114 245 5629

2 COMPOSITION/INFORMATION ON INGREDIENTS

Name	EC No.	CAS-No.	Content	Classification
COCONUT DIETHANOLAMIDE		68603-42-9	1-2.5%	Xi;R41.
DISTILLATES (PETROLEUM), HYDROTREATED HEAVY NAPHTHENIC	265-155-0	64742-52-5	2.5-10%	-
DISTILLATES (PETROLEUM), HYDROTREATED LIGHT; KEROSINE - UNSPECIFIED	265-149-8	64742-47-8	2.5-10%	Xn;R65
SOLVENT NAPHTHA (PETROLEUM), HEAVY AROMATIC; KEROSINE - UNSPECIFIED	265-198-5	64742-94-5	1-2.5%	Xn;R65. N;R51/53. R66,R67.
TRIETHANOLAMINE		102-71-6	1-2.5%	Xi;R36/37/38.

The Full Text for all R-Phrases are Displayed in Section 16

COMPOSITION COMMENTS

Refer to Section 16 for information as required by the EU Detergents Regulations (EC) No 648/2004.

3 HAZARDS IDENTIFICATION

Not regarded as a health or environmental hazard under current legislation.

4 FIRST-AID MEASURES

GENERAL INFORMATION

In all cases of doubt, or when symptoms persist, seek medical attention. Never give anything by mouth to an unconscious person.

INHALATION

Remove to fresh air, keep the patient warm and at rest. If breathing has stopped administer artificial respiration. Give nothing by mouth. If unconscious, place in the recovery position and seek medical advice.

INGESTION

If accidentally swallowed obtain immediate medical attention. Keep at rest. Do NOT induce vomiting.

SKIN CONTACT

Remove contaminated clothing. Wash skin thoroughly with soap and water, or use a proprietary skin cleanser. Do NOT use solvents or thinners. Seek medical advice if any irritation persists.

Report Date: 06/02/2006 2 / 5 10088

REVISION DATE: 25-11-2005 SDS No :

THOMPSON'S uPVC RESTORER

EYE CONTACT

Contact lenses should be removed. Irrigate copiously with clean, fresh water for at least 10 minutes, holding the eyelids apart, and seek medical advice.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

This product is not flammable. Fire can be extinguished using: alcohol resistant foam, carbon dioxide (CO2), powder, water spray/ mist. Do not use water jet.

SPECIAL FIRE FIGHTING PROCEDURES

As the product contains combustible organic components, fire will produce dense black smoke containing hazardous of combustion (see Section 10). Exposure to decomposition products may be hazardous to health. Appropriate selfcontained breathing apparatus may be required. Cool closed containers exposed to fire with water spray. Do not allow runoff from fire fighting to enter drains or watercourses.

6 ACCIDENTAL RELEASE MEASURES

SPILL CLEAN UP METHODS

Exclude sources of ignition and ventilate the area. Exclude non-essential personnel. Refer to protective measures listed in Section 7 and 8. Contain and collect spillage with non-combustible absorbent materials, e.g. sand, earth or vermiculite, and place in a suitable container for disposal in accordance with the waste regulations (see Section 13). Clean preferably with a detergent; avoid the use of solvents. If the product enters drains or sewers, immediately contact the local water company; in the case of contamination of streams, rivers or lakes, the relevant environment agency.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Keep away from heat, sparks and open flame. Smoking, eating and drinking should be prohibited in areas of storage and use. Avoid skin and eye contact. Provide good ventilation. Avoid inhalation of vapour. Avoid inhalation of dust. For Occupational Exposure Controls, refer to Section 8.

The Manual Handling Operations Regulations may apply to the handling of containers/packages of this product.

STORAGE PRECAUTIONS

Observe the label precautions. Store between 5°C and 25°C. Keep in a cool, dry, well ventilated place, away from sources of heat, ignition and direct sunlight. No smoking

The principles contained in the HSE Guidance Note: Storage of Packaged Dangerous Substances, should be observed when storing this product.

To avoid the risk of spillage, always store and transport in a secure and upright position.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	LT - ppm	LT - mg/m3	ST - ppm	ST - mg/m3
DISTILLATES (PETROLEUM), HYDROTREATED LIGHT; KEROSINE - UNSPECIFIED	SUP	165 ppm	1200 mg/m3	No std.	No std.
DISTILLATES (PETROLEUM), HYDROTREATED HEAVY NAPHTHENIC			5 mg/m3		10 mg/m3
TRIETHANOLAMINE		No std.	No std.	No std.	No std.
COCONUT DIETHANOLAMIDE		No std.	No std.	No std.	No std.
SOLVENT NAPHTHA (PETROLEUM), HEAVY AROMATIC ; KEROSINE - UNSPECIFIED		No std.	No std.	No std.	No std.

INGREDIENT COMMENTS

WEL = Workplace Exposure Limits SUP = Supplier's recommendation.

ENGINEERING MEASURES

Provide adequate ventilation. Where reasonably practicable, this should be achieved by the use of local exhaust ventilation and good general extraction. If these are not sufficient to maintain concentrations of particulates and/or solvent vapours below the relevant occupational exposure limits, suitable respiratory protective equipment should be worn.

RESPIRATORY EQUIPMENT

If exposure to hazardous substances identified above cannot be controlled by the provision of local exhaust ventilation and good general extraction, suitable respiratory protective equipment should be worn.

Report Date: 06/02/2006 3 / 5 10088

REVISION DATE: 25-11-2005 SDS No :

THOMPSON'S uPVC RESTORFR

HAND PROTECTION

When skin exposure may occur, advice should be sought from glove suppliers on appropriate types. Barrier creams may help to protect exposed areas of skin but are not substitutes for full physical protection. They should not be applied once exposure has occurred.

EYE PROTECTION

Eye protection designed to protect against liquid splashes should be worn.

OTHER PROTECTION

Cotton or cotton/synthetic overalls or coveralls are normally suitable. Grossly contaminated clothing should be removed and the skin washed with soap and water or a proprietary skin cleaner.

All personal protective equipment, including respiratory protective equipment, used to control exposure to hazardous substances must be selected to meet the requirements of the COSHH Regulations.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE Low viscosity liquid. COLOUR Beige. to Light brown **ODOUR** Characteristic solvent type. SOLUBILITY Slightly soluble in water.

FLASH POINT (°C) > 61 CC (Closed cup). VOLATILE ORGANIC COMPOUND (330 max g/litre

VOC)

10 STABILITY AND REACTIVITY

STABILITY

Stable if stored under recommended storage and handling conditions.

CONDITIONS TO AVOID

Keep away from oxidising agents and strongly alkaline and strongly acidic materials.

HAZARDOUS DECOMPOSITION PRODUCTS

In a fire, hazardous decomposition products such as smoke, carbon monoxide, carbon dioxide and alcohols may be produced

11 TOXICOLOGICAL INFORMATION

TOXICOLOGICAL INFORMATION

There is no data available on the product itself. The product has been assessed following the conventional method in CHIP and is classified for toxicological hazards accordingly. This takes into account, where known, delayed and immediate effects and also chronic effects from components from short-term and long-term exposure by oral, inhalation and dermal routes of exposure and eye contact. See Sections 3 and 15 for details of the resulting hazard classification.

Exposure to organic solvent vapours in excess of the stated occupational exposure limit may result in adverse health effects such as irritation of the mucous membrane and the respiratory system and adverse effects on the kidney, liver and central nervous systems. Symptoms and signs include headache, dizziness, fatigue, muscular weakness, drowsiness and in extreme cases loss of consciousness.

Solvents may cause some of the above effects by absorption through the skin.

Repeated or prolonged contact with the product may lead to removal of natural fats from the skin resulting in non-allergic contact dermatitis and absorption through the skin. Splashes in the eyes may cause irritation and reversible local damage.

INGESTION

This product contains an in-can biocide, may be harmful if swallowed.

12 ECOLOGICAL INFORMATION

ECOTOXICITY

The product has been assessed following the conventional method for CHIP and is not classified as dangerous for the environment, but contains substances so classified. See Section 2 for details.

DEGRADABILITY

There is no data available on the product itself.

ACUTE FISH TOXICITY

There is no data available on the product itself.

Report Date: 06/02/2006 SDS No : 10088

REVISION DATE: 25-11-2005

THOMPSON'S uPVC RESTORER

WATER HAZARD CLASSIFICATION

There is no data available on the product itself. The product should not be allowed to enter drains or watercourses, or be deposited where it can affect ground or surface waters.

13 DISPOSAL CONSIDERATIONS

DISPOSAL METHODS

Do not allow into drains or watercourses, or dispose of where ground or surface waters may be affected. Wastes, including emptied containers, are controlled wastes and should be disposed of in accordance with regulations made under the Control of Pollution Act and the Environmental Protection Act. Using information provided in this data sheet, advice should be obtained from the Waste Regulation Authority whether the Special Waste Regulations apply.

14 TRANSPORT INFORMATION

GENERAL This product is not classified as dangerous for carriage.

> Transport within user's premises: always transport in closed containers that are upright and secure. Ensure that person's transporting the product know what to do in an accident or

spillage.

UN NO. ROAD ADR CLASS N/C Not dangerous according to

ADR.

UN NO. SEA N/C

15 REGULATORY INFORMATION

ISK		

NC Not classified.

SAFETY PHRASES

S2 Keep out of the reach of children

S25 Avoid contact with eyes.

S26 In case of contact with eyes, rinse immediately with plenty of water and seek

medical advice.

Wear suitable gloves. S37

Use only in well-ventilated areas. S51

UK REGULATORY REFERENCES

The information contained in this safety data sheet does not constitute the user's own assessment of workplace risks as required by other health and safety legislation.

The provisions of the Health and Safety at Work etc. Act and the Control of Substances Hazardous to Health Regulations apply to the use of this product at work.

The Manual Handling Operations Regulations

The Chemicals (Hazard Information and Packaging for Supply) Regulations.

The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations.

European Agreement concerning the International Carriage of Dangerous Goods by Road [ADR]

EU DIRECTIVES

Dangerous Substance Directive 67/548/EEC. Dangerous Preparations Directive 1999/45/EEC. Safety Data Sheet Directive 91/155 EC Detergents Regulations No 648/2004

GUIDANCE NOTES

Workplace Exposure Limits EH40.

16 OTHER INFORMATION

GENERAL INFORMATION

The information contained in this safety data sheet is based on the present state of knowledge and current national legislation. It provides guidance on health, safety and environmental aspects of the product and should not be construed as any guarantee of technical performance or suitability for particular applications.

Report Date: 06/02/2006

5 / 5

REVISION DATE: 25-11-2005 10088 SDS No :

THOMPSON'S uPVC RESTORER

The product should not be used for purposes other than those shown in section 1 without first referring to the supplier and obtaining written handling instructions. As the specific conditions of use of the product are outside the supplier's control, the user is responsible for ensuring that the requirements of relevant legislation are complied with. Information shown on product label, as required by Annex VII A of the EC Detergents Regulations No. 648/2004/EU.

Contains less than 5% non-ionic surfactants

Contains 1, 3-bis(hydroxymethyl)-5, 5-dimethylimidazolidine-2, 4-dione [DMDM Hydantoin]

Contains Formaldehyde

For specific guidance contact Ronseal Technical Services. [Helpline +44 (0) 114 240 9469]; Email: enquiry@ronseal.co. uk

REVISION COMMENTS

Revised to meet the requirements of the Detergents Regulations (EC) No 648/2004.

REVISION DATE 25-11-2005 REV. NO./REPL. SDS 111188/1 **GENERATED** SDS NO. 10088/0

SAFETY DATA SHEET STATUS

Approved.

DATE 25-11-2005 **SIGNATURE** K. R. P. Winder

RISK PHRASES IN FULL

NC Not classified.

R36/37/38 Irritating to eyes, respiratory system and skin.

R41 Risk of serious damage to eyes.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65 Harmful: may cause lung damage if swallowed.

R66 Repeated exposure may cause skin dryness or cracking.

R67 Vapours may cause drowsiness and dizziness.