



SAFETY DATA SHEET
SCRATCH COVER

Page: 1

Compilation date: 17/04/2013

Revision date: 18/09/2018

Revision No: 4

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: SCRATCH COVER

Product code: SC

Synonyms: SCRATCH COVER - LIGHT, MEDIUM & DARK

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Company name: Rustins Ltd

Waterloo Road

Cricklewood

London

NW2 7TX

United Kingdom

Tel: +44 (0)208 450 4666

Fax: +44 (0)208 452 2008

Email: rustins@rustins.co.uk

1.4. Emergency telephone number

Emergency tel: .+44(0)2084504666 (Office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Flam. Liq. 3: H226

Most important adverse effects: Flammable liquid and vapour.

2.2. Label elements

Label elements:

Hazard statements: H226: Flammable liquid and vapour.

Hazard pictograms: GHS02: Flame



Signal words: Warning

Precautionary statements: P210: Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P240: Ground and bond container and receiving equipment.

[cont...]

SAFETY DATA SHEET

SCRATCH COVER

Page: 2

P241: Use explosion-proof equipment.

P280: Wear eye protection.

P303+P361+P353: IF ON SKIN (or hair): Take off immediately all contaminated clothing.

Rinse skin with water .

P370+P378: In case of fire: Use media other than water to extinguish.

2.3. Other hazards

Other hazards: In use, may form flammable / explosive vapour-air mixture.

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

LOW BOILING POINT HYDROGEN TREATED NAPHTHA - NAPHTHA (PETROLEUM), HYDROTREATED HEAVY

EINECS	CAS	PBT / WEL	CLP Classification	Percent
265-150-3	64742-48-9	-	Asp. Tox. 1: H304; Flam. Liq. 3: H226	70.000%

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water.

Inhalation: Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Alcohol resistant foam. Water spray. Carbon dioxide. Dry chemical powder.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Flammable. In combustion emits toxic fumes. Forms explosive air-vapour mixture.

[cont...]

SAFETY DATA SHEET

SCRATCH COVER

Page: 3

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Notify the police and fire brigade immediately. Eliminate all sources of ignition. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Do not use equipment in clean-up procedure which may produce sparks.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Smoking is forbidden. Use non-sparking tools. Ensure there is sufficient ventilation of the area. Avoid the formation or spread of mists in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. Keep away from sources of ignition. Prevent the build up of electrostatic charge in the immediate area. Ensure lighting and electrical equipment are not a source of ignition.

Suitable packaging: Glass. Coated steel.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

[cont...]

SAFETY DATA SHEET

SCRATCH COVER

Page: 4

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. Ensure lighting and electrical equipment are not a source of ignition.

Respiratory protection: Respiratory protection not required.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Light brown and Dark brown

Odour: Paraffinic.

Evaporation rate: No data available.

Oxidising: No data available.

Solubility in water: Not miscible

Also soluble in: Most organic solvents.

Viscosity: Non-viscous

Boiling point/range°C: 150-190

Melting point/range°C: No data available.

Flammability limits %: lower: No data available.

upper: No data available.

Flash point°C: 38

Part.coeff. n-octanol/water: No data available.

Autoflammability°C: No data available.

Vapour pressure: No data available.

Relative density: 0.814-0.819

pH: No data available.

VOC g/l: No data available.

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions. Stable at room temperature.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat. Hot surfaces. Sources of ignition. Flames.

[cont...]

SAFETY DATA SHEET

SCRATCH COVER

Page: 5

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: No symptoms.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

[cont...]

SAFETY DATA SHEET

SCRATCH COVER

Page: 6

Section 14: Transport information

14.1. UN number

UN number: UN1263

14.2. UN proper shipping name

14.3. Transport hazard class(es)

Transport class: 3

14.4. Packing group

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: Yes

14.6. Special precautions for user

Special precautions: No special precautions.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H226: Flammable liquid and vapour.

H304: May be fatal if swallowed and enters airways.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.