



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 7

SDS No. : 215595
V001.9

Solvite Paste The Wall Extra Strong Wallpaper Adhesive

Revision: 02.11.2017

printing date: 23.05.2020

Replaces version from: 18.08.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Solvite Paste The Wall Extra Strong Wallpaper Adhesive

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Wallcovering adhesive, powder

1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Adhesives

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

Fax-no.: +44 (1442) 278071

ua-productsafety.uk@henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 0 8701 906777 - For further general health & safety, technical and practical advice on this product, please call +44 (0) 1606 593933 or write to: Technical Services; Henkel Limited; Road 5; Winsford Industrial Estate; Winsford; Cheshire; CW7 3QY- Email: technical.services@henkel.co.uk

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.2. Label elements

Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General chemical description:

Adhesive

Base substances of preparation:

Starch

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Contains no dangerous substances exceeding the limits of the EU-Regulation

SECTION 4: First aid measures

4.1. Description of first aid measures

General information:

In case of adverse health effects seek medical advice.

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing.

Eye contact:

Rinse immediately with plenty of running water, seek medical advice if necessary.

Do not rub eyes; mechanical action may cause corneal damage.

Ingestion:

Rinse mouth and throat. Drink 1-2 glasses of water. Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

carbon dioxide, foam, powder, water spray jet, fine water spray

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO₂) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Wear protective equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Remove mechanically.

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Avoid skin and eye contact.

Ensure that workrooms are adequately ventilated.

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Store in sealed original container protected against moisture.

Store in a cool, dry place.

Temperatures between 0 °C and + 30 °C

Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

7.3. Specific end use(s)

Wallcovering adhesive, powder

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**

Valid for

Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Starch 9005-25-8 [STARCH, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Starch 9005-25-8 [STARCH, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL

Occupational Exposure Limits

Valid for

Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Starch 9005-25-8 [STARCH, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Starch 9005-25-8 [STARCH, TOTAL INHALABLE DUST]		10	Time Weighted Average (TWA):		IR_OEL

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:

In case of dust formation, we recommend wearing of appropriate respiratory protection equipment with particle filter P (EN 14387).

This recommendation should be matched to local conditions.

Hand protection:

Not needed.

Eye protection:

Not needed.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	powder flakes Off white
Odor	soap-like
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Relative vapour density:	No data available / Not applicable
Density (20 °C (68 °F))	0,3 g/cm ³
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (23 °C (73.4 °F); Solvent: Water)	Insoluble
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity**10.1. Reactivity**

None if used for intended purpose.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

None if used properly.

10.6. Hazardous decomposition products

None known.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General toxicological information:

To the best of our knowledge no harmful effects are to be expected if the product is handled and used properly.

Skin irritation:

Primary skin irritation: slightly irritating, does not require labeling

Eye irritation:

Primary eye irritation: slightly irritating, does not require labeling

SECTION 12: Ecological information

General ecological information:

Do not empty into drains, soil or bodies of water.

12.1. Toxicity

No data available.

12.2. Persistence and degradability

No data available.

12.3. Bioaccumulative potential / 12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of waste and residues in accordance with local authority requirements.

Disposal of uncleaned packages:

Use packages for recycling only when totally empty.

Waste code

080410

SECTION 14: Transport information

14.1. UN number

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content 0,00 %
(VOCV 814.018 VOC regulation
CH)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.

