



HG coffee machine descaler

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.
Issue date: 22/02/2023 Version: 1.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : HG coffee machine descaler
UFI : 70JU-MW44-000Q-DD1T
Product code : 323 ART
Type of product : Cleaner for machines and kitchen appliances
Product group : Trade product

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Intended for general public
Main use category : Consumer use
Use of the substance/mixture : Descaling products

1.2.2. Uses advised against

Restrictions on use : All other uses not recommended above

1.3. Details of the supplier of the safety data sheet

Manufacturer

HG International B.V.
P.J. Oudweg 41
NL- 1314 CJ Almere
The Netherlands
T +31 (0)36 54 94 700
safety@hg.eu - www.hg.eu

Importer

HG UKI LTD
Weston Business Centre
Parsonage Road
UK- CM22 6PU Takeley – Essex
United Kingdom
T +44 (0) 1206 822 744
www.hg.eu

1.4. Emergency telephone number

Emergency number : +31 (0)36 54 94 777
Only for medical personnel
Mon-Fri 09:00 AM - 05:00 PM (CEST)

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH	0344 892 0111	Only for healthcare professionals
United Kingdom	Guy's & St Thomas' Poisons Unit Medical Toxicology Unit, Guy's & St Thomas' Hospital Trust	Avonley Road SE14 5ER	+44 20 7188 7188	

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Serious eye damage/eye irritation, Category 2 H319
Full text of H- and EUH-statements: see section 16

Adverse physicochemical, human health and environmental effects

Causes serious eye irritation.

HG coffee machine descaler

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS07

Signal word (CLP) : Warning
Hazard statements (CLP) : H319 - Causes serious eye irritation.
Precautionary statements (CLP) : P101 - If medical advice is needed, have product container or label at hand.
P102 - Keep out of reach of children.
P264 - Wash hands thoroughly after handling.
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
Child-resistant fastening : Not applicable
Tactile warning : Not applicable

2.3. Other hazards

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII
This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII
Contains no PBT/vPvB substances $\geq 0,1\%$ assessed in accordance with REACH Annex XIII

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	Conc. (% w/w)	Classification according to Regulation (EC) No. 1272/2008 [CLP]
Citric acid	CAS-No.: 77-92-9 EC-No.: 201-069-1 EC Index-No.: 607-750-00-3 REACH-no: 01-2119457026-42	$\geq 15 - < 25$	Eye Irrit. 2, H319 STOT SE 3, H335

Full text of H- and EUH-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact : Wash skin with plenty of water.
First-aid measures after eye contact : Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. If eye irritation persists: Get medical advice/attention.
First-aid measures after ingestion : Call a poison center or a doctor if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after eye contact : Eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

HG coffee machine descaler

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.
Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

Fire hazard : Intense heat may cause container to burst.
Hazardous decomposition products in case of fire : Carbon dioxide. Carbon monoxide.

5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area. Evacuate unnecessary personnel. Do not touch or walk on the spilled product. Avoid contact with skin and eyes. Do not breathe vapours.

6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

For containment : Stop leak if safe to do so. Move containers from spill area. Dilute spills with water and mop up.
Methods for cleaning up : Take up liquid spill into absorbent material.
Other information : Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For disposal of contaminated materials refer to section 13 : "Disposal considerations".

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Avoid contact with skin and eyes. Wear personal protective equipment.
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Keep cool. Protect from sunlight. Store in a well-ventilated place. Keep container tightly closed.
Storage temperature : 10 – < 30 °C
Heat and ignition sources : Keep away from heat and direct sunlight.
Special rules on packaging : Keep only in original container. Opened containers must be carefully closed and kept upright to avoid leakage.

HG coffee machine descaler

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

No additional information available

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

Citric acid (77-92-9)	
PNEC (Water)	
PNEC aqua (freshwater)	0.44 mg/l
PNEC aqua (marine water)	0.044 mg/l
PNEC (Sediment)	
PNEC sediment (freshwater)	34.6 mg/kg dwt
PNEC sediment (marine water)	3.46 mg/kg dwt
PNEC (Soil)	
PNEC soil	33.1 mg/kg dwt
PNEC (STP)	
PNEC sewage treatment plant	1000 mg/l

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Emergency eye wash fountains and safety showers should be available in the immediate vicinity of any potential exposure. Ensure good ventilation of the work station.

8.2.2. Personal protection equipment

Personal protective equipment:

Safety glasses. Gloves. Protective clothing. Wear foot protection.

Personal protective equipment symbol(s):



8.2.2.1. Eye and face protection

Eye protection:

Safety glasses with side shields

HG coffee machine descaler

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

Eye protection			
Type	Field of application	Characteristics	Standard
Safety glasses with side shields	Normal use conditions		EN 166

8.2.2.2. Skin protection

Skin and body protection:

Not required for normal conditions of use. If there is a risk of liquid being splashed : Long sleeved protective clothing. Chemical resistant safety shoes

Skin and body protection	
Type	Standard
Long sleeved protective clothing	
Chemical resistant safety shoes	EN ISO 20345
Use chemically protective clothing	EN 13034

Hand protection:

Protective gloves

Hand protection					
Type	Material	Permeation	Thickness (mm)	Penetration	Standard
Disposable gloves	Butyl rubber	6 (> 480 minutes)	0.5		EN ISO 374
Disposable gloves	Nitrile rubber (NBR)	6 (> 480 minutes)	0.35		EN ISO 374

8.2.2.3. Respiratory protection

Respiratory protection:

No respiratory protection needed under normal use conditions. Where exposure through inhalation may occur from use, respiratory protection equipment is recommended

Respiratory protection			
Device	Filter type	Condition	Standard
Half-mask	FFA2P3	Mist formation, Vapour protection	EN 405
Dust mask	FFFP2	Dust protection	EN 149

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Environmental exposure controls:

Avoid release to the environment.

Other information:

Handle in accordance with good industrial hygiene and safety procedures. Do not eat, drink or smoke when using this product.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Appearance	: clear.
Colour	: Colourless.
Odour	: No data available
Odour threshold	: No data available
pH	: 1.2 – 2.2

HG coffee machine descaler

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

pH solution	: 100 %
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: No data available
Boiling point	: No data available
Flash point	: No data available
Auto-ignition temperature	: No data available
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20°C	: No data available
Relative density	: No data available
Density	: 1.066 – 1.076 g/ml
Solubility	: Soluble in the following materials: cold water and hot water.
Partition coefficient n-octanol/water (Log Pow)	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: No data available

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

Alkalines. Attacks metals.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity (oral)	: Not classified (Conclusive but not sufficient for classification)
Acute toxicity (dermal)	: Not classified (Conclusive but not sufficient for classification)
Acute toxicity (inhalation)	: Not classified (Conclusive but not sufficient for classification)

Citric acid (77-92-9)

LD50 oral	5400 mg/kg bodyweight Animal: mouse, Guideline: OECD Guideline 401 (Acute Oral Toxicity), Remarks on results: other:, 95% CL: 4500 - 6400
LD50 dermal rat	> 2000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 402 (Acute Dermal Toxicity)

HG coffee machine descaler

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

Skin corrosion/irritation	: Not classified (Conclusive but not sufficient for classification) pH: 1.2 – 2.2
Serious eye damage/irritation	: Causes serious eye irritation. pH: 1.2 – 2.2
Respiratory or skin sensitisation	: Not classified (Conclusive but not sufficient for classification)
Germ cell mutagenicity	: Not classified (Conclusive but not sufficient for classification)
Carcinogenicity	: Not classified (Conclusive but not sufficient for classification)
Reproductive toxicity	: Not classified (Conclusive but not sufficient for classification)
STOT-single exposure	: Not classified (Conclusive but not sufficient for classification)

Citric acid (77-92-9)

STOT-single exposure	May cause respiratory irritation.
STOT-repeated exposure	: Not classified (Conclusive but not sufficient for classification)

Citric acid (77-92-9)

LOAEL (oral, rat, 90 days)	8000 mg/kg bodyweight Animal: rat
NOAEL (oral, rat, 90 days)	4000 mg/kg bodyweight Animal: rat
Aspiration hazard	: Not classified (Conclusive but not sufficient for classification)

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	: The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
Hazardous to the aquatic environment, short-term (acute)	: Not classified (Conclusive but not sufficient for classification)
Hazardous to the aquatic environment, long-term (chronic)	: Not classified (Conclusive but not sufficient for classification)

Citric acid (77-92-9)

LC50 - Fish [1]	440 mg/l
EC50 - Crustacea [1]	1535 mg/l
EC50 - Other aquatic organisms [1]	85 mg/l waterflea
EC50 96h - Algae [1]	1690000 mg/l Source: Ecological Structure Activity Relationships

12.2. Persistence and degradability

HG coffee machine descaler

Persistence and degradability	Readily biodegradable.
-------------------------------	------------------------

Citric acid (77-92-9)

Biochemical oxygen demand (BOD)	0.526 g O ₂ /g substance
Chemical oxygen demand (COD)	0.728 g O ₂ /g substance
Biodegradation	97 %

12.3. Bioaccumulative potential

HG coffee machine descaler

Bioaccumulative potential	No bioaccumulation potential.
---------------------------	-------------------------------

Citric acid (77-92-9)

Partition coefficient n-octanol/water (Log Pow)	-1.67
---	-------

HG coffee machine descaler

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

12.4. Mobility in soil

HG coffee machine descaler

Ecology - soil

Expected to be highly mobile in soil.

12.5. Results of PBT and vPvB assessment

HG coffee machine descaler

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII

This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

12.6. Other adverse effects

Other adverse effects : Before neutralisation, the product may represent a danger to aquatic organisms.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Regional legislation (waste) : Dispose of in accordance with relevant local regulations.
Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.
Product/Packaging disposal recommendations : Empty containers retain product residue and can be hazardous. Do not dispose of the packaging without first carrying out the necessary cleaning. Empty containers should be taken for recycling, recovery or waste in accordance with local regulation.
Ecology - waste materials : Recycling is preferred to disposal or incineration.
European List of Waste (LoW) code : 20 01 29* - detergents containing dangerous substances
20 01 39 - plastics
HP Code : HP4 - "Irritant – skin irritation and eye damage:" waste which on application can cause skin irritation or damage to the eye.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.2. UN proper shipping name				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.3. Transport hazard class(es)				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.4. Packing group				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.5. Environmental hazards				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
No supplementary information available				

14.6. Special precautions for user

Overland transport

Not applicable

HG coffee machine descaler

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

Transport by sea

Not applicable

Air transport

Not applicable

Inland waterway transport

Not applicable

Rail transport

Not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

REACH Annex XVII (Restriction List)

Contains no substance(s) listed on REACH Annex XVII (Restriction Conditions)

REACH Annex XIV (Authorisation List)

Contains no substance(s) listed on REACH Annex XIV (Authorisation List)

REACH Candidate List (SVHC)

Contains no substance(s) listed on the REACH Candidate List

PIC Regulation (Prior Informed Consent)

Contains no substance(s) listed on the PIC list (Regulation EU 649/2012 concerning the export and import of hazardous chemicals)

POP Regulation (Persistent Organic Pollutants)

Contains no substance(s) listed on the POP list (Regulation EU 2019/1021 on persistent organic pollutants)

Ozone Regulation (1005/2009)

Contains no substance(s) listed on the Ozone Depletion list (Regulation EU 1005/2009 on substances that deplete the ozone layer)

Explosives Precursors Regulation (2019/1148)

Contains no substance(s) listed on the Explosives Precursors list (Regulation EU 2019/1148 on the marketing and use of explosives precursors)

Drug Precursors Regulation (273/2004)

Contains no substance(s) listed on the Drug Precursors list (Regulation EC 273/2004 on the manufacture and the placing on market of certain substances used in the illicit manufacture of narcotic drugs and psychotropic substances)

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Abbreviations and acronyms:

ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate

HG coffee machine descaler

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

Abbreviations and acronyms:	
BCF	Bioconcentration factor
BLV	Biological limit value
BOD	Biochemical oxygen demand (BOD)
COD	Chemical oxygen demand (COD)
DMEL	Derived Minimal Effect level
DNEL	Derived-No Effect Level
EC-No.	European Community number
EC50	Median effective concentration
EN	European Standard
IARC	International Agency for Research on Cancer
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LC50	Median lethal concentration
LD50	Median lethal dose
LOAEL	Lowest Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
NOAEL	No-Observed Adverse Effect Level
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
ThOD	Theoretical oxygen demand (ThOD)
TLM	Median Tolerance Limit
VOC	Volatile Organic Compounds
CAS-No.	Chemical Abstract Service number
N.O.S.	Not Otherwise Specified
vPvB	Very Persistent and Very Bioaccumulative
ED	Endocrine disrupting properties

Training advice

: Normal use of this product shall imply use in accordance with the instructions on the packaging. Ensure personnel is aware of the potential hazards of the load and knows what to do in the event of an accident or an emergency.

HG coffee machine descaler

Safety Data Sheet

According to REACH Regulation (EC) No 1907/2006, as retained and amended in UK law, and based on EU 2015/830.

Other information

: **DISCLAIMER OF LIABILITY** The information in this SDS was obtained from sources which we believe are reliable. However, the information is provided without any warranty, express or implied, regarding its correctness. The conditions or methods of handling, storage, use or disposal of the product are beyond our control and may be beyond our knowledge. For this and other reasons, we do not assume responsibility and expressly disclaim liability for loss, damage or expense arising out of or in any way connected with the handling, storage, use or disposal of the product. This SDS was prepared and is to be used only for this product. If the product is used as a component in another product, this SDS information may not be applicable.

Full text of H- and EUH-statements:

Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
H319	Causes serious eye irritation.
H335	May cause respiratory irritation.
STOT SE 3	Specific target organ toxicity – Single exposure, Category 3, Respiratory tract irritation

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.