

# SAFETY DATA SHEET

Ultimate Black Silicone



## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1 Product identifier

**Product name** : Ultimate Black Silicone  
**UFI** : RKHV-62YC-T00P-A9SP  
**Product code** : 32329  
**Product description** : Sealants and adhesives  
**Product type** : Paste.  
**Other means of identification** : 32329, 32929 (Ultimate Black Silicone Gasket Maker and Sealer) - Oxime Silicones

### 1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified uses
Sealants

#### Uses advised against

Not applicable.

### 1.3 Details of the supplier of the safety data sheet

JRP Distribution Ltd.  
Unit 10A, Business Park, City Fields Way  
Tangmere, PO20 2FT, United Kingdom  
info@jbweld.com  
Tel: +44 1903 750355  
Website: www.jbweld.com.eu  
**e-mail address of person responsible for this SDS** : info@jbweld.com

### 1.4 Emergency telephone number

#### National advisory body/Poison Centre

**Telephone number** : International: +1 (352) 323-3500 (INFOTRAC® INTL)  
National Emergency Poison Centre (24hrs) : 111

## SECTION 2: Hazards identification

### 2.1 Classification of the substance or mixture

**Product definition** : Mixture

#### Classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Not classified.

The product is not classified as hazardous according to Regulation (EC) 1272/2008 as amended.

**Ingredients of unknown toxicity** : 48 percent of the mixture consists of component(s) of unknown acute oral toxicity  
48 percent of the mixture consists of component(s) of unknown acute dermal toxicity  
48 percent of the mixture consists of component(s) of unknown acute inhalation toxicity

**Ingredients of unknown ecotoxicity** : Contains 48% of components with unknown hazards to the aquatic environment

See Section 11 for more detailed information on health effects and symptoms.

## SECTION 2: Hazards identification

### 2.2 Label elements

**Signal word** : No signal word.  
**Hazard statements** : No known significant effects or critical hazards.

#### Precautionary statements

**Prevention** : Not applicable.  
**Response** : Not applicable.  
**Storage** : Not applicable.  
**Disposal** : Not applicable.

**Supplemental label elements** : Not applicable.

**Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles** : Not applicable.

#### Special packaging requirements

**Containers to be fitted with child-resistant fastenings** : Not applicable.  
**Tactile warning of danger** : Not applicable.

### 2.3 Other hazards

**Product meets the criteria for PBT or vPvB according to Regulation (EC) No. 1907/2006, Annex XIII** : This mixture does not contain any substances that are assessed to be a PBT or a vPvB.  
**Other hazards which do not result in classification** : None known.

## SECTION 3: Composition/information on ingredients

**3.2 Mixtures** : Mixture

There are no ingredients present which, within the current knowledge of the supplier and in the concentrations applicable, are classified as hazardous to health or the environment, are PBTs, vPvBs or Substances of equivalent concern, or have been assigned a workplace exposure limit and hence require reporting in this section.

## SECTION 4: First aid measures

### 4.1 Description of first aid measures

**Eye contact** : Immediately flush eyes with plenty of water, occasionally lifting the upper and lower eyelids. Check for and remove any contact lenses. Get medical attention if irritation occurs.  
**Inhalation** : Remove victim to fresh air and keep at rest in a position comfortable for breathing. Get medical attention if symptoms occur. In case of inhalation of decomposition products in a fire, symptoms may be delayed. The exposed person may need to be kept under medical surveillance for 48 hours.  
**Skin contact** : Flush contaminated skin with plenty of water. Remove contaminated clothing and shoes. Get medical attention if symptoms occur.  
**Ingestion** : Wash out mouth with water. If material has been swallowed and the exposed person is conscious, give small quantities of water to drink. Do not induce vomiting unless directed to do so by medical personnel. Get medical attention if symptoms occur.  
**Protection of first-aiders** : No action shall be taken involving any personal risk or without suitable training.

### 4.2 Most important symptoms and effects, both acute and delayed

## SECTION 4: First aid measures

### Over-exposure signs/symptoms

Eye contact	: No specific data.
Inhalation	: No specific data.
Skin contact	: No specific data.
Ingestion	: No specific data.

### 4.3 Indication of any immediate medical attention and special treatment needed

Notes to physician	: In case of inhalation of decomposition products in a fire, symptoms may be delayed. The exposed person may need to be kept under medical surveillance for 48 hours.
Specific treatments	: No specific treatment.

## SECTION 5: Firefighting measures

### 5.1 Extinguishing media

Suitable extinguishing media	: Use an extinguishing agent suitable for the surrounding fire.
Unsuitable extinguishing media	: None known.

### 5.2 Special hazards arising from the substance or mixture

Hazards from the substance or mixture	: No specific fire or explosion hazard.
Hazardous combustion products	: Decomposition products may include the following materials: carbon dioxide carbon monoxide nitrogen oxides metal oxide/oxides

### 5.3 Advice for firefighters

Special protective actions for fire-fighters	: Promptly isolate the scene by removing all persons from the vicinity of the incident if there is a fire. No action shall be taken involving any personal risk or without suitable training.
Special protective equipment for fire-fighters	: Fire-fighters should wear appropriate protective equipment and self-contained breathing apparatus (SCBA) with a full face-piece operated in positive pressure mode. Clothing for fire-fighters (including helmets, protective boots and gloves) conforming to European standard EN 469 will provide a basic level of protection for chemical incidents.

## SECTION 6: Accidental release measures

### 6.1 Personal precautions, protective equipment and emergency procedures

For non-emergency personnel	: No action shall be taken involving any personal risk or without suitable training. Evacuate surrounding areas. Keep unnecessary and unprotected personnel from entering. Do not touch or walk through spilt material. Put on appropriate personal protective equipment.
For emergency responders	: If specialised clothing is required to deal with the spillage, take note of any information in Section 8 on suitable and unsuitable materials. See also the information in "For non-emergency personnel".

6.2 Environmental precautions	: Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers. Inform the relevant authorities if the product has caused environmental pollution (sewers, waterways, soil or air).
-------------------------------	---

### 6.3 Methods and material for containment and cleaning up

## SECTION 6: Accidental release measures

**Small spill** : Move containers from spill area. Vacuum or sweep up material and place in a designated, labelled waste container. Dispose of via a licensed waste disposal contractor.

**Large spill** : Move containers from spill area. Prevent entry into sewers, water courses, basements or confined areas. Vacuum or sweep up material and place in a designated, labelled waste container. Dispose of via a licensed waste disposal contractor.

**6.4 Reference to other sections** : See Section 1 for emergency contact information.  
See Section 8 for information on appropriate personal protective equipment.  
See Section 13 for additional waste treatment information.

## SECTION 7: Handling and storage

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

### 7.1 Precautions for safe handling

**Protective measures** : Put on appropriate personal protective equipment (see Section 8).

**Advice on general occupational hygiene** : Eating, drinking and smoking should be prohibited in areas where this material is handled, stored and processed. Workers should wash hands and face before eating, drinking and smoking. Remove contaminated clothing and protective equipment before entering eating areas. See also Section 8 for additional information on hygiene measures.

### 7.2 Conditions for safe storage, including any incompatibilities

Store in accordance with local regulations. Store in original container protected from direct sunlight in a dry, cool and well-ventilated area, away from incompatible materials (see Section 10) and food and drink. Keep container tightly closed and sealed until ready for use. Containers that have been opened must be carefully resealed and kept upright to prevent leakage. Do not store in unlabelled containers. Use appropriate containment to avoid environmental contamination. See Section 10 for incompatible materials before handling or use.

### 7.3 Specific end use(s)

**Recommendations** : Sealants

**Industrial sector specific solutions** : Professional uses

## SECTION 8: Exposure controls/personal protection

The information in this section contains generic advice and guidance. Information is provided based on typical anticipated uses of the product. Additional measures might be required for bulk handling or other uses that could significantly increase worker exposure or environmental releases.

### 8.1 Control parameters

#### Occupational exposure limits

No exposure limit value known.

#### Biological exposure indices

No exposure indices known.

**Recommended monitoring procedures** : Reference should be made to monitoring standards, such as the following: European Standard EN 689 (Workplace atmospheres - Guidance for the assessment of exposure by inhalation to chemical agents for comparison with limit values and measurement strategy) European Standard EN 14042 (Workplace atmospheres - Guide for the application and use of procedures for the assessment of exposure to chemical and biological agents) European Standard EN 482 (Workplace atmospheres - General requirements for the performance of procedures for the measurement of chemical agents) Reference to national guidance documents for methods for the determination of hazardous substances will also be required.

#### DNELs/DMELs

## SECTION 8: Exposure controls/personal protection

No DNELs/DMELs available.

### PNECs

No PNECs available

### 8.2 Exposure controls

**Appropriate engineering controls** : Good general ventilation should be sufficient to control worker exposure to airborne contaminants.

### Individual protection measures

**Hygiene measures** : Wash hands, forearms and face thoroughly after handling chemical products, before eating, smoking and using the lavatory and at the end of the working period. Appropriate techniques should be used to remove potentially contaminated clothing. Wash contaminated clothing before reusing. Ensure that eyewash stations and safety showers are close to the workstation location.

**Eye/face protection** : Safety eyewear complying with an approved standard should be used when a risk assessment indicates this is necessary to avoid exposure to liquid splashes, mists, gases or dusts. If contact is possible, the following protection should be worn, unless the assessment indicates a higher degree of protection: safety glasses with side-shields.

### Skin protection

**Hand protection** : Chemical-resistant, impervious gloves complying with an approved standard should be worn at all times when handling chemical products if a risk assessment indicates this is necessary.

**Body protection** : Personal protective equipment for the body should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

**Other skin protection** : Appropriate footwear and any additional skin protection measures should be selected based on the task being performed and the risks involved and should be approved by a specialist before handling this product.

**Respiratory protection** : Based on the hazard and potential for exposure, select a respirator that meets the appropriate standard or certification. Respirators must be used according to a respiratory protection program to ensure proper fitting, training, and other important aspects of use.

**Environmental exposure controls** : Emissions from ventilation or work process equipment should be checked to ensure they comply with the requirements of environmental protection legislation. In some cases, fume scrubbers, filters or engineering modifications to the process equipment will be necessary to reduce emissions to acceptable levels.

## SECTION 9: Physical and chemical properties

The conditions of measurement of all properties are at standard temperature and pressure unless otherwise indicated.

### 9.1 Information on basic physical and chemical properties

#### Appearance

<b>Physical state</b>	: Solid.
<b>Colour</b>	: Black.
<b>Odour</b>	: Not available.
<b>Odour threshold</b>	: Not available.
<b>Melting point/freezing point</b>	: Not available.
<b>Initial boiling point and boiling range</b>	: >200°C (>392°F)
<b>Flammability</b>	: Not available.
<b>Lower and upper explosion limit</b>	: Not applicable.
<b>Flash point</b>	: Closed cup: >93.3°C (>199.9°F)

## SECTION 9: Physical and chemical properties

**Auto-ignition temperature** : Not applicable.

**Decomposition temperature** : Not available.

**pH** : Not available.

**Viscosity** : Not applicable.

**Solubility in water** : Not available.

**Partition coefficient: n-octanol/ water** : Not applicable.

**Vapour pressure** : Not available.

**Relative density** : 1.3 to 1.4

**Vapour density** : Not applicable.

### Particle characteristics

**Median particle size** : Not available.

### 9.2.1 Information with regard to physical hazard classes

**Explosive properties** : Not available.

**Oxidising properties** : Not available.

### 9.2.2 Other safety characteristics

**Miscible with water** : No.

## SECTION 10: Stability and reactivity

**10.1 Reactivity** : No specific test data related to reactivity available for this product or its ingredients.

**10.2 Chemical stability** : The product is stable.

**10.3 Possibility of hazardous reactions** : Under normal conditions of storage and use, hazardous reactions will not occur.

**10.4 Conditions to avoid** : No specific data.

**10.5 Incompatible materials** : No specific data.

**10.6 Hazardous decomposition products** : Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## SECTION 11: Toxicological information

### 11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

#### Acute toxicity

**Conclusion/Summary** : Not available.

#### Acute toxicity estimates

N/A

#### Irritation/Corrosion

**Conclusion/Summary** : Not available.

#### Sensitisation

**Conclusion/Summary** : Not available.

#### Mutagenicity

**Conclusion/Summary** : Not available.

#### Carcinogenicity

**Conclusion/Summary** : Not available.

## SECTION 11: Toxicological information

### Reproductive toxicity

**Conclusion/Summary** : Not available.

### Teratogenicity

**Conclusion/Summary** : Not available.

### Specific target organ toxicity (single exposure)

Not available.

### Specific target organ toxicity (repeated exposure)

Not available.

### Aspiration hazard

Not available.

**Information on likely routes of exposure** : Not available.

### Potential acute health effects

**Eye contact** : No known significant effects or critical hazards.

**Inhalation** : No known significant effects or critical hazards.

**Skin contact** : No known significant effects or critical hazards.

**Ingestion** : No known significant effects or critical hazards.

### Symptoms related to the physical, chemical and toxicological characteristics

**Eye contact** : No specific data.

**Inhalation** : No specific data.

**Skin contact** : No specific data.

**Ingestion** : No specific data.

### Delayed and immediate effects as well as chronic effects from short and long-term exposure

#### Short term exposure

**Potential immediate effects** : Not available.

**Potential delayed effects** : Not available.

#### Long term exposure

**Potential immediate effects** : Not available.

**Potential delayed effects** : Not available.

### Potential chronic health effects

Not available.

**Conclusion/Summary** : Not available.

**General** : No known significant effects or critical hazards.

**Carcinogenicity** : No known significant effects or critical hazards.

**Mutagenicity** : No known significant effects or critical hazards.

**Reproductive toxicity** : No known significant effects or critical hazards.

## 11.2 Information on other hazards

### 11.2.1 Endocrine disrupting properties

Not available.

### 11.2.2 Other information

Not available.



Ultimate Black Silicone

SECTION 12: Ecological information

12.1 Toxicity

Conclusion/Summary : Not available.

12.2 Persistence and degradability

Conclusion/Summary : Not available.

12.3 Bioaccumulative potential

Not available.

12.4 Mobility in soil

Soil/water partition coefficient (K<sub>oc</sub>) : Not available.

Mobility : Not available.

12.5 Results of PBT and vPvB assessment

This mixture does not contain any substances that are assessed to be a PBT or a vPvB.

12.6 Endocrine disrupting properties

Not available.

12.7 Other adverse effects

No known significant effects or critical hazards.

SECTION 13: Disposal considerations

The information in this section contains generic advice and guidance. The list of Identified Uses in Section 1 should be consulted for any available use-specific information provided in the Exposure Scenario(s).

13.1 Waste treatment methods

Product

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements. Dispose of surplus and non-recyclable products via a licensed waste disposal contractor. Waste should not be disposed of untreated to the sewer unless fully compliant with the requirements of all authorities with jurisdiction.

Hazardous waste : Within the present knowledge of the supplier, this product is not regarded as hazardous waste, as defined by EU Directive 2008/98/EC.

Packaging

Methods of disposal : The generation of waste should be avoided or minimised wherever possible. Waste packaging should be recycled. Incineration or landfill should only be considered when recycling is not feasible.

Special precautions : This material and its container must be disposed of in a safe way. Empty containers or liners may retain some product residues. Avoid dispersal of spilt material and runoff and contact with soil, waterways, drains and sewers.



Ultimate Black Silicone

## SECTION 14: Transport information

	ADR/RID	ADN	IMDG	IATA
14.1 UN number or ID number	Not regulated.	Not regulated.	Not regulated.	Not regulated.
14.2 UN proper shipping name	-	-	-	-
14.3 Transport hazard class(es)	-	-	-	-
14.4 Packing group	-	-	-	-
14.5 Environmental hazards	No.	No.	No.	No.

**14.6 Special precautions for user** : **Transport within user's premises:** always transport in closed containers that are upright and secure. Ensure that persons transporting the product know what to do in the event of an accident or spillage.

**14.7 Maritime transport in bulk according to IMO instruments** : Not available.

## SECTION 15: Regulatory information

### 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

EU Regulation (EC) No. 1907/2006 (REACH)

Annex XIV - List of substances subject to authorisation

Annex XIV

None of the components are listed.

Substances of very high concern

None of the components are listed.

Annex XVII - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles

No listed substance

Other EU regulations

**Industrial emissions (integrated pollution prevention and control) - Air** : Not listed

**Industrial emissions (integrated pollution prevention and control) - Water** : Not listed

**Explosive precursors** : Not applicable.

Ozone depleting substances (1005/2009/EU)

Not listed.

Prior Informed Consent (PIC) (649/2012/EU)

Not listed.

Persistent Organic Pollutants

Ultimate Black Silicone

SECTION 15: Regulatory information

Not listed.

Seveso Directive

This product is not controlled under the Seveso Directive.

International regulations

Chemical Weapon Convention List Schedules I, II & III Chemicals

Not listed.

Montreal Protocol

Not listed.

Stockholm Convention on Persistent Organic Pollutants

Not listed.

Rotterdam Convention on Prior Informed Consent (PIC)

Not listed.

UNECE Aarhus Protocol on POPs and Heavy Metals

Not listed.

Inventory list

- Australia : All components are listed or exempted.
- Canada : All components are listed or exempted.
- China : All components are listed or exempted.
- Eurasian Economic Union : Russian Federation inventory: Not determined.
- Japan : Japan inventory (CSCL): All components are listed or exempted.  
Japan inventory (ISHL): All components are listed or exempted.
- New Zealand : All components are listed or exempted.
- Philippines : All components are listed or exempted.
- Republic of Korea : Not determined.
- Taiwan : All components are listed or exempted.
- Thailand : All components are listed or exempted.
- Turkey : All components are listed or exempted.
- United States : All components are listed or exempted.
- Viet Nam : All components are listed or exempted.

15.2 Chemical safety assessment : This product contains substances for which Chemical Safety Assessments are still required.

SECTION 16: Other information

Indicates information that has changed from previously issued version.

- Abbreviations and acronyms
- ATE = Acute Toxicity Estimate
  - CLP = Classification, Labelling and Packaging Regulation [Regulation (EC) No. 1272/2008]
  - DMEL = Derived Minimal Effect Level
  - DNEL = Derived No Effect Level
  - EUH statement = CLP-specific Hazard statement
  - N/A = Not available
  - PBT = Persistent, Bioaccumulative and Toxic
  - PNEC = Predicted No Effect Concentration
  - RRN = REACH Registration Number
  - SGG = Segregation Group
  - vPvB = Very Persistent and Very Bioaccumulative

Procedure used to derive the classification according to Regulation (EC) No. 1272/2008 [CLP/GHS]

Not classified.

Ultimate Black Silicone

SECTION 16: Other information

Full text of abbreviated H statements

Not applicable.

Full text of classifications [CLP/GHS]

Not applicable.

Date of printing : 4/3/2024  
Date of issue/ Date of revision : 4/3/2024  
Date of previous issue : No previous validation  
Version : 1

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above-named supplier, nor any of its subsidiaries, assumes any liability whatsoever for the accuracy or completeness of the information contained herein.  
Final determination of suitability of any material is the sole responsibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.