

SAFETY DATA SHEET

(REACH regulation (EC) n° 1907/2006 - n° 2015/830)

SECTION 1 : IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name : LIBERON - NATURAL FINISH STONE FLOOR SEALER - 5 L

Product code : 126764

1.2. Relevant identified uses of the substance or mixture and uses advised against

Floor care product

1.3. Details of the supplier of the safety data sheet

Registered company name : LIBERON Ltd

Address : .Mountfield Industrial Estate KENT TN28 8XU NEW ROMNEY GB

Telephone : + (44) 1797 367 555. Fax: + (44) 1797 367 575. Telex: .

fds.produits@v33.com

www.liberon.co.uk

1.4. Emergency telephone number : .

Association/Organisation : .

Other emergency numbers

UK - National Poisons Information Service

SECTION 2 : HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

In compliance with EC regulation No. 1272/2008 and its amendments.

May produce an allergic reaction (EUH208).

This mixture does not present a physical hazard. Refer to the recommendations regarding the other products present on the site.

This mixture does not present a health hazard with the exception of possible occupational exposure thresholds (see paragraphs 3 and 8).

This mixture does not present an environmental hazard. No known or foreseeable environmental damage under standard conditions of use.

2.2. Label elements

In compliance with EC regulation No. 1272/2008 and its amendments.

Additional labeling :

EUH208 Contains 1,2-BENZISOTHIAZOL-3(2H)-ONE. May produce an allergic reaction.

Precautionary statements - General :

P102 Keep out of reach of children.

Precautionary statements - Prevention :

P271 Use only outdoors or in a well-ventilated area.

Precautionary statements - Disposal :

P501 Dispose of contents/container to a waste collection center (contact the local authority)

2.3. Other hazards

The mixture does not contain substances classified as 'Substances of Very High Concern' (SVHC) $\geq 0.1\%$ published by the European CHemicals Agency (ECHA) under article 57 of REACH: <http://echa.europa.eu/fr/candidate-list-table>

The mixture satisfies neither the PBT nor the vPvB criteria for mixtures in accordance with annexe XIII of the REACH regulations EC 1907/2006.

SECTION 3 : COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

Composition :

Identification	(EC) 1272/2008	Note	%
INDEX: 613_088_00_6	GHS06, GHS05, GHS09		0 \leq x % < 0.05
CAS: 2634-33-5	Dgr		
EC: 220-120-9	Acute Tox. 4, H302		
	Skin Irrit. 2, H315		
1,2-BENZISOTHIAZOL-3(2H)-ONE	Skin Sens. 1, H317		
	Eye Dam. 1, H318		
	Acute Tox. 2, H330		
	Aquatic Acute 1, H400		
	M Acute = 1		

SECTION 4 : FIRST AID MEASURES

As a general rule, in case of doubt or if symptoms persist, always call a doctor.
NEVER induce swallowing by an unconscious person.

4.1. Description of first aid measures

In the event of exposure by inhalation :

In the event of an allergic reaction, seek medical attention.

In the event of splashes or contact with skin :

In the event of an allergic reaction, seek medical attention.

In the event of swallowing :

Seek medical attention, showing the label.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

No data available.

SECTION 5 : FIREFIGHTING MEASURES

Non-flammable.

5.1. Extinguishing media

Suitable methods of extinction

In the event of a fire, use :

- sprayed water or water mist
- foam
- multipurpose ABC powder
- BC powder
- carbon dioxide (CO₂)

Unsuitable methods of extinction

In the event of a fire, do not use :

- water jet

5.2. Special hazards arising from the substance or mixture

A fire will often produce a thick black smoke. Exposure to decomposition products may be hazardous to health.

Do not breathe in smoke.

In the event of a fire, the following may be formed :

- carbon monoxide (CO)
- carbon dioxide (CO₂)

5.3. Advice for firefighters

No data available.

SECTION 6 : ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Consult the safety measures listed under headings 7 and 8.

For first aid worker

First aid workers will be equipped with suitable personal protective equipment (See section 8).

6.2. Environmental precautions

Contain and control the leaks or spills with non-combustible absorbent materials such as sand, earth, vermiculite, diatomaceous earth in drums for waste disposal.

Prevent any material from entering drains or waterways.

6.3. Methods and material for containment and cleaning up

Clean preferably with a detergent, do not use solvents.

6.4. Reference to other sections

No data available.

SECTION 7 : HANDLING AND STORAGE

Requirements relating to storage premises apply to all facilities where the mixture is handled.

7.1. Precautions for safe handling

Always wash hands after handling.

Fire prevention :

Prevent access by unauthorised personnel.

Recommended equipment and procedures :

For personal protection, see section 8.

Observe precautions stated on label and also industrial safety regulations.

Prohibited equipment and procedures :

No smoking, eating or drinking in areas where the mixture is used.

7.2. Conditions for safe storage, including any incompatibilities

No data available.

Storage

Keep out of reach of children.

Do not allow to freeze

Packaging

Always keep in packaging made of an identical material to the original.

7.3. Specific end use(s)

No data available.

SECTION 8 : EXPOSURE CONTROLS/PERSONAL PROTECTION**8.1. Control parameters**

No data available.

8.2. Exposure controls**Appropriate engineering controls**

Use personal protective equipment that is clean and has been properly maintained.

Store personal protective equipment in a clean place, away from the work area.

Never eat, drink or smoke during use. Remove and wash contaminated clothing before re-using. Ensure that there is adequate ventilation, especially in confined areas.

- Eye / face protection

Avoid contact with eyes.

Use eye protectors designed to protect against liquid splashes

Before handling, wear safety goggles in accordance with standard EN166.

- Hand protection

Wear suitable protective gloves in the event of prolonged or repeated skin contact.

Type of gloves recommended :

- Natural latex
- Nitrile rubber (butadiene-acrylonitrile copolymer rubber (NBR))
- PVC (polyvinyl chloride)
- Butyl Rubber (Isobutylene-isoprene copolymer)

- Body protection

Work clothing worn by personnel shall be laundered regularly.

After contact with the product, all parts of the body that have been soiled must be washed.

SECTION 9 : PHYSICAL AND CHEMICAL PROPERTIES**9.1. Information on basic physical and chemical properties****General information :**

Physical state :	Fluid liquid.
------------------	---------------

Important health, safety and environmental information

pH :	Not stated.
	Slightly basic.
Boiling point/boiling range :	Not relevant.
Flash point interval :	Not relevant.
Vapour pressure (50°C) :	Not relevant.
Density :	= 1
Water solubility :	Dilutable.
Melting point/melting range :	Not relevant.
Self-ignition temperature :	Not relevant.
Decomposition point/decomposition range :	Not relevant.

9.2. Other information

No data available.

SECTION 10 : STABILITY AND REACTIVITY

10.1. Reactivity

No data available.

10.2. Chemical stability

This mixture is stable under the recommended handling and storage conditions in section 7.

10.3. Possibility of hazardous reactions

No data available.

10.4. Conditions to avoid

Avoid :

- frost

10.5. Incompatible materials

10.6. Hazardous decomposition products

The thermal decomposition may release/form :

- carbon monoxide (CO)

- carbon dioxide (CO₂)

SECTION 11 : TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

No data available.

11.1.1. Substances

No toxicological data available for the substances.

11.1.2. Mixture

Respiratory or skin sensitisation :

Contains at least one sensitising substance. May cause an allergic reaction.

SECTION 12 : ECOLOGICAL INFORMATION

12.1. Toxicity

12.1.1. Substances

1,2-BENZISOTHIAZOL-3(2H)-ONE (CAS: 2634-33-5)

Fish toxicity :

Duration of exposure : 96 h

Crustacean toxicity :

Duration of exposure : 48 h

NOEC = 1.21 mg/l

Species : Daphnia magna

Duration of exposure : 21 jours

Algae toxicity :

Duration of exposure : 72 h

12.1.2. Mixtures

No aquatic toxicity data available for the mixture.

12.2. Persistence and degradability

No data available.

12.2.1. Substances

1,2-BENZISOTHIAZOL-3(2H)-ONE (CAS: 2634-33-5)

Biodegradability :

Rapidly degradable.

12.3. Bioaccumulative potential

No data available.

12.3.1. Substances

1,2-BENZISOTHIAZOL-3(2H)-ONE (CAS: 2634-33-5)

Octanol/water partition coefficient :

log K_{ow} = 0.7

OCDE Ligne directrice 117 (Coefficient de partage (n-octanol/eau), méthode

HPLC)

Bioaccumulation :

BCF = 6.95

OCDE Ligne directrice 305 (Bioconcentration: Essai dynamique chez le poisson)

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Other adverse effects

No data available.

SECTION 13 : DISPOSAL CONSIDERATIONS

Proper waste management of the mixture and/or its container must be determined in accordance with Directive 2008/98/EC.

13.1. Waste treatment methods

Do not pour into drains or waterways.

Waste :

Waste management is carried out without endangering human health, without harming the environment and, in particular without risk to water, air, soil, plants or animals.

Recycle or dispose of waste in compliance with current legislation, preferably via a certified collector or company.

Do not contaminate the ground or water with waste, do not dispose of waste into the environment.

Soiled packaging :

Empty container completely. Keep label(s) on container.

Give to a certified disposal contractor.

SECTION 14 : TRANSPORT INFORMATION

Exempt from transport classification and labelling.

Transport product in compliance with provisions of the ADR for road, RID for rail, IMDG for sea and ICAO/IATA for air transport (ADR 2013 - IMDG 2012 - ICAO/IATA 2014).

SECTION 15 : REGULATORY INFORMATION**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****- Classification and labelling information included in section 2:**

The following regulations have been used:

- EU Regulation No. 1272/2008 amended by EU Regulation No. 758/2013.

- Container information:

No data available.

- Particular provisions :

No data available.

15.2. Chemical safety assessment

No data available.

SECTION 16 : OTHER INFORMATION

Since the user's working conditions are not known by us, the information supplied on this safety data sheet is based on our current level of knowledge and on national and community regulations.

The mixture must not be used for other uses than those specified in section 1 without having first obtained written handling instructions.

It is at all times the responsibility of the user to take all necessary measures to comply with legal requirements and local regulations.

The information in this safety data sheet must be regarded as a description of the safety requirements relating to the mixture and not as a guarantee of the properties thereof.

Wording of the phrases mentioned in section 3 :

H302	Harmful if swallowed.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H330	Fatal if inhaled.
H400	Very toxic to aquatic life.

Abbreviations :

ADR : European agreement concerning the international carriage of dangerous goods by Road.

IMDG : International Maritime Dangerous Goods.

IATA : International Air Transport Association.

ICAO : International Civil Aviation Organisation

RID : Regulations concerning the International carriage of Dangerous goods by rail.

WGK : Wassergefährdungsklasse (Water Hazard Class).