



SAFETY DATA SHEET

(REACH regulation (EC) n° 1907/2006 - n° 2015/830)

SECTION 1 : IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name : TOUTES LES COULEURS
Product code : TOUTES LES COULEURS

1.2. Relevant identified uses of the substance or mixture and uses advised against

Used for internal combustion fastener driving tools.

1.3. Details of the supplier of the safety data sheet

Registered company name : SPIT PASLODE.
Address : 150, route de Lyon.26500.BOURG LES VALENCE.France.
Telephone : 0 810 102 102. Fax : 0 810 432 432.
Email : msds-reach@spit.com
<http://www.spit.fr>

1.4. Emergency telephone number : 112.

Association/Organisation : European emergency number.

Other emergency numbers

http://echa.europa.eu/help/nationalhelp_contact_en.asp

SECTION 2 : HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

In compliance with EC regulation No. 1272/2008 and its amendments.

Aerosol, Category 1 (Aerosol 1, H222 - H229).

This mixture does not present a health hazard with the exception of possible occupational exposure thresholds (see paragraphs 3 and 8).

This mixture does not present an environmental hazard. No known or foreseeable environmental damage under standard conditions of use.

2.2. Label elements

Mixture for aerosol application.

In compliance with EC regulation No. 1272/2008 and its amendments.

Hazard pictograms :



GHS02

Signal Word :

DANGER

Hazard statements :

H222 Extremely flammable aerosol.
H229 Pressurised container: May burst if heated.

Precautionary statements - General :

P102 Keep out of reach of children.

Precautionary statements - Prevention :

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.

P211 Do not spray on an open flame or other ignition source.

P251 Do not pierce or burn, even after use.

Precautionary statements - Storage :

P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.

2.3. Other hazards

The mixture does not contain substances classified as 'Substances of Very High Concern' (SVHC) >= 0.1% published by the European Chemicals Agency (ECHA) under article 57 of REACH: <http://echa.europa.eu/fr/candidate-list-table>

The mixture fulfils neither the PBT nor the vPvB criteria for mixtures in accordance with annexe XIII of the REACH regulations EC 1907/2006.

SECTION 3 : COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

Composition :

Identification	(EC) 1272/2008	Note	%
INDEX: 601-011-00-9 CAS: 115-07-1 EC: 204-062-1 REACH: 01-2119447103-50	GHS02, GHS04 Dgr Flam. Gas 1, H220	[1]	30 <= x % < 70
PROPENE			
INDEX: 601-012-00-4 CAS: 106-98-9 EC: 203-449-2 REACH: 01-2119456615-34	GHS02, GHS04 Dgr Flam. Gas 1, H220	C [1]	25 <= x % < 50
BUT-1-ENE			

Information on ingredients :

[1] Substance for which maximum workplace exposure limits are available.

SECTION 4 : FIRST AID MEASURES

As a general rule, in case of doubt or if symptoms persist, always call a doctor.

NEVER induce swallowing by an unconscious person.

4.1. Description of first aid measures

In the event of exposure by inhalation :

If inhaled, move the patient into the fresh air and keep warm and at rest.

If breathing is irregular or has stopped, proceed with artificial respiration and seek medical attention.

In the event of splashes or contact with eyes :

Wash thoroughly with fresh, clean water for 15 minutes holding the eyelids open.

In the event of swallowing :

In the event of swallowing, if the quantity is small (no more than one mouthful), rinse the mouth with water and consult a doctor.

Keep the person exposed at rest. Do not force vomiting.

Seek medical attention, showing the label.

If swallowed accidentally, call a doctor to ascertain whether observation and hospital care will be necessary. Show the label.

4.2. Most important symptoms and effects, both acute and delayed

No data available.

4.3. Indication of any immediate medical attention and special treatment needed

No data available.

SECTION 5 : FIREFIGHTING MEASURES

Flammable.

Chemical powders, carbon dioxide and other extinguishing gas are suitable for small fires.

5.1. Extinguishing media

Keep packages near the fire cool, to prevent pressurised containers from bursting.

Suitable methods of extinction

In the event of a fire, use :

- sprayed water or water mist
- water with AFFF (Aqueous Film Forming Foam) additive
- halon
- foam
- multipurpose ABC powder
- BC powder
- carbon dioxide (CO₂)

Prevent the effluent of fire-fighting measures from entering drains or waterways.

Unsuitable methods of extinction

In the event of a fire, do not use :

- water jet

5.2. Special hazards arising from the substance or mixture

A fire will often produce a thick black smoke. Exposure to decomposition products may be hazardous to health.

Do not breathe in smoke.

In the event of a fire, the following may be formed :

- carbon monoxide (CO)
- carbon dioxide (CO₂)

5.3. Advice for firefighters

Due to the toxicity of the gas emitted on thermal decomposition of the products, fire-fighting personnel are to be equipped with autonomous insulating breathing apparatus.

SECTION 6 : ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Consult the safety measures listed under headings 7 and 8.

For non first aid worker

Because of the organic solvents contained in the mixture, eliminate sources of ignition and ventilate the area.

For first aid worker

First aid workers will be equipped with suitable personal protective equipment (See section 8).

6.2. Environmental precautions

Contain and control the leaks or spills with non-combustible absorbent materials such as sand, earth, vermiculite, diatomaceous earth in drums for waste disposal.

Prevent any material from entering drains or waterways.

6.3. Methods and material for containment and cleaning up

Clean preferably with a detergent, do not use solvents.

6.4. Reference to other sections

No data available.

SECTION 7 : HANDLING AND STORAGE

Requirements relating to storage premises apply to all facilities where the mixture is handled.

7.1. Precautions for safe handling

Always wash hands after handling.

Ensure that there is adequate ventilation, especially in confined areas.

Fire prevention :

Handle in well-ventilated areas.

Vapours are heavier than air. They can spread along the ground and form mixtures that are explosive with air.

Prevent the formation of flammable or explosive concentrations in air and avoid vapor concentrations higher than the occupational exposure limits.

Do not spray on a naked flame or any incandescent material.

Do not pierce or burn, even after use.

Use the mixture in premises free of naked flames or other sources of ignition and ensure that electrical equipment is suitably protected.

Keep packages tightly closed and away from sources of heat, sparks and naked flames.

Do not use tools which may produce sparks. Do not smoke.

Prevent access by unauthorised personnel.

Recommended equipment and procedures :

For personal protection, see section 8.

Observe precautions stated on label and also industrial safety regulations.

Do not breathe in aerosols.

Packages which have been opened must be reclosed carefully and stored in an upright position.

Prohibited equipment and procedures :

No smoking, eating or drinking in areas where the mixture is used.

7.2. Conditions for safe storage, including any incompatibilities

No data available.

Storage

Keep out of reach of children.

Keep the container tightly closed in a dry, well-ventilated place.

Keep away from all sources of ignition - do not smoke.

Keep well away from all sources of ignition, heat and direct sunlight.

The floor must be impermeable and form a collecting basin so that, in the event of an accidental spillage, the liquid cannot spread beyond this area.

Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C.

Packaging

Always keep in packaging made of an identical material to the original.

7.3. Specific end use(s)

No data available.

SECTION 8 : EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Occupational exposure limits :

- ACGIH TLV (American Conference of Governmental Industrial Hygienists, Threshold Limit Values, 2010) :

CAS	TWA :	STEL :	Ceiling :	Definition :	Criteria :
115-07-1	500 ppm			A4	
106-98-9	250 ppm				

- Switzerland (SUVA 2015) :

CAS	VME	VLE	Valeur plafond	Notations
115-07-1	10000 ppm 17500 mg/m3			

- Belgium (Order of 19/05/2009, 2010) :

CAS	TWA :	STEL :	Ceiling :	Definition :	Criteria :
115-07-1	500 ppm 875 mg/m3				
106-98-9	250 ppm 583 mg/m3				

8.2. Exposure controls

Personal protection measures, such as personal protective equipment

Pictogram(s) indicating the obligation of wearing personal protective equipment (PPE) :



Use personal protective equipment that is clean and has been properly maintained.

Store personal protective equipment in a clean place, away from the work area.

Never eat, drink or smoke during use. Remove and wash contaminated clothing before re-using. Ensure that there is adequate ventilation, especially in confined areas.

- Eye / face protection

Avoid contact with eyes.

Use eye protectors designed to protect against liquid splashes

Before handling, wear safety goggles in accordance with standard EN166.

- Hand protection

Wear suitable protective gloves in the event of prolonged or repeated skin contact.

Type of gloves recommended :

- Nitrile rubber (butadiene-acrylonitrile copolymer rubber (NBR))

- PVA (Polyvinyl alcohol)

- Body protection

Work clothing worn by personnel shall be laundered regularly.

After contact with the product, all parts of the body that have been soiled must be washed.

SECTION 9 : PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

General information :

Physical state :	Fluid liquid.
	Spray.

Important health, safety and environmental information

pH :	Not relevant.
Boiling point/boiling range :	0 °C.
Vapour pressure (50°C) :	Below 110 kPa (1.10 bar).
Density :	< 1
Water solubility :	Insoluble.

Self-ignition temperature :	455 °C.
Chemical combustion heat :	>= 30 kJ/g.

9.2. Other information

No data available.

SECTION 10 : STABILITY AND REACTIVITY**10.1. Reactivity**

No data available.

10.2. Chemical stability

This mixture is stable under the recommended handling and storage conditions in section 7.

10.3. Possibility of hazardous reactions

When exposed to high temperatures, the mixture can release hazardous decomposition products, such as carbon monoxide and dioxide, fumes and nitrogen oxide.

10.4. Conditions to avoid

Any apparatus likely to produce a flame or to have a metallic surface at high temperature (burners, electric arcs, furnaces etc.) must not be allowed on the premises.

Avoid :

- heating
- heat
- humidity

10.5. Incompatible materials

Keep away from :

- water

10.6. Hazardous decomposition products

The thermal decomposition may release/form :

- carbon monoxide (CO)
- carbon dioxide (CO₂)

SECTION 11 : TOXICOLOGICAL INFORMATION**11.1. Information on toxicological effects**

Splashes in the eyes may cause irritation and reversible damage

11.1.1. Substances

No toxicological data available for the substances.

11.1.2. Mixture

No toxicological data available for the mixture.

Monograph(s) from the IARC (International Agency for Research on Cancer) :

CAS 115-07-1 : IARC Group 3 : The agent is not classifiable as to its carcinogenicity to humans.

SECTION 12 : ECOLOGICAL INFORMATION**12.1. Toxicity****12.1.2. Mixtures**

No aquatic toxicity data available for the mixture.

12.2. Persistence and degradability

No data available.

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

No data available.

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Other adverse effects

No data available.

German regulations concerning the classification of hazards for water (WGK) :

Nicht wassergefährdend (VwVwS vom 27/07/2005, KBws) : Not hazardous for water.

SECTION 13 : DISPOSAL CONSIDERATIONS

Proper waste management of the mixture and/or its container must be determined in accordance with Directive 2008/98/EC.

13.1. Waste treatment methods

Do not pour into drains or waterways.

Waste :

Waste management is carried out without endangering human health, without harming the environment and, in particular without risk to water, air, soil, plants or animals.

Recycle or dispose of waste in compliance with current legislation, preferably via a certified collector or company.

Do not contaminate the ground or water with waste, do not dispose of waste into the environment.

Soiled packaging :

Empty container completely. Keep label(s) on container.

Give to a certified disposal contractor.

SECTION 14 : TRANSPORT INFORMATION

Transport product in compliance with provisions of the ADR for road, RID for rail, IMDG for sea and ICAO/IATA for air transport (ADR 2015 - IMDG 2014 - ICAO/IATA 2015).

14.1. UN number

1950

14.2. UN proper shipping name

UN1950=AEROSOLS, flammable

14.3. Transport hazard class(es)

- Classification :



2.1

14.4. Packing group

-

14.5. Environmental hazards

-

14.6. Special precautions for user

ADR/RID	Class	Code	Pack gr.	Label	Ident.	LQ	Provis.	EQ	Cat.	Tunnel
	2	5F	-	2.1	-	1 L	190 327 344 625	E0	2	D
IMDG	Class	2°Label	Pack gr.	LQ	EMS	Provis.	EQ			
	2.1	See SP63	-	SP277	F-D,S-U	63 190 277 327 344 959	E0			
IATA	Class	2°Label	Pack gr.	Passager	Passager	Cargo	Cargo	note	EQ	
	2.1	-	-	Forbidden	Forbidden	203	150 kg	A1 A145 A167 A802	E0	
	2.1	-	-	Forbidden	Forbidden	-	-	A1 A145 A167 A802	E0	

For limited quantities, see part 2.7 of the OACI/IATA and chapter 3.4 of the ADR and IMDG.

For excepted quantities, see part 2.6 of the OACI/IATA and chapter 3.5 of the ADR and IMDG.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

No data available.

SECTION 15 : REGULATORY INFORMATION**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****- Classification and labelling information included in section 2:**

The following regulations have been used:

- Directive 75/324/CEE modified by directive 2013/10/UE
- EU Regulation No. 1272/2008 amended by EU Regulation No. 487/2013.
- EU Regulation No. 1272/2008 amended by EU Regulation No. 758/2013.

- EU Regulation No. 1272/2008 amended by EU Regulation No. 944/2013.
- EU Regulation No. 1272/2008 amended by EU Regulation No. 605/2014.

- Container information:

No data available.

- Particular provisions :


No data available.

- German regulations concerning the classification of hazards for water (WGK) :

Nicht wassergefährdend (VwVwS vom 27/07/2005, KBws) : Not hazardous for water.

- Standardised American system for the identification of hazards presented by the product in view of emergency procedures (NFPA 704) :

NFPA 704, Labelling: Health=0 Inflammability=1 Instability/Reactivity=1 Specific Risk=none

**15.2. Chemical safety assessment**

No data available.

SECTION 16 : OTHER INFORMATION

Since the user's working conditions are not known by us, the information supplied on this safety data sheet is based on our current level of knowledge and on national and community regulations.

The mixture must not be used for other uses than those specified in section 1 without having first obtained written handling instructions.

It is at all times the responsibility of the user to take all necessary measures to comply with legal requirements and local regulations.

The information in this safety data sheet must be regarded as a description of the safety requirements relating to the mixture and not as a guarantee of the properties thereof.

Wording of the phrases mentioned in section 3 :

H220	Extremely flammable gas.
------	--------------------------

Abbreviations :

ADR : European agreement concerning the international carriage of dangerous goods by Road.

IMDG : International Maritime Dangerous Goods.

IATA : International Air Transport Association.

ICAO : International Civil Aviation Organisation

RID : Regulations concerning the International carriage of Dangerous goods by rail.

WGK : Wassergefährdungsklasse (Water Hazard Class).

GHS02 : Flame