



# Ready to use skimcoat filler

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878  
Revision date: 3/5/2021 Version: 1.0

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

Product form : Mixture  
Trade name : Ready to use skimcoat filler  
Product code : EN-BAT-TTEGFAP-P  
Type of product : Paste  
Product group : Trade product

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

##### 1.2.1. Relevant identified uses

Main use category : Professional use  
Use of the substance/mixture : Fillers, putties, plasters, modelling clay

##### 1.2.2. Uses advised against

No additional information available

#### 1.3. Details of the supplier of the safety data sheet

TOUPRET UK LTD  
Capital Business Centre - Unit 58  
22 Carlton Road  
CR2 0BS South Croydon - United Kingdom  
T +44 208 916 2134 - F +44 208 916 2136  
[fdstoupret@toupret.fr](mailto:fdstoupret@toupret.fr) - <https://www.toupret.co.uk/>

#### 1.4. Emergency telephone number

Country	Organisation/Company	Address	Emergency number	Comment
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	
United Kingdom	National Poisons Information Service (Cardiff Centre) Gwenwyn Ward, Llandough Hospital	Penarth CF64 2XX Cardiff	0344 892 0111	
United Kingdom	National Poisons Information Service Edinburgh Royal Infirmary of Edinburgh	Little France Crescent EH16 4SA Edinburgh	0344 892 0111	
United Kingdom	Guy's & St Thomas' Poisons Unit Medical Toxicology Unit, Guy's & St Thomas' Hospital Trust	Avonley Road SE14 5ER London	+44 20 7188 7188	
United Kingdom	National Poisons Information Service (Newcastle Centre) Regional Drugs and Therapeutics Centre, Wolfson Unit	Claremont Place Newcastle-upon-Tyne NE1 4LP Newcastle	0344 892 0111	
United Kingdom	National Poisons Information Service (Belfast Centre) Royal Victoria Hospital	Grosvenor Road BT12 6BA Belfast	0344 892 0111	

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

# Ready to use skimcoat filler

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

### Adverse physicochemical, human health and environmental effects

To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.

## 2.2. Label elements

### Labelling according to Regulation (EC) No. 1272/2008 [CLP]

EUH-statements : EUH208 - Contains 1,2-benzisothiazol-3(2H)-one, reaction mass of 5-chloro-2-méthyl-2H-isothiazol-3-one and de 2-méthyl-2H-isothiazol-3-one (3:1), 1,2-Benzisothiazol-3(2H)-one, 2-méthyl-. May produce an allergic reaction.  
EUH210 - Safety data sheet available on request.

## 2.3. Other hazards

Other hazards which do not result in classification : Product dust may cause mechanical irritation to the skin and mucous membranes.

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII

This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

### Component

1,2-Benzisothiazol-3(2H)-one, 2-méthyl- (2527-66-4)	This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII
---	---

## SECTION 3: Composition/information on ingredients

### 3.1. Substances

Not applicable

### 3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
1,2-Benzisothiazol-3(2H)-one, 2-méthyl-	(CAS-No.) 2527-66-4	< 0.1	Acute Tox. 3 (Oral), H301 (ATE=100 mg/kg de poids corporel) Acute Tox. 4 (Dermal), H312 (ATE=1100 mg/kg de poids corporel) Acute Tox. 4 (Inhalation), H332 Skin Corr. 1C, H314 Eye Dam. 1, H318 Skin Sens. 1A, H317 Aquatic Acute 1, H400 Aquatic Chronic 2, H411

### Specific concentration limits:

Name	Product identifier	Specific concentration limits
1,2-Benzisothiazol-3(2H)-one, 2-méthyl-	(CAS-No.) 2527-66-4	( 0.0015 ≤C < 100) Skin Sens. 1A, H317

Full text of H-statements: see section 16

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

First-aid measures after inhalation : Remove person to fresh air and keep comfortable for breathing.  
First-aid measures after skin contact : Wash skin with plenty of water. If skin irritation or rash occurs: Get medical advice/attention.

# Ready to use skimcoat filler

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

First-aid measures after eye contact : Rinse eyes with water as a precaution.  
First-aid measures after ingestion : Call a poison center or a doctor if you feel unwell.

### 4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects : Product dust may cause mechanical irritation to the skin and mucous membranes.  
Symptoms/effects after skin contact : Repeated or prolonged contact may cause allergic reactions in very susceptible persons.

### 4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

Suitable extinguishing media : Water spray. Dry powder. Foam. Carbon dioxide.  
Unsuitable extinguishing media : Do not use a heavy water stream.

### 5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released. Carbon oxides (CO, CO<sub>2</sub>).

### 5.3. Advice for firefighters

Protection during firefighting : Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

#### 6.1.1. For non-emergency personnel

Emergency procedures : Ventilate spillage area. Do not breathe dust.

#### 6.1.2. For emergency responders

Protective equipment : Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

### 6.2. Environmental precautions

Avoid release to the environment.

### 6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Clear up rapidly by scoop or vacuum. Do not use any water to clean up. Product forms slippery surface when combined with water.  
Other information : Dispose of materials or solid residues at an authorized site.

### 6.4. Reference to other sections

For further information refer to section 13.

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Precautions for safe handling : Ensure good ventilation of the work station. Wear personal protective equipment. Do not breathe dust.  
Hygiene measures : Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

### 7.2. Conditions for safe storage, including any incompatibilities

Storage conditions : Store in a well-ventilated place. Keep cool. Protect from moisture.

# Ready to use skimcoat filler

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

Incompatible materials : Acids.

### 7.3. Specific end use(s)

No additional information available

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### 8.1.1 National occupational exposure and biological limit values

No additional information available

#### 8.1.2. Recommended monitoring procedures

No additional information available

#### 8.1.3. Air contaminants formed

No additional information available

#### 8.1.4. DNEL and PNEC

No additional information available

#### 8.1.5. Control banding

No additional information available

### 8.2. Exposure controls

#### 8.2.1. Appropriate engineering controls

##### Appropriate engineering controls:

Ensure good ventilation of the work station.

#### 8.2.2. Personal protection equipment

##### Personal protective equipment:

Gloves. In case of dust production: protective goggles. Dust production: dust mask with filter type P2.

##### Personal protective equipment symbol(s):



#### 8.2.2.1. Eye and face protection

##### Eye protection:

In case of dust production: protective goggles

#### 8.2.2.2. Skin protection

##### Skin and body protection:

Wear suitable protective clothing

##### Hand protection:

Protective gloves

#### 8.2.2.3. Respiratory protection

##### Respiratory protection:

In order to avoid inhalation of dust, all sanding must be done wearing adequate respirator. dust mask P2

#### 8.2.2.4. Thermal hazards

No additional information available

# Ready to use skimcoat filler

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

### 8.2.3. Environmental exposure controls

#### Environmental exposure controls:

Avoid release to the environment.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: white.
Appearance	: Paste.
Odour	: characteristic.
Odour threshold	: Not available
Melting point	: Not available
Freezing point	: Not applicable
Boiling point	: Not available
Flammability	: Not applicable
Explosive properties	: Not explosive.
Oxidising properties	: Non oxidizing.
Explosive limits	: Not applicable
Lower explosive limit (LEL)	: Not available
Upper explosive limit (UEL)	: Not available
Flash point	: Not applicable
Auto-ignition temperature	: Not applicable
Decomposition temperature	: Not available
pH	: 8.2 – 9.3 (20 °C)
Viscosity, kinematic	: Not applicable
Solubility	: Dispersible.
Partition coefficient n-octanol/water (Log Kow)	: Not available
Vapour pressure	: Not available
Vapour pressure at 50 °C	: Not available
Density	: Not available
Relative density	: 1.34 – 1.45
Relative vapour density at 20 °C	: Not available
Particle size	: Not applicable
Particle size distribution	: Not applicable
Particle shape	: Not applicable
Particle aspect ratio	: Not applicable
Particle aggregation state	: Not applicable
Particle agglomeration state	: Not applicable
Particle specific surface area	: Not applicable
Particle dustiness	: Not applicable

### 9.2. Other information

#### 9.2.1. Information with regard to physical hazard classes

No additional information available

#### 9.2.2. Other safety characteristics

VOC content : < 0.02 %

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

### 10.2. Chemical stability

Stable under normal conditions.

# Ready to use skimcoat filler

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

### 10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

### 10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

### 10.5. Incompatible materials

Acids.

### 10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

## SECTION 11: Toxicological information

### 11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity (oral)	: Not classified (Based on available data, the classification criteria are not met)
Acute toxicity (dermal)	: Not classified (Based on available data, the classification criteria are not met)
Acute toxicity (inhalation)	: Not classified (Based on available data, the classification criteria are not met)
Skin corrosion/irritation	: Not classified (Based on available data, the classification criteria are not met) pH: 8.2 – 9.3 (20 °C)
Additional information	: Product dust may cause mechanical irritation to the skin and mucous membranes.
Serious eye damage/irritation	: Not classified (Based on available data, the classification criteria are not met) pH: 8.2 – 9.3 (20 °C)
Additional information	: May cause slight temporary irritation to ocular mucous membranes
Respiratory or skin sensitisation	: Not classified (Based on available data, the classification criteria are not met)
Additional information	: Repeated or prolonged contact may cause allergic reactions in very susceptible persons
Germ cell mutagenicity	: Not classified (Based on available data, the classification criteria are not met)
Carcinogenicity	: Not classified (Based on available data, the classification criteria are not met)
Reproductive toxicity	: Not classified (Based on available data, the classification criteria are not met)
STOT-single exposure	: Not classified (Based on available data, the classification criteria are not met)
Additional information	: May be irritating to the mucous membranes and to the respiratory system
STOT-repeated exposure	: Not classified (Based on available data, the classification criteria are not met)
Aspiration hazard	: Not classified (Based on available data, the classification criteria are not met)

### Ready to use skimcoat filler

Viscosity, kinematic

Not applicable

### 11.2. Information on other hazards

No additional information available

## SECTION 12: Ecological information

### 12.1. Toxicity

Hazardous to the aquatic environment, short-term (acute)	: Not classified (Based on available data, the classification criteria are not met)
Hazardous to the aquatic environment, long-term (chronic)	: Not classified (Based on available data, the classification criteria are not met)
Not rapidly degradable	

# Ready to use skimcoat filler

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

### 12.2. Persistence and degradability

#### Ready to use skimcoat filler

Persistence and degradability	Not established.
-------------------------------	------------------

### 12.3. Bioaccumulative potential

#### Ready to use skimcoat filler

Bioaccumulative potential	Not established.
---------------------------	------------------

### 12.4. Mobility in soil

No additional information available

### 12.5. Results of PBT and vPvB assessment

#### Ready to use skimcoat filler

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII

This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

#### Component

1,2-Benzisothiazol-3(2H)-one, 2-methyl- (2527-66-4)	This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII
---	---

### 12.6. Endocrine disrupting properties

No additional information available

### 12.7. Other adverse effects

Other adverse effects : May cause pH changes in aqueous ecological systems

## SECTION 13: Disposal considerations

### 13.1. Waste treatment methods

Waste treatment methods : Dispose of contents/container in accordance with licensed collector's sorting instructions.

## SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

### 14.1. UN number or ID number

UN-No. (ADR)	: Not applicable
UN-No. (IMDG)	: Not applicable
UN-No. (IATA)	: Not applicable
UN-No. (ADN)	: Not applicable
UN-No. (RID)	: Not applicable

### 14.2. UN proper shipping name

Proper Shipping Name (ADR)	: Not applicable
Proper Shipping Name (IMDG)	: Not applicable
Proper Shipping Name (IATA)	: Not applicable
Proper Shipping Name (ADN)	: Not applicable
Proper Shipping Name (RID)	: Not applicable

# Ready to use skimcoat filler

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

### 14.3. Transport hazard class(es)

#### ADR

Transport hazard class(es) (ADR) : Not applicable

#### IMDG

Transport hazard class(es) (IMDG) : Not applicable

#### IATA

Transport hazard class(es) (IATA) : Not applicable

#### ADN

Transport hazard class(es) (ADN) : Not applicable

#### RID

Transport hazard class(es) (RID) : Not applicable

### 14.4. Packing group

Packing group (ADR) : Not applicable

Packing group (IMDG) : Not applicable

Packing group (IATA) : Not applicable

Packing group (ADN) : Not applicable

Packing group (RID) : Not applicable

### 14.5. Environmental hazards

Dangerous for the environment : No

Marine pollutant : No

Other information : No supplementary information available

### 14.6. Special precautions for user

#### Overland transport

Not applicable

#### Transport by sea

Not applicable

#### Air transport

Not applicable

#### Inland waterway transport

Not applicable

#### Rail transport

Not applicable

### 14.7. Maritime transport in bulk according to IMO instruments

Not applicable

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### 15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

VOC content : < 0.02 %

Other information, restriction and prohibition regulations : Directive 2004/42/EC on the limitation of emissions of volatile organic compounds. Regulation (EU) No 861/2010 related to Customs Nomenclature.



# Ready to use skimcoat filler

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

### 15.1.2. National regulations

No additional information available

### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out

## SECTION 16: Other information

### Indication of changes:

This sheet was updated (refer to the date at the top of this page). This sheet has been revised completely (changes were not marked).

### Abbreviations and acronyms:

ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
EC50	Median effective concentration
LC50	Median lethal concentration
DNEL	Derived-No Effect Level
ED	Endocrine disrupting properties
ATE	Acute Toxicity Estimate
BCF	Bioconcentration factor
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
LD50	Median lethal dose
N.O.S.	Not Otherwise Specified
OECD	Organisation for Economic Co-operation and Development
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
OEL	Occupational Exposure Limit
vPvB	Very Persistent and Very Bioaccumulative

Data sources : ECHA (European Chemicals Agency). Supplier's safety documents.

### Full text of H- and EUH-statements:

Acute Tox. 3 (Oral)	Acute toxicity (oral), Category 3
Acute Tox. 4 (Dermal)	Acute toxicity (dermal), Category 4
Acute Tox. 4 (Inhalation)	Acute toxicity (inhal.), Category 4
Aquatic Acute 1	Hazardous to the aquatic environment — Acute Hazard, Category 1
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Skin Corr. 1C	Skin corrosion/irritation, Category 1, Sub-Category 1C
Skin Sens. 1A	Skin sensitisation, category 1A
H301	Toxic if swallowed.

# Ready to use skimcoat filler

## Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2020/878

H312	Harmful in contact with skin.
H314	Causes severe skin burns and eye damage.
H317	May cause an allergic skin reaction.
H318	Causes serious eye damage.
H332	Harmful if inhaled.
H400	Very toxic to aquatic life.
H411	Toxic to aquatic life with long lasting effects.
EUH208	Contains 1,2-Benzisothiazol-3(2H)-one, 2-methyl- . May produce an allergic reaction.
EUH210	Safety data sheet available on request.

fds eu toupret

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.