

SAFETY DATA SHEET

Date of Issue: March 01, 2020
SDS No.: RI-131
Version: 001



1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

For ink unless otherwise specified.

1.1. Product identifier.

Product name : Cartridge for V BOARD MASTER

Product code : WBS-VBM-V

Mixture name : WMAM-V

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses : Ink for writing instrument

1.3. Details of the supplier of the safety data sheet

Name of manufacture : PILOT CORPORATION OF EUROPE
/ supplier

Address : PAE de la Caille 74350 ALLONZIER-LA-CAILLE (France)

Telephone number : +33 (0)4 50 08 33 00
Working hours (from 8.30am to 12.30pm and from 01.30pm to 05.30pm
: 04.00pm on Friday-French time)

Facsimile number : +33 (0)4 50 46 43 59

E-mail address : pilotfrance@piloteurope.com

1.4. Emergency telephone number

Telephone number : +33 (0)1 45 42 59 59

Association /Organization : ORFILA /INRS <http://www.centres-antipoison.net>

2. HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Flammable Liquid Category 2 H225

Eye Damage / Eye Irritation Category 2 H319

2.2. Label elements

Labeling according Regulation (EC) No 1272/2008

Hazard Pictograms



Signal word : Danger

Hazard statement(s)

H225 : Highly flammable liquid and vapour

H319 : Causes serious eye irritation

Precautionary statement(s)

Prevention

P210 Keep away from heat/sparks/open flames/hot surfaces. -No smoking.

P102 Keep out of reach of children.

Response

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

2.3. Other hazards None

3. COMPOSITION / INFORMATION ON INGREDIENTS

Ingredients	CAS No.	EC No.	Index No.	REACH Registration No.	% Weight	Classification	Component
						(EC)No 1272/2008	
Ethanol	64-17-5	200-578-6	603-002-00-5	01-21194-57610-43-xxxx	75	Flam Liq.2 H225	Violet
Propan-2-ol	67-63-0	200-661-7	603-117-00-0	01-21194-57558-25-xxxx	5.5	Flam Liq.2 H225 Eye Irrit. 2 H319 STOT SE 3 H336	Violet
Propan-1-ol	71-23-8	200-746-9	603-003-00-0	-	1.5	Flam liq. 2 H225 Eye Dam.1 H318 STOT SE3 H336	Violet

H318: Causes serious eye damage.

H336: May cause drowsiness or dizziness.

4. FIRST AID MEASURES

4.1. Description of first aid measures

Inhalation : Remove subject to ventilated fresh air. Consult physician if necessary.

Ingestion : Refer for medical attention.

Skin contact : Wash the affected area under tepid running water using a mild soap.
And refer for medical attention if irritation continues.

Eye contact : Gently rinse the affected eyes with clean water for at least 15 minutes.
And refer for medical attention if irritation continues.

First aid facilities : Ensure eyewash and water service are available.

4.2. Most important symptoms and effects, both acute and delayed

In case of skin or eye contamination treat as under First Aid Measures.

4.3. Indication of any immediate medical attention and special treatment needed

There is no specific antidote. Treat symptoms.

5. FIRE-FIGHTING MEASURES

- 5.1. Extinguishing media : In case of fire, use water spray, foam, dry, chemical powder or carbon dioxide.
- 5.2. Special hazards arising from the substance or mixture : CO₂, CO, NO_x, and SO_x, is produced after combustion.
- 5.3. Advice for firefighters : None

6. ACCIDENTAL RELEASE MEASURES

- 6.1. Personal precautions, protective equipment and emergency procedures
: Use proper ventilation. Use eye and skin protection.
- 6.2. Environmental precautions
: Do not dispose of waste to the sewer.
- 6.3. Methods and material for containment and cleaning up
: Absorb spill with material (cloth or paper), then place in a chemical waste containers.
- 6.4. Reference to other sections : None

7. HANDLING AND STORAGE

- 7.1. Precautions for safe handling
: Use proper ventilation.
Avoid rough handling or dropping.
Wear protective gloves / protective clothing / eye protection / face protection.
Keep out of reach of children and do not drink ink.
- 7.2. Conditions for safe storage, including any incompatibilities
: Store in a dry, cool, well-ventilated location.
- 7.3. Specific end use(s)
: Not use it except the ink for writing instruments.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

- 8.1. Control parameters

Data of France.

	Limit value - Eight hours	Limit value - Short term
Ethanol	1000 ppm	5000 ppm
Propan-2-ol	—	400 ppm

- 8.2. Exposure controls

: Wear protective gloves / protective clothing / eye protection / face protection.

9. PHYSICAL AND CHEMICAL PROPERTIES

- 9.1. Information on basic physical and chemical properties

(a) Appearance	: Violet Liquid
(b) Odour	: Alcohol odour
(c) Odour threshold	: No data
(d) pH	: Not applicable
(e) Melting point / Freezing point	: No data
(f) Boiling point / boiling range	: 78.3 degrees Celsius (Ethanol)

(g) Flash point	: 14.0 degrees Celsius (Ethanol)
(h) Evaporation rate	: No data
(i) Flammability (solid, gas)	: Flammable
(j) Upper/lower flammability or explosive limits	: None
(k) Vapor pressure	: 40hPa (at 20 degrees Celsius, Ethanol)
(l) Vapor density	: 1.6 (at 20 degrees Celsius, Ethanol)
(m) Relative density	: 0.82-0.83 (at 20 degrees Celsius)
(n) Solubility(ies)	: Not applicable
(o) Partition coefficient: n-octanol / water	: Not available
(p) Auto-ignition temperature	: No data
(q) Decomposition temperature	: No data
(r) Viscosity	: 6.0-9.0 mPa · s (at 20 degrees Celsius)
(s) Explosive properties	: No data
(t) Oxidising properties	: No data
9.2. Other information	: None

10. STABILITY AND REACTIVITY

10.1. Reactivity	: This material is stable.
10.2. Chemical stability	: This material is stable.
10.3. Possibility of hazardous reactions	: This material is stable.
10.4. Conditions to avoid	: Direct sunshine, the high temperature and source of ignition.
10.5. Incompatible materials	: Strong oxidizing agents and reducing agents.
10.6. Hazardous decomposition products	: Heating can release vapours which can be ignited. : Burning produces obnoxious and toxic fumes, carbon oxides.

11. TOXICOLOGICAL INFORMATION

Mixture: No data

11.1. Information on toxicological effects		
(a) acute toxicity	Ethanol	: LD ₅₀ 11,500 mg/kg (rat oral)
	Propan-2-ol	: LD ₅₀ 3,437 mg/kg (rat oral) : LD ₅₀ 4,059 mg/kg (rabbit skin)
	Propan-1-ol	: LD ₅₀ 2,695 mg/kg (rat oral)
(b) skin corrosion/irritation	Ethanol	: 400 mg open ; MILD (rabbit skin)
	Propan-2-ol	: 500 mg open ; MILD (rabbit skin)
	Propan-1-ol	: 500 mg open ; MILD (rabbit skin)
(c) serious eye damage/irritation	Ethanol	: 100 mg/24h ; MODERATE (rabbit eye)
	Propan-2-ol	: 100 mg/24h ; MODERATE (rabbit eye)

	Propan-1-ol	: 100 mg/24h ; MODERATE (rabbit eye)
(d) respiratory or skin sensitisation	No data available	
(e) germ cell mutagenicity	No data available	
(f) carcinogenicity	No data available	
(g) reproductive toxicity	No data available	
(h) STOT-single exposure	Propan-2-ol	: May cause drowsiness or dizziness.
	Propan-1-ol	: May cause drowsiness or dizziness.
(i) STOT-repeated exposure	No data available	
(j) aspiration hazard	No data available	

12. ECOLOGICAL INFORMATION

Mixture: No data.

12.1. Toxicity	Ethanol	: LC ₅₀ - Salmo gairdneri-13,000 mg/L-96H EC ₅₀ - Daphnia magna-12,340 mg/L-48H
	Propan-2-ol	: LC ₅₀ - Fathead minnow- 11,130mg/L-96H
	Propan-1-ol	: EC ₅₀ - Daphnia magna(Water flea)- 3,025 mg/L-48H
12.2. Persistence and degradability	No data available	
12.3. Bioaccumulative potential	No data available	
12.4. Mobility in soil	No data available	
12.5. Results of PBT and vPvB assessment	No data available	
12.6. Other adverse effects	No data available	

13. DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

- Follow all regulations in your country.

14. TRANSPORT INFORMATION

14.1. UN number	: 1993
14.2. UN proper shipping name	: Flammable liquid N.O.S (Ethanol)
14.3. Transport hazard class(es)	: 3
14.4. Packing group	: II
14.5. Environmental hazards	: Not applicable.
14.6. Special precautions for user	: Not applicable.
14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	: Not applicable.

15. REGULATORY INFORMATION

- 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

- Follow all regulations in your country.

15.2. Chemical safety assessment

- No data

16. OTHER INFORMATION

Hazard statement according to (EC) No 1272/2008

Precautionary Statements		
Prevention	P233	Keep container tightly closed.
	P240	Ground / bond container and receiving equipment.
	P241	Use explosion-proof electrical, ventilating and lighting equipment.
	P242	Use only non-sparking tools.
	P243	Take action to prevent static discharges.
	P280	Wear protective gloves/protective clothing/eye protection/face protection.
	P264	Wash hands thoroughly after handling.
Response	P303+P361 +P353	IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse affected areas with water.
	P337+P317	If eye irritation persists: Get medical help.
	P370 + P378	In case of fire: Use water spray, foam, dry chemical powder or carbon dioxide for extinguish.
Storage	P403+P235	Store in a well-ventilated place. Keep cool.
Disposal	P501	Dispose of contents and container in accordance with all local, regional, national and international regulations.

The information here is given in good faith, but no warranty, express or implied, is made.

Final determination of suitability of any material is the sole responsibility of the user.

End of SDS