




### Features:



- UL Approved
- High Quality Open Style Toroidal Transformer
- Single Primary/ Dual Secondary windings
- Very low level radiated magnetic field
- Supplied with mounting Kit
- 100% electrical and flash tested.
- Thermal Fuse on Primary.
- Compliant Standards, EN61558, EN60950, UL, C-UL and CE



Lead Length: 150mm stripped and tinned ends

VA Rating	Part No	Input Voltage (Vac)	Output Voltage (Vac)	Output Current (A)	Regulation (Typ. %)	Temp Rise (°C)	Height x Dia. (mm)	Weight (Kg)
15	VTX-146-015-106	230	2 x 6	1.25	16	26	28 x 60	0.3
15	VTX-146-015-109	230	2 x 9	0.83	16	26	28 x 60	0.3
15	VTX-146-015-112	230	2 x 12	0.63	16	26	28 x 60	0.3
15	VTX-146-015-115	230	2 x 15	0.5	16	26	28 x 60	0.3
15	VTX-146-015-118	230	2 x 18	0.42	16	26	28 x 60	0.3
30	VTX-146-030-106	230	2 x 6	2.5	14	40	31 x 74	0.48
30	VTX-146-030-109	230	2 x 9	1.67	14	40	31 x 74	0.48
30	VTX-146-030-112	230	2 x 12	1.25	14	40	31 x 74	0.48
30	VTX-146-030-115	230	2 x 15	1	14	40	31 x 74	0.48
30	VTX-146-030-118	230	2 x 18	0.83	14	40	31 x 74	0.48
30	VTX-146-030-125	230	2 x 25	0.6	14	40	31 x 74	0.48

Please contact Vigortronix for any enquires. Products can be altered to suit custom requirements  
The information contained in this document is subject to change without notice.



VA Rating	Part No	Input Voltage (Vac)	Output Voltage (Vac)	Output Current (A)	Regulation (Typ. %)	Temp Rise (°C)	Height x Dia. (mm)	Weight (Kg)
50	<b>VTX-146-050-106</b>	230	2 x 6	4.17	14	42	34 x 81	0.60
50	<b>VTX-146-050-109</b>	230	2 x 9	2.78	14	42	34 x 81	0.60
50	<b>VTX-146-050-112</b>	230	2 x 12	2.08	14	42	34 x 81	0.60
50	<b>VTX-146-050-115</b>	230	2 x 15	1.67	14	42	34 x 81	0.60
50	<b>VTX-146-050-118</b>	230	2 x 18	1.39	14	42	34 x 81	0.60
50	<b>VTX-146-050-125</b>	230	2 x 25	1	14	42	34 x 81	0.60
50	<b>VTX-146-050-155</b>	230	2 x 55	0.45	14	42	34 x 81	0.60
80	<b>VTX-146-080-109</b>	230	2 x 9	4.44	11	50	40 x 90	1
80	<b>VTX-146-080-112</b>	230	2 x 12	3.33	11	50	40 x 90	1
80	<b>VTX-146-080-115</b>	230	2 x 15	2.67	11	50	40 x 90	1
80	<b>VTX-146-080-118</b>	230	2 x 18	2.22	11	50	40 x 90	1
80	<b>VTX-146-080-125</b>	230	2 X 25	1.6	11	50	40 x 90	1
80	<b>VTX-146-080-155</b>	230	2 X 55	0.73	11	50	40 x 90	1
120	<b>VTX-146-120-112</b>	230	2 x 12	5	10	55	44 X 98	1.32
120	<b>VTX-146-120-115</b>	230	2 x 15	4	10	55	44 X 98	1.32
120	<b>VTX-146-120-118</b>	230	2 x 18	3.33	10	55	44 X 98	1.32
120	<b>VTX-146-120-125</b>	230	2 x 25	2.4	10	55	44 X 98	1.32
120	<b>VTX-146-120-155</b>	230	2 x 55	1.09	10	55	44 X 98	1.32
160	<b>VTX-146-160-112</b>	230	2 x 12	6.67	8	55	<b>46 X 105</b>	1.6
160	<b>VTX-146-160-115</b>	230	2 x 15	5.33	8	55	<b>46 X 105</b>	1.6
160	<b>VTX-146-160-118</b>	230	2 x 18	4.44	8	55	<b>46 X 105</b>	1.6
160	<b>VTX-146-160-125</b>	230	2 x 25	3.2	8	55	<b>46 X 105</b>	1.6
160	<b>VTX-146-160-130</b>	230	2 x 30	2.67	8	55	<b>46 X 105</b>	1.6
160	<b>VTX-146-160-155</b>	230	2 x 55	1.45	8	55	<b>46 X 105</b>	1.6
225	<b>VTX-146-225-112</b>	230	2 x 12	9.38	7	60	<b>50 X 110</b>	2.2
225	<b>VTX-146-225-115</b>	230	2 x 15	7.5	7	60	<b>50 X 110</b>	2.2
225	<b>VTX-146-225-118</b>	230	2 x 18	6.3	7	60	<b>50 X 110</b>	2.2
225	<b>VTX-146-225-125</b>	230	2 x 25	4.5	7	60	<b>50 X 110</b>	2.2
225	<b>VTX-146-225-130</b>	230	2 x 30	3.75	7	60	<b>50 X 110</b>	2.2
225	<b>VTX-146-225-155</b>	230	2 x 55	2.05	7	60	<b>50 X 110</b>	2.2



VA Rating	Part No	Input Voltage (Vac)	Output Voltage (Vac)	Output Current (A)	Regulation (Typ. %)	Temp Rise (°C)	Height x Dia. (mm)	Weight (Kg)
250	VTX-146-250-112	230	2 x 12	10.42	7	60	55 X 120	2.5
250	VTX-146-250-115	230	2 x 15	8.33	7	60	55 X 120	2.5
250	VTX-146-250-118	230	2 x 18	6.95	7	60	55 X 120	2.5
250	VTX-146-250-125	230	2 x 25	5	7	60	55 X 120	2.5
250	VTX-146-250-130	230	2 x 30	4.16	7	60	55 X 120	2.5
250	VTX-146-250-155	230	2 x 55	2.27	7	60	55 X 120	2.5
300	VTX-146-300-125	230	2 x 25	6	6	60	54 X 125	2.8
300	VTX-146-300-130	230	2 x 30	5	6	60	54 X 125	2.8
300	VTX-146-300-135	230	2 x 35	4.28	6	60	54 X 125	2.8
300	VTX-146-300-155	230	2 X 55	2.73	6	60	54 X 125	2.8
500	VTX-146-500-125	230	2 x 25	10	6	68	59 X 135	4.3
500	VTX-146-500-130	230	2 x 30	8.33	6	68	59 X 135	4.3
500	VTX-146-500-135	230	2 x 35	7.14	6	68	59 X 135	4.3
500	VTX-146-500-140	230	2 x 40	6.25	6	68	59 X 135	4.3
500	VTX-146-500-145	230	2 x 45	5.56	6	68	59 X 135	4.3
500	VTX-146-500-150	230	2 x 50	5	6	68	59 X 135	4.3
500	VTX-146-500-155	230	2 x 55	4.55	6	68	59 X 135	4.3
625	VTX-146-625-140	230	2 x 40	7.8	5	70	71 X 139	5.2
625	VTX-146-625-145	230	2 X 45	6.95	5	70	71 X 139	5.2
625	VTX-146-625-150	230	2 x 50	6.25	5	70	71 X 139	5.2
625	VTX-146-625-155	230	2 x 55	5.68	5	70	71X 139	5.2
800	VTX-146-800-140	230	2 x 40	10	5	72	65 X 163	6.3
800	VTX-146-800-145	230	2 x 45	8.88	5	72	65 X 163	6.3
800	VTX-146-800-150	230	2 x 50	8	5	72	65 X 163	6.3
800	VTX-146-800-155	230	2 x 55	7.27	5	72	65 X 163	6.3
1000	VTX-146-1000-140	230	2 x 40	12.5	4	75	71 X 167	7.5
1000	VTX-146-1000-145	230	2 x 45	11.11	4	75	71 X 167	7.5
1000	VTX-146-1000-150	230	2 x 50	10	4	75	71 X 167	7.5
1000	VTX-146-1000-155	230	2 x 55	9.09	4	75	71 X 167	7.5

The information contained in this document is subject to change without notice.