



Programming

Adafruit Feather	47	Kano	12	Pi Motor & Power Driver Boards	27
Adafruit Fona	48	Makey Makey	19	Pi Power Supplies & Heat Management	27
Adafruit NeoPixel LED	44	Microbit	16	Pi-top	15
Adafruit Trinket	44	Microcontroller Project Kits	33	Pi Touch Sensing	27
Arduino	36	OrangePi	40	Programming	18
Breakout Sensor Boards	49	Pi Breakout & Proto Boards	23	Raspberry Pi	22
DFRobot	18	Pi Camera Modules	24	Raspberry Pi Robotics	25
DFRobot Arduino Boards & Kits	33	Pi Cases	28	PICAXE	28
Flowol	51	Pi Kits	22	RFID/NFC	49
GENIE Microcontrollers	30	Pi Light, Sound & Display Add-on Boards	26	Wearables	46

Full range of Programming products available at:

www.rapidonline.com




Kano PC

A new way of learning

KANO EDUCATION

Make a computer

Students follow the simple steps, connect the battery, speaker, case, and keyboard, then bring their computer to life. They discover how computers work as they build it.




Creative Curriculum


Students learn to code with simple, step-by-step lessons, that offer real learning outcomes. The Kano PC delivers standard-aligned curriculum and other educational resources.

Everything the classroom needs

Kano PC comes with Office Suite, Minecraft Education Edition, and our creative apps. With Microsoft 365 education (sold separately) you can simplify set-up and make the most of class time.



Windows 10



Kano Code – make games and animations

How Computers Work - play with pixels, touch, sound, emojis, and binary

Make Art - code artistic masterpieces

Order code 79-9999

£299.99

Tech Specs



Intel Celeron Processor

4GB RAM DDR3L



Storage

64GB (eMMC) – Upgradeable via Micro SD



11.6" touchscreen

1366 x 768, 720p HD



Battery

8-10 hours (Wi-Fi streaming video)



Windows 10 Pro

Extensible Platform

Kano



Computer Kit Touch



Build your own tablet!

Learn to code with 100+ stories and challenges. Make art, games, music, Hack Minecraft. Play with sound, touch, and voice. Browse the internet, draw with Tux Paint, use YouTube and Scratch, compose with Google's Song Maker, and more. Create with the Kano World community.

Learn to code Step-by-step challenges level you up slowly. Type code, drag blocks, unlock programming powers, earn rewards as you go. Learn about logic, loops, and variables. Projects with Python, Javascript, and Terminal commands.

Make art, music, games Code pictures, build animations, and make musical masterpieces. Don't just play games, change the rules. Take control of Minecraft, Pong and Snake. Play with voice, sound, and touch projects. Compose with Google's Song Maker.

- All in one box - step-by-step book, 10.1 inch HD screen, Raspberry Pi 3, battery, DIY speaker, wireless keyboard, case and stand, memory, 3 USB ports, HDMI and power cables, sound sensor, stickers, Kano's unique operating system
- Learn to code with 100+ creative challenges and stories
- Endless play - make your own art, games and music
- Hack Minecraft to do something new
- Play with Google's Song Maker
- Browse the internet, watch YouTube, write stories, 100+ apps
- Be inspired, make and play with 700,000+ creations made by the Kano World community
- Open any creation, tweak the code to make it your own
- No technical knowledge required
- Includes Kano Lifetime Care and 1 year warranty
- Suitable for ages 6+

Type	Order code	1+
Computer kit touch	79-9994	279.99

568540



Computer Kit



Build your own real computer - browse the internet, download apps. Watch YouTube, draw with Tux Paint, code with Scratch, send messages with WhatsApp and Gmail, research with Wikipedia, and much more.

Learn to code with 100+ stories and challenges. Create art, games, music, Hack Minecraft, make lights flash. Browse the internet, download apps, use YouTube, and more. Create with the Kano World community.

Learn to code with step-by-step challenges that level you up slowly. Type code, drag blocks, unlock programming powers, earn rewards as you go. Learn about logic, loops, and variables. Make projects with Python, Javascript, and Terminal commands.

Make art, music, games, create landscapes and geometric rainbows. Code your own musical masterpieces, and animations. Don't just play games, hack them to do something new. Take control of Minecraft, Pong and Snake.

- Build your own computer
- Comes with step-by-step book, Raspberry Pi 3, programmable LED lights, DIY case, power button, wireless keyboard with trackpad, memory, HDMI and power cables, stickers, Kano's unique operating system, 100+ coding challenges and 100+ apps
- Learn to code with 100+ creative challenges and stories
- Endless play - make your own art, games and music
- Hack Minecraft to do something new
- Be inspired, make and play with 700,000+ creations made by the Kano World community
- Open any creation, tweak the code to make it your own
- Plugs into any HDMI screen
- Browse the internet, watch YouTube, write stories, 100+ apps
- Trusted by over 2000 schools and code clubs



- Winners of the family choice award, webby award, red dot award, Cannes gold lions and more
- No technical knowledge required
- Includes Kano Lifetime Care and 1 year warranty
- Suitable for ages 6+

Type	Order code	1+
Computer kit	79-9995	149.99

568541



Motion Sensor Kit



Build an infra-red sensor that detects distance and direction. Learn to code by making music and games, controlled with a wave of your hand. Create, share, and play with the Kano World community.

Learn to code with step-by-step challenges that level you up slowly. Connect code blocks, see the Javascript, learn about loops, logic, live data, and variables. Wave your hand and make your code move.

Make art, music, and games including guitars to pluck, records to scratch, aliens that laugh, flowers that grow, drums to bang and pigs that fly, all controlled with a wave of your hand. It's instant and beautiful.

- Build an infra-red sensor that detects distance and direction
- Comes with step-by-step book, sensor, cable, sucker-pad, stickers, and free Kano app
- Learn to code step-by-step with 30+ creative challenges
- Make your own art, games and music, controlled with a wave of your hand
- Be inspired, make and play with 700,000+ creations made by the Kano World community
- Open any creation, tweak the code to make it your own
- Plug and play - works with Mac, PC, Linux and any Kano Computer Kit
- Includes Kano Lifetime Care and 1 year warranty
- Suitable for ages 6+

Type	Order code	1+
Motion sensor kit	79-9996	29.99

568542



Frozen 2 - order code 79-9997


AVAILABLE NOW!

FROZEN 2 AND STAR WARS CODING KITS

See www.rapidonline.com for details



Star Wars - order code 79-9998



DID YOU KNOW WE ARE ARDUINO'S EDUCATION PARTNER IN THE UK?

By working together it is Arduino's and Rapids aim to bring STEM solutions to schools by working closely with teachers, providing rich content and resources and ensuring they have everything they need from training to support to implement STEM subjects in schools.

pi-top



Raspberry Pi Modular Desktop Computer

£75.95

Order code 75-1001

RASPBERRY PI 3B+ NOT INCLUDED (70-1005)

- Gives everyone the opportunity to be inspired by STEAM and making
- Full pi-topOS software bundle
- Slimmer form factor
- Adjustable viewing angles
- 14" HD screen
- Modular components
- Plug and Play Ready
- Forward-facing access to your hardware
- Built in stand adjustable up to 180°
- Pre-loaded SD card included


micro:bit barely needs any introduction. Since its launch in 2016 when 1 million devices were delivered to students across the UK, micro:bit's popularity has continued to grow and the device has been used by students all over the world to learn coding and basic electronics.

What is micro:bit?

micro:bit is a small, handheld programmable computer that can be used for making all sorts of fun projects from robots and remote controls to wearable electronic devices.

It has an LED matrix on the front for displaying messages and shapes, two push-button inputs, a 3-axis accelerometer to detect movement in all directions and a compass to detect heading. It can also transmit to and receive data from another micro:bit which means it can be used to send messages or act as a remote control.

* Starter kit contains micro:bit, USB cable, switched battery box and 2x AAA batteries.



Programming the micro:bit

The easiest way to write code for your micro:bit is by using the MakeCode editor. It runs in your browser window and allows your students to create programs in a graphical block editor or by using the text-based JavaScript editor. When you build a block program, the equivalent JavaScript is automatically created so you can start to understand the syntax.



Visit www.microbit.org/code to get programming



4tronix Bit:Bot and Bit:Bot XL Robots for BBC micro:bit



The **Bit:Bot** Robot is a feature-packed little robot that is almost ready to go, requiring no soldering, no wires and nothing more than a screwdriver to complete it.

The Bit:Bot turns your micro:bit from a stand-alone programmable computer to an awesome mobile robot allowing you to explore and code the **BBC micro:bit** using any of the languages available.

The Bit:Bot is powered by 3x AA batteries which are also used to power your micro:bit so the original micro:bit battery holder is not needed. The micro:bit itself is easily plugged in and removed using the edge connector on the top of the robot.

Two versions of the optional Ultrasonic Distance Sensor are available. The removable version unplugs easily from its socket to aid access to the micro:bit download port. The soldered version is more stable and robust, but you may need a right-angled USB download cable to download a program with the sensor in situ.

Batteries and micro:bit sold separately.

Also available are a range of accessories designed to complement the Bit:Bot.

There is a **pen holder** available that is designed for use with either the Bit:Bot or CrumbleBot. The nifty little, and extremely thin PCB allows you to connect a pin to the back of your robot, and because the PCB is so thin it is very flexible, ensuring that it can exert downward pressure on the pen without lifting the robot off the ground. A rubber grommet with a 10mm internal diameter accepts Sharpie-type pens and the pen holder is easily fitted onto the battery support pillar of the robot. There are two versions, with or without a ring of 8x bright white LEDs that enhance the looks and shine light onto where the pen is writing.

The **Talon Grabber** has a jaw that you can control the opening of using standard servo code, as well as the specific code added to the Bit:Bot package.

- 2x micro-metal gear motors which can be controlled with both speed and direction
- Wheels with rubber tyres for maximum grip
- Super-smooth metal ball front caster
- 12x neopixel LEDs - select any colour for any pixel to produce stunning lighting effects as your Bit:Bot moves around
- 2x line following sensors - code your own line-following robots and race them to see which programmer can produce the fastest lap!

- 2x analogue light sensors so your Bit:Bot can be programmed to follow a light source such as a torch or hide in the darkest place it can find
- Sounder for making beeps wherever you go!
- Extension port for adding more neopixel LEDs
- Expansion connections at the front for adding the optional Ultrasonic Distance Sensor
- Pen holder and talon grabber also available

Type	Order code	1+
Bit:Bot Robot	75-0117	29.75
Bit:Bot XL Robot	N 75-5019	34.90
Bit:Bot XL Bundle	N 75-0299	36.95
Socketed ultrasonic	75-0121	3.71
Soldered ultrasonic	75-0119	3.71
Talon/grabber	75-5007	10.00
Pen holder Mk2	N 75-5015	2.50



Robo:Bit for BBC micro:bit and Accessories



If you have a **BBC micro:bit** then you should get the **Robo:Bit** buggy. Using the basic kit, you can learn about controlling motors and use the accelerometers or compass on the micro:bit to aid navigation and collision detection. You can also make a very cool remote control robot by using another micro:bit and the radio function.

The **Robo:Bit buggy** can be assembled very quickly using only a screwdriver. No soldering is required making it a great beginners kit and the chunky wheels and powerful motors mean it works well on any surface.

There are also available a number of optional accessories to make the Robo:Bit buggy even more versatile:

The **Ultrasonic Distance Sensor** lets the robot detect objects before it collides with them allowing you to program it to avoid them. It can also be used to create a 'follow me' program where the robot tries to stay a certain distance from the object in front of it.

The **Line Follower Sensor Pack** uses two line sensors to follow a black line and keep the buggy on track. You can write more complex programs that behave as required when you meet a T-junction or crossroads.

We all like adding blinky LEDs to our electronic creations, whether it is a robot, weather station or something that reads and displays sensor data. Now with **McRoboFace** you can add emotions to everything at the same time as adding blinkies. It also comes in grey or white.

All the 17 RGB LEDs are fully addressable and can be controlled by most processors in the field using standard 'neopixel' code. This includes Raspberry Pi, Crumble, Arduino, ESP8266, micro:bit and Codebug.

The **Robo:Bit** robotics controller is a ready-assembled robotics controller board that's ready to be used with your **BBC micro:bit**, just add battery power (3 or 4 AA is ideal, but not included) and motors of your choice to make your own DIY robot. Use a small box, ice-cream carton or similar to house everything and you can build a really affordable robot for your school, coding club or home.

Robo:Bit has been cleverly designed so that with a few hexagonal pillars and screws, you can fit the motors, battery box, front casters, line following sensors and even ultrasonic distance sensors and have a very neat and simple robot!

Robo:Bit uses the ever popular DRV8833 motor driver which allows you to use most small motors that operate in the 3 to 6V range.

Connections are provided for lots of the BBC micro:bit pins, and all have immediate 3-pin access to power (3.3V) and ground. There are three separate pins for 5V if you need the extra voltage (but don't feed back 5V to the micro:bit as it won't like it!). This is the GVS (Ground, Volts, Signal) system for sensors and servos etc.

On the left side of the board (the 'front' of the robot) is a set of 4 offset holes into which you can simply poke an HC-SR04 ultrasonic distance sensor. The offset holes and gold plating ensure a good connection, but you can also solder it in permanently for added robustness.

The Robo:Bit fixings pack contains screws, hexagonal pillars and a Pololu caster. This allows you to fit standard yellow motors (not included) and immediately get a robot working.

Also available is the **Talon Grabber (75-5008)** that has a jaw that can be controlled using standard servo code, as well as the specific code added to the Bit:Bot package.

Also available is the **Robo:Bit MK3 (75-5014)** that includes, along with the buggy, the line following sensor, ultrasonic distance sensor, integrated pen holder, and the LED light bar.

- Have fun and learn robotics at the same time
- Quick to assemble with just a screwdriver
- Chunky wheels and powerful motor
- Ideal for many projects
- Batteries and micro:bit sold separately

Type	Order code	1+
Robo:Bit Buggy	75-0123	22.00
Robo:Bit Buggy MK3	75-5014	29.90
Line sensor	75-0127	5.00
McRoboFace white	75-0147	7.00
HC-SR04 v2	75-0146	3.50
Talon/grabber	75-5008	10.00



BBC micro:bit Switched Battery Box Upgrade

This battery box upgrade has a built-in on/off switch and has the same connector as used on the BBC micro:bit. Using this box makes it much easier to switch your micro:bit on and off and will help to protect the fragile connector on your micro:bit.

- Battery holder upgrade
- Built-in on/off switch
- Avoids repeated plugging and unplugging
- Holds 2x AAA batteries
- Connector fully compatible with the BBC micro:bit



Batteries not included.

Type	Order code	1+
micro:bit battery box	18-2899	0.85

Super Alkaline Mercury Free Manganese Batteries

See page 310



Programming



Music Box Base and LED Santa for BBC micro:bit

If you're looking for some extra twinkly fun this festive season look no further than this bundle of goodies from 4tronix.

75-0149 - Music Box Base:Bit for BBC micro:bit

This clever little unit works as a standalone music box for your micro:bit (not included) or can be used to drive a range of shapes. The unit provides battery power, voltage regulation, On/Off switch with indicator and mounting for the micro:bit and up to two plugins. There is also a mini speaker with powered driver so you can make music using the music modules in micro:bit programming languages.

75-0150 - Santa Claus for Music Box Base:Bit

You may only see him once a year, but he's always welcome. The big fella is designed to plug into one of the two positions on the Music Box Base. As examples of coding exercises why not try:

- Flashing each pixel with random colours
- Sweep a single colour from bottom to top
- Make the LEDs on his belt and hat flash alternately
- Make Santa walk by changing the colours on his legs

- See blog for more information and coding examples
- Bundle includes 1 Music Box and 1 Santa
- Santa is protected from incorrect insertion
- Great for learning how to code simple patterns of light
- Simple screw mounting for Micro:Bit (Micro:Bit not included)
- Music Box has:
 - 3 x AAA battery holder (batteries not included)
 - Robust on/off switch
 - Blue LED power indicator
 - Connectors for up to 2 plug in neopixel shapes

Type	Order code	1+
Neopixel Santa	75-0150	6.50
Music box base	75-0149	7.50



Bit:2:Pi BBC micro:bit Raspberry Pi HAT Adaptor - Fully Assembled

The **Bit:2:Pi** adaptor allows the BBC micro:bit to connect to, and re-use all those hundreds of Raspberry Pi add-on boards and HATS.

Simply plug your **micro:bit** into the edge connector and the required Raspberry Pi Hat onto the GPIO

connector, then program your micro:bit to control the new board. Most Raspberry Pi boards are very simple to program as they are controlled by simple On/Off signals on the GPIO connector which are easily copied in the micro:bit. We have also used Neopixel hats (eg. Unicorn from Pimoroni) with great success and are happily communicating via I2C as well.

Selecting which micro:bit pin is connected to which GPIO pin, is via a set of configurable jumpers. There is a default set of connections that works for the most common boards, including I2C and SPI connections, but it is a simple matter to unplug a jumper or two, and replace it with a longer wire jumper (4 included) to connect your preferred pins.

Of course, the original code for the Raspberry Pi won't run directly on the micro:bit but with support from our



community we will get more and more boards working and with example micro:bit code.

Current boards tested are:

4tronix: PlayHat, Picon Zero, PiStop, motor controllers
Pimoroni: Pibrella, Unicorn pHat/HAT, Explorer, Enviro pHat

Power is supplied to the board and the micro:bit via the micro-USB connector on the side, but there is also an option to add a battery holder (not supplied) to allow completely wire-free operation.

- Fully assembled and ready to go

Note: BBC micro:bit is not included.

Type	Order code	1+
Bit:2:Pi Adaptor	75-0131	11.29

RK Education

RKUB SB Shield Base for BBC micro:bit and Arduino

The RKUB SB is a shield base edge connector powered **breakout board** with headers that allow **Arduino** shields to be mounted onto the PCB, as well as breaking out the **BBC micro:bit** to provide a prototyping area for testing and development. The self-build kit is very easy to build, with surface mount voltage regulators that are easy to solder. The board uses a professional standard, double sided PCB with high quality plated through holes in the prototyping area.

There is a power switch and a 2.1mm DC power socket (12V DC recommended) that powers the board (therefore powering the micro:bit and the shield).

- Self-build kit
- Very easy to use
- Power circuitry with a 3.3V and 5V voltage regulators
- Designed and manufactured in the UK

Note: Neither Arduino nor BBC micro:bit are included.

Type	Order code	1+
Shield base	75-0261	4.75

RK Education

RKUB PT2 Prototyping Board for BBC micro:bit

The RKUB PT2 is a powered prototype edge connector breakout board for the BBC micro:bit. Supplied as a self-build kit that is easy to assemble, with surface mount voltage regulators that are easy to solder. The professional standard, double sided PCB features a large prototyping area that has high quality, plated through holes. The assembly has a power switch and a 2.1mm DC power socket (12V DC recommended), powering the board and the micro:bit.

- Self-build kit
- Very easy to use
- Power circuitry with a 3.3V and 5V voltage regulator
- Designed and manufactured in the UK


Note: The BBC micro:bit is not included.

Type	Order code	1+
Prototyping board	75-0262	4.75

RK Education

RKUB2 Powered Breakout Board for BBC micro:bit

The RKUB2 is a powered edge connector **breakout board** solder kit for the **BBC micro:bit**. Supplied as a self-build kit that is easy to assemble, with surface mount voltage regulators



that are easy to solder. The assembly has a power switch and a 2.1mm DC power socket (12V DC recommended), powering the board and the micro:bit.

- Self-build kit
- Allows you to breakout the BBC micro:bit
- Very easy to use
- Power circuitry with a 3.3V and 5V voltage regulator
- Designed and manufactured in the UK

Note: The BBC micro:bit is not included.

Type	Order code	1+
Breakout board	75-0263	3.75

RK Education

RKUB1 Breakout Board for BBC micro:bit

The RKUB1 is an edge connector **breakout board** solder kit designed for use with the BBC micro:bit. Supplied as a self-build kit that is easy to construct and very easy to use.

- Self-build kit
- Allows you to breakout the BBC micro:bit
- Includes a 2mm JST header for power pack
- Onboard power switch
- Designed and manufactured in the UK

Note: The BBC micro:bit is not included.

Type	Order code	1+
Breakout board	75-0264	2.50

DF Robot



KIT0138 Gravity IoT starter Kit for micro:bit

The IoT Starter Kit is an all-in-one bundle for micro:bit beginners to quickly experience and build Internet of Things projects.

The kit comes with a micro:bit microcontroller, a Wi-Fi module and 7 sensors/actuators that are widely used in real-life IoT applications.

You can easily setup the Wi-Fi connection in MakeCode Block Editor, program your micro:bit and eventually interact with your smart devices. To make things even easier and fun, EasyIoT, a free educational IoT platform, allows subscribers to exchange and visualize the data.

This starter kit is compatible with hundreds of DFRobot Gravity Series modules, bringing endless possibilities to your IoT applications.

Features:

- micro:bit with internet connectivity
- The kit comes with a plug and play Wi-Fi module, Obloq, that adds Internet connectivity to micro:bit
- To start internet connection, simply fill in your Wi-Fi name and password into the coding blocks

Type	Order code	1+
Gravity for micro:bit	75-0109	62.06



FIT0533 micro:bit Enclosure (LEGO Compatible)

Snap this case around your micro:bit and connect common building bricks in seconds.

- A and B buttons still accessible



- Transparent case - matrix LED display still visible
- Cut-outs for battery connector, USB socket and edge connector
- Use your original micro:bit battery box

Type	Order code	1+
LEGO compatible box	75-0104	1.99

568371



DFR0518 Micro: Mate Mini Expansion Board for micro:bit Gravity Compatible

Micro: Mate is a tiny micro:bit I/O expansion board for learning electronics and building DIY projects.



Micro: Mate expands 6 sets of 3-pin I/O interfaces, capable of connecting DFRobot Gravity series modules, servo motors, sensors and jumper wires. Additionally, pins 8, 12, 16 support voltage switch between 3V and 5V, allowing up to 5V, 2A digital (PWM) output.

Micro: Mate is the same size as the micro:bit. It connects to micro:bit through spring-loaded contact pins, ensuring easy, compact and secure connection. The rubber bumpers and the 3.5mm audio jack on the back keep the expansion board installed stable on the board and prevents reversed connection.

Features:

- Colour-coded Gravity 3-pin interface, compatible with hundreds of plug & play electronic modules
- 3-way analog input; 6-way digital input/output (PWM); 3V/5V jumper switch; 3.5mm audio jack
- External Micro USB power port, up to 5V, 2A power output
- Well-designed component layout and silk-screen
- Reversed connection protection
- **Specification:**
- Interface: 6x Gravity 3-pin
- Operating voltage: 5V/3.3V
- Input power: <10W
- Measuring range: 0 to 3.3V (analog), 0 to 5V (digital)
- Dimensions: 68.5 x 53.3mm (2.7 x 2.1in.)
- Weight: 22.8g
- **DFRobot type DFR0518**

Note: The mounting screws should be well tightened to ensure a secure connection. Micro: Mate only supports 3V (3.3V) analog input from pins 0, 1 & 2. The Micro USB power port on Micro: Mate cannot be used for data transmission. Components with large power consumption should be connected to pin 8, 12 or 16 with 5V power supply.

Type	Order code	1+
Micro: Mate	N75-0106	4.87

568372



DFR0521 micro:bit Expansion Board for Boson (Gravity Compatible)

micro:bit is a pocket-sized microcontroller designed for kids and beginners to learn coding and electronics, letting them easily bring ideas into DIY digital games, interactive projects and robotics.



However, on-board I/O rings and crocodile clips sometimes are not handy and safe enough to connect peripherals. To explore more possibilities with micro:bit, we have designed the micro:bit Expansion Board for Boson, a carry-on board that connects to the micro:bit via an edge connector.

The expansion board comes with 6 fool-proof 3-pin sockets, compatible with hundreds of DFRobot's Boson and Gravity modularised electronic blocks, covering most popular digital and analog sensors and actuators, supporting sound, light and motion interaction.

Moreover, the on-board 3.5mm headphone jack and volume knob supports direct connection of a headphone. To ensure a steady current supply for these peripherals, the expansion board can be powered externally through the USB power port.

Features:

- 3-pin fool-proof connectors x6
- Headphone jack with volume knob
- External power port and ON/OFF switch
- DFRobot Gravity and Boson electronic module compatible
- **Specification:**
- Micro USB power port voltage: 5V
- PH2.0 input/output voltage: 3.3V
- Input/output ring voltage: 3.3V
- Maximum current: 500mA
- Working temperature: 0 to 85°C
- Dimensions: 80 x 70mm / (3.15 x 2.76in.)
- Weight: 48g


Type	Order code	1+
micro:bit expansion	N75-0107	7.42

568373



ROB0150 micro: Circular RGB LED Expansion Board

This circular expansion board for your micro:bit has 24 RGB addressable LEDs that can be individually configured to show any colour. This means you can create bright, eye-catching patterns in thousands of variations.



The A and B buttons as well as the original LED matrix display of the micro:bit is still visible when the board is mounted and it also provides a microphone and buzzer for additional inputs and outputs such as using the LEDs as a colourful audio level meter or to turn on the display when sound is sensed.

- Power from micro-USB or using your original micro:bit battery box
- micro:bit sold separately


Type	Order code	1+
LED expansion board	75-0103	9.45

568370

Makey Makey



Inventors Kit



The Makey Makey® kit can turn almost anything into a keyboard or mouse, even unlikely things like your cat, a carrot or a coin. Anything that can conduct even the smallest amount of electricity will work completely safely, there's no danger of shocking the cat!

See what works for you - plants, coins, your grandma, silverware, anything that is wet, most foods, dogs as well as cats, aluminium foil, rain, and a lot more. The list goes on and you can always experiment with more.

Plug the Makey Makey® into your computer, connect yourself to the earth bar simply by holding an alligator clip, and then touch any of the shiny pads to make it work. You will see an LED flash every time you touch the board. Now attach one end of the alligator clips to the shiny pads and the other end to almost anything, touch that and the LEDs light up again. Every flashed LED is a key press or mouse command sent to the PC to control your favourite software.

Find music programs, games on the internet and let your imagination run away as you design a custom controller for them. Try drawing a game controller in pencil, hook up the alligator clips and the drawing IS the controller.

The kit comes with 7 alligator clips and 6 connector wires as well as a USB cable. No extra purchases are necessary to get the thing to work, not even fruit. For the dedicated inventor you can plug in two or more boards at once and create an orchestra of Makey Makeys! (tested with up to 3, but could work for more).

The software is Open Source so you can find it on the internet and modify to it to really experiment. Makey Makey® is compatible with the Arduino development environment (IDE).

- Arduino compatible
- Simple USB connection
- Challenge your imagination
- Invent ways to experiment and play
- Expand your imagination
- Almost anything can be used as a keyboard

Type	Order code	1+
Inventors Kit	73-5500	39.94

539085



GO with Case and Magnet, Croc Lead, Keyring and Instruction Guide

The Makey Makey® GO brings inventing - on the go - to tinkerers, makers, and anyone who wants a fun and exciting way to transform a host of everyday objects, with just the snap of a croc clip, into an internet touchpad!



See what you've got to hand - banana, plant, frying pan, pencil line, coin, pet or friend (doesn't work with imaginary friends, which are non-conductive), or anything even a little bit conductive, and use it to send a signal, through the USB Invention Stick to a computer. Just plug, clip and play - no complicated setup, no programming knowledge needed, no software to install and works on both PC and Mac.

There are 1000s of possibilities for projects! You can make cardboard smart swords, slack line score boards, animal skype phones - whatever your imagination can conjure up. The USB Invention Stick is small enough for a keychain, bag or pocket - making it a doddle to take with you, wherever you go.

The Makey Makey® GO promises to inspire even more science, technology, engineering, and math (STEM) projects than the original, award-winning Makey Makey® - named one of Consumer Reports' "Best Tech Toys of 2014."

- Contents: USB Invention Stick, case with magnet, 1 white crocodile lead, key ring, and instruction guide
- Simple USB connection
- Have fun and expand your imagination
- For ages 6 to infinity

Type	Order code	1+
Makey Makey GO	73-5502	17.68

564675

Free Delivery*
on all orders over £30 (excl. VAT)
(UK mainland only)

* See Terms & Conditions for full details - www.rapidonline.com/terms



Inventors Kit
£39.94
Order code
73-5500

Makey Makey is an invention kit that allows you to turn everyday items into a touch pad that can be used to control your computer. But it is much more than just a replacement for your keyboard – by integrating Makey Makey with Scratch, you can now bring control and sensing to your programs.

So what is so cool about Makey Makey?


Well, you can turn just about anything that is conductive into an input device for your computer. Tin foil, fruit and veg, or just by drawing a shape with a normal pencil, the list goes on and on. Your students will learn about conductivity as well as getting to design their own input device or adding additional functionality to their Scratch programs.

Sounds great, so give me some examples of what I could do.

OK, let's start with something really simple – some Play Dough bongos. You can use off-the-shelf stuff or make your own from basic store-cupboard ingredients. Check out our Makey Makey page for a recipe!


Example 1

- 1) Once you have some Play Dough, make a couple of bongo shapes, one larger and one smaller.
- 2) Now visit apps.makeymakey.com/bongos in your browser.
- 3) Plug your Makey Makey into your USB port
- 4) Connect one crocodile clip lead to the left arrow pad and put the other end in the large bongo. Now connect another crocodile clip to the space pad and put the other end in the small bongo.
- 5) Make sure you are touching the earth on the Makey Makey with one hand and play the Play Dough bongos with the other!



www.rapidonline.com/makeymakey

Now try integrating your Makey Makey with a Scratch program. This one times a small toy car travelling along a track. You'll need some card, split pins, paperclips, a car and some track. You'll also need Scratch running on a computer with your Makey Makey connected to it.



Example 2


- 1) Using card, paper fasteners and paper clips, make some gates to suit your car track similar to those shown. The aim is to make the paperclips touch when the gate is closed and so they can be pushed open by the car as it passes through.
- 2) Place the gates one metre apart near the end of the track
- 3) Connect one side of each gate to the earth of the Makey Makey
- 4) Connect the first gate to the space pad and the second gate to the left arrow.
- 5) In Scratch, create the program as shown and run it

```

when clicked
  repeat until key left arrow pressed? and key space pressed?
  say Make sure the track is reset
  say Ready to go!
  wait until not key space pressed?
  reset timer
  repeat until not key left arrow pressed?
  think timer
  set finishTime to timer
  say Your time will be for 2 secs
  say finishTime
  
```

- 6) Make sure both gates are closed, the program will prompt you if they aren't. You will also see green lights on the Makey Makey next to the arrow and space keys if your gates are closed
- 7) Run the car down your track - the program will time how long it takes to pass between the two gates

Can you modify the program to tell you the speed in metres per second?



Raspberry Pi

Unfamiliar with Raspberry Pi?

It is a credit-card sized computer with USB ports for devices such as a mouse and keyboard and an HDMI output for HDTVs. Millions have been sold worldwide into education, to home users and even into industry. This gives the Raspberry Pi the backing of a very active community which is constantly producing tutorials, software examples and programs you can download from the Internet for free. There's also a huge range of add-on hardware available, from cameras to robotics and more, making it a fantastic base for electronic projects. The Raspberry Pi is also a capable computer that will perform many of the functions that a desktop PC will, like spreadsheets, word processing and games, it will also play high definition video.



Raspberry Pi Model 4 2GB and 4GB Starter Kits



These **Raspberry Pi 4 starter kits** have been designed to help get you up and running as easily as possible.

Each kit contains a Raspberry Pi 4 (2GB or 4 GB), plug-in power supply* with USB C connector, blank 32GB microSD memory card and a 2m HDMI cable with gold connectors.

* **The Raspberry Pi 4 needs more power than previous models and has a different power connector, so you won't be able to use power supplies from older versions.**

The Raspberry Pi 4 Model B is the latest product in the popular Raspberry Pi range of computers.

It offers ground-breaking increases in processor speed, multimedia performance, memory, and connectivity compared to the previous generation Raspberry Pi 3 Model B+, while retaining backwards compatibility and similar power consumption.

For the end user, Raspberry Pi 4 Model B provides desktop performance comparable to entry-level x86 PC systems.

The product's key features include a high-performance 64-bit quad-core processor, dual-display support at resolutions up to 4K via a pair of micro-HDMI ports, hardware video decode at up to 4Kp60, up to 4GB of RAM, dual-band 2.4/5.0GHz wireless LAN, Bluetooth 5.0, Gigabit Ethernet, USB 3.0, and PoE capability (via a separate PoE HAT add-on).

The dual-band wireless LAN and Bluetooth have modular compliance certification, allowing the board to be designed into end products with significantly reduced compliance testing, improving both cost and time to market.

The kit is supplied with a 32GB microSD memory card that is blank so that customers may choose which operating system to install. Operating system installation is easy and instructions can be found here .

Starter kits contain:

- Raspberry Pi model 4
- Plug-in power supply with USB C connector
- 32GB microSD card (blank)
- 2m HDMI cable with gold connectors

Raspberry Pi 4 specification:

- 2.4GHz and 5.0GHz IEEE 802.11b/g/n/ac wireless LAN, Bluetooth 5.0, BLE
- True Gigabit Ethernet
- 2x Micro HDMI ports supporting up to 4K 60Hz video resolution
- Applications include embedded design & development, IoT
- PCB size 85 x 56mm
- **Available in 2GB and 4GB models**

Technical specification

Processor:	Broadcom BCM2711, quad-core Cortex-A72 (ARM v8) 64-bit SoC @ 1.5GHz
Memory:	2GB or 4GB LPDDR4-2400 SDRAM (depending on model)
Connectivity:	2.4GHz and 5.0GHz IEEE 802.11b/g/n/ac wireless LAN, Bluetooth 5.0, BLE Gigabit Ethernet 2x USB 3.0 ports 2x USB 2.0 ports
GPIO:	Standard 40-pin GPIO header, (fully backwards-compatible with previous boards)
Video & sound:	2x micro HDMI ports (up to 4Kp60 supported) 2-lane MIPI DSI display port 2-lane MIPI CSI camera port 4-pole stereo audio and composite video port
Multimedia:	H.265 (4Kp60 decode) H.264 (1080p60 decode, 1080p30 encode) OpenGL ES, 3.0 graphics
SD card support:	Micro SD card slot for loading operating system and data storage (blank SD card supplied)
Input power:	5V DC via USB-C connector (minimum 3A) 5V DC via GPIO header (minimum 3A) Power over Ethernet (PoE) - enabled (requires separate PoE HAT)

Type	Order code	1+
Model 4 2GB	75-1009	52.51
Model 4 4GB	75-1012	61.80



Raspberry Pi 3 Model B+ 1 Quad Core 1.4GHz 1GB RAM WiFi & Bluetooth



The **Raspberry Pi 3 Model B** has been given a makeover. It's time to meet the **3B+**.

This addition to the Raspberry Pi range has a 64-bit quad-core processor which runs at a more powerful **1.4GHz**. It also offers dual-band wireless LAN, Bluetooth 4.2/BLE and a Gigabit ethernet port.

It's definitely a more powerful beast, but it retains the easy connectivity and software of the Raspberry Pi 3. In short, if you love the Raspberry Pi 3, you'll love the 3 Model B+ even more.

Unfamiliar with Raspberry Pi? It is a credit-card sized computer with USB ports for devices such as a mouse and keyboard and an HDMI output for HDTVs. Millions have been sold worldwide into education, to home users and even into industry. This gives the Raspberry Pi the backing of a very active community which is constantly producing tutorials, software examples and programs you can download from the Internet for free. There's also a huge range of add-on hardware available, from cameras to robotics and more, making it a fantastic base for electronic projects. The Raspberry Pi is also a capable computer that will perform many of the functions that a desktop PC will, like spreadsheets, word processing and games, it will also play high definition video.

- Broadcom BCM2837B0, Cortex-A53 (ARMv8) 64-bit SoC @ 1.4GHz
- 1GB LPDDR2 SDRAM
- 2.4GHz and 5GHz IEEE 802.11b/g/n/ac wireless LAN, Bluetooth 4.2, BLE
- Gigabit Ethernet over USB 2.0 (maximum throughput 300 Mbps)
- Extended 40-pin GPIO header
- Full-size HDMI
- 4 x USB 2.0 ports

- CSI camera port for connecting a Raspberry Pi camera
- DSI display port for connecting a Raspberry Pi touchscreen display
- 4-pole stereo output and composite video port
- Micro SD port for loading your operating system and storing data
- 5V/2.5A DC power input
- Power-over-Ethernet (PoE) support (requires separate PoE HAT)

Type	Order code	1+
Model B+	75-1005	28.39



16GB microSD Card Preloaded with NOOBS for Raspberry Pi

With **Raspberry Pi** users there are some people who like to roll their sleeves up and get stuck in straight away, and there are others, especially new users, who like some assistance when starting out on the Raspberry Pi experience.

To provide help to the Raspberry Pi beginner, **Transcend** have produced a 16GB microSD card pre-installed with the **New Out Of Box Software (NOOBS)** for Raspberry Pi. **NOOBS** is software that makes it much easier to set up a Raspberry Pi. You just use the microSD card to boot your Pi for the first time and follow the menu instructions to quickly and simply install the operating system of your choice onto the card. Once your operating system of choice is installed, the Raspberry Pi will boot as normal.

- Provides a choice of operating systems
- Class 10 microSD card
- Capacity 16GB

Type	Order code	1+
NOOBS microSD card	75-0755	8.42

Pi Kits



Raspberry Pi3 B+ Basic Student Kit



The **Raspberry Pi 3 Model B** has been given a makeover. The latest addition to the Raspberry Pi range, the **3B+** has a 64-bit quad-core processor which runs at a more powerful 1.4GHz. It also offers dual-band wireless LAN, Bluetooth 4.2/BLE and a Gigabit ethernet port. It's definitely a more powerful beast, but it retains the easy connectivity and software of the Raspberry Pi 3.

To help users get started Rapid has produced a basic student kit that contains a Raspberry Pi 3 model B+ plus a new PiBow 3 case, MicroSDHC card, cables, keyboard and mouse.

For programming, the latest version of the operating system for the Raspberry Pi can be downloaded for free, and can be loaded onto the microSDHC card for use on the Pi.

- Kit contains everything you need to get started
- Easy to use
- Large online community of users

Kit contents:

- 75-1005** Raspberry Pi 3 Model B+ 1 Quad Core 1.4GHz 1GB RAM WiFi & Bluetooth
- 75-0532** Stontronics T5875DV Official Raspberry Pi International PSU (5.2V, 2.5A) with UK, Euro, Aus & US Plugs
- 73-5433** Pimoroni PiBow 3 Coupé Case for Raspberry Pi
- 19-9222** Kingston SDC10G2/8GB microSDHC UHS-I Card (Class 10) - 8GB
- 19-4921** TruConnect URT-601G 1m Green Cat5e Utp Moulded Lead
- 16-1361** RVFM CDLHD-303 HDMI Lead Gold Plated 3m
- 19-4042** Trust 20623 ClassicLine Keyboard
- 19-4114** Trust 16591 USB Optical Mouse - Black

Type	Order code	1+
Basic student kit	75-0813	61.38

566636



Raspberry Pi B+ Intermediate Student Kit



The **Raspberry Pi 3 Model B** has been given a makeover. The latest addition to the Raspberry Pi range, the **3B+** has a 64-bit quad-core processor which runs at a more powerful 1.4GHz. It also offers dual-band wireless LAN, Bluetooth 4.2/BLE and a Gigabit ethernet port. It's definitely a more powerful beast, but it retains the easy connectivity and software of the Raspberry Pi 3.

To help users get started Rapid has produced this intermediate student kit that contains a Raspberry Pi 3 model B+ plus all the accessories you need to start programming.

- Kit contains everything you need to get started
- Easy to use
- Large online community of users

Type	Order code	1+
Intermediate student kit	75-0814	69.31

566637



Raspberry Pi 3 B+ Advanced Student Kit



The **Raspberry Pi 3 Model B** has been given a makeover. The latest addition to the Raspberry Pi range, the **3B+** has a 64-bit quad-core processor which runs at a more powerful 1.4GHz. It also offers dual-band wireless LAN, Bluetooth 4.2/BLE and a Gigabit ethernet port. It's definitely a more

powerful beast, but it retains the easy connectivity and software of the Raspberry Pi 3.

Rapid have produced the advanced student kit to enable students to really get into the Raspberry Pi experience. The kit contains everything required to carry out advanced projects including a Raspberry Pi 3 model B+ plus a case, power supply, and microSDHC.

For programming, the latest version of the operating system for the Raspberry Pi can be downloaded for free, and can be loaded onto the microSDHC card for use on the Pi.

- Comprehensive kit
- Easy to use
- Large online community of users

Type	Order code	1+
Advanced student kit	75-0815	83.26

566638



Raspberry Pi 3 B+ Bare Bones Kit



If you want to get started with **Raspberry Pi** you should have a kit. Rapid's **BareBones** kit includes the essentials, but doesn't include the things you generally have around the house, workshop, classroom, etc.

This kit includes the Raspberry Pi 3 Model B+, a 5.1V 2.5A plug-in power supply, and an 8GB Class 4 microSDHC card. Everything else you need you probably already have - a keyboard, mouse, HDMI cable. They're probably in that drawer just behind you - go on, have a look.

Raspberry Pi 3 Model B+ (order code **75-1005**).

This iteration of the Pi features a brand new Broadcom 64-bit quad-core processor, built-in Wi-Fi and Bluetooth, as well as all the usual Raspberry Pi goodness.

Power Supply for Raspberry Pi (order code **75-0715**).

A plugtop power supply designed especially for the Raspberry Pi. Has a universal input of 90 to 264V AC and a 5.1V DC 2.5A output.

Kingston Class 4 8GB microSDHC Card (order code **19-9222**).

This SD card is ideal for use with the Raspberry Pi 3 Model B, enabling you to store programs and data for easy and fast storage and retrieval.

- Ideal starter kit for **Raspberry Pi**
- Lots of support, free tutorials, etc.
- Perfect introduction to electronics and computing
- Join millions of Raspberry Pi users

Type	Order code	1+
BareBones kit	75-0816	38.42

566639



We bring **STEM** to life



Adventures in Raspberry Pi Component Companion Kit



This kit contains a host of components suitable for prototyping work. Includes a solderless breadboard, headers, pots, switches, LEDs, buttons, resistors and cables. The kit is an ideal companion to the book 'Adventures In Raspberry Pi' by Carrie Anne Philbin.

- Suitable for any prototyping project

Technical specification

Adventures in Raspberry Pi Component Companion Kit		Qty
50-5441	Solderless Breadboard EIC-102 830 Point 165 x 55 x 8.5mm	1
57-2224	Compatible 16x2 3V3 LCD Display (pre-soldered header)	1
50-8082	1 x 20 Pin Header 2.54mm Pitch 3A Gold Plated	1
68-0242	10K 3/8 1-Turn Finger-Adjust Pot	1
78-0640	7.3mm Square 12x12 Tact switch	4
78-1186	Green Button 12x12mm Square	1
78-1185	Black Button 12x12mm Square	1
78-1184	Ivory Button 12x12mm Square	1
78-1182	Blue Button 12x12mm Square	1
55-0868	Kingbright L-53GD 5mm Green LED Diffused 30mcd	2
55-0864	Kingbright L-53ID 5mm Red LED Diffused 50mcd	2
62-0358	330r Cr25 0.25w Cf Resistor - Pack of 100	1
62-0394	10k Cr25 0.25w Cf Resistor - Pack of 100	1
34-0679	Jumpier Wires Dupont Cable M-F 26AWG 1 Pin 2.54mm Pitch - 15cm - Pack Of 10	2
34-0677	Jumpier Wires Dupont Cable M-M 26AWG 1 Pin 2.54mm Pitch - 15cm - Pack Of 10	2

Type	Order code	1+
Companion kit	75-0037	14.33

559345

Pi Breakout & Proto Boards



Raspberry Pi Relay Board

The **Raspberry Pi Relay Board** from **Seeed Studio** gives you 4 relays

that will switch 15A at 30V DC/250V AC each, easily enough for most applications. The board uses the older 26-pin GPIO connector so it's compatible with every Pi



from the old A to the new Zero. Screw terminals are provided for the connections to the device being switched and an LED indicator shows the status of each relay's normally open (NO) contacts. Your Pi can control the board via I2C and each board has a programmable address making it possible to drive multiple boards. PCBs with high voltages including mains electricity can be dangerous, please take precautions to prevent shocks and short circuits.



- 4 x relays with 1 x NO and 1 x NC contacts each
- 3-bit I2C address selection (8 addresses)
- LED indicators on each relay
- Screw terminals for switched devices

Type	Order code	1+
Relay board	75-0396	20.41

566356

FREE DESIGN & TECHNOLOGY and SCIENCE POSTERS

Email education@rapidonline.com for your pack





Pi T-Cobbler Plus Kit Breakout GPIO to Breadboard for RasPi A+ B+ or 2



The **T-Cobbler Plus + cable** is a fully assembled add-on **prototyping board** kit that is specifically designed for use with the Raspberry Pi B+ and Pi 2 and is also compatible with the A+ model. The breakout board is T-shaped, making it easier to read the labels and a 40-pin ribbon cable is supplied that connects between the Pi and the T-Cobbler, giving access to the power, GPIO, I²C and SPI pins on the Pi.

- Designed for use with Raspberry Pi Model A+/B+/Pi 2/Pi 3
- Makes 'cobbling together' prototypes with the Pi very easy
- Comes with a 40-pin ribbon cable
- Can plug into any solderless breadboard or prototyping board
- All the pins conveniently labelled
- No soldering required

Type	Order code	1+
T-Cobbler kit	75-0507	7.14

559290



PIGRRL 2.0 Custom Gamepad PCB Only

The **Adafruit PIGRRL 2.0 Custom Gamepad PCB** powers up your PIGRRL build by removing the need for point to point wiring for the buttons and switches. The board needs a 40-pin header cable to connect all the GPIO signals, 2 x wires for the power and 4 x wires for the left and right shoulder buttons. That's all the wiring you need to connect 12 x switches! As you'll see from the tutorial there's still quite a bit to do, but the Gamepad PCB takes away a lot of tedious soldering.



The board needs a 40-pin header cable to connect all the GPIO signals, 2 x wires for the power and 4 x wires for the left and right shoulder buttons. That's all the wiring you need to connect 12 x switches! As you'll see from the tutorial there's still quite a bit to do, but the Gamepad PCB takes away a lot of tedious soldering.

New to the PIGRRL? The Raspberry Pi is a tiny Linux computer which can run a number of emulators of classic game systems such as the 8-bit NES and MAME. These have proved so popular that there's a complete distribution aimed at retro gaming, and that's the RetroPie project. If you can think of an 8-bit game, the chances are that it will run on the Raspberry Pi. The PIGRRL project brings these great old games, with their blocky graphics and plinky 8-bit 'music' into a small, hand-held, battery powered, full colour console. Retro games are always a big hit with kids and adults so bring some more retro into your life and build a PIGRRL.

Supplied as a bare PCB, you will need to source the rest of the components required to build a working PIGRRL. Adafruit supply a free and very detailed tutorial to guide you through the whole process of building your very own hand-held retro gaming console.


- Mounts 10 x tact switches
- Get a head start on your PIGRRL game console build
- Dimensions 85 x 48 x 1.6mm (3.35 x 1.9 x 0.06in.)
- Adafruit part no.: 3015

Type	Order code	1+
Gamepad PCB only	73-5249	4.45

563226



Raspberry Pi B+ & Pi 2 GPIO Breakout Boards, Cobbler, Split and Paddle



The Raspberry Pi B+ has 40 GPIO pins compared to the Pi B's 26. Take advantage of the increased number of pins using a **CynTech Raspberry Pi breakout board**. Each board carries the GPIO signals from the Pi to either a breadboard or spring loaded terminal blocks for prototyping. The Split+ and SplitMini+ are supplied as a kit of parts and require soldering before use. The Paddle+ is supplied fully assembled and ready to go.

- Split+ T shaped pcb for breakout boards (**73-6008**)
- Split Mini+ I shaped PCB for breakout boards (**73-6009**)
- Paddle+ with spring loaded terminal blocks for tool free connections (**73-6010**)

Order code	Name	Description
73-6008	Split+	T shaped PCB for breakout boards
75-0045	Split+	T shaped PCB for breakout boards assembled
73-6009	Split Mini+	I shaped PCB for breakout boards
73-6010	Paddle+	with spring loaded terminal blocks for tool free connections

Type	Order code	1+
T-cobbler breakout	73-6008	4.53
Cobbler breakout	73-6009	3.61
Paddle+ breakout	73-6010	8.35
Split assembled	75-0045	4.43

547707



Perma-Proto HAT for Raspberry Pi A+, B+ or 2

The **Adafruit Perma-Proto HAT** is a plug-in daughterboard that is compatible with the Raspberry Pi A+, B+ and Pi 2. The board has a grid of 0.1" prototyping solder holes for attaching chips, resistors, LEDs, potentiometers, etc. to create a versatile and easy to use prototyping area. The holes are connected underneath with traces to mimic solderless breadboards and there are long power strips for +3V, +5V and earth connections. There is also an area where there is broken out nearly every pin on the Raspberry Pi.

- Design a Pi HAT, attach custom circuitry
- Comes with a PCB and a single 2 x 20 GPIO header for Raspberry Pi
- Light soldering is required to attach the header to the PCB

Type	Order code	1+
Perma-Proto HAT	75-0511	4.65

559293

BBC Micro:bit Pocket Sized Codeable Computer

See page 16

Only

£10.49

Order code 75-0115



Pi Camera Modules



Camera Board v2 8MP 3280 x 2464

This camera module add-on board version 2 features a high quality 8 megapixel Sony IMX219 image sensor that is custom designed for the **Raspberry Pi**. The camera sensor has a fixed focus lens and the sensor is capable of producing images of 3280 x 2464 and capturing video at resolutions of 1080p30, 720p60 and 640 x 480p90. Connection between the module and board is via the dedicated Camera Serial Interface (CSI) which is specifically designed for interfacing to cameras, with attachment via a short ribbon cable.



The small size and light weight of this add-on board make it perfect for mobile or other applications where size and weight are important. Suitable applications include CCTV security camera, motion detection, time lapse photography, etc.

- Turn a Raspberry Pi into a high quality still and video camera
- Software supported within the Raspbian Operating System
- Tiny board is just 25 x 23 x 9mm
- Weighs just over 3g

Type	Order code	1+
Camera board	75-0530	19.25

563364



NOIR Camera Board v2 8MP 3280 x 2464



A camera module add-on board version 2 that features a HD 8 megapixel Sony IMX219 image sensor that is custom designed for use with the Raspberry Pi. The NOIR (no infrared) module omits the infrared filter from the lens, increasing sensitivity to the infrared band for IR and low light photography. A fixed focus lens and sensitive sensor gives the capability of taking still images of 3280 x 2464 pixels as well as capturing HD videos of 1080p30, 720p60 and 640x480p60/90.

The module connects to the Pi using the dedicated Camera Serial Interface (CSI) with attachment via a short ribbon cable from a socket on the upper surface of the camera module. The small size and light weight of this module make it perfect for mobile applications and for IR photography, low light photography, monitoring plant growth, CCTV security camera, etc.

- Turn a Raspberry Pi into an IR and low light HD still and video camera
- Software supported within the Raspbian Operating System
- Ideal for twilight conditions
- Tiny board is just 25 x 23 x 9mm
- Weighs just over 3g

Type	Order code	1+
NOIR Camera board	75-0531	19.25

563365



We bring
STEM to life



Cyntech LISIPARO1 LED Ring/Flash for Raspberry Pi Cameras

The LISIPARO1 light ring/flashes from Cyntech gives your Raspberry Pi camera the extra light it needs to capture better images or capture images in interesting new situations. Choose the right light for your camera; the standard camera needs the white light ring while the Noir can use either but really comes into its own when used with the IR ring. They can be used either as a fixed light source or like a traditional flash unit. You can control the duration of the flash, or the brightness of the light. A pair of holes is provided for attaching the Pi camera, and these can also be used to mount the light to other hardware. The IR LED ring allows your Pi Noir to capture images in low light conditions, or even total darkness. Try your hand at time lapse photography, build a security system, or a perhaps a baby monitor.

- Choose between cool white LEDs and IR
- Operating voltage 5V DC
- Only uses 1 x GPIO pin

Type	Order code	1+
White LEDs	75-0042	10.28
IR Leds	75-0043	9.95

Raspberry Pi Robotics



Bit:2:Pi BBC micro:bit Raspberry Pi HAT Adaptor - Fully Assembled

The Bit:2:Pi adaptor allows the BBC micro:bit to connect to, and re-use all those hundreds of Raspberry Pi addon boards and HATs.


Simply plug your micro:bit into the edge connector and the required Raspberry Pi Hat onto the GPIO

connector, then program your micro:bit to control the new board. Most Raspberry Pi boards are very simple to program as they are controlled by simple On/Off signals on the GPIO connector which are easily copied in the micro:bit. We have also used Neopixel hats (eg. Unicorn from Pimoroni) with great success and are happily communicating via I2C as well.

Selecting which micro:bit pin is connected to which GPIO pin, is via a set of configurable jumpers. There is a default set of connections that works for the most common boards, including I2C and SPI connections, but it is a simple matter to unplug a jumper or two, and replace it with a longer wire jumper (4 included) to connect your preferred pins.

Of course, the original code for the Raspberry Pi won't run directly on the micro:bit but with support from our community we will get more and more boards working and with example micro:bit code.

Current boards tested are:
4tronix: PlayHat, Picon Zero, PiStop, motor controllers
Pimoroni: Pibrella, Unicorn pHat/HAT. Explorer, Enviro pHat
Power is supplied to the board and the micro:bit via the micro-USB connector on the side, but there is also an option



to add a battery holder (not supplied) to allow completely wire-free operation.

- Fully assembled and ready to go

Note: BBC micro:bit is not included.

Type	Order code	1+
Bit:2:Pi Adaptor	75-0131	11.29



RPI-Stop Educational Traffic Light for Raspberry Pi

The Pi-Stop is an educational traffic light project for Raspberry Pi. The low cost hardware module is designed to allow you to use your Raspberry Pi to take the first steps into interfacing with the real world. You'll be on the first rung of the Internet of Things ladder as soon as the lights change to green. The brilliant thing about the Pi-Stop is the familiarity of the elements, everyone knows what they are and how they can be used.

The beauty of this kit is that it removes the uncertainty that people face when asked to use hardware with a Raspberry Pi, what components to use, how to connect them, etc. The Pi-Stop makes it easy by plugging directly onto pre-set positions on the Raspberry GPIO connector. This removes the need for bundles of extra cables or wires and because the Pi-Stop does not block unused GPIO pins, keeping them available for other uses. The Pi-Stop can be fitted in four standard locations, allowing up to four Pi-Stops to be controlled independently or combined with other hardware.

The Pi-Stop provides a flexible and non-restrictive way to building understanding through experimentation, providing a simple stepping stone between pure screen-based programming and actually using hardware to interact with the real world. The programming of hardware can first be introduced to students and, at a later stage, the electronics can be introduced - allowing students to understand the control of hardware and then to be able to construct and control their own circuits.

Documentation, guides, tutorials and workshop material are openly available for educational use, and it is encouraged that similar materials can be submitted back for others also to share and make use of.

- Real world hardware makes understanding easier
- Low cost
- Designed for teaching both programming and hardware
- Fully supported with many resources

Note: Raspberry Pi not included.

Type	Order code	1+
Traffic light RasPi	75-0287	2.95



RoboHAT Robotics Controller Board for Raspberry Pi

The RoboHAT is the complete robotics controller for your Raspberry Pi based mobile robot. The board supports all models of Raspberry Pi that have the 40-pin connector (Model A+/B+, as well as Pi 2 and 3 Model B).



The controller board comes fully assembled, no soldering or gluing is required. There are 2x mounting pillars and fixings supplied so it can be easily and securely mounted to your Raspberry Pi.

Amongst the many features of this board are:

- 5V Switching regulator to safely power the robot and the Pi from 7V to 10V batteries (not supplied)
- LED Indication of 5V power status
- High efficiency, dual H-Bridge driver that drives 2 DC motors (or 2 sets of 2 if using paired motors on each side of the robot)
- 6, 5V level shifted GPIO inputs with GVS 3-pin connectors (ground, volts, signal)
- 4, 5V level shifted GPIO outputs with GVS 3-pin connectors
- 4-pin Male header to directly plug in an ultrasonic distance sensor (not supplied)
- I2C Breakout connector (standard 4tronix I2C port)
- Output connectors can be used directly to drive servos

See the Blog entry on the 4tronix website for more information, software and examples.


- Fully HAT specification compliant
- Replacement for the Pirocon
- Programming is fully supported in both Python and Scratch GPIO
- Python library module and examples freely available

Note: Raspberry Pi not included. **Note:** Batteries not included.

Type	Order code	1+
RoboHAT control board	75-0284	19.95



PZM Motor Controller Shim for Raspberry Pi Zero



The PZM Pi Zero Motor Shim is a brilliant way to adding motor control to (almost) any Raspberry Pi project. Although specifically designed for use with the Raspberry Pi Zero, the board can be used with any other Pi. When fitted, the board provides dual H-Bridge control of two DC motors. The board is so small (38 x 16 x 0.8mm) that it can be soldered onto the bottom of the connector (assuming you have added one to your Pi Zero), or you can solder on the female or male headers included in the kit so you can connect and remove it, however you have configured your Pi Zero.

Included in the kit are the ready assembled PZM Shim, 3x screw terminals, 3 x 2 male header, 3 x 2 female header. The board can be powered from an external 3 to 11V supply or, if you are using low power motors, you can use 5V from the Pi. The pzm.py library module provides basic functions for forward, reverse, spin left, spin right, turn left/right forward, turn left/right reverse. Download library and examples from the 4tronix website.

- PZM Shim supplied ready assembled
- Mount with supplied headers
- OR solder directly to bottom of Pi header
- Reverse polarity protection

Note: Raspberry Pi not included.

Type	Order code	1+
PZM Motor controller	75-0286	4.50

Super Alkaline Mercury Free Manganese Batteries

See page 310





PiStep2 Dual/Quad Stepper Motor Controllers for Raspberry Pi

These **stepper motor** control boards are designed for use with all versions of the Raspberry Pi with the 40-pin GPIO connector. The boards are available in **dual** (2 steppers) or **quad** (4 steppers) versions. This neat little board plugs directly into the Raspberry Pi GPIO header and provides 2 or 4 connectors for stepper motors. There are various power options - powered from the Raspberry Pi 5V, micro-USB 5V, from the 2-pin terminal (voltage dependent on motor requirements).



- Fully assembled - no soldering required
- Raspberry Pi Zero form factor
- Each pin has an associated LED to see stepper signals

Note: Stepper motors not included.

Note: Raspberry Pi not included.

Type	Order code	1+
Quad Stepper cont.	75-0289	10.50

565331



Ultimate Initio 4WD Robot Platform for Raspberry Pi with RoboHAT

The **Ultimate Initio** is a 4WD robot platform that is ideal for use with **Raspberry Pi** single board computer. The platform is a doddle to assemble and easy to use and comes with the RoboHAT robotics board and an assembled 2DOF pan-tilt servo assembly, as well as a number of other sensors that make this platform extremely flexible and perfect for a wide range of projects.



The main chassis comes pre-built, with the wheels, motors, gearboxes, battery box, wheel sensors all in place. The powerful 170-size motor is coupled to a high-quality gearbox and there are built-in speed encoders on each side. Each wheel can be individually decoupled from the gearbox so you can run the robot in 1WD, 2WD or 3WD modes if you want.

Kit contents:

- Main Initio chassis (with wheels, motors, gearboxes, battery box, wheel sensors, screws and all mountings)
- RoboHAT Robotics Controller Board **75-0824**
- Pan-Tilt 2DOF assembly with servos (ready assembled)
- 2x IR Obstacle sensors
- 2x IR Line sensors
- 1x Ultrasonic sensor
- All connecting cables as required for above items

Build instructions and example code can be found on the **4tronix** website.

- Ideal for line following projects
- 6-cell battery box with switch (batteries not supplied)
- No soldering or gluing required
- Wiring already assembled
- Fixings for replacement stepper motors (not included)
- Injection moulded from tough ABS
- Includes mountings for additional boards and sensors
- Wheel size ø55 x 28mm
- Chassis size 180 x 120 x 93mm
- Height of top plate with wheels attached 110mm

Note: Raspberry Pi not included. **Note:** Batteries not included.

Type	Order code	1+
Ultimate Initio	75-0282	97.02

565325

Pi Light, Sound & Display Add-on Boards



PiTF+ 3.5" 480x320 TFT Touchscreen Display Raspberry Pi A+, B+ or 2

The **PiTF Plus** is a 480 x 320 3.5in touchscreen TFT that has been

designed for use with the Raspberry Pi 2 and models A+ and B+. The 16-bit colour pixels and resistive touch overlay make this display a valuable addition to any **Raspberry Pi** project, where it can be used as a console, X window port, displaying images or video etc.



A custom kernel package based on Notro's awesome framebuffer work has been created, so that it can be installed over existing Raspbian (or derivative) images using just a few commands.

- High speed SPI interface
- Comes fully assembled and ready to plug into a Pi
- Backlight may be dimmed by PWM
- 2 x 16 'classic Pi' connection GPIO header on bottom
- Use as a display for running the X interface, or pygame

Type	Order code	1+
Touchscreen	75-0493	38.46

559276



PiTF+ 2.8" 320x240 TFT Touchscreen Display Raspberry Pi A+, B+ or 2

The **PiTF Plus** is a 320 x 240 2.8in touchscreen TFT that has been

designed for use with the Raspberry Pi 2 and models A+ and B+. The 16-bit colour pixels and resistive touch overlay make this display a valuable addition to any **Raspberry Pi** project, where it can be used as a console, X window port, displaying images or video etc.



A custom kernel package based off Notro's awesome framebuffer work has been created, so that it can be installed over existing Raspbian (or derivative) images using just a few commands.

- Comes fully assembled and ready to plug into a Pi
- Includes 4 tactile switches soldered on
- High speed SPI interface
- Backlight may be dimmed by PWM
- 40x GPIO pins brought out as an interface
- Use as a display for running the X interface, or pygame

Type	Order code	1+
Touchscreen	75-0495	30.08

559277

Free Delivery*

on all orders over £30 (excl. VAT)
(UK mainland only)

* See Terms & Conditions for full details - www.rapidonline.com/terms



Pibrella Add-On Makes Sounds, Drives Motors, Lights LEDs and More!

The **Pimoroni Pibrella** is a one stop shop of gadgets to interface to your Raspberry Pi (A, A+, B, and B+). It gives you a tactile switch (big red button), 3 x LEDs (Red, Amber, Green), a Piezo speaker, 4 x protected inputs, and 4 x high-power outputs. Each of the 8 inputs and outputs has its own LED so that you can see what's happening. All the on-board gadgets can be used from Python and Scratch with code libraries available from the **pip** Python package installer. For examples and getting started guide, go to pibrella.com, the Pibrella dedicated website.



The high power interfacing is performed by a ULN2003A Darlington array which supports 500mA per channel as long as the total current draw for the entire chip is kept below 500mA. This means you can have one channel draw 500mA or 4 channels draw 125mA each. Of course, that current has to come from somewhere and the standard 1A supply on the B for example hasn't got much to spare. Consider upgrading to the 2A PSU recommended for the B+. With this kind of power at your disposal you can be more adventurous in your projects by including devices like motors, relays, solenoids etc.

The Pibrella is a great tool for learning electronics; make noises, run traffic lights, spin motors, don't press the big red button.

- Tactile switch
- Red, green, and amber LEDs
- Piezo speaker
- 4 x protected inputs
- 4 x high-power outputs


Type	Order code	1+
Pibrella	73-6044	8.15

550308



Unicorn HAT 8x8 RGB LED Matrix for Raspberry Pi Model B+

The **Pimoroni Unicorn HAT 8 x 8 LED matrix** is specifically designed for the new B+ HAT specification (Hardware Attached on Top). The HAT specification uses two dedicated pins on the extended 40-way



GPIO header to tell Linux which drivers to load for whatever device has landed on top of the Pi. The Unicorn provides 64 individually addressable RGB LEDs (WS2812B) which are driven by PWM to create dazzling displays. Or not, you may prefer soft shades and subtle animation. As usual with add-ons for the Pi there is excellent software support with a library and examples in C and Python on Pimoroni's Github repository.

The LEDs can draw up to an amp which isn't much considering they can be turned up to eye-watering brightness (you have been warned) so be sure to use a good PSU with your Pi; 2A is good. If you intend to use them at full brightness then you should consider using a diffuser to protect your eyes.

As it uses PWM on the Pi and GPIO18 it will interfere with analogue audio, HDMI audio isn't affected. The Pibow Coupe cases are ideal, the Pibow Ninja, Rainbow and Timber cases won't do unfortunately. As it uses PWM and GPIO18 on the Pi it will interfere with analogue audio, HDMI audio isn't affected. The Pibow Coupe cases are ideal, the Pibow Ninja, Rainbow and Timber cases won't do unfortunately. Whilst the Unicorn sits neatly on the B+, it won't do that with the B but it's possible to hack it to work, letting B owners enjoy the blinkiness.

- 8 x 8 LED matrix (64 x WS2812B)
- For Raspberry Pi A+ and B+
- HAT compatible for automatic configuration

Type	Order code	1+
8x8 RGB LED matrix	73-6042	17.50

550306

PIMORONI

Piano HAT 13-Key Full Octave for Raspberry Pi A+, B+ or Pi 2

This Piano HAT is a mini musical companion for the Raspberry Pi and features a touch sensitive, 13-key full chromatic octave piano keyboard, plus octave up/down and instrument patch change keys. Using Python it is possible to play music, control software synths as well as controlling midi-enabled hardware synths.



Use the Piano HAT to play .wav samples with PyGame, or create piano-controlled contraptions. An included MIDI example enables music to be played with Sunvox, Yoshimi and others. Includes a PyGame example that includes a few octaves of piano and some drums.

- Compatible with Raspberry Pi A+, B+ and Pi 2
- Comes fully assembled
- 16 LEDs that can light automatically, or be driven with Python
- Output regular MIDI commands via a USB to MIDI adaptor
- Full Python library, documentation and examples

Type	Order code	1+
Piano HAT	75-0514	11.28

559278

Pi Touch Sensing



Capacitive Touch HAT for Raspberry Pi A+ B+ Pi 2

A **capacitive touch** HAT that works with the **Raspberry Pi** models A+, B+ and Pi 2. The HAT has 12x capacitive touch sensors that are broken out to 'figure 8' board connections that can be connected, via crocodile clips and wire, to an electrically-conductive (e.g. metal) object or water-filled (e.g. vegetables/fruit) object, making it possible to create practical and fun controllers for a wide range of projects.



- Similar to the Makey Makey concept
- Works with Raspberry Pi Model A+, B+, or Pi 2
- Comes with a 2 x 20 socket header
- Can be used with Model A or B but requires an extra-tall 2 x 13 header (not included)

Type	Order code	1+
Capacitive touch HAT	75-0508	12.85

559291

How do I ...

Email baskets?
Register Online?
Find invoices?

www.rapidonline.com/schools-faq

Pi Motor & Power Driver Boards



16 Channel Servo HAT/PWM for Raspberry Pi A+, B+ or 2

This HAT adds the capability to control up to 16 servos as well as providing 12-bit PWM of up to 1.6kHz. The module has the features and performance to produce the very specific and repetitive timing pulses required to precisely set servos while reducing the processing load of the Raspberry Pi. For use with Raspberry Pi Model A+, B+, or Pi 2 can be used with the Model A or B with a tall 2 x 13 header instead of the included 2 x 20. Perfect solution for any project that requires a lot of servos or PWM outputs.



- Drive up to 16 servos or PWM outputs over I2C with only 2 pins
- On-board PWM controller will drive all 16 channels simultaneously
- Stack up to 62 modules to control up to 992 servos
- Python library to get up and running instantly
- Supplied with a Servo HAT, a 2-pin terminal block, four 3 x 4 headers and a 2 x 20 socket header

Type	Order code	1+
Servo HAT/PWM	75-0505	15.26

559288

PIMORONI

Explorer HAT Pro for Raspberry Pi A+, B+ and Pi 2

The Explorer HAT Pro is a prototyping board that is compatible with the Raspberry Pi A+, B+ and Pi 2. The board features: 4x buffered 5V tolerant inputs, 4x powered 5V outputs, 4x capacitive touch pads, 4x capacitive crocodile clip pads, 4x coloured LEDs, 4x analog inputs, 2x H-bridge motor drivers, mini breadboard.



- Can supply up to 500mA per channel
- Motor drivers can drive 2x 5V motors bidirectionally with 200mA per channel
- Ideal for driving motors, analog sensors, etc.
- Comes fully assembled

Type	Order code	1+
Explorer HAT Pro	73-6052	17.80

559224



Stepper Motor & DC HAT for Raspberry Pi A+, B+ or 2

This new DC+Stepper Motor HAT from **Adafruit** is a Raspberry Pi add-on that is perfect for any **motion** project, being able to drive up to 4x DC or 2x stepper motors with full PWM speed control. An onboard fully-dedicated PWM driver chip controls both motor speed and direction, with commands coming over via I2C. Up to 32 motor HATs can be stacked together for controlling up to 64 stepper motors



or 128 DC motors (or a mix of the two). The motors are controlled by TB6612 MOSFET drivers with 1.2A per channel and 3A peak current capability and built-in flyback diodes.

- Compatible with Raspberry Pi model A+, B+, or Pi 2
- Polarity protection FET on the power pins
- Small prototyping area
- Thermal shutdown protection
- Can run motors on 4.5VDC to 13.5VDC
- Big terminal block connectors for 18-26AWG wires and power
- Comes with HAT, terminal blocks, and 2 x 20 plain header
- Raspberry Pi and motors are not included

Type	Order code	1+
Stepper motor HAT	75-0512	17.33

559294

Pi Power Supplies & Heat Management



ENER002 Raspberry Pi-mote Single RF Mains Socket

This is a single RF socket only, you will also need the Raspberry Pi (B or B+) and an Energenie Pi-mote GPIO board to create a working system. Once activated, sockets can be switched on or off from up to 30m away using the Pi or manually using the button on the socket and can accommodate any mains appliance up to 3kW.



- Wireless Mains Socket for Pi-mote
- Uses 433.92MHz (not WiFi)
- Control up to 3kW per socket
- Control 4 addressable sockets
- Multiple sockets on one address

Type	Order code	1+
Mains RF socket	73-6015	3.25

548678

Did You Know We Do Robots?

See page 65
www.rapidonline.com

Pi Cases



Raspberry Pi Model B+/2/3 Case in Black or Clear

The **Cynotech Raspberry Pi model B+, 2 and Pi 3 cases** have a wear resistant matt finish while the centre top is highly polished allowing you an excellent view of your Pi with the clear case. The cases include a set of light pipes which transfer the light from the Pi's activity LEDs to the outside of the case so that you always know what the Pi is doing. Available in clear or black.



- Compatible with the Raspberry Pi 3 model
- Raspberry Pi B+ clip fit with optional screw locking (screws included)
- Positive and secure case locking via screws (screws included)
- Available in clear or black
- GPIO 40-pin ribbon cable slot
- CSI camera cable slot
- DSI LCD video cable slot
- Strong and durable ABS plastic
- 50mm VESA mount and wall mount features

Type	Order code	1+
Clear Pi B+/2/3 case	73-6004	4.95
Black Pi B+/2/3 case	73-6017	5.32

547699



Raspberry Pi Enclosure with Fan for B+ & 2

The **Raspberry Pi Enclosure with Fan from Seeed Studio** protects your Pi and keeps it cool with a built-in 30mm fan. Made from clear acrylic the case will house the Pi B+ or the Pi 2.



- Made from 3mm acrylic
- Light and easy to transport
- Good heat dispersion
- Compatible with Raspberry Pi B+/2
- Case size: 95x65.5x34.5mm
- Fan size: 30x30x7mm
- M3 screws and nut included

Type	Order code	1+
Enclosure with fan	75-0393	6.03

560357

PICAXE



PICAXE Chips

PICAXE is a microcontroller system that uses low cost FLASH memory based microcontrollers with a unique, pre-programmed **PICAXE** bootstrap code. This gives a device that may be reprogrammed typically 100,000 times without the need for an expensive and complicated programmer. **PICAXE** is programmed using a simple BASIC language or via the **Logicator** flowcharting software. Windows, Mac and Linux are all supported by the free BASIC software which can be downloaded from www.picaxe.co.uk.

Programming is carried out via a simple USB (**13-0849**) or serial (**13-0847**) cable. In addition to the microcontroller chips, starter, tutorial, and upgrade kits are available to provide a complete **PICAXE** solution. **PICAXE** microcontroller chips are available in 8, 14, 18, 20, 28 and 40-pin versions, giving a choice of the number of input and output lines, and also in several variants which offer differing amounts of memory and extra features so a choice can be made according to project need.

- Suitable for education, industry and hobbyists
- Low cost and simple to use
- Wide range of variants
- Can be programmed using an intuitive graphical flowchart
- Free, easy to use Programming Editor software

NOTE: See also the **PICAXE X2** chips section for the **X2** variant **PICAXE** chips.



Technical specification

PICAXE	Pins	Variant	Lines of memory	Total I/O pins	No. of inputs	No. of outputs	ADC (L-low)	Order code
PICAXE-08M2	8	M2+	800-1800	5	1-4	1-4	3	13-5022
PICAXE-14M2	14	M2	800-1800	11	5	6	7	13-5024
PICAXE-18M2	18	M2+	600-1800	16	1-8	1-8	10	13-5026
PICAXE-20M2	20	M2	80-1800	18	8	8	11	13-5028
PICAXE-28X1	28	X1	1000-2200	22	0-12	9-17	4	13-0862

Variant feature highlights:

M2 variants:	Infra red, servo and ring tone music features	Touch sensor support
	Greater memory and RA	Parallel task processing
X/X1 variants:	Greater memory and RAM	Higher baud rate
	Scratchpad RAM area	Enhanced maths capabilities
	PC, SPI, I2C, UART interfaces	

Type	Order code	1+	25+	100+	250+
PICAXE-08M2	13-5022	2.75	2.64	2.24	2.09
PICAXE-14M2	13-5024	3.46	3.10	3.00	2.91
PICAXE-18M2	13-5026	4.00	3.74	3.55	3.29
PICAXE-20M2	13-5028	3.64	3.39	3.30	
PICAXE-28X1	13-0862	8.31	8.11	8.04	

079611



PICAXE X2 Chips

PICAXE is a microcontroller system that uses low cost FLASH memory based microcontrollers with a unique, pre-programmed **PICAXE** bootstrap code. This gives a device that may be reprogrammed typically 100,000 times without the need for an expensive and complicated programmer.



PICAXE is programmed using a simple BASIC language or by using an intuitive graphical flowchart system, enabling younger students and hobbyists to start generating programs quickly and easily.

Programming is carried out via a simple serial or USB cable which means that a simple project kit is easily assembled. In addition to the microcontroller chips, starter, tutorial, and upgrade kits are available to provide a complete **PICAXE** solution.

PICAXE X2 microcontroller chips are available in 20, 28 and 40-pin versions, giving a choice of the number of input and output lines. Every pin is individually configurable for greater I/O flexibility. These latest designs of the **PICAXE** chip feature increased memory, scratchpad and RAM, plus additional features such as the ability to boot or run programs from I2C memory, additional timers, a SRLatch and additional interrupts.

- Suitable for education, industry and hobbyists
- Low cost and simple to use
- Can be programmed using an intuitive graphical flowchart
- Easy to use Program Editor software

Technical specification

Type	Pins	Variant	Lines of memory	Total I/O pins	No. of inputs	No. of outputs	ADC	Order code
PICAXE-20X2	20	X2	2000 to 3200	13	1 - 16	1 - 16	11	13-5000
PICAXE-28X2	28	X2	4x 2000 to 3200	22	1 -	1 -	11	13-5002
PICAXE-40X2	40	X2	4x 2000 to 3200	33	1 -	1 -	12	13-5004

Type	Part no.	Order code	1+	25+	100+
20-Pin chip	AXE012X2	13-5000	5.45	5.29	5.20
28-Pin Chip	AXE010X2	13-5002	9.05	8.89	8.79
40-Pin chip	AXE014X2	13-5004	9.05	8.89	8.79

180699



PICAXE SMD X1/X2/M2 Chips



PICAXE is a microcontroller system that uses low cost FLASH memory based microcontrollers with a unique, pre-programmed **PICAXE** bootstrap code. This gives a device that may be reprogrammed typically 100,000 times without the need for an expensive and complicated programmer.

PICAXE is programmed using a simple BASIC language or via the intuitive **Logicator** flowcharting software that especially enables younger students and hobbyists to start generating programs quickly and easily. Windows, Mac and Linux are all supported by the free BASIC software which can be downloaded from www.picaxe.co.uk.

Programming is carried out via a simple USB (**13-0849**) or serial (**13-0847**) cable. In addition to the microcontroller chips, starter, tutorial, and upgrade kits are available to provide a complete **PICAXE** solution.

These **PICAXE** microcontroller chips are available in surface mounting 8, 14, 18, 20, 28 and 44-pin versions, giving a choice of the number of input and output lines, and pins are individually configurable for greater I/O flexibility. As well as the standard X1 types, M2 and X2 variants are offered that provide differing amounts of memory and extra features so a choice can be made according to project need.

- Surface mount devices
- Suitable for education, industry and hobbyists
- Low cost and simple to use
- Wide range of variants
- Can be programmed using an intuitive graphical flowchart
- Free, easy to use Programming Editor software

Technical specification

Type	Pins	Variant	Lines of memory	Total I/O pins	No. of inputs	No. of outputs	ADC	Order code
PICAXE-08M2	8	M2	800-1800	5	1-4	1-4	3	13-5036
PICAXE-14M2	14	M2	800-1800	11	5	6	7	13-5052
PICAXE-18M2	18	M2	600-1800	16	1-8	1-8	10	13-5050
PICAXE-20M2	20	M2	80-1800	16	8	8	11	13-5042
PICAXE-28X2	28	X2	4x 2000 to 3200	22	21	21	16	13-5040

Type	Package	Order code	1+	25+	100+
PICAXE-08M2	S0-8	13-5036	2.91	2.86	2.81
PICAXE-14M2	S0-14	13-5052	3.44	3.35	3.19
PICAXE-18M2	S0-18	13-5050	3.60	3.51	3.35
PICAXE-20M2	S0-20	13-5042	3.60	3.51	3.35
PICAXE-28X2	S0-28	13-5040	4.77		


519054

PICAXE

PICAXE-08 Proto Board Kit

The proto board kit consists of a small self-assembly board to allow rapid prototyping of PICAXE-08 circuits.

- The board provides the basic circuit and download connector, with a small prototyping area to allow connection of input and output interfacing circuits
- Supplied as a self-assembly kit of PCB and all parts, excluding the PICAXE-08 chip which is available separately



Type	Order code	1+
PICAXE-08 Proto board	13-1202	2.69

061441

PICAXE

USB Download Cable

The PICAXE USB download cable has been designed to facilitate the downloading of PICAXE programs into PICAXE chips. The cable connects via the USB port on the computer to a 3.5mm jack for connection to the PICAXE. Moulded into the body of the USB connector is a circuit board that contains a USB to serial converter chip that ensures that the data transfer is via a 5V logic level serial connection.

- For use on computers without a serial port
- High quality connectors with 1.8m cable
- Software drivers for the cable assembly are downloadable for free from www.picaxe.co.uk
- Driver versions for Windows XP, XP (64-bit edition), 2003, 2000, ME, 98SE, Vista, Windows 7, Windows 8.1 and Windows 10



Note: There is no operating system support for Windows 95 or NT.

Type	Order code	1+	15+
PICAXE USB Cable	13-0849	22.46	20.46

077630

PICAXE

Microcontroller Project Boards

A choice of project boards suitable for 18-pin microcontrollers.

- The standard board includes Darlington drivers for eight outputs
- The high power board includes four high power FETs and offers the option to add an L293D motor driver IC (order code **82-0192**) to enable the control of two DC motors

Note: The boards are not supplied with microcontrollers.



Type	Order code	1+
Standard board	13-0855	8.89
High power board	13-0860	11.00

077547

PICAXE

T4 Trainer Starter Kit (USB)

This PICAXE starter kit, although designed to meet the T4 technology curriculum in Ireland, is also ideal as a general purpose training aid - serving as a self-contained introduction to the PICAXE system.



The kit is based around the T4 control training board (AXE055) which comes pre-assembled and is supplied with analogue and digital inputs as well as a range of output devices. The training board can be used with any software application that supports the PICAXE hardware, including the free 'PICAXE Programming Editor' and/or 'Logicator' software.

Key features of the T4 Control Training Board (AXE055):

- LED on each output (can be enabled/disabled)
- 7-Segment display output (can be enabled/disabled)
- Piezo sounder output (can be enabled/disabled)
- Servo output connector
- Stepper motor output connector
- 4x Darlington driver buffered outputs
- 2x Reversible motor driver outputs
- LDR light sensor analogue input
- DS18B20 temperature sensor input
- Variable resistor analogue input
- Push switch inputs
- Input, output and power test points

- The trainer starter pack includes both the training board, download cable and a power supply
- The software needed is free, so all extra you need to get started, is a computer
- Board supplied with PICAXE-18M2 microcontroller
- Also available in a bulk pack of 5

Type	Order code	1+
T4 PICAXE trainer	13-1548	74.29
T4 PICAXE trainer x5	13-1546	288.00

526212

PICAXE

Development System

The PICAXE AXE091U development board is compatible with any size or revision of PICAXE chip and allows circuits to be quickly tested using its prototyping breadboard. A PICAXE 18M2 chip is supplied which operates at 32MHz and has 2048bytes of program memory, 512bytes RAM, 512bytes of table memory, 2 PWM channels, I2C, SPI and an internal temperature sensor.



The development board provides connectors for computer downloads and power, as well as simple input, output devices, such as LEDs and switches to get you started faster. Supplied with a PICAXE 18M2 chip, a USB download cable, battery holder, and a CDROM containing software and manuals.

- Supports all 8/14/18/20/28 and 40-pin PICAXE chips
- Large breadboard area (300 holes + 100 power supply holes)
- Regulated power supply or battery powered, with LED power indicator
- 3 LED indicator outputs and 3 switch inputs
- On-board 7-segment display
- LDR and 10kΩ potentiometer analogue inputs
- DS18B20 digital temperature sensor
- Infrared input/output (sensor and LED)
- Keyboard connector (PS2)
- Serial (inverted and true (MAX202 buffered)) RS232 connectors
- Sockets for I2C and SPI memory chips (not supplied)
- Support for DS1307 Real Time Clock (not supplied)

Type	Order code	1+
PICAXE dev kit	13-1550	78.00

547654

Order online

Save time, and place your order at:

www.rapidonline.com



PICAXE-08 USB Starter Kit



This starter kit contains everything required to gain familiarity with the **PICAXE-08** system, using the **PICAXE-08** microcontroller.

The kit includes a **PICAXE** microcontroller, **PICAXE** project board, USB download cable and battery box.

Software may be downloaded from Picaxe.

- Low cost and simple to use
- Program using BASIC or by graphical flowcharts
- Easy to use Program Editor software
- Extensive online documentation and online support forum

Kit contains:


PICAXE-08M microcontroller USB download cable
Proto board and instruction leaflet 4.5V Battery box for 3x AA batteries

Type	Order code	1+
PICAXE-08 USB kit	13-5020	19.00

080318



PICAXE-18 USB Trainer Starter Pack with USB Cable



This Picaxe starter pack contains everything required to gain familiarity with the **PICAXE-18** system, using the **PICAXE-18** microcontroller.

An ideal starter pack for UK development, the kits include a **PICAXE** microcontroller, **PICAXE** project board, USB download cable and a battery box. The project board can be used with any of the software applications that support the PICAXE hardware, including the Logicator for PIC Micros software and / or the free PICAXE Programming Editor.

The training board comes pre-assembled and is ready for use with all the PICAXE-18M2's analogue and digital inputs and outputs. Wires can be soldered directly onto the board, or used with screw terminal blocks.

Software may be downloaded from Picaxe.

- Picaxe Kits are pre-assembled
- Low cost and simple to use
- Program using BASIC or by graphical flowcharts
- Easy to use Program Editor software
- Extensive manuals and online support forum

Requires either 3x AA alkaline batteries (not included), or a regulated 5V DC supply.

Kit contains:

PICAXE-18 microcontroller Battery clip
Standard project board and instruction leaflet USB download cable
4.5V Battery box for 3x AA batteries

Type	Order code	1+
PICAXE-18 USB kit	13-5018	25.32

079665



PICAXE-20 USB Starter Kit



This starter kit contains everything required to gain familiarity with the **PICAXE-20** system, which features the **PICAXE-20M** microcontroller.

The kit includes a project board (unassembled), **PICAXE-20M** microcontroller USB download cable, and battery box.

- USB to serial interface
- Low cost and simple to use
- Program using BASIC or by graphical flowcharts
- Easy to use Program Editor software
- Extensive online documentation and online support forum

Requires either 3x AA alkaline batteries (not included), or a regulated 5V DC supply.

Technical specification

PICAXE-20M microcontroller
20-pin Project board and instruction leaflet
USB download cable
4.5V Battery box for 3x AA batteries

Type	Order code	1+
PICAXE-20 Starter kit	13-0874	33.59

081641




Editor Software CD

The Programming Editor software provides a complete programming environment for generating BASIC programs for the PICAXE.

Programs can be edited, compiled and downloaded to the PICAXE

chips (all sizes) from within the same free software. This software supports both textual 'BASIC' program listings and the generation of programs via graphical flowcharts. Flowcharts can be created and simulated on screen, and then automatically converted into BASIC program listings. The software runs under any Windows operating system (Windows 95, 98, ME, NT, 2000, XP). No other platforms (DOS, Linux, Mac etc.) are currently supported, although Linux is under development.

- Supports flowcharts, BASIC, logic diagrams and assembler code programming.
- Supports on-screen simulation of BASIC and flowchart programs
- Supports serial and USB direct cable downloading of all PICAXE products.
- Has inbuilt BASIC-assembler interpreter so that BASIC programs can be automatically converted into sequential assembler code (requires Serial PIC Programmer)
- Full assembler code development environment with easy to use interface and programmer



Type	Order code	1+
Editor software CD	13-1262	1.86

061483

GENIE Microcontrollers




GENIE is a low-cost microcontroller programming system designed exclusively for schools and colleges. The free, user-friendly flowchart software allows you to add intelligence and control to your new and existing design projects. No separate programmer is required and downloading is via a USB or serial cable.

The heart of the **GENIE** microcontroller system is the microcontroller IC, available in 8, 14, 18, 20 and 28-pin versions. It is possible to run multiple programs at the same time on a single chip and also to run and test programs live on a connected **GENIE** chip.



Microcontrollers Version 1



GENIE is a low-cost microcontroller programming system designed exclusively for schools and colleges. The free, user-friendly flowchart software allows you to add intelligence and control to your new and existing design projects. No separate programmer is required and downloading is via a USB or serial cable.

The heart of the **GENIE** microcontroller system is the microcontroller IC, available in 8, 14, 18, 20 and 28-pin versions. It is possible to run multiple programs at the same time on a single chip and also to run and test programs live on a connected **GENIE** chip.

The chips are designed to work with the **GENIE** flowchart programming software for Microsoft Windows™ and there are free online resources and community website at www.genieonline.com.

- Developed by the authors of **Livewire**, **PCB Wizard** and **Circuit Wizard**
- Free, user-friendly **GENIE** flowchart programming software
- More memory means more commands and better programs
- On-screen monitoring and calibration of digital and analogue signals
- Polyphonic (multi-channel) music support
- Plug & play operation automatically detects a **GENIE** IC when it is connected
- Supports advanced I/O such as events, interrupts and infrared
- Also available is a plug & play USB download cable, which eliminates COM port problems

Note: The **GENIE Design Studio** software is free to download directly from www.genieonline.com. For convenience, **Rapid** can also supply this software on CD-ROM (see **13-6024**).


Technical specification								
Device	Package	Pins	In	Out	ADC	Starts	Memory *	Order code
C08	DIL-8	8	1 - 4	1 - 4	3	2	160	13-6001
C14	DIL-14	14	5	6	2	2	160	13-6002
E18	DIL-18	18	5	9	3	4	2200	13-6004
C20	DIL-20	20	8	9	4	2	160	13-6003
E28	DIL-28	28	8	9	4	4	2200	13-6005

* Approx. no. of commands

Type	Package	Order code	1+	25+	100+	250+
GENIE C08 IC	DIL-8	13-6001	3.23	3.09	2.63	2.46
GENIE C14 IC	DIL-14	13-6002	2.99	2.67	2.61	
GENIE E18 IC	DIL-18	13-6004	3.62			
GENIE C20 IC	DIL-20	13-6003	3.44	3.25	3.03	
GENIE E28 IC	DIL-28	13-6005	5.09	4.97	4.92	



Microcontrollers Version 2



The new version 2 **GENIE** microcontrollers have been designed as replacements for the older version 1 devices. The version 2 MCUs are faster and more powerful and are capable of storing larger flowchart or BASIC programs.

GENIE is a low-cost microcontroller programming system designed exclusively for schools and colleges. The free, user-friendly flowchart software allows you to add intelligence and control to your new and existing design projects. No separate programmer is required and downloading is via a USB or serial cable.

The heart of the microcontroller system are the new version 2 microcontroller ICs, available in 8, 14, 18 and 20-pin versions. It is possible to run multiple programs at the same time on a single chip and also to run and test programs live on a connected **GENIE** chip.

The chips are designed to work with either the **Circuit Wizard 3** software or the **GENIE** flowchart programming software for Microsoft Windows™ and there are free online resources and community website at www.genieonline.com.

- Developed by the authors of **Livewire**, **PCB Wizard** and **Circuit Wizard**
- Free, user-friendly **GENIE** flowchart programming software
- 32 MHz 'turbo' speed mode
- 1-Wire, I2C and serpo support
- On-screen monitoring and calibration of digital and analogue signals
- Plug & play operation automatically detects a **GENIE** IC when it is connected
- Also available is a plug & play USB download cable, which eliminates COM port problems

Note: In order to program these version 2 **GENIE** microcontrollers, either **Circuit Wizard 3** or the free **GENIE** Programming Editor software is required.

Technical specification						
Device	Pins	Analogue inputs	ADC res.	Digital inputs	Digital outputs	Program memory
GENIE 08 8	3	8 bits	1-4	1-4	2	1KB
GENIE 14 14	2	8 bits	5	6	16	10KB
GENIE 18 18	3	8 bits	6	9	16	10KB
GENIE 20 20	4	8 bits	8	9	16	10KB

Type	Order code	1+	25+	100+	250+
GENIE 08 MCU	13-6040	1.96	1.89	1.61	1.50
GENIE 14 MCU	13-6041	2.42	2.15	2.10	
GENIE 18 MCU	13-6042	2.51	2.44	2.33	
GENIE 20 MCU	13-6043	2.71	2.57	2.40	

Type	Order code	1+	15+
USB Download cable	13-6023	13.34	12.88



USB Download Cable

A Plug & Play download cable that allows your computer to talk to a **GENIE** Microcontroller. The cable has a USB connector at one end and a 3.5mm stereo jack at the other.




- Plug & Play download cable
- Allows your computer to talk to a **GENIE** Microcontroller
- USB connector at one end and a 3.5mm stereo jack at the other
- Please see the PDF datasheet for step-by-step details of how to use this cable

Type	Order code	1+	15+
Genie Download Cable	13-6023	13.34	12.88



Serial LCD Kit

The **GENIE** Serial LCD module allows **GENIE**-based projects to display messages on a LCD. The kit includes full instructions on how to construct the LCD module and then explains how to connect to **GENIE** microcontrollers in order to output text and graphics.



- 16 character by 2 row liquid crystal display (LCD)
- Contrast dial for display
- All components included in kit
- A spare LCD control chip (**13-6036**) is also available separately
- Testing mode included


Note: The **GENIE Design Studio** software is free to download directly from www.genieonline.com.

Technical specification			
Order code	Mfrs Part No.	GENIE Serial LCD kit	
13-6026	13-6026	LCD Control chip	
13-6036	LCDDIC-5	LCD Control chip	

Type	Order code	1+	26+
GENIE Serial LCD kit	13-6026	14.88	11.44
LCD Control chip	13-6036	3.00	



8-pin Microcontroller System Kits



GENIE is a low-cost microcontroller programming system designed exclusively for schools and colleges. The free, user-friendly flowchart software allows you to add intelligence and control to your new and existing design projects. No separate programmer is required and downloading is via a USB or serial cable.

Available from **Rapid** are three exclusive kits that have been designed to provide a fun and challenging introduction to the **GENIE** microcontroller system.

13-6009 GENIE 08 Activity kit

This kit provides a great introduction to the **GENIE** system. It allows students to control two LEDs and a piezo sounder for making sounds. These outputs can be made to respond to a push switch (for sensing touch) and an LDR (for sensing light).

13-6011 GENIE 08 Project kit

This 8-pin kit is ideal for adding intelligence to student projects. It is based on an 8-pin **GENIE** 08 microcontroller providing off-board connections for 2 digital inputs (1 of which can also be used for sensing an analogue signal) and 3 outputs (one of which is buffered to provide medium-power output suitable for controlling lamps and small motors).

13-6012 GENIE 08 Jukebox kit

This kit allows students to have fun with 2-channel polyphonic music by making use of **GENIE's** unique ability to play several notes at the same time. Two LED outputs flash in time to the music. A single digital input switch is provided to control the music, such as when creating a musical box project that starts the music playing when the lid is opened.

The kits are designed to work with the **GENIE** flowchart programming software for Microsoft Windows™.

- Developed by the authors of **Livewire**, **PCB Wizard** and **Circuit Wizard**
- Free, user-friendly **GENIE** flowchart programming software
- On-screen monitoring and calibration of digital and analogue signals
- Supports advanced I/O such as events, interrupts and infrared
- The bare PCBs from the kits are also available, enabling the design of custom projects
- Download cables are also available, see **13-0847** or **13-6023**

Note: These kits are supplied with Version 2 **GENIE** microcontrollers. To program them, **Circuit Wizard 3** or the free **GENIE** Programming Editor software is required.

Note: The **GENIE Design Studio** software is free to download directly from www.genieonline.com.

Technical specification		
Order code	Description	Quantity
13-6009	GENIE 08 Activity kit	
13-6040	Genie C08 Microcontroller IC	1
13-6020	Genie C08 activity PCB	1
18-0585	Battery clip	1
18-0564	3x AA Battery holder - studs	1
20-0137	3.5mm Stereo PCB socket	1
22-0107	Tube (60) 8-pin 7.62mm DIL socket	1
35-0200	Uncased piezo transducer	1
55-1790	5mm red LED	1
55-1792	5mm green LED	1
58-0134	Miniature photoresistor	1
62-0358	330R 0.25W CF resistor	2
62-0394	10K 0.25W CF resistor	2
62-0402	22K 0.25W CF resistor	1
62-0418	100K 0.25W CF resistor	1
78-0620	Tactile switch 6 x 6mm height 4.3mm	1

13-6011 GENIE 08 Project kit		
Order code	Description	Quantity
13-6040	Genie C08 Microcontroller IC	1
13-6021	Genie C08 project PCB	1
08-0235	100n 5mm Pitch ceramic disc capacitor	1
11-1400	220µ 10V 85° radial electrolytic	1
18-0585	Battery clip PP3 - end entry	1
18-0564	3x AA Battery holder - studs	1
20-0137	3.5mm Stereo PCB socket	1
22-0107	Tube (60) 8-pin 7.62mm DIL socket	1
47-3130	1N4001 1A 50V Silicon rectifier diode	1
47-3309	1N4148 75V 150mA Signal diode	1
55-1792	5mm green LED	1
62-0358	330R 0.25W CF resistor	1
62-0370	1K 0.25W CF resistor	1
62-0394	10K 0.25W CF resistor	2
62-0402	22K 0.25W CF resistor	1
62-0418	100K 0.25W CF resistor	1
81-0466	BC548B Transistor TO-92 30V NPN TRU	1

13-6012 GENIE 08 Jukebox kit		
Order code	Description	Quantity
13-6040	Genie Microcontroller IC	1
13-6022	Genie C08 jukebox PCB	1
18-0585	Battery clip PP3 - end entry	1
18-0564	3x AA Battery holder - studs	1
20-0137	3.5mm Stereo PCB socket	1
22-0107	Tube (60) 8-pin 7.62mm DIL socket	1
35-0044	PCB mounted piezo transducer	2
55-1790	5mm red LED	1
55-1792	5mm green LED	1
62-0358	330R 0.25W CF resistor	2
62-0394	10K 0.25W CF resistor	1
62-0402	22K 0.25W CF resistor	1
62-0418	100K 0.25W CF resistor	1
78-0620	Tactile switch 6 x 6mm height 4.3mm	1

Type	Order code	1+	5+	25+
GENIE C08 Activity kit	13-6009	4.53	4.17	3.97
GENIE C08 Project kit	13-6011	4.50	4.23	3.94
GENIE C08 Jukebox kit	13-6012	4.43	4.16	3.88

Type	Order code	1+	25+	50+
GENIE L08 Activity PCB	13-6020	1.22	1.13	0.86
GENIE C08 Project PCB	13-6021	1.22	1.06	0.86
GENIE C08 Jukebox PCB	13-6022	0.50		



We bring STEM to life

GENIE

C08 Light Kit

GENIE is a low-cost microcontroller programming system designed exclusively for schools and colleges. The **GENIE C08 Light Kit** is an ideal project kit for introducing students to simple lighting projects, such as an electronic die, a wearable badge or a night-time warning system. The kit is based around the **GENIE C08** 8-pin microcontroller and the **GENIE Design Studio** flowchart programming software for Microsoft Windows™. The kit contains all components required for construction and requires only the download cable (**13-6023**) to connect to the computer for downloading programs.

- Perfect introduction to simple light projects
- PCB also available separately
- Also available in a plug and play USB download cable, which eliminates COM port problems
- Battery power is 3 to 5V supplied by either AA or AAA batteries or by a 3V coin-cell battery
- PCB Mounting holes
- PCB Dimensions 52.5 x 49mm

Note: The **GENIE Design Studio** software is free to download directly from www.genieonline.com. For convenience, **Rapid** can also supply this software on CD-ROM (see **13-6024**).

Technical specification

Component	Qty	Order Code	Component	Qty	Order Code
GENIE C08 IC	1	-	Red LED	7	55-1790
PCB508 Light PCB	1	-	100R resistor	4	62-0946
8-pin DIL socket	1	22-0107	180R resistor	1	62-0352
3.5mm stereo socket	1	20-0137	10k resistor	1	62-0394
Battery clip	1	18-0092	22k resistor	1	62-0402
3 x AA battery holder	1	18-0126	100k resistor	1	62-0418
6 x 6mm switch	1	78-0620			

Type	Order code	1+	5+	25+
GENIE C08 Light kit	13-6029	4.21	3.89	3.70
GENIE Light kit PCB	13-6035	0.89	0.75	0.71

GENIE

14-Pin Microcontroller Project Kit

Featuring the **GENIE C14** microcontroller, this project board is ideal for adding intelligence to design or electronic projects. Simply wire up to the digital or analogue inputs, connect to the low or medium power outputs for a world of microcontrolled magic.

- Developed by the authors of **Livewire, PCB Wizard** and **Circuit Wizard**
- Free, user-friendly **GENIE** flowchart programming software
- On-screen monitoring and calibration of digital and analogue signals
- Supports advanced I/O such as events, interrupts and infrared
- Also available is the PCB board associated with this kit (**13-6030**), enabling the design of custom projects
- Download cables are also available, see **13-0847** or **13-6023**

Note: The **GENIE Design Studio** software is free to download directly from www.genieonline.com. For convenience, **Rapid** can also supply this software on CD-ROM (see **13-6024**).

Type	Order code	1+	5+	25+
GENIE 14-pin project kit	13-6013	3.87	3.51	3.22
GENIE 14-pin PCB	13-6030	1.28	1.14	0.99

GENIE

Microcontroller System Kits 18-pin



This **GENIE Elite** range of electronic kits features the **GENIE E18** microcontroller. The available kits are:

Activity Kit:

This activity kit allows students to experiment with a variety of inputs and outputs. Features built-in speaker, LEDs, switches and an LDR light sensor.

Project Board:

This project board is ideal as a basic board for adding intelligence to design or electronic projects. The analogue or digital inputs and the medium power outputs, together with the driver chip which drives even higher power outputs, make this a powerful design tool.

Motor Board:

This powerful board provides the solution for adding motor control to design projects. Connect a control signal to the analogue or digital inputs and wire up a DC, stepper or servo motor to the outputs for precise forward and backwards control.

- Developed by the authors of **Livewire, PCB Wizard** and **Circuit Wizard**
- Free, user-friendly **GENIE** flowchart programming software
- On-screen monitoring and calibration of digital and analogue signals
- Supports advanced I/O such as events, interrupts and infrared
- Also available are the PCB boards associated with these kits, enabling the design of custom projects
- Download cables are not supplied but are also available, see **13-0847** or **13-6023**

Note: These kits are supplied with Version 2 **GENIE** microcontrollers. To program them, **Circuit Wizard 3** or the free **GENIE Programming Editor** software is required.

Note: The **GENIE Design Studio** software is free to download directly from www.genieonline.com.

Type	Order code	1+	5+	25+
GENIE 18-pin activity kit	13-6014	5.57	5.32	4.94
GENIE 18-pin project kit	13-6015	5.39	5.12	4.73
GENIE 18-pin motor kit	13-6016	7.33	6.94	6.39
GENIE activity kit PCB	13-6031	1.39	1.29	
GENIE project kit PCB	13-6032	1.78	1.58	1.39
GENIE motor kit PCB	13-6033	1.61	1.46	1.32

GENIE

20-pin Microcontroller Project Kit

The **GENIE C20** microcontroller is at the heart of this project board. Features eight inputs, including provision for connection of an analogue sensor and eight medium-power outputs driven by a dedicated driver chip. Adds powerful microcontrolled intelligence to design or electronic projects.

- Developed by the authors of **Livewire, PCB Wizard** and **Circuit Wizard**
- On-screen monitoring and calibration of digital and analogue signals
- Supports advanced I/O such as events, interrupts and infrared
- Also available is the PCB board associated with this kit (**13-6034**), enabling the design of custom projects
- Download cables are also available, see **13-0847** or **13-6023**
- The **GENIE Design Studio** software for programming the **Genie** is available free to download from www.genieonline.com, or for convenience to buy from **Rapid** in CD-ROM format; see **13-6024**

Note: The **GENIE Design Studio** software is free to download directly from www.genieonline.com. For convenience, **Rapid** can also supply this software on CD-ROM (see **13-6024**).

Type	Order code	1+	5+	25+
GENIE 20-pin project kit	13-6017	4.13	3.73	3.49
GENIE 20-pin PCB	13-6034	1.07	0.954	

GENIE

Circuit Wizard v3 Electronics, CAD/CAM, Simulation, Programming Software

Circuit Wizard 3 is the latest version of the revolutionary design software that combines circuit design, PCB design, electronic circuit simulation and CAD/CAM manufacturing - all in one complete package designed exclusively for schools and colleges. By integrating the entire design process, the software provides all the tools necessary to produce an electronics project from start to finish - including on-screen simulation and testing prior to production.

Version 3 of the software features a host of notable improvements, including: new panel design, enhanced component library, new teaching resource centre.

- Available in 5, 10, 15, 20 and 25 user licences - plus site licence and home user licence
- Supports latest (v2) **GENIE** microcontrollers
- Incorporates a suite of powerful CAD/CAM tools
- Full support for Microsoft Windows 8

No. of licences	Order code	1+
5 User	13-6047	311.05
10 User	13-6048	415.08
15 User	13-6049	519.11
20 User	13-6050	623.14
25 User	13-6051	727.17
Site licence	13-6052	831.20
Home user	13-6053	311.05

Need a product urgently?

We can offer a next day, before noon, delivery service
01206 751166

GENIE

14 Audio Kit

The **GENIE 14 Audio Kit** is a project kit that enables the playing of 16-channel MIDI and realistic sound effects through the kits' 50mm loudspeaker. The kit consists of a PCB on to which the components are soldered. All required components, including a 14-pin microcontroller are supplied and the kit is easily assembled by anyone with soldering skills.


To showcase the **GENIE 14 Audio Kit** it is possible to produce two signature projects: the **GENIE Cuddly Creatures** and the **GENIE Rock Star**. The audio PCB and 50mm loudspeaker are also available for purchase separately.

- Uses a **GENIE 14** version 2 microcontroller
- Digital push switch input
- Light sensor input
- Two LED outputs
- 50mm Loudspeaker output
- Two spare low-power outputs

Kit contents

Qty.	Description	Qty.	Description
1x	GENIE Audio PCB	2x	10kΩ resistor
1x	GENIE 14 (14-pin) IC	1x	22kΩ resistor
1x	3x AA battery pack	1x	100kΩ resistor
1x	Battery clip	1x	220µF electrolytic capacitor
1x	50mm loudspeaker	1x	1N4001 diode
1x	14-pin chip socket	1x	BC337 transistor
1x	Download socket	1x	Push switch
2x	330Ω resistor	1x	Light-dependent resistor (LDR)
1x	1kΩ resistor	2x	Green LEDs

Type	Order code	1+	5+	25+
GENIE 14 Audio kit	13-6046	4.77	4.59	4.24
GENIE 14 Audio PCB	13-6044	0.931		
GENIE 14 Loudspeaker	13-6045	0.604		



DFROBOT
DRIVE THE FUTURE


Full range of **DFROBOT** products available online

www.rapidonline.com/DFRobot




Romeo

Ethernet Shield V2.1



Analogue Sound
Level Meter



IOT Module



Heart Rate
Monitor Sensor


and many more ...

Microcontroller Project Kits

RK Education

Blank PCB for RKP18HP High Power Project Board

A blank PCB designed for use with the RK Education RKP18HP High Power Project Board.



Type	Order code	1+
PCB only	70-9014	1.50

DFRobot Arduino Boards & Kits



DFR0100 Beginner Kit for Arduino (Best Starter Kit)

The Arduino Beginner/ Starter Kit is ideal for those who are interested in learning about Arduino and electronics, starting from basic LED control to more advanced environmental sensing, monitoring and actuators.



The kit will guide you through the world of sensing and controlling the physical world using sensors and the Arduino microcontroller via carefully designed projects. It comes with 20 high quality components and 15 project flash-cards which make the kit easy to learn and teach. Also included in the kit is a DFRduino UNO R3 (compatible with Arduino Uno R3), the most stable and commonly used Arduino processor which is 100% compatible with Arduino IDE, together with DFRobot's best selling Arduino prototype shield.

The kit also includes premium quality jumper wires, resistors, LEDs, a 9g servo, an IR remote transmitter and receiver, a relay, a motor, a fan and a potentiometer. Project reference flash-cards with wiring guides of each project help you make it faster and minimize errors. All the components packaged inside the kit are extremely easy to locate and relocate quickly with our customised black labels.


Kit contains:

- DFRduino UNO R3 x1
- Prototyping shield x1
- Jumper cables male/male x30, female/male x10
- Resistor 220R x20, 4.7K x20, 10K x20, 1K x20
- 5mm LED x10
- IR receiver diode x1
- Mini push button x4
- Ambient light sensor x1
- Tilt switch sensor x1
- 8-segment LED x1
- LM35 temperature sensor x1
- Relay x1
- Buzzer x1
- Fan x1
- 130 motor x1
- 10K potentiometer x3
- Micro servo x1
- Mini controller (with CR2025 battery) x1
- Battery holder for 6xAA batteries x1
- 400 tie-point interlocking solderless breadboard x1

Type	Order code	1+
Arduino starter kit	N75-0114	38.95

RK Education

RKPT18 Project Board



RKPT18 prototype board with large prototype area for use with 18-pin PIC and Genie® microcontrollers.

- A low-cost method of prototyping PIC, Genie® and other projects
- Professional double-sided PCB
- Compact design
- Includes software download socket and circuit
- Can be mains-powered
- Large prototype area with high quality plated-through holes
- Empty PCBs are available separately, order code **70-9020**
- Suitable for **Key Stages 4 & A Level** (ages 14 to 18)

Type	Order code	1+
Project board	70-6004	3.68
PCB only	70-9020	0.98



We bring **STEM** to life



DFR0575 Beetle ESP32 Microcontroller

The Beetle-ESP32 Microcontroller is only 35 x 34mm (1.38 x 1.34in.) in size and is a simplified version of FireBeetle-ESP32, specially designed for electronic engineering fans and DIY lovers. It is equipped with 4 analogue ports, 4 digital ports, UART and I2C interfaces, making it a perfect replacement for many physically larger boards.

The microcontroller enables users to directly burn programs via the on-board USB interface and has Bluetooth and WIFI integrated in the microcontroller for supporting more applications.

Features:

- Small size: only 35 x 34mm
- Directly download and debug programs via Micro USB without a programmer
- Large-scale I/O ports with gold plating, easy to twist wire on it or sew on to clothes with wires, no need to solder
- A group of gold plated power interfaces of honeycomb type, convenient to use
- Integrated WIFI and Bluetooth

Specification:

- USB supply voltage: 5.0V
- VIN supply voltage: DC 3.5 to 6.5V
- Processor: Tensilica LX6 dual-core processor (One for high speed connection; one for independent programming)
- Frequency: 240MHz
- SRAM: 520KB
- Flash: 16Mbit
- Wi-Fi standard: FCC/CE/TELEC/KCC
- Wi-Fi protocol: 802.11 b/g/n/d/e/i/k/r (802.11n, high speed can reach to 150Mbps), converge A-MPDU and A-MSDU, supporting 0.4us protecting interval
- Frequency range: 2.4 to 2.5GHz Bluetooth protocol: complies with BR/EDR/BLE standard of Bluetooth v4.2
- On-chip Clock: 40MHz crystal and 32.768kHz crystal
- Digital interface: D2, D3, D4, D7
- Analogue interface: A0, A1, A2, A3
- I2C: 1
- Serial port: 1
- Dimensions: 35 x 34mm

Type	Order code	1+
Beetle ESP32	N75-0217	12.18



KIT0126 Bone Sound Conduction Kit



Bone conduction is a method of sound transmission. Sound is converted into different frequencies of mechanical vibration and transmitted through human skull to the bone labyrinth, inner ear lymphatic transmission, helix, auditory nerve and auditory centre.

NEW

This kit consists of a bone conduction speaker, a speaker driver board and accessories. It is intended to help understand the principles of bone conduction technology, making hearing aids or bone conduction headphones.

The speaker driver board is based on the MAX9814 microphone amplifier and PAM8406 amplifier. The kit includes a potentiometer which has a power switch function making the kit easy to control.

- Operating voltage: 3 to 5.5V DC
- Board wiring pitch: 2.54mm
- Phone cable: 1m
- Speaker cable: 300mm
- Headphone size: 13mm diameter x 5mm height
- Board dimension: 50 x 20mm
- Weight: 36g
- Supplied complete with bone conduction speaker, speaker driver board and 3.5mm earphone cable
- DFRobot type KIT0126

Technical specification

Components	Description
Volume switch	
Power input	3 to 5.5V
AGC switch	Plugged: AGC OFF, Unplugged: AGC ON
Input	Audio
Output	Audio output (Left/Right)
Gain	Gain = VDD, gain = 40dB
	Gain = GND, gain = 50dB
	Gain = vacant, gain = 60dB
A/R	Activate/release ratio, control the AGC activate/release time ratio:
	A/R = GND: activate/release ratio = 1:500
	A/R = VDD: activate/release ratio = 1:2000
	A/R = vacant: activate/release ratio = 1:4000

Type	Order code	1+
Bone conduction kit	75-0203	22.74



KIT0133 Gravity: Arduino Zero to Hero Kit



The DFRobot KIT0133 Gravity: Arduino Zero to Hero Kit comes complete with an online course created by a well-known Australian Robotics Engineer and Teacher: Sanjin Dedić.

The online course is perfect for ambitious beginners and intermediate Arduino users trying to take their circuitry and programming to the next level.

Kit includes:

- DFRduino UNO R3 x1
- USB cable type A to type B x1
- Jumper cables male to male x30, female to male x10
- Resistors: 220R x20, 4.7K x20, 10K x20, 1K x20
- 5mm LED x10
- IR receiver diode x1
- Mini push-button x4
- Ambient light sensors: PT5I850AC x1, GL5528 x1
- 2N3904 transistor x1
- Tilt switch sensor x1
- 8-segment LED x1
- LM35 temperature sensor x1
- Buzzer x1
- 10K potentiometer x3
- Mini controller (with CR2025 battery) x1
- 400 tie-point interlocking solderless breadboard x1, Acrylic breadboard holder for Arduino x1
- Gravity IO expansion shield for Arduino V7.1 x1
- Gravity: analog sound sensor for Arduino x1
- Gravity: digital speaker module x1
- Gravity: digital PIR (motion) sensor for Arduino x1
- 6 DOF sensor - MPU6050 x1
- MicroSD card module for Arduino x1

Specification:

Microcontroller: DFRduino UNO R3
Power supply: 5V USB power
Dimensions: 220 x 165 x 65mm
Weight: 300g

Technical specification

CIRCUITRY ONLY TUTORIALS:

1. LED Button Circuit
2. Potentiometer LED Control
3. Simple Current Amplifier
4. Darlington Bridge Current Amplifier
5. Glow in the Dark Circuit
6. And Logic Gate
7. Or Logic Gate
8. NOT Logic Gate

BASIC TUTORIALS:

9. LED Blink Rate Investigation
10. Using Random To Select LEDs Control Delays
11. Programming Input/Output with Push Buttons

INTERMEDIATE TUTORIALS:

12. Analog Input Demonstrations with Voltage Dividers
13. Photodiodes and LDR in Voltage Divider Light Sensing Circuits
14. Arduino Light Theremin
15. LM 35 Temperature Sensor with Graph Plotting
16. Maxwell Colour Wheel with RGB LED
17. RGB LED Colour Mixer with 3 Potentiometers
18. Microphone Clap Switch
19. Microphone Calibrated Double Clap Switch
20. Sound/Music Reacting Circuit
21. Button Controlled Frequency Generator
22. Piano Circuit with 4 Tones
23. Sound Effects Generator (Fibonacci, Space Guns etc...)
24. Temperature Plotting Program
25. 7 Segment Display Circuit
26. 7 Segment Guess The Number Game
27. Reaction Time Measuring Circuit (using LED and Sound Triggers)

ADVANCED TUTORIALS:

28. Creating Arrays to Store Reaction Time Results
29. Saving Reaction Time Results to SD Card
30. Plotting the SD Card Results in Excel
31. Memory Training Game
32. Infrared Remote Control Circuit
33. Infrared Remote Controlling a Speaker and LED Panel
34. Reading Accelerometer and Gyroscope Values
35. Connecting Arduino to Processing
36. Control LEDs via Computer Mouse (using Processing)
37. Visualising Gyroscope and Accelerometer Values (using Processing)

Type	Order code	1+
Zero to hero kit	N75-0126	60.32



ROB0050 4WD MiniQ Arduino Robot V2.0



This 4WD MiniQ mobile robot kit is especially designed for education and learning purposes. It comes fully assembled and all you need is a PC with Arduino IDE and 4x AA batteries.

This new version of MiniQ 4WD Arduino Robot Kit comes with Arduino Leonardo controller (ATmega32u4) and also integrates modules such as RGB LED, photosensitive diode, infra-red transmitters, infra-red receivers, infra-red line tracking sensors, light sensors, additional buttons and buzzer.

Along with this mobile robot kit, there are 8 lessons for beginners, from entry-level to line-following, obstacle avoidance and remote control. Users can easily grasp the principles by working through the tutorial. All coding and tutorials are open and free to download.

- Lesson 1. Get to Know Your Robot
- Lesson 2. Control Buzzer
- Lesson 3. Light Direction Indication
- Lesson 4. Line-following
- Lesson 5. RGB LED
- Lesson 6. Obstacle Avoidance
- Lesson 7. Encoder
- Lesson 8. IR Remote Control

Specification

- Controller: Atmega 32U4 (Arduino Leonardo)
- Power supply: 4x AA batteries or micro-USB
- Working voltage: 4.5 to 6V
- Driving mode: 4WD
- Max. speed: 79cm/s
- Size: 115 x 110 x 45mm (4.5 x 4.3 x 1.8in.)
- Supplied complete with 1x IR remote controller & 1x micro USB cable
- **DFRobot type ROB0050**

Type	Order code	1+
4WD Arduino robot	N75-0166	80.04

568383



TOY0060 4-Soldering Light Chaser Beam Robot Kit



The DFRobot TOY0060 4-Soldering Light Chaser Beam Robot can help students and novice electronics enthusiasts to learn about subjects like soldering and the basics of an electronic circuit.

The robot, Mr Neon, is designed to look like a three-leg monster whose eyes or tentacles glow in accordance with ambient light level. The stronger the light is, the faster he moves. There is no programming involved and all soldering is intuitive and rookie-friendly, so it is perfect for the novice electronics enthusiast. The kit includes a supply of stickers so Mr Neon's face can be changed to give him various expressions.

Kit includes:

- 1x Light Chaser PCB
- 1x CR1220 battery
- 1x battery clip
- 1x On/Off switch
- 2x transistor
- 2x vibration motor
- 2x photodiode
- 4x 20kΩ resistor
- 1x plastic paper
- 1x plastic tubing
- 1x adhesive sticker
- 1x base sticker
- 1x face sticker set

Type	Order code	1+
Light chase robot kit	N75-0161	11.48

568380



TOY0057 Creator-4Claying Interactive Kit



This 4 Claying electronic DIY kit is a fun-to-play kit that combines the fun of sculpting with ultra-light clay and building interactive circuits around it. It is a great way of helping kids to learn the basics of electronics and to play with a sensor kit in an easy and intuitive way.



The kit contains not only vibrant coloured, non-toxic lightweight modelling clay, but also high quality colour LEDs and motion sensors to bring your sculptures to 'life'.

With up to 5 colours of clay and 2 colours of LEDs, you will be able to create a full colour spectrum and make your creation look fabulous. You can make use of these LEDs as eyes, stars or whatever you want, and use the motion sensor as a trigger. For example, a cat that blinks its eyes when you walk close to it. The PIR motion sensor detects the infra-red heat from people or animals moving close by and produces a switching signal.

Notes for clay:

- Fully knead before use
- Sprinkle with water and continue to knead if the surface is dry
- Keep unused clay sealed to preserve it
- Avoid storing in direct sunlight
- Dry naturally in air
- Do not eat
- Fully dry electronic components, if they get wet
- Slowly pull and plug to replace the LEDs
- If LEDs don't light, check the battery

Type	Order code	1+
Interactive clay kit	N75-0162	21.46

568381



KIT0003 EcoDuino - An Auto Planting Kit



EcoDuino is designed by DFRobot to help you grow plants. By using a series of microcontrollers, sensors and actuators, the EcoDuino system can make your efforts to grow plants much easier. In this system, sensors are used to collect data which can show you plant conditions like temperature, humidity, light intensity, etc. If you want, EcoDuino can message you and tell you how your plants are doing through wireless communications. It will also water your plants automatically when they are thirsty, or at a pre-determined interval.

The only thing you may need to do is manage your EcoDuino system through a PC with a graphic user interface. The cool thing about the EcoDuino is that it is developed based on Arduino which means you can not only program EcoDuino in the Arduino IDE environment but also use any Arduino compatible hardware in your EcoDuino system.

EcoDuino is evolving and has a new enclosure that protects it from water splashes, so it is safe to use beside your plants. It now sports an Atmega32U4 which removes the need for an adapter. Sketches can simply be uploaded via Micro USB just like Arduino Leonardo. Another improvement is that the DS18B20 sensor is now directly supported.

Specification:

- Board power supply: 6 to 12V DC
- Micro controller: Atmega32U4 (Bootloader: Leonardo)
- 4 Analog I/O ports, 5 Digital I/O ports
- Terminal for interfacing a Carbon rod (Soil moisture sensor)
- Terminal for interfacing a DS18B20 temperature sensor (Soil temperature sensor)

- Terminal for interfacing a motor or a solenoid valve
- Potentiometer to set the threshold soil moisture value of watering
- Xbee slot
- Micro USB
- 3.5mm screw terminal
- Board dimensions: 75 x 50mm
- Diving pump power supply: 4.5 to 12V DC
- Pumping head: 200cm
- Flow capacity: 100 to 350L/H
- Power range: 0.5W to 5W
- Pump dimensions: 38 x 38 x 29mm
- Pump weight: 125g

Type	Order code	1+
Auto plant kit	N75-0137	42.92

568379



KIT0111 Gravity: Starter Kit for Arduino



The Gravity Arduino Starter kit is a plug & play electronics toolkit that provides Arduino beginners and makers with the easiest experience of learning and playing with the Arduino platform.

The kit includes a DFRduino UNO R3 microcontroller, which functions exactly the same as Arduino UNO, and 12 most popular and interesting electric components and sensors. With the IO expansion shield, sensors can be connected directly onto the board without jumper wires or bread-board. The sensors in the kit belong to DFRobot's Gravity Series and are built highly modularised and interact with microcontrollers via a 3-pin header. Moreover, different types of sensors can be easily identified by the logo printed on the back of the PCB board. All components included in the kit are fully compatible with Arduino microcontrollers.

The Gravity Starter Kit also includes a tutorial, which aims to help Arduino learners understand Arduino programming. The tutorial goes through the installation of the software, the Arduino IDE, and its programming language, then teaches you how to build electric circuits, how to use different electric components and their function. It also includes instructions for building projects, from lighting up an LED, to using multiple components to making a real project such as 'Fire Alarm' or 'Weather Station'. The tutorial is full of graphics and is written in such a way that anyone can build their own project.

Specification:

- Microcontroller: DFRduino UNO R3
- Power supply: 6x AA batteries or 6 to 12V AC power adapter
- Dimensions: 220 x 165 x 65mm
- Weight: 300g

Type	Order code	1+
Gravity for Arduino	N75-0111	42.95

568375

Order online

Save time, and place your order at:

www.rapidonline.com



Bluetooth 2.0 Modules For Arduino

These DFRobot Bluetooth 2.0 modules are ideal for use with Arduino microcontrollers.


- **TEL0026** is compatible with the APC220 communication interface and can be directly used in I/O Expansion Shield, Romeo, XBoard, etc. It uses either a 3.5 to 8V DC or a 3.3V DC/50mA power supply
- **TEL0023** can be plugged into the Arduino controller using the XBEE base for Bluetooth wireless control. It uses a 3.3V power supply
- Both modules use the CSR BC417143 chip and operate at 2.4 to 2.48GHz on the unlicensed ISM band.

Type	Order code	1+
Bluetooth 2.0 V3	75-0208	15.54
Bluetooth 2.0 Bee	75-0209	16.12

NEW



TEL0108 Bluetooth Audio Receiver and Playback Module (Bluetooth 4.0)



This Bluetooth 4.0 audio receiver module also includes a USB port and a TF card slot. With its pre-amp level output, it can drive headphones or a 3W speaker directly. You can also add an active power amplifier and connect a loudspeaker for more volume.

The module supports MP3, WMA, WAV and lossless FLAC audio formats. It supports playback from either a TF card or USB flash drive or via Bluetooth. All playback is controlled by push-buttons and the built-in sound equalizer can be adjusted to your favourite settings.

With its compact size and simple 5V DC power requirement, this is an ideal module to add a Bluetooth feature to your car or turn an old hi-fi loudspeaker into a wireless Bluetooth speaker.

NEW

- Power supply: 5V DC (MicroUSB connector)
- Audio decoding: MP3, WMA, WAV, FLAC
- Audio input: Bluetooth, USB, TF card
- Dimensions: 40 x 53mm
- Weight: 12g
- **DFRobot type TEL0108**

Type	Order code	1+
Bluetooth audio	75-0204	11.48



TEL0002 Bluetooth Adapter Mini

This version 4.0 Bluetooth adapter has a bandwidth of approximately 3Mbps and is widely used for small file transfer (less than 10MB) for pictures, ring tones, e-books, manuscripts, etc. The device does not include any drivers or software, however, you shouldn't need any as it supports the native Windows Bluetooth stack (Windows XP, Vista, 7). Plug it in and Windows should handle the rest.



Bluetooth is a type of wireless network transmission technology originally used to replace infra-red. Compared with infra-red technology, Bluetooth can transmit data without needing a clear line of sight and the transmission distance is greater. Bluetooth technology is ideal for low power digital devices to share data with each other, e.g. mobile phones, hand-held computers. Bluetooth devices can also be used to transmit sound, e.g. Bluetooth headsets.

Specification:

- Bluetooth standard 4.0
- USB interface: USB2.0 standard
- Operates in the 2.4 to 2.483GHz frequency band using FHSS (Frequency Hopping Spread Spectrum) technology
- Operational range in open space approx. 20m
- Intuitive software user interface, without complicated settings
- For Win7, Win8, Win10, WinXP, Mac OS X operating system
- Sensitivity <-85dBm
- Data transfer rate up to 3Mbps
- **Features:**
- PC/Mac: Bluetooth dial-up internet access (subject to mobile phones and other devices with Bluetooth)
- PC: Bluetooth wireless local area network
- PC: Bluetooth wireless fax (computer must be equipped with fax software)
- PC/Mac: Bluetooth File Transfer
- PC/Mac: Bluetooth wireless data synchronization
- PC: Bluetooth Virtual Serial Port
- PC: Bluetooth wireless printing
- PC/Mac: Bluetooth Human Interface e.g. Bluetooth mouse and Bluetooth keyboard
- Bluetooth serial port with the computer, microcontroller, Basic Stamp 2, DF-Bluetooth Bluetooth module, Roboduino or Arduino controller connection, to achieve Bluetooth wireless remote control

Type	Order code	1+
Bluetooth 4.0 adaptor	N75-0206	2.90

NEW

Arduino



What is Arduino?

Arduino is an open-source single board microcontroller platform. The boards are pre-assembled and the software can be downloaded for free. It makes using microcontrollers much easier by mapping the inputs/outputs and breaking them out to defined headers.

Who is it for?

It is intended for artists, designers, hobbyists, and anyone interested in creating interactive projects. The amazing community support on the Arduino forum means it's suitable for new and advanced users alike.

What can it be used for?


The Arduino can essentially act as the brain of your project. Use sensors to feed data into the Arduino's inputs and the outputs to trigger the required outcome. You could use a temperature sensor to monitor the temperature and have the Arduino activate an output such as a fan when the desired temperature has been reached.

How do I start?

The official Arduino Starter Kit below (**73-4642**) is an ideal place to start. It contains a book with lessons to follow to teach you the basics. If you prefer to go your own way, why not grab the most popular board, the Uno (**73-4440**) and hit the Arduino forum and find something that inspires you!



Small Form Factor Development Boards



Arduino is an innovative and exciting open source prototyping platform that is based around hardware and software that is easily obtainable and easy-to-use. To further make things easier, Arduino provide an open-source and easy-to-use Integrated Development Environment (**IDE**) that enables the writing of code and uploading of code to the board.

- Arduino Nano v3
- Arduino Micro
- Arduino Mini with pin headers

Type	Order code	1+
Nano	73-4448	13.26
Micro	73-4614	13.28



ARDUINO CERTIFICATION

Take the Arduino Fundamentals exam to officially certify your knowledge of programming, electronics and physical computing.

To learn more contact the **Education Team** at Education@RapidOnline.com



Order code **73-4642** **£59.16**

Starter Kit including Uno Board

This starter kit serves as a hands-on introduction to the basics of the Arduino system. Using the accompanying 170-page project book and the comprehensive kit contents, you will learn to build useful, creative projects. Beginning with the basics of electronics and progressing to more complex projects, the kit will enable control of the physical world through sensors and actuators.

The contents of the Arduino starter kit is listed below:

Qty	Description	Qty	Description
1	Arduino projects book (170 pages)	1	Small DC motor 6/9V
1	Arduino UNO board Rev. 3	1	Small servo motor 1USB cable
1	Piezo capsule [PKM17EPP-4001-B0]	1	Breadboard
1	H-bridge motor driver [L293D]	1	Easy-to-assemble wooden base
2	Optocouplers [4N35]	1	9V Battery snap
5	Transistor [BC547]	70	Solid core jumper wires
2	MOSFET transistors [IRF520]	2	Stranded jumper wires
5	Capacitors 100nF	6	Photoresistor [VT90N2 LDR]
3	Capacitors 100µF	3	Potentiometer 10kΩ
5	Capacitor 100pF 10Pushbuttons	5	Diodes [1N4007]
1	Temperature sensor [TMP36]	3	Transparent gels (red, green, blue)
1	Tilt sensor	1	Male pins strip (40 x 1)
1	Alphanumeric LCD (16 x 2 characters)	20	Resistors 220Ω
1	LED (bright white)	5	Resistors 560Ω
1	LED (RGB)	5	Resistors 1kΩ
8	LEDs (red)	5	Resistors 4.7Ω
8	LEDs (green)	20	Resistors 10Ω
8	LEDs (yellow)	5	Resistors 1MΩ
3	LEDs (blue)	5	Resistors 10MΩ



KEYBOARD INSTRUMENT - play music and make some noise with this keyboard

DIGITAL HOURGLASS - a light-up hourglass that can stop you from working too much

MOTORIZED PINWHEEL - a colour wheel that will have your head spinning

ZOETROPE - create a mechanical animation you can play forward or reverse

CRYSTAL BALL - a mystical tour to answer all of your tough questions

KNOCK LOCK - tap out the secret code to open the door

TOUCHY-FEEL LAMP - a lamp that responds to your touch

TWEAK THE ARDUINO LOGO - control your personal computer from your Arduino

HACKING BUTTONS - create a master control for all your devices!

The projects that are covered in this kit, using the accompanying book, are:

GET TO KNOW YOUR TOOLS - an introduction to the concepts you'll need to use this kit

SPACESHIP INTERFACE - design a control panel for your spaceship

LOVE-O-METER - measure how hot-blooded you are

COLOUR MIXING LAMP - produce any colour with a lamp that uses light as an input

MOOD CUE - clue people in to how you're feeling

LIGHT THEREMIN - create a musical instrument you play by waving your hands



Open-Source Single Board Computer Boards

Arduino is an innovative and exciting open source prototyping platform that is based around hardware and software that is easily obtainable and easy-to-use. To further make things easier, Arduino provide an open-source and easy-to-use Integrated Development Environment (IDE) that enables the writing of code and uploading of code to the board.



The main building block of any Arduino project is the **Arduino board**. They are available in 8-bit and 32-bit MCU versions and are able to read inputs, such as light, proximity or air quality from a sensor, or an SMS or Twitter message, and process it into an output for example activating a motor, turning on a light, publishing content online or triggering external events.

The **Arduino** range has revolutionised electronics by providing a number of **open source** standard designs. These designs are the starting point for complete ecosystems of hardware, software and tutorials dramatically shortening the time taken to develop even quite complex systems. Our collection of Arduino standard boards includes the popular types including **UNO**, **YUN** and **MEGA**.

- Inexpensive and flexible hardware
- Simple programming environment
- Cross-platform
- Open source and extensible hardware and software

Type	Order code	1+	5+
Uno board	73-4440	16.60	
Leonardo board	73-4441	15.02	14.73
Uno SMD board	73-4443	14.24	
Due board	73-4445	26.44	25.11
Mega2560 board	73-4450	28.01	

563355



Motor & Servo Driver Boards

The **Arduino Motor and Servo Driver Shields** will help you bring movement into your next Arduino project. Whether you're building a robot, animatronics or maybe a motorised camera dolly, there will be a board in this collection to suit your needs.



Technical specification

Order code	Mfrs. Part no.	Features
73-4455	A000079	L298 2 x H-bridge shield, TinkerKit compatible
73-4497	E000003	4 x H-bridge shield, plus 2 x 5V servo channels
73-4526	KA03	L298 2 x H-bridge shield, self assembly

Type	Order code	1+
Motor shield rev.3	73-4455	18.00
Mtr./strp./srv shield	73-4497	20.20
Motor shield kit	73-4526	13.78

556650



The MKR IoT Bundle Learn by Making 5 IoT Projects

The **MKR IoT Bundle** is a kit based around the **MKR1000**, and is a great way to get started with developing projects involving the **Internet of Things (IoT)**.



The best way to learn is by doing, and the bundle includes everything you need to build five creative IoT projects, walking you through the basics of using the **Arduino MKR1000** for IoT applications, following step-by-step online tutorials on the Arduino Project Hub online platform.

The **MKR IoT Bundle** is based around the **MKR1000**, a powerful and feature-rich board that combines all the functionality of the **Zero** and the **Wi-Fi Shield**, in the compact MKR form factor. The whole bundle has been designed to enable makers to add Wi-Fi connectivity to their IoT designs with minimal prior networking experience.

The 5 experiments you can make:

- I Love You Pillow
- Puzzle Box
- Pavlov's Cat
- The Nerd
- Plant Communicator
- External 5V supply via USB port
- Runs with or without the LiPo battery connected
- Limited power consumption
- Supports certificate SHA-256
- 32 bit ARM technology
- 3.3V Operating voltage
- Microusb connector

Caution: The MKR1000 runs at 3.3V. The maximum voltage that the I/O pins can tolerate is 3.3V. Applying voltages higher than 3.3V to any I/O pin could damage the board.

Type	Order code	1+
MKR to IoT bundle	73-4845	57.35

566447



ARDUINO

EVERYTHING STUDENTS
NEED FOR OVER 25
EXCITING PROJECTS
THAT EXPLORE
INTERACTIVITY,
PROGRAMMING,
ELECTRONICS,
AND MECHANICS

Arduino CTC 101

£1277.83

Order code 73-4463

CTC stands for **Creative Technologies in the Classroom** and is a modular STEM program consisting of a toolbox with more than 25 projects and easy to assemble experiments, an online platform, and guided teacher support.

What does CTC 101 include?

- **Toolbox:** More than 700 components to suit a class with up to 30 students
- **Online platform:** Access to the Arduino Education Learning Management System with step-by-step instructions and lessons for more than 25 hands-on experiments based on themed modules.
- **Support:** Guided educators training, live webinars, and forum monitored by Arduino Education experts.

What is the Arduino Education Learning Management System?

The online platform helps students get started with programming, electronics and building fully functional, interactive projects under the guidance of teachers. Adapt your lesson plans with more engaging and creative techniques and integrate the latest technologies into your curriculum. The content and class dynamics are specially designed to enhance students' problem-solving and teamwork skills in a collaborative environment.

What is in the Toolbox?

Six Arduino 101 boards

One of the most powerful Arduino boards for Education, it includes wireless communication (Bluetooth) and an integrated IMU (Inertial Measurement Unit). They are programmable, able to read inputs (e.g., light on a sensor) and control outputs (e.g., activating a motor).

Six Arduino Education shields

Add-on boards that connect to the Arduino 101 and Uno boards to extend their functionality. The Education Shield is a custom-made shield designed by Arduino Education specially tailored for educational purposes to enable quick and easy learning while building projects.

10 mini breadboards

Used to make circuits easier to build. They can be either attached on top of the Education Shield or used separately to connect other components.

Set of electronic components

Used to create interactive electronic circuits, includes resistors, potentiometers, LEDs, push buttons, capacitors, and diodes.

Set of plug and play modules

Sensors and actuators with all the necessary components onboard so they can be connected to the Education shield board directly. Modules include a joystick, light and tilt sensors, and an infrared array.

Set of sensors and actuators

Sensors include light, knock, touch / capacitive, and infrared. Actuators include, standard and continuous servo motors.

Set of batteries

Includes both 9V and 1.5V batteries, and 4-slot and 8-slot battery holders.



Media and storage

Includes webcam, SD card and a speaker. The Education Shield features an SD card reader and an audio connector.

Set of cables

Includes all the cables needed such as USB cables, jumper wires, module cables, battery snaps, alligator cables and single core wires.

MDF parts

Laser-cut MDF parts can be used for 10 different projects.

Storage and sorting boxes

Electronic components can be sorted inside boxes based on their functions and sizes. After MDF parts are removed from their frames, they can be stored in the resealable storage bags to keep them organized for later use. The sorting box with dividers can be used to organize small components.

Arduino Science Kit Physics Lab

£144.90

Order code 73-4865

Developed in partnership with Google, the Arduino Science Kit Physics Lab is an Arduino-based physics lab, fully compatible with Google Science Journal available on Android.


Aimed at students in KS3 working in small groups of 2 or 3, the Physics Lab provides a hands-on experience exploring forces, motion and conductivity.

What does Physics Lab include?

Everything comes in a handy storage box for future use, with all the necessary parts to assemble and conduct experiments. The kit features a range of sensors to measure light, temperature, motion, magnetic fields, and most importantly, full access to online course content for teachers and students alike. You'll just need to provide a few essential classroom supplies (pencils, rulers, etc.) and a LiPo battery or a Power bank.



1x Arduino MKR WiFi 1010	1x Hook-and-loop Velcro™ strap
1x Arduino Science Carrier Board	1x Hook-and-loop Velcro™ dot
1x PCB encoder	2x PCB sticks
1x Arduino Light Sensor with Grove Connector	8x M3 screws
1x Arduino Temperature Sensor with Grove Connector	8x M3 bolts
2x Grove Cable 20cm - universal 4-pin connector	4x Rubber bands
2x Double-ended cable: crocodile clip/banana plug (50 cm)	4x Small silicone gaskets
2x Double-ended cable crocodile clip/banana plug (20 cm)	2x Big silicone gaskets
1x Mini slinky metal spring	2x Silicone standoffs
1x Magnet	1x Flat micro USB cable



Physics Lab Experiments

ELECTROMAGNETISM AND THERMODYNAMICS

- **Electronic Fortune Teller:** Investigate resistivity and voltage of different materials.
- **Buzz Wire:** Steadiest hand wins! Build a conductive 'maze' and then try to avoid the buzzer as you guide the loop around your course.
- **Haunted House Theremin:** Did you hear that? Make paranormal noise with a magnet.
- **Thermo Magic Show:** It's not magic, it's science! Learn about how different materials conduct or insulate heat.

KINETICS AND KINEMATICS

- **The Drop Zone:** Can you slide faster than your friends? Explore gravity and measure the acceleration of your Arduino board.
- **The Gravitron:** Scream if you want to go faster! Learn about rotations per minute, circular motion, the force required to spin this ride, and the relationship to centrifugal forces.
- **The Pirate Ship:** Captain the ship and test the oscillation of a pendulum.
- **The Ejection Seat:** 3... 2... 1... Ignition! Make your board bounce to learn about harmonic motion.
- **The Spherotron:** Don't get dizzy... Learn more about potential energy and motion.



GIVES A ZEST FOR LEARNING!



WHAT IS ORANGEPIP?

See your projects grow with Orangepip – a distinctive range of open source boards which offer a colourful introduction to coding and prototyping. Based on the ATmega328 and ATmega2560 microcontrollers, the Orangepip boards are fully compatible with Arduino shields, sensors, accessories and software – giving users access to the global Arduino community of makers and projects.

The boards themselves are rich with features, including 16MHz oscillator, ATmega16u2 for serial conversion, 14 digital GPIO I/O pins (Kona328) and 54 I/O pins (Mega2560), quick reset buttons and machine screw holes. The high performance ATmega 8-bit AVR RISC-based microcontrollers give Orangepip users enough power and memory to store and run multiple lines of complex code.



Kona328

The Orangepip Kona328 is an Arduino UNO compatible development board that is based around the ATmega328 microcontroller. The board features 14x digital I/O pins (six of which may be used as PWM outputs), 6 analog inputs and a 16MHz crystal oscillator. The board is simple to use, just requiring connection to a computer via USB to get started.

Only
£8.58
per board when
bought in a
classpack
Almost half the price
of an Arduino Uno!

Only
£11.95
Order code 75-0550
Individually

Only
£128.72
Order code 75-0592
Class Pack of 15

Mega2560

The Orangepip Mega2560 is an Arduino Mega2560 compatible development board that is based around the ATmega2560 microcontroller. The board features 54x digital I/O pins (14 of which may be used as PWM outputs), 16 analog inputs, 4x UARTs (hardware serial ports) and a 16MHz crystal oscillator. The board is simple to use, just requiring connection to a computer via USB to get started. The Orangepip Mega2560 is also compatible with shields designed for the Arduino Mega2560.

Only
£21.61
Order code 75-0551
Individually

Only
£195.86
Order code 75-0593
Class Pack of 10

BUILD YOUR OWN ARDUINO!

Orange pip Segments328

- An Arduino compatible board you can use in your own projects.
- Test your soldering skills!
- Understand the components needed to support a microcontroller.

SINGLE

£11.95

Order code 75-1200

CLASSPACK OF 15

£90.00

Order code 75-1201




ORANGEPIP SEGMENTS328 BUILD YOUR OWN ARDUINO KIT

You may well be familiar with an Arduino board and aware of all the clever things it can help you to do. But how many people understand how the Arduino works? Do you know what components make up the “magic” box?

This Segments328 kit from Orange pip will let you into the secret - and will encourage you to develop your soldering skills in the process.

Ideal for students in higher or further education, the Build Your Own Arduino Kit includes all the through-hole components required. Just follow the easy-to-understand instructions to produce your own fully-programmable open source prototyping platform.

All you need is access to a soldering iron and solder, cutters and pliers and ideally a multimeter and you're good to go.



Contents includes:

- 1 Orange pip Segments328 PCB
- 1 x 16MHz crystal
- 1 ATmega328 microcontroller
- 1 Dual in line socket
- 1 Tactile switch
- 1 Red LED
- 1 Green LED
- 1 x 6-pin dual row header
- 2 x 8-pin single row sockets
- 2 x 6-pin single row sockets
- 1 ISB socket
- 1 Power supply jack socket
- 1 x 10K resistor
- 2 x 330R resistors
- 2 x 1K resistors
- 2 x 47µF electronic capacitors
- 1 x 1N4007 diode
- 1 x 7805 voltage regulator
- 1 x 7133 voltage regulator
- 1 PTC resettable fuse
- 5 x 0.1µF ceramic capacitors
- 2 x 22pF ceramic capacitors

Order code
73-4866

£1,141.00



AKX00015 CTC GO! Core Module

The Arduino CTC GO! core module is an educational program that consists of several modules that can be combined to teach different STEAM (Science, Technology, Engineering, Arts, and Mathematics) subjects.

The modules are:

Toolbox: All the materials to build several guided experiments and projects per module for a class with up to 24 students.

Online Platform: Access to the Arduino Education Learning Management System with step-by-step instructions and lessons for 24 students and 3 teachers.

Premium Training and Support: Online welcome training webinar with an Arduino Education expert, training video lessons explaining concepts that the educators will use with the students, extra knowledge video pills which expands the content of the lesson plans and a support email to get the assistance of an education expert.

With the Core Module you will go through the foundations of CTC and build 8 exciting projects based on teamwork and learning by doing activities.

- The program is tailored for ages 14 to 17
- Additional information is available online
- Discover the potential of the Arduino CTC GO with the WHACK-A-MOLE



Order code
73-4867

£1,499.00

AKX00002SL CTC 101 - SELF

The Arduino CTC 101 is a modular STEAM program consisting of a toolbox with 26 projects and easy to assemble experiments, an online platform, and guided educators support.

Creative Technologies in the Classroom 101, or CTC 101, is a 5x module STEAM program, tailored for students ages 13 to 17. It is the flagship Arduino Educational Program for schools. CTC 101 uses "project-based" learning methodology. Students are introduced to the foundations of programming, electronics, and mechanics through series of playful, well-documented projects and easy-to-assemble experiments.

The CTC 101 has been certified by the Finish Kokoa Education Standard that guarantees high educational value and robust pedagogical design on global learning.

Toolbox: Boards, shields and components for a class of up to 30 students, and for the educators to get trained. More than 700 components for a class.

Online Platform: Access to the Arduino Education Learning Management System with step-by-step instructions and lessons for 26 experiments based on themed modules.

Support: Self-administered training, onboarding webinar, and forum monitored by Arduino Education experts.

- Tailored for students ages 13 to 17
- Additional information is available online
- You can also download the full brochure



AKX00004 Engineering Kit

The Arduino Engineering Kit brings together the power of the Arduino MKR1000 with MATLAB and Simulink.

The kit is intended for students, educators and makers who want to learn and/or teach the more advanced concepts in engineering. The kit covers system modelling, controls, image processing, robotics, signal processing, among many others. Concepts are not covered at an advanced level.

The Arduino Engineering Kit includes three cutting-edge Arduino-based projects so that students can learn fundamental engineering concepts, key aspects of mechatronics, and MATLAB and Simulink programming. These projects will challenge them intellectually and help them develop physical engineering skills — and they're also fun to do.

Self-Balancing Motorcycle

This motorcycle will manoeuvre on its own on various terrains and remain upright using a flywheel for balance. It's very exciting to build and to see in action.

Mobile Rover

This vehicle can navigate between given reference points, move objects with a forklift and much more. It's very fun to make and use.

Whiteboard Drawing Robot

This amazing robot can take a drawing it's given and duplicate it on a whiteboard. It's most impressive.

The Arduino Engineering Kit is built on its own education Learning Management System (LMS) with step-by-step instructions and lessons.

The content of this kit is divided into six chapters, featuring a short introduction, a getting-started guide for the tools that will be used, a concepts section, and finally the projects themselves. Users will receive access to the online platform for one year and can purchase additional licenses to extend platform access.

The online platform will help students learn fundamental engineering concepts, key aspects of mechatronics, and MATLAB and Simulink programming.

The kit comes in a super-sturdy hard plastic, stackable box that will provide years of storage and reuse. Inside the box is an easy-to-use Arduino MKR1000 board, several customised parts, and a complete set of electrical and mechanical components needed to assemble all three projects.

In addition to the state-of-the-art, high-quality, open-source hardware provided, after registering online, the student will have access to a dedicated e-learning platform and other learning materials. Additionally, they are granted a one-year individual license for MATLAB and Simulink. This provides them with hands-on experience in system modelling and embedded algorithm development.

- Based on the Arduino MKR1000 SBC
- Includes motor shield and IMU shield
- Comprehensively equipped kit
- Great as a practical resource for demonstrating engineering concepts
- For full details visit www.rapidonline.com



Order code
75-0999

£143.87



10201004 Seeeduno V4 Arduino Compatible Board with Upgrades

The **Seeeduno v4.0** is an open source development board based around the **ATmega328P-MU** MCU. The board inherits all the features of the Arduino **Duemilanove** and **Uno** but also adds some of its own. The **Seeeduno** has pin layout compatibility with the Duemilanove and Uno, as well as compatibility with the Duemilanove's screw holes and board dimensions. The board features upgrades that improve performance and useability such as micro-USB to keep a low profile, switchable 3.3 and 5V DC input and solder pads for all GPIOs.



Seeed provide technical documentation, example projects and software libraries on their product pages.

- Easy-to-use development board
- 14x Digital I/O pins
- ICSP for the ATMEGA16U2 USB to serial chip
- Micro-USB instead of USB type B

Type	Order code	1+
Seeeduno V4	75-0401	17.49



110060024 Grove Starter Kit V3 for Arduino

The **Grove Starter Kit for Arduino from Seeed Studio** gets you off to a flying start on your next project. It includes 10 of their most popular Grove modules, but what is Grove? Seeed describe it as "a modular electronic platform for quick prototyping", where each module has a specific function. You take a building block approach, adding just the functionality you need, without overloading your Arduino with useless bits and bobs. This kit consists of an Arduino shield which has Grove connectors, a set of sensors, a set of output modules, a manual and a handy storage case. Within minutes of unpacking you could be using the light sensor to control servo rotation or touch to send information to the LCD display. Simply add an Arduino.



Seeed provide technical documentation, example projects and software libraries on their product pages.

- Part of the Grove system, other modules available
- Other base modules are available, i.e. for the Raspberry Pi
- Extensive demo code, tutorials and documentation

Kit contains:

- 1x Base Shield
- 1x Grove - LCD RGB Backlight
- 1x Grove - Smart Relay
- 1x Grove - Buzzer
- 1x Grove - Sound Sensor
- 1x Grove - Touch Sensor
- 1x Grove - Rotary Angle Sensor
- 1x Grove - Temperature Sensor
- 1x Grove - LED
- 1x Grove - Light Sensor
- 1x Grove - Button
- 1x DIP LED Blue-Blue
- 1x DIP LED Green-Green
- 1x DIP LED Red-Red
- 1x Mini Servo
- 10x Grove Cables
- 1x 9V to Barrel Jack Adapter
- 1x Grove starter kit Manual
- 1x Green Plastic Box

Type	Order code	1+
Grove starter kit	75-0383	37.42



Arduino Grove Base Shield V2

The **Arduino Grove Base Shield from Seeed Studio** is switchable between 5V and 3.3V making it compatible with the official and a wide range of unofficial Arduinos. This board is the hub for a whole system of sensors, actuators, displays and more. Starting with simple LEDs and building to more complicated devices such as accelerometers, Bluetooth, sound / light / temperature sensors, the Grove system seems to have one of everything you could want. Adding a new module is as simple as plugging it into the Grove base shield and adding a few lines of code, thanks to extensive sample code available online. The Grove base shield has 4 x analog, 6 x digital, 4 x I2C and 1 x UART connectors, plus the standard GPIO headers. All the Grove products are supported with getting started guides, manuals, wiki pages, code snippets and libraries.



- Hub for the Grove family of add-on modules
- Dozens of add-on modules available
- Comprehensive documentation and code samples

Type	Order code	1+
Grove Base Shield	75-0392	7.78



110060025 Sidekick Basic Component Starter Kit for Arduino V2

The **SideKick Basic Component Starter Kit for Arduino from Seeed Studio** is a great learning resource with components to build 7 different projects. Seeed's website has instructions on how to build the projects, arranged as a series of lessons, which introduce you to every aspect of the SideKick kit. They range from blinking an LED through to controlling the position of a servo motor. Take the lessons at your own pace and feel free to branch out on your own at any stage if you get sudden inspiration. This kit isn't just for the Arduino family of boards, it's useful for any microcontroller project.



Seeed provide technical documentation, example projects and software libraries on their product pages.

- Learning resources online
- Compatible with Arduinos and other microcontroller boards
- Supplied in a handy storage box

Kit contains:

- 1x Breadboard
- 5x Green LED
- 5x Red LED
- 1x RGB Common Anode LED
- 20x Ceramic Capacitors (10nF x 10, 100nF x 10)
- 5x Aluminium capacitors (100uF x 5)
- 30x Resistors (330R x 10, 1k x 10, 10k x 10)
- 1x Tilt switch
- 1x Thermistor
- 1x Photo resistor
- 1x Diode
- 1x Buzzer
- 5x Button
- 5x Switch
- 1x Mini Servo
- 1x Potentiometer with knob
- 25x Breadboard jumper wires (5 x long, 20 x short)
- 4x Box

Type	Order code	1+
SideKick for Arduino	75-0390	14.93



110060004 ARDX Arduino Starter Kit includes UNO Board

The **ARDX Starter Kit for Arduino from Seeed Studio** is a great learning resource with components to build 13 different projects. Seeed's web-site has instructions on how to build the projects, arranged as a series of lessons, which introduce you to every aspect of the ARDX kit. They range from the usual blinking an LED through to using the Piezo sensor to detect vibration. Take the lessons at your own pace and feel free to branch out on your own at any stage if you get sudden inspiration. The great thing about this kit is that it comes complete with a set of paper circuit templates that you lay over the breadboard and push the components through. These take away all the worry of wiring the project incorrectly, you will be able to get the projects working.



Seeed provide technical documentation, example projects and software libraries on their product pages.

- Learning resources online
- Emphasis on fun, informal learning
- Arduino UNO R3 included
- Innovative circuit templates simplifies building the projects
- Supplied in a handy storage box

Kit contains:

- 1x Arduino UNO R3
- 75x Premium jumper wires
- 1x Type B USB cable
- 1x 9V battery clip
- 1x 5mm diffused RGB LED
- 1x Piezo Sensor - Minisensor 100
- 10x 5mm red LEDs
- 10x 5mm green LEDs
- 1x 10mm blue LED
- 1x Toy DC motor
- 1x 9g High Sensitive Mini sensor
- 1x 74HC595
- 1x Buzzer
- 1x 1M resistor
- 2x Pushbuttons
- 1x Potentiometer (10K)
- 1x Light sensor (5528)
- 1x TMP36
- 1x Relay (5v, 3A/120VAC)
- 2x P2N2222A
- 25x 560 Ohm resistors
- 3x 2.2k Ohm resistors
- 3x 10k Ohm resistors
- 1x 220uf capacitor
- 2x 1N4001
- 1x Breadboard
- 1x Male pin header
- 4x Plastic rivet
- 1x Acrylic holder
- 4x Rubber bumpers
- 13x Colour breadboard layout sheets
- 1x Full colour printed Experimenter's Guide

Type	Order code	1+
Arduino starter kit	75-0391	43.55


New Kano PC
See page 12
www.rapidonline.com

Adafruit Trinket



Small Form Factor Development Boards ATmega328 MCU

The **Adafruit Pro Trinket** is based around the **ATmega328** MCU and has a feature set that makes it similar to the **Arduino Pro Mini** but with a USB interface and more pins.



The Pro Trinket is Arduino compatible, working with 99% of existing Arduino **sketches**. Programming of the board can be done via **AVRdude** and/or the **Arduino IDE** and a reset button is provided for entering the bootloader or restarting the program.

- Available in 3.3 or 5V versions
- Onboard USB bootloading support
- Optiboot support
- LED indication for bootloading
- PCB Dimensions only 1.5 x 0.7 x 0.2mm
- Mounting holes
- Up to 16V input
- Ultra low dropout regulator
- Reverse polarity protection, thermal and current-limit protection
- Power with either USB or external output (e.g. battery) - with automatic switch over

Type	Order code	1+
Adafruit 2000	75-0509	9.25
Adafruit 2010	75-0510	8.64

56336



Pro Trinket Li-Ion/Li-Poly Backpack Add-On

The **Adafruit Pro Trinket Li-Ion / Li-Poly Backpack Add-On** has been cleverly designed to sit on top of the **Adafruit Pro Trinket (75-0509 & 75-0510)** and connect to its power inputs with header pins. Not only does it give you



somehow convenient to connect a battery, it will also charge the battery when the Trinket is powered from its USB port. Once USB power is removed, the fully charged battery will take over. The backpack has a RED charging LED and a green fully charged LED. It uses a 3-stage process, starting with a preconditioning charge, then a constant current fast charge and a final constant voltage trickle charge to keep the battery topped up. By default it uses a 100mA charging current but this can be increased to 500mA by closing a solder jumper for 500mAh or larger batteries. Please only use 3.7 or 4.2V Li-ion or Li-poly batteries, not the older 3.6 or 4.1V types. If you need an On/Off button, carefully cut the marked trace between the pair of solder pads then solder the switch to the pads, nice and easy.

Supplied as a fully assembled and tested charger board plus a strip of 3 x 0.1in. header pins for you to solder between the charger and the Pro Trinket. This tiny add-on board saves you time and effort while greatly extending the use of the Pro Trinket and keeping your project as small as possible.

- Mounts onto a Pro Trinket power lines via a 3-pin header
- 3-stage charging process for 3.7 and 4.2V Li-ion and LiPo batteries
- Dimensions: 15 x 17 x 2mm (0.6 x 0.7 x 0.08in.)
- Adafruit part no.: 2124

Type	Order code	1+
Trinket backpack	73-5418	5.54

563240



Trinket ATtiny85 Arduino Compatible

The **Adafruit Trinket mini-microcontrollers** are tiny (27 x 15mm) Arduino compatible processor boards which are programmable via their micro-USB socket.

Their ATtiny85 processor has 8k bytes of flash (programme) memory, 512 bytes of SRAM (static RAM), 512 bytes of EEPROM and runs at 8MHz. The boards are capable of outputting 150mA and have an ultra-low drop-out regulator which will switch between USB and battery supply automatically. Adafruit provide a free tutorial and example code to get you started, imagine driving 150 NeoPixels with such a dinky board.

There are two versions, 75-0580 which uses 3.3V and runs at 8MHz or 75-0581 which uses 5V and runs at 8 or 16MHz.

- Arduino IDE and AVRdude compatible
- 3.3 or 5VDC internal voltage regulator
- 8k bytes flash memory, 5 x GPIO lines including analogue inputs and PWM outputs
- Hardware I2C and SPI channels
- 8MHz clock speed, and 16MHz for 5V version
- Power supply up to 16V DC, reverse polarity, thermal and current-limit protection
- Dimensions 27 x 15 x 4mm (1.1 x 0.6 x 0.2in.)

Type	Order code	1+
3.3V Trinket	75-0580	6.26
5V Trinket	75-0581	6.12

561301



Adafruit NeoPixel LED



NeoPixel 8x8 Addressable RGB LED Matrix

The **Adafruit 8 x 8 NeoPixel matrix** lets you address every single one of the 64 LEDs and set its 24-bit RGB value. Make subtly shaded displays or light up the room at full power, the choice and the responsibility is yours.

The matrix has 3 x solder pads, 2 x for power (5V DC) and 1 x for the data input. A matching set of pads has a data out line allowing you to daisy chain the panels for even larger displays. Since the data protocol has strict timing requirements, the panel is best controlled by a real-time microcontroller (MCU) such as the Arduino rather than a Linux board like the Raspberry Pi. Use an MCU with a clock speed of 8MHz or greater (Arduino is 16MHz). Adafruit have published a driver library to save you the trouble and let you get on with designing eye catching displays.

- 64 NeoPixels
- 24-bits of RGB for each
- Power supply: 5V DC at 2A
- Max. current: 3.5A (all LEDs white)


Type	Order code	1+
8x8 RGB LED matrix	60-8815	28.73

56036



NeoPixel Rings Addressable RGB LEDs

The **Adafruit NeoPixel Rings** let you address every single one of the 24, 16 or 12 LEDs and set its 24-bit RGB value. These seemingly simple gadgets have triggered an amazing array of creative projects, from watches and compasses to steampunk goggles and more. Each ring has solder pads for 5V DC and Gnd, plus data in and data out. Simply feed the data out from one into the data in of another to control them both from the same microcontroller (MCU).



Since the data protocol has strict timing requirements, the ring is best controlled by a real-time microcontroller such as the Arduino rather than a Linux board like the Raspberry Pi. Use an MCU with a clock speed of 8MHz or greater (Arduino is 16MHz). Adafruit have published a driver library to save you the trouble and let you get on with designing eye catching displays.

- 24, 16 or 12 NeoPixels
- 24-bits of RGB for each
- ~18mA per NeoPixel
- Can be daisy-chained


Type	Order code	1+
24 NeoPixel ring	60-8816	14.72
16 NeoPixel ring	60-8817	9.63
12 NeoPixel ring	60-8818	6.88

560439



NeoPixel Shield for Arduino 40 Addressable RGB LEDs

The **Adafruit 40 NeoPixel Shield** lets you Arduino address every single one of the 40 LEDs and set its 24-bit RGB value. The result is a very 53 x 69mm (2.1 x 2.7in.) neat rectangle of bling. These seemingly simple gadgets have



triggered an amazing array of creative projects, from watches and compasses to steampunk goggles and more. The shield only uses 1 x digital output pin on the Arduino and more NeoPixel shields can be daisy-chained together and still use just that one pin. A 2-pin terminal block is supplied so that you can power the LEDs with an external supply if you intend adding more boards or driving the first one at full white. Adafruit have published a driver library to save you the trouble and let you get on with designing eye catching displays.

- Drive 40 NeoPixels with 1 x digital output
- 24-bits of RGB for each
- Can be daisy-chained
- 2-pin terminal block for external supply

Type	Order code	1+
NeoPixel shield	60-8819	23.38

560440

Order online

Save time, and place your order at:
www.rapidonline.com



NeoPixel Stick with 8 Addressable RGB LEDs



The **Adafruit 8 NeoPixel Stick** lets you address any one of the 8 LEDs and set its 24-bit RGB value. The result is a diminutive 51mm (2in.) tall column of LEDs and is the height of bling. These seemingly simple gadgets have triggered an amazing array of creative projects, from watches and compasses to steampunk goggles and more, perhaps a full RGB Larsen scanner. Each stick has solder pads for 5V DC and Gnd, plus data in and data out. Simply feed the data out from one into the data in of another to control them both from the same microcontroller (MCU).

Since the data protocol has strict timing requirements, the stick is best controlled by a real-time microcontroller such as the Arduino rather than a Linux board like the Raspberry Pi. Use an MCU with a clock speed of 8MHz or greater (Arduino is 16MHz). Adafruit have published a driver library to save you the trouble and let you get on with designing eye catching displays.

- 8 NeoPixels
- 24-bits of RGB for each
- ~18mA per NeoPixel
- Can be daisy-chained
- Operating voltage: 4 to 7V DC

Type	Order code	1+
8 x NeoPixel stick	60-8820	5.78



NeoPixel Addressable 5050 LED Rings RGBW

The popular **Adafruit NeoPixel Addressable LED Rings** have had an upgrade and now feature 12, 16 or 24 x 5050 RGB + White LEDs. The white LEDs are very intense and add a new dimension to your NeoPixel projects, with the 8-bit PWM you get 32-bits of colour. These seemingly simple gadgets have triggered an amazing array of creative projects, from watches and compasses to steampunk goggles and more. Each ring has solder pads for 5V DC and Gnd, plus data in and data out, using just 1 x GPIO pin on your microcontroller. Simply feed the data out from one ring into the data in of another to control them both from the same microcontroller (MCU).



Since the data protocol has strict timing requirements, the ring is best controlled by a real-time microcontroller such as the Arduino rather than a Linux board like the Raspberry Pi. Use an MCU with a clock speed of 8MHz or greater (Arduino is 16MHz).

• RGB plus white NeoPixel rings
 • Natural white (4500K) and Warm White (3000K)
 • Available with 12, 16 and 24 LEDs
 • Requires 5V DC power
 • Rings can be daisy-chained together
 • Outside diameter 37mm (1.45in.)

Type	Order code	1+
12x LED ring natural	73-5273	8.47
12x LED ring warm	73-5274	8.47
16x LED ring natural	73-5276	10.55
16x LED ring warm	73-5275	7.73
24x LED ring natural	73-5269	17.20
24x LED ring warm	73-5270	16.03



wNeoPixel Jewels 7 x 5050 RGB/RGBW LEDs with Integrated Drivers

The **Adafruit NeoPixel Addressable LED Jewels** have had an upgrade and now feature 7 x 5050 RGB + White LEDs. The white LEDs are very intense and add a new dimension to your NeoPixel projects; with the 8-bit PWM you get 32-bits of colour. These seemingly simple gadgets have triggered an amazing array of creative projects, from watches and compasses to steampunk goggles and more. Each jewel has solder pads for 5V DC and Gnd, plus data-in and data-out, using just 1 x GPIO pin on your microcontroller. Simply feed the data-out from one jewel into the data-in of another to control them both from the same microcontroller (MCU).



We also supply the RGB Jewels, **73-5411**. Since the data protocol has strict timing requirements, the jewels are best controlled by a real-time microcontroller such as the Arduino rather than a Linux board like the Raspberry Pi. Use an MCU with a clock speed of 8MHz or greater (Arduino is 16MHz).

Adafruit have published a driver library to save you the trouble and let you get on with designing eye catching displays. They have a reputation for the quality of their supporting documentation and you will find their Uberguide to NeoPixels and their Best Practices guides invaluable. In particular the Best Practices guide will help you prolong the life of your NeoPixels and avoid common mistakes. Please make sure you use the NeoPixel RGBW library for the RGBW jewels, and the RGB library for the RGB jewels.

• 7-pixel RGBW or RGB NeoPixel Jewels
 • Available without white, with warm white (3000K) and natural white (4500K)
 • Requires 5V DC power
 • Jewels can be daisy-chained together
 • Dimensions 23mm diameter x 2mm (0.9 x 0.1in.)

Type	Order code	1+
RGB	73-5411	5.78
RGB & natural white (4500K)	73-5271	6.49
RGB & warm white(3000K)	73-5272	6.49



NeoPixel Addressable LED Sticks 8 x 5050 RGBW

The **Adafruit NeoPixel Addressable LED Sticks** have had an upgrade and now feature 8 x 5050 RGB + White LEDs. The white LEDs are very intense and add a new dimension to your NeoPixel projects; with the 8-bit PWM you get 32-bits of colour. These seemingly simple gadgets have triggered an amazing array of creative projects, from watches and compasses to steampunk goggles and more. Each stick has solder pads for 5V DC and Gnd, plus data-in and data-out, using just 1 x GPIO pin on your microcontroller. Simply feed the data-out from one stick into the data-in of another to control them both from the same microcontroller (MCU).



Since the data protocol has strict timing requirements, the sticks are best controlled by a real-time microcontroller such as the Arduino rather than a Linux board like the Raspberry Pi. Use an MCU with a clock speed of 8MHz or greater (Arduino is 16MHz).

Adafruit have published a driver library to save you the trouble and let you get on with designing eye catching displays. They have a reputation for the quality of their supporting documentation and you will find their Uberguide

to NeoPixels and their Best Practices guides invaluable. In particular the Best Practices guide will help you prolong the life of your NeoPixels and avoid common mistakes. Please make sure you use the NeoPixel RGBW library, the RGB library will give odd results.


- 8-pixel RGBW NeoPixel Stick
- Warm white (3000K) or natural white (4500K)
- Requires 5V DC power
- Sticks can be daisy-chained together
- Dimensions: 10.2 x 51.1 x 3.2mm (0.4 x 2.0 x 0.13in.)

Type	Order code	1+
Natural white (4500K)	73-5277	7.24
Warm white (3000K)	73-5278	7.24



Breadboard-friendly RGB NeoPixels (Pack of 4)

The **Adafruit Breadboard-friendly RGB NeoPixels** take the FLORA NeoPixels and rework them for your breadboard with 3 x input pins and 3 x output pins on a 0.1in. pitch. The pin arrangement allows the data and power lines to be easily daisy chained together on a breadboard or a stripboard.



NeoPixels are individually addressable and can give you 24-bits of colour with 8-bit PWM. These seemingly simple gadgets have triggered an amazing array of creative projects, from watches and compasses to steampunk goggles and more. Each jewel has solder pads for 5V DC and Gnd, plus data-in and data-out, using just 1 x GPIO pin on your microcontroller. Simply feed the data-out from one jewel into the data-in of another to control them both from the same microcontroller (MCU).

Since the data protocol has strict timing requirements, the jewels are best controlled by a real-time microcontroller such as the Arduino rather than a Linux board like the Raspberry Pi. Use an MCU with a clock speed of 8MHz or greater (Arduino is 16MHz).

Adafruit have published a driver library to save you the trouble and let you get on with designing eye catching displays. They have a reputation for the quality of their supporting documentation and you will find their Uberguide to NeoPixels and their Best Practices guides invaluable. In particular the Best Practices guide will help you prolong the life of your NeoPixels and avoid common mistakes.

- Supplied in a pack of 4 x NeoPixels
- Breadboard and stripboard friendly pin layout and pitch
- 60mA current draw per NeoPixel at maximum brightness
- Adafruit part no.: 1312

Type	Order code	1+
RGB LEDs NeoPixel	73-5352	7.40



www.rapidonline.com



We bring STEM to life



RGB NeoPixel Mini PCB - Pack of 5

The **Adafruit Mini PCB NeoPixels** are the smallest breakout boards for NeoPixels you can get. They measure a neat 8 x 10mm and have 2 x sets of 3 x pads on the back for power, data-in and data-out.



NeoPixels are individually addressable and can give you 24-bits of colour with 8-bit PWM. These seemingly simple gadgets have triggered an amazing array of creative projects, from watches and compasses to steampunk goggles and more. Each NeoPixel has solder pads for 5V DC and Gnd, plus data-in and data-out, using just 1 x GPIO pin on your microcontroller. Simply feed the data-out from one NeoPixel into the data-in of another to control them both from the same microcontroller (MCU).

Since the data protocol has strict timing requirements, the NeoPixels are best controlled by a real-time microcontroller such as the Arduino rather than a Linux board like the Raspberry Pi. Use an MCU with a clock speed of 8MHz or greater (Arduino is 16MHz).

Adafruit have published a driver library to save you the trouble and let you get on with designing eye catching displays. They have a reputation for the quality of their supporting documentation and you will find their Uberguide to NeoPixels and their Best Practices guides invaluable. In particular the Best Practices guide will help you prolong the life of your NeoPixels and avoid common mistakes.

- Supplied in a pack of 5 NeoPixels
- 800kHz protocol speed
- Dimensions 8 x 10mm (0.3 x 0.4in.)
- Adafruit part no.: 1612

Type	Order code	1+
RGB LEDs mini PCB	73-5385	5.00



Easy-Sew Battery Holders

The Light Stitches Battery Holder has been specifically designed with large attachment holes that make it easy to sew or tie the Light Stitches conductive thread to it. The battery holder houses a standard 3V, CR 2032 lithium coin cell battery to power various Light Stitches projects.

The battery holder is available with or without an On/Off switch.

- Large attachment holes for easy attachment
- Easy to connect to conductive thread
- Houses a standard 3V, CR 2032 battery
- Available with or without an On/Off switch



Type	Order code	1+
Battery holder	87-6113	1.28
Battery holder+switch	87-6159	1.72



Silicone Elastomer 4x4 Keypad and Driver Board

The **Adafruit Silicone Elastomer 4 x 4 Button Keypad** is a little different from most microcontroller keyboards, instead of hard plastic buttons, these are squishy elastomer. Each button has room for a 3mm LED



so that you can illuminate just those keys that are active in your project. You don't have to add LEDs, but it does look pretty cool; diffused LEDs are the best. Because they're made from soft silicon, they're washable and you can trim off any buttons you don't want. Adafruit have also made the keypads edge to edge tileable to create larger arrangements. Each button has a conductive ring which makes contact with a properly designed PCB underneath. Adafruit provide an EagleCad library so that you can design your own. Alternatively you can pick up an Adafruit Trellis driver PCB which will do it for you. The elastomer 4 x 4 keypad and the Trellis driver PCB are sold separately.

- 4 x 4 button matrix with room for 3mm LEDs in each button
- Buttons are wipe clean, tileable, cuttable
- 3mm travel per button
- 4 x 4 keypad and LED driver PCB with I2C connectivity
- Tileable for up to 8 x boards in total
- Dimensions: 60 x 60mm (2.4 x 2.4in.)

Type	Order code	1+
Elastomer button pad	73-5381	4.62
Driver PCB	73-5380	6.58
RGB driver board	73-5431	10.93



Bluefruit BLE Bluetooth Low Energy Boards

The **Adafruit Bluefruit Low Energy range** lets you cut through the pile of Bluetooth Classic APIs, development tools and licences, and treat a Bluetooth LE connection just like a serial link. Send and receive keystrokes from your favourite terminal software, from software such as Python (via PySerial) or from your smartphone. Adafruit have built



a software stack right into the Bluetooth LE boards, so you can focus on sending and receiving the data you want for your application. The optional command mode lets you create GATT services and characteristics, make them into a UriBeacon and set the device advertising. The UriBeacon is part of the Google "Physical Web" initiative where a Bluetooth LE device broadcasts a URI which smartphone and tablet apps can detect. For example, the URI could lead to your home page for a wearable project or an interactive page for sensor data. Another particularly useful feature is the over the air (OTA) programming from any BLE capable iOS or Android device.

The Bluetooth boards are based around the very capable MDBT40 chipset (similar to the Nordic nRF51822) with Adafruit's own 100% custom firmware. The MDBT40 has an ARM Cortex M0 core running at 16MHz, 256kbytes Flash memory, 32kbytes SRAM. It talks to the host microcontroller over 4 or 5 wire SPI.

Supplied as a wearable FLORA Bluetooth board (**73-5314**) or as a Bluetooth Friend breadboard friendly module (**73-5296**).

See Adafruit's "Quick Start" guide, part of their massive free tutorial with software examples. They also provide an Android app and an iOS app which can talk BLE to your project.


- Easily create Bluetooth Low Energy (BLE) connections with compatible devices
- Supports Google's "Physical Web" initiative with UriBeacons
- Uses simple serial UART commands
- Secure over the air programmable

Type	Order code	1+
Bluetooth LE friend	73-5296	14.52
Wearable Bluetooth LE	73-5314	13.45



GEMMA v2 - Miniature Wearable Electronic Platform

The **Adafruit GEMMA v2 Miniature Wearable Electronic Platform** takes small wearable microcontrollers to a new level of tiny. Measuring just 28mm across the board features a micro-USB connector for power and programming, a 2-pin JST battery connector, a regulated power output, 3 x GPIO pads and an On/Off switch. Based around the super small ATtiny85 with 8kbytes of Flash, 512 bytes of RAM and 512 bytes of EEPROM running at 8MHz the board only draws 9mA when running. Compatible with the Arduino IDE although a couple of simple configuration tweaks are required. The 3 x GPIO pins can be configured to have 1 x analogue input and 2 x PWM outputs and 1 x hardware I2C bus as well as the normal digital IO functions.



The on board ultra-low dropout 3.3V power regulator supplies up to 150mA and will accept voltages up to 16V. It has reverse polarity, thermal cut-out and current limit protection. The board can be powered from either the USB or from an external source such as a battery and it will automatically switch from one to the other.

Supplied as a fully assembled and tested board. Adafruit supply a free tutorial to get you started with this seriously small, low cost board. Please note that GEMMA doesn't have a serial port for debugging, something had to give to make it so small.

Supplied as a fully assembled and tested board. Adafruit supply a free tutorial to get you started with this seriously small, low cost board. Please note that GEMMA doesn't have a serial port for debugging, something had to give to make it so small.

- ATtiny85 Arduino IDE compatible MCU @8MHz
- On/Off switch, Reset switch on board
- Power LED and 1 x user blinky LED
- Micro-USB for power and programming
- 2-pin JST connector for external power
- Hardware I2C
- Dimensions 28mm diameter x 7mm high (1.1in. x 0.28in.)
- Adafruit part no.: 1222

Type	Order code	1+
GEMMA v2	73-5320	9.00

Wearables



Conductive Thread

This highly conductive thread is ideal for introducing electronics into textile projects. The thread looks and behaves like conventional sewing thread with the added bonus of being highly conductive.




- Thread has a resistance of approximately 0.4Ω/cm, or 12Ω/foot
- Resistance does not vary significantly from one length of thread to the next as some are reported to do, so you should be able to use this thread without concern for "dead" sections
- The thread has a breaking strain of around 4.2kg (9.3 pounds)
- It comprises roughly 96 individual filaments, each coated with a micron-thick layer of natural silver. 16 of these filaments are wound together to form an initial twist; two of these twists are then twisted together, and finally three of these twists are combined
- In thread terms, thickness is approximately 18 denier
- This thread does not fray: there are no loose ends of filaments except where they have been cut
- Available on **bobbins of 6m**

For more information, visit our [Light Stitches minisite](http://LightStitches.com) at www.rapidonline.com/lightstitches

Type	Order code	1+
6m Bobbin	87-6147	2.52



FLORA Wearable Sensors, Modules and NeoPixels



The **Adafruit FLORA range** is a purpose designed suite of electronic modules for wearable and sewable projects. Based around the Arduino-compatible FLORA main board there are add-on boards with the ever popular NeoPixels, sensors, and even a GPS module. Each one has been carefully designed and thought out with real world applications in mind and using the best components for the job. Each product page contains links to Adafruit's resources.

- A range of compatible modules
- Sewable using conductive thread
- Communicate via I2C
- Excellent documentation and support online

Type	Order code	1+
Accelerometer/compass	73-5353	12.92
20 x RGB NeoPixels	73-5369	30.00
Wearable GPS module	73-5376	35.08
FLORA colour sensor	73-5356	6.49



GEMMA Wearable Starter Pack



The **Adafruit Gemma Wearables Starter Pack** gets your first wearable project off to a flying start. The pack contains a GEMMA main board, 4 x RGB NeoPixel LEDs, 1 x coin cell battery holder with on/off switch, 2 x CR2032 coin cell batteries, a spool of thin, stainless conductive thread, a 20-piece needle set, a USB programming cable and a pack of 12 x crocodile clip test leads.

The Adafruit GEMMA V2 Miniature Wearable Electronic Platform takes small wearable microcontrollers to a new level of tiny. Measuring just 28mm across the board features a micro-USB connector for power and programming, a 2-pin JST battery connector, a regulated power output, 3 x GPIO pads and an On/Off switch. Based around the super small ATtiny85 with 8kbytes of Flash, 512 bytes of RAM and 512 bytes of EEPROM running at 8MHz the board only draws 9mA when running. Compatible with the Arduino IDE although a couple of simple configuration tweaks are required. The 3 x GPIO pins can be configured to have 1 x analogue input and 2 x PWM outputs and 1 x hardware I2C bus as well as the normal digital IO functions.

The on board ultra-low dropout 3.3V power regulator supplies up to 150mA and will accept voltages up to 16V. It has reverse polarity, thermal cut-out and current limit protection. The board can be powered from either the USB or from an external source such as a battery and it will automatically switch from one to the other.

- Arduino IDE compatible (ATtiny85)
- Main board is only 28mm in diameter
- Needles and conductive thread included
- Battery holder and batteries are included!
- Adafruit part no.: 1657

Type	Order code	1+
Gemma starter pack	73-5383	23.14



LED Sequins for Wearables - Pack of 5

The **Adafruit Wearable LED Sequins** can hook to your Gemma or Flora board to show off your coding and your design skills at the same time. Use PWM to make them fade or sparkle for your next wearable or cosplay project. They consist of a 1206 size LED with a 100 Ohm limiting resistor and only draw 5mA at 3.3V letting you stack 4 or 5 of them on a single GPIO pin. You don't strictly need an MCU either, simply power them from a LiPo or coin battery.



- 1206 size LEDs with 100 Ohm series resistor
- 4 x 9mm (0.16 x 0.35in.)
- 2mm thick
- Holes are 7mm (0.28in.) apart
- Sold in packs of 5

Type	Order code	1+
LED sequins green	73-5391	3.68
LED sequins blue	73-5392	3.31
LED sequins red	73-5390	3.68
LED sequins white	73-5393	3.68

Type	Order code	1+
LED sequins green	73-5391	3.68
LED sequins blue	73-5392	3.31
LED sequins red	73-5390	3.68
LED sequins white	73-5393	3.68



FLORA Wearable Electronics Board Arduino Compatible

The **Adafruit FLORA V2** is their latest wearable Arduino compatible microcontroller board and it features a programmable NeoPixel for added blinkiness. They have put a lot of thought into this board, with a 2A power FET attached to the tiny on-off switch, a 3.3V regulator with protection diode and USB fuses. It can drive up to 50 NeoPixels using the onboard supply or up to 500 with an external 5V source. You can program it either via Adafruit's version of the Arduino IDE or with Arduino IDE version 1.6.4+ with a little tweaking to install FLORA support.

Adafruit supply a comprehensive getting started guide for FLORA and an Arduino IDE 1.6.4 guide.

- Wearable Arduino with 14 x sewable pads
- Onboard 2-pin JST connector for battery power
- Onboard reset button
- Diameter 44.45mm (1.75in.), weighs 4.4g
- Adafruit part no. 659

Type	Order code	1+
FLORA main board	75-0569	14.17

Adafruit Feather



HUZZAH32 ESP32 Feather Board

The HUZAH32 is the ESP32-based Feather, made with the official WROOM32 module. Adafruit have packed in everything you love about Feathers: built in USB-to-serial converter, automatic bootloader reset, lithium-ion/polymer charger, and just about all of the GPIOs brought out, so you can use it with any of our Feather Wings.



That module nestled in at the end of this Feather contains a dual-core ESP32 chip, 4MB of SPI Flash, tuned antenna, and all the passives you need to take advantage of this powerful new processor. The ESP32 has both WiFi and Bluetooth Classic/LE support. That means it's perfect for just about any wireless or Internet-connected project.

Because it's part of the Feather eco-system, you can take advantage of the 50+ Wings that Adafruit have designed to add all sorts of cool accessories.

The ESP32 is a perfect upgrade from the ESP8266 that has been so popular. In comparison, the ESP32 has way more GPIO, plenty of analog inputs, two analog outputs, multiple extra peripherals (like a spare UART), two cores so you don't have to yield to the WiFi manager, much higher-speed processor, etc.

Comes fully assembled and tested, with a USB interface that lets you quickly use it with the Arduino IDE or the low-level ESP32 IDE. Includes headers so you can solder it in and plug into a solderless breadboard. Lithium polymer battery and USB cable are not included.

- 240MHz dual core Tensilica LX6 microcontroller with 600 DMIPS
- Integrated 520KB SRAM
- Integrated 802.11b/g/n HT40 Wi-Fi transceiver, baseband, stack and LWIP
- Integrated dual mode Bluetooth (classic and BLE)
- 4MByte flash include in the WROOM32 module
- On-board PCB antenna
- Ultra-low noise analog amplifier
- Hall sensor
- 10x capacitive touch interface
- 32kHz crystal oscillator
- 3x UARTs (only two are configured by default in the Feather Arduino IDE support, one UART is used for boot-loading/debug)
- 3x SPI (only one is configured by default in the Feather Arduino IDE support)
- 2x I2C (only one is configured by default in the Feather Arduino IDE support)
- 12x ADC input channels
- 2x I2S Audio
- 2x DAC
- PWM/timer input/output available on every GPIO pin
- OpenOCD debug interface with 32kB TRAX buffer
- SDIO master/slave 50MHz
- SD-card interface support
- Dimensions: 51.0 x 22.7 x 7.3mm (2.0 x 0.9 x 0.3in.)
- Weight: 6.8g (0.2oz.)

Please note: The ESP32 is still targeted to developers.

Not all of the peripherals are fully documented with example code and there are some bugs still being found and fixed. Adafruit got all of their Featherwings working under Arduino IDE, so you can expect things like I2C and SPI and analog reads to work. But other elements are still under development.

For that reason, we recommend this Feather for makers who have some experience with microcontroller programming and **not as a first development board.**

Type	Order code	1+
ESP32 feather board	73-5436	18.56



Feather Main Boards

Adafruit are setting a new standard for single board microcontrollers and it's called Feather. The range is based around a small collection of microcontrollers and a large collection of add-on cards, all with the same small footprint.



New to Feather? Adafruit have designed a range of processor boards with a consistent board shape and pinout together with a range of add-on boards with a huge range of functionality. The main boards are based on several popular 3.3V DC microcontrollers (MCU) so that you can choose the one that suits your requirements or your budget. MCUs include the Atmel 32U4, Atmel ATSAM21G18 with an ARM Cortex A0 core, and the popular ESP8266 which is widely used in Internet of Things (IoT) projects. Because Adafruit has used the smallest components available there's room at one end of each board for a specialist function such as an SD-card holder, Bluetooth LE, packet radio, LoRa, a prototyping area or even WiFi.

The **Feather main boards** feature a USB port for power and programming, a LiPo battery connector, and support for serial, I2C and SPI in hardware. The various processors offer different numbers of GPIO pins and analogue inputs, please refer to the individual product pages and the technical specification for details. Each one has a 3.3V DC regulator which is able to supply up to 500mA peak current. The boards have a 100mA LiPo charging function with a status indicator LED and there's also a general purpose LED for blinking. The Feather boards are about one third the size of an Arduino UNO and there's even a Reset button.

Once you've chosen your processor, select one or more FeatherWing add-on boards and get developing. The range includes development tools such as prototype boards and an over-size board with screw terminal blocks for external wiring.

- 4 x mounting holes
- Dimensions 51 x 23 x 8mm (2.0 x 0.9 x 0.28in.)


Technical specification

Order code	Adafruit part no.	MCU	GPIO	Analogue inputs	PWM	Function
73-5250	3076	32U4	20	10	8	Packet radio
73-5301	2795	32U4	20	10	8	Data logging
73-5308	2829	32U4	20	10	8	Bluetooth LE
73-5309	2771	32U4	20	10	8	Prototyping
73-5299	2821	ESP8266	9	1	-	WiFi
73-5300	2772	MO	20	6	20	Prototyping
73-5306	2796	MO	20	6	20	Data logging

Type	Order code	1+
32u4 Bluetooth LE	73-5308	25.40
32u4 basic proto	73-5309	16.71
32u4 RFM69HCW	73-5250	20.86
ATSAMD21 cortex MO	73-5300	16.81
Cortex MO datalogger	73-5306	18.12
ESP8266 WiFi	73-5299	16.84



FeatherWing Add-ons for all Feather Boards



The **Adafruit FeatherWing** range of add-on boards is a large and growing collection of useful modules you can use for your Feather projects. Current add-ons include precision real-time clocks, prototyping, eye-watering LED displays and more. The modules are compatible with all the Feather main boards although there is the occasional exception which is noted on the individual product page.

Some soldering may be required as boards are usually supplied with strips of 0.1in. header where appropriate.

New to Feather? Adafruit have designed a range of processor boards with a consistent board shape and pinout together with a range of add-on boards with a huge range of functionality. The main boards are based on several popular microcontrollers (MCU) so that you can choose the one that suits your requirements or your budget. MCUs include the 32U4, Atmel ATSAM21G18 with an ARM Cortex A0 core, and the popular ESP8266 which is widely used in Internet of Things (IoT) projects. Each main board has a micro-USB socket for power and programming, a battery connector with charging function and a special function. Because Adafruit has used the smallest components available there's room at one end of the board for a specialist function such as an SD-card holder, Bluetooth LE, packet radio, LoRa, a prototyping area or even WiFi.

The **Atmel ATSAM21G18** is a very interesting chip, it's the one chosen to power the **Arduino Zero** so you know it will be supported by Arduino development tools, libraries and IDEs. It has a Cortex M0 core with 256kbytes of Flash memory, 32kbytes of RAM, and runs at 48MHz and 3.3V DC. Compared to the **Atmel 32U4** it has 8 x the Flash memory, 16 x RAM and a much faster clock speed, 48MHz compared to 8MHz.

Once you've chosen your processor, select one or more add-on boards and get developing. The FeatherWing range includes development tools such as prototype boards and an over-size board with screw terminal blocks for external wiring.

- Standard Feather pinout, plug and play
- Standard Feather board size 51.2 x 22.8 x 8mm (2.0 x 0.9 x 0.28in.)

Type	Order code	1+
PWM & Servo FeatherWing	73-5303	7.50
Data logger FeatherWing	73-5268	7.71
DC motor & stepper ctrl.	73-5304	15.04
Real-time clock	73-5258	10.85
Doubler prototype add-on	73-5302	5.59
128x32 OLED display	73-5305	12.52
Prototyping add-on	73-5307	4.39
4x8 RGB LED	73-5298	12.79
Terminal block breakout	73-5267	11.44

Free Delivery*

on all orders over £30 (excl. VAT)
(UK mainland only)

* See Terms & Conditions for full details - www.rapidonline.com/terms

Adafruit FONA



FONA 3G Cellular/GPS Breakout Board

The **Adafruit FONA 3G Cellular Breakout Board** adds to their impressive 2G phone breakouts with 3G and GPS built in. You can expect better coverage, backwards compatibility with GSM and a fast GPS with a 1s hot start time to first fix



(TTFF). On the phone side, it's quad-band and will connect to any GSM network with a 2G SIM, plus dual-band UMTS/HSPA. It can send and receive SMS messages, and send and receive GPRS data. Plug the module into your PC USB and you can send AT commands at up to 4Mbits/sec, talk GPS NMEA, and use it as a modem. The GPS module has 16 x acquisition channels, 1s hot start time to first fix and an accuracy of 2.4m; an active GPS antenna is highly recommended to achieve best results.

Adafruit have surrounded this fine module with a host of extras including 500mAh LiPo and Li-ion battery charging, a TRRS headphone jack, and breakouts for an 8Ω speaker plus electret mic. Plus 2.8 to 5V power and logic compatibility, LEDs for power, battery charge and network, uFL connectors for phone and GPS antennas and a SIM socket. You will need a few things to complete a working gadget including a 2G or 3G SIM card, a 500mAh or larger battery, a micro USB cable, external uFL antennas for GSM and GPS, and a TRRS headset.

Daunted? This is quite an advanced product and best suited to the experienced. However, Adafruit has a simpler products, the FONA mini cellular breakout (75-0587) and FONA 800 Shield for Arduino (73-5316), with more mature libraries, instructions and community.

Supplied as a fully assembled and tested 3G breakout board plus a strip of 0.1in. header pins for you to solder on as required.

- Mobile phone and GPS in one module
- Accepts 2G and 3G SIMs
- On board GPS, accurate to 2.4m
- Built-in battery charger for 500mA+ LiPo and Li-ion batteries
- Dimensions: 50 x 46 x 7mm (2.0 x 1.8 x 0.3in.)
- Adafruit part no.: 2691

Type	Order code	1+
FONA 3G / GPS	73-5311	63.80



FONA Mini Cellular GSM Breakout SMA Version

The **Adafruit FONA Mini Cellular GSM breakout boards** could put your next project in touch



with the world. Send and receive SMS messages and GPRS data, make and answer phone calls, and listen to FM radio. In fact enough functions to build a working phone, including driving a vibration motor and recharging a LiPo battery from the USB power. The boards need a microcontroller to drive them and will work with any microcontroller that can send and receive serial data, from an Arduino to a Raspberry Pi. The example wiring uses only 4 x microcontroller pins, though you can probably get by with just Tx/Rx. Adafruit have a FONA tutorial which demonstrates how to wire them up and interact with them using the AT command set from a serial terminal. While

Did you know we offer CPD's on Robotics?

Email education@rapidonline.com

you're developing your application you can use a serial terminal to send commands and get responses so that you can see exactly what's happening.

There are two versions, 75-0587 which has an SMA connector and 75-0588 which has a uFL connector.

- Use mobile voice, text, SMS and data in your next project
- SMA or uFL antenna connector versions
- Add a headset or speaker & electret mic for voice calls
- AT serial command interface
- 3 to 5V power and logic compatible

Type	Order code	1+
FONA SMA	75-0587	38.03
FONA uFL	75-0588	33.14

561307

RFID/NFC



MiFare Classic 13.56MHz RFID/NFC Cards, Tags and Fobs 1KB

The **Adafruit MiFare Classic 13.56MHz RFID/NFC devices** can be read by almost any RFID/NFC reader that can handle ISO/IEC 14443 Type A cards.



With 1kbytes of stored data the cards also have a permanent 4-byte ID burned into each one so that you can uniquely identify them. They support up to 100,000 re-writes. We also supply a suitable reader, **73-5294**. Adafruit's learning site has tutorials describing how to get the breakout board working with the Raspberry Pi or with an Arduino.

Please note that the NFC forum decided not to support ISO/IEC 14443 Type A in 2014 so newer phones don't support this standard. If your project isn't phone or tablet based then this shouldn't be an issue.

- 1 kbyte (8 kbit) non-volatile EEPROM storage
- Built in encryption engine with 48-bit key
- 4-byte unique identifier burned into the chip
- Reading distance approx. 50 to 100mm (2 to 4in.)

Type	Order code	1+
RFID / NFC card	73-5288	2.35
RFID / NFC clear fob	73-5290	2.35
RFID / NFC clear tag	73-5291	2.35
RFID/NFC leather fob	73-5289	3.67
RFID / NFC sticker	73-5292	1.92

563203



PN532 NFC RFID Controller Breakout Board v1.6

The **Adafruit PN532 NFC/RFID Controller Breakout Boards** are the perfect complement to Adafruit's range of RFID tags and cards. Based on the PN352 NFC chip, the most popular chip on the market, these boards are very capable and flexible. They can read and write NFC/RFID



Type 1 to 4 tags and cards, they can appear to other devices to actually be a card and they can perform bi-directional communication with mobile phones and tablets.

Talking to the boards is simple, using 3.3V TTL serial communications at any baud rate, I2C or SPI. Because the NFC chip is so popular it is supported by the Open Source package libnfc which will let you control a board via an FTDI cable using any Linux, Mac or Windows computer. Each board has an FTDI header for just this purpose. The boards have a built in 13.56MHz antenna for compatibility with

popular cards and tags. Adafruit have produced a tutorial to get you started which has links to useful libraries and other downloads.

Supplied with the PN532 breakout board, 0.1in. header strip, a pair of jumpers, a 4040 level shift chip and an RFID card.

- Uses popular PN532 chip
- Built-in 13.56MHz antenna
- Drive the boards using free libnfc and an FTDI cable
- Dimensions 51 x 117.7 x 1.1mm (2 x 4.7 x 0.425in.)
- Adafruit part no.: 364

Type	Order code	1+
NFC / RFID controller	73-5294	31.98

563277



Grove - User Interface and Control Modules

The **User Interface and Control Modules** from **Seeed Studio** are a selection from Seeed's collection of Grove add-ons which allow the user to interact with their projects.



- 6 x 2 LCD Display RGB Backlight
- Relay Add on Board 250V @ 10A
- Thumb Joystick
- 125KHz RFID Reader

Type	Order code	1+
16x2 LCD	75-0430	10.57
125KHz RFID reader	75-0434	9.77
Relay board	75-0436	2.38
Thumb joystick	75-0457	4.85

563073



NFC Shield with Antenna SPI Interface V2.0

The **NFC Shield from Seeed Studio** lets your Arduino read and write 13.56MHz RFID tags. A separate PCB antenna is included giving you more flexibility. The shield itself has two Grove connectors for access to Seeed's large array of add-on modules, extension headers to plug in other shields and an extension connector for the ICSP signals. Seeed have provided a software library and several examples on the [NFC Shield](#) page of their wiki.



- 50mm max. effective range
- SPI pin saving interface
- Serve for contactless communication at 13.56MHz
- Supports P2P communication
- Supports ISO14443 Type A and B protocols

Type	Order code	1+
NFC shield	75-0478	22.30

563080



RFID Tags 13.56MHz

The **13.56MHz M1 RFID Fob from Seeed Studio** is a small, easy to carry tag which operates at 13.56MHz. If your NFC/RFID reader can read Mifare cards at 13.56MHz then it can probably read these. Applications include access control, customer identification, object tracking and others.



Type	Order code	1+
Combo pack	75-0485	2.23

563059

Breakout Sensor Board



Triple-Axis Accelerometer Breakout Boards

The **Adafruit Triple-Axis Accelerometers** offer adjustable sensitivity and a choice of either I2C or SPI bus connectivity. Select from ±2, 4, 8 or 16g sensitivity; ±2g gives a higher resolution for slow movements while ±16g is best for high speed tracking. They can be configured to detect various events, such as a single tap or free-fall.



Supplied as a fully assembled and tested accelerometer boards plus a strip of 0.1in. pitch header pins for you to solder on as required. Adafruit provide a free tutorial to help get you started, please refer to the individual product pages for details.

- 3-axis accelerometers with adjustable full scale
- Detect free-fall events etc.
- I2C or SPI connectivity
- Breadboard friendly

Type	Order code	1+
ADXL345	73-5332	14.88
LS3DH	73-5283	5.89

563257



VCNL4010 Proximity/Light sensor I2C

The **Adafruit VCNL4010 Proximity/Light sensor** is a useful board for measuring proximity from 10 to 150mm. Proximity sensing is always handy for robotics applications, but this sensor could also be used for touchless switching etc.



It has built-in I2C connectivity making it compatible with most microcontrollers. Adafruit have also added a voltage regulator and level shifters to make it 3.3 to 5V logic and power compatible. Depending on your application, it's worth powering the board with 5V DC as this provides more power to its infra-red emitter for better illumination of nearby objects. Additional features include a visible light sensor and an interrupt output so that your microcontroller doesn't have to keep polling the sensor.

Supplied as a fully assembled and tested proximity sensor board plus a strip of 0.1in. header pins for you to solder on as required. Adafruit provide working example code to help get you started.

- Measure proximity between 10 and 150mm using infra-red
- Additional visible light sensor approximates human eye response
- I2C connectivity
- 3.3 to 5V DC logic and power compatible
- Dimensions: 23 x 23 x 3.2mm (0.9 x 0.9 x 0.125in.)
- Adafruit part no.: 466

Type	Order code	1+
VCNL4010	73-5285	8.16

563266

Need a product urgently?

We can offer a next day, before noon, delivery service
01206 751166



Barometric Pressure/Altitude/ Temperature Sensors

The **Adafruit I2C Barometric Pressure/Altitude/Temperature Sensors** use only 2 x GPIO pins (I2C) and provide you with precision air pressure measurements. Each board contains a 3.3V regulator, an I2C level shifter and pull-up resistors on the I2C bus making it 5V ready.



Adafruit supply a libraries and example code to get you started, please see the individual product pages for the appropriate links. Supplied with a fully assembled and tested sensor board plus a strip of 0.1in. header pins for you to solder on as required.

- Measure temperature and pressure, and altitude
- 3 to 5V logic compatible
- Pressure range: 500 to 1100hPa (9000m to -500m above sea level)
- Temperature range: -40 to +85°C

Type	Order code	1+
BMP280	73-5286	9.31
MPL3115A2	73-5402	9.00

563265



BME280 I2C or SPI Temperature Humidity Pressure Sensor

The **Adafruit BME280 Temperature, Humidity, Pressure Sensor** is an excellent choice for your next environmental/weather project with the advantage of I2C and SPI connectivity. See below for details about its measurement accuracy, in particular the pressure sensor is accurate enough to reliably measure altitude to within 1m. The board has an onboard regulator and level shifting to make it 3.3 and 5V compatible for logic and power.



Supplied as a fully assembled and tested sensor board plus a strip of 0.1in. header pins for you to solder on as required. Adafruit provide a free tutorial and software library to help get you started.

- Humidity accuracy ±3%
- Temperature accuracy ±1.0°C
- Barometric pressure accuracy ±1hPa
- Altitude accuracy ±1m
- 3.3 to 5V logic and power compatible
- Dimensions: 19.0 x 18.0 x 3.0mm (0.7 x 0.7 x 0.1in.)
- Adafruit part no.: 2652

Type	Order code	1+
BME280	73-5287	17.39

563265



Digital Infra-red/Visible Light Sensors with I2C, 5V ready

The **Adafruit Digital Light Sensors** let your next project measure the illuminance under a variety of ambient conditions. Ideal for adjusting LCD brightness according to the ambient illumination or for setting photographic exposure times etc.



If you need the UV index, use **73-5395**. For measurements tuned to the human eye's response use **73-5327** or the extremely sensitive **73-5410**. They're all 3 to 5V compatible and can communicate via I2C.

Adafruit supply information and software to get you started, please see the individual product pages for details. Supplied as a fully assembled and tested sensor board plus a strip of 0.1in. header pins for you to solder on as required.

- Measure Infra-red and visible illuminance
- 3 to 5V compatible
- Communicate via I2C

Type	Order code	1+
SI1145	73-5395	8.57
TSL2591	73-5410	6.14

563265



Electret Microphone with Built-in Amplifier

The **Adafruit Electret Microphone Boards** feature a built-in microphone and use specialist microphone amplifier chips. Choose between automatic gain control (AGC) and adjustable gain versions. Suitable for purely analogue applications such as sound recording or digital applications attached to a microcontroller and suitable software. For example, use Adafruit's FFT library to extract frequency information to make a sound visualising display. Please see the individual product pages for links to Adafruit's tutorials.



If you want to connect one to a Line Input then use a blocking capacitor of between 1 and 100µF unless you have a differential amplifier or it already has its own blocking capacitor. Blocking capacitors aren't necessary when connecting to an analogue to digital converter of an Arduino for example.

Supplied with a fully assembled amplifier board, and a strip of 0.1in. header pins for you to solder on if required.

- Built-in electret microphone
- Built-in amplifier drives small headphones, Line Input or ADC

Type	Order code	1+
Auto gain control	73-5387	8.04
Adjustable gain	73-5328	7.13

563260



AD8495 Analogue Output K-Type Thermocouple Amplifier Breakout

The **Adafruit K-Type Thermocouple Amplifiers** offer a quick and easy way of hooking up a thermocouple to your next project. Thermocouples need a cold-compensation reference and a good amplifier which is where these breakout boards come in. They handle all the electrical complications and provide you with either an analogue (**73-5399**) or digital SPI output (**73-5329**) which you can feed into your microcontroller or other circuitry if you are going old school.



The analogue output amplifier (**73-5399**) has a measurement temperature range of -24 to +400°C while the digital output (**73-5329**) amplifier has a -200 to +1350°C range.

Supplied as a fully assembled and tested thermocouple amplifier board plus a strip of 0.1in header pins and a 2-way screw terminal block for you to solder on as required. Adafruit only recommend these amplifiers for K-type thermocouples although the datasheets mentions other types. Feel free to experiment, but we only support their use with K-type thermocouples. We supply the thermocouples separately.

- Choose from analogue or SPI output
- For use with K-type thermocouples only

Type	Order code	1+
AD8495	73-5399	9.60
MAX31855K	73-5329	12.76

563295



Contact-less Infrared Thermopile Sensor Breakout

The **Adafruit Contactless Infrared Thermopile Sensor Breakout** is unusual in that it uses a thermopile which senses infra-red radiation at a distance in order to measure temperature. It has an almost 180° field of view and measures the average temperature across that view. In order to focus in on a specific target the sensor has to be close enough that the object occupies a significant portion of its field of view. Please refer to the datasheet and manual for details. It's possible to have up to 8 x thermopile sensors on one I2C bus.



Supplied as a fully assembled and tested infrared sensor board plus a strip of 0.1in. header pins for you to solder on as required.

- Contactless temperature measurement
- 2 x mounting holes
- Dimensions: 20mm x 20mm (0.8 x 0.8in)
- Adafruit part no.: 1296

Type	Order code	1+
Thermopile sensor	73-5331	9.00

563264



RGB Colour Sensor with IR filter Arduino Compatible

The **Adafruit RGB Colour Sensor** uses the TCS34725 sensor which includes 4 x photodiodes covered by an IR blocking filter for greater accuracy. Three of the photodiodes are covered with coloured filters to provide the individual RGB values and the fourth is left clear for an overall value. With a dynamic range of 3.8 million to 1 and adjustable integration time and gain it's even possible to use this sensor behind darkened glass or possibly fabric. Adafruit have added a neutral white LED to provide consistent illumination when you are trying to measure the colour of a surface. It is under software control so it can be switched off when not in use to save power or kept off depending on your application. The board has a 3.3V regulator and level shifting circuitry to make it 3.3 to 5V logic and power compatible.



Adafruit provide a free tutorial and an open source software library for you to download to help you get started.


- Separate R, G, B and white photodiodes
- IR filter for increased accuracy
- On board neutral white LED (4150K) for consistent illumination
- Uses high speed I2C, up to 400KHz
- 3,800,000:1 dynamic range
- 2 x mounting holes
- Dimensions mm diameter 20.4 x 20.3mm (0.8 x 0.79in.)
- Adafruit part no.: 1334

Type	Order code	1+
RGB colour sensor	73-5333	7.21

563270

Dash
Robot
£134.99

Order code
70-1100
Page 58



Flowol



Licences and Licence Upgrades



Flowol 4 allows students of all ages to develop logical reasoning and problem solving talents, develop programming skills and explore the world of automatic, autonomous systems and robots.

Programming visually with a flowchart allows the student to focus on the logic of their solution rather than the syntax of a written program.

The Flowol 4 software is distributed as an internet download. Your purchase will include full download and installation instructions and a license key for either the Windows PC or Apple Mac version of Flowol 4.

Supports numerous pieces of well known hardware including:

- VEX Robotics
- PICAXE
- Arduino
- Fischertechnik ... and more.

Flowol supports many programming elements:

- Sequences of instructions
- Branching using decisions
- Loops (infinite, or based on a condition or count)
- Variables and simple variable manipulation
- Sub-procedures (parameters optional)
- Multiple parallel threads

System Requirements for Windows PC:

- Microsoft Windows XP, Vista, Windows 7 or Windows 8 (both 32bit and 64bit supported)
- 512 MB of RAM
- 120 MB of available hard-disk space
- Internet connection to download and activate the software (Flowol 4 includes an MSI for installation on networks)

System Requirements for Apple Mac:

- Apple Mac computer with Intel processor
- Mac OS X 10.8 (Mountain Lion), 10.7 (Lion), 10.6 (Snow Leopard) or 10.5 (Leopard)
- 512 MB of RAM
- 100 MB of available hard-disk space
- Internet connection to download and activate the software

Type	Order code	1+
Flowol 4 Single	70-0290	29.90
Flowol 4 Primary	70-0291	149.00
Flowol 4 Middle	70-0292	219.00
Flowol 4 Secondary	70-0293	299.00
Flowol 2 to 4 Upgrade	70-0294	88.90

519522

How do I ...

- Email baskets?
- Register Online?
- Find invoices?

www.rapidonline.com/schools-faq

Order online

Save time, and place your order at:
www.rapidonline.com



Primary 3D Mimic Pack 1 for Flowol 4



Mimics are on-screen simulations of real-life situations that can be controlled by your Flowol program as if they were real machines. The Primary Mimic Pack 1 is available as a Single-User licence or a School Site licence.

- **The Horse Ride Mimic** is controlled by two independent motors so the type of ride can be varied. Virtual inputs can be used to stop the ride in its lowest position
- **The Pirate Ship Mimic** uses motors to control the motion of the ship and the sliding doors on its side. Virtual inputs are also available to detect the ship in its mid position and to indicate when the doors are shut
- **The Teacup Ride Mimic** uses motors to control the rotation of the ride, the spin of the cups and the opening of gates. Lights on the rim of the base can be illuminated and a virtual input detects the position of the ride
- **The Grabber Game Mimic** allows the user to win a teddy bear by controlling the four motors needed to manipulate the grab

Type	Order code	1+
Primary Mimic Pk1 Single	70-0296	9.90
Primary Mimic Pk1 School	70-0297	47.90

519523



Secondary 3D Mimic Pack 1 for Flowol 4



Mimics are on-screen simulations of real-life situations that can be controlled by your Flowol program as if they were real machines. The Secondary 3D Mimic Pack 1 is available as a Single-User licence or a School Site licence.

- **The Car Park Mimic** gives students the opportunity to explore the control features of car park barriers. Input switches on the ticket posts and pressure mats can be used to operate the articulated barrier. A variable can be used to count the cars in and out, control the Full sign and illuminate the seven segment display to indicate the available spaces
- **The Bridge Mimic** gives students the opportunity to explore the operation and safety features of a lifting road bridge. The beacons and road signals can be controlled and the left and right road barriers operated separately. The main bridge and barriers each have virtual input switches to detect when they are fully open or closed
- **The Lift Mimic** gives students the opportunity to explore the control features of a lift. The position of the lift is detected by virtual sensors on each floor. These can be used to stop the lift accurately and operate the floor indicator lights. By combining the inputs from the call buttons and position sensors, the lift's movement can be controlled. When the doors operate, warning messages can be added by using the sound files included with the mimic
- **The Flume Mimic** gives students the opportunity to explore and control the excitement and safety of a theme park ride. The sign, camera and fountain can be activated by the virtual inputs tripped by the moving logs. The log movements can be controlled by gates and feedback switches. (Initially choose one log with two gates and then introduce two logs with three gates)

Type	Order code	1+
Secondary Mimic Pk1 Single	70-0298	9.90
Secondary Mimic Pk1 School	70-0299	57.90

519524



Use Flowol to program VEX IQ, PICAXE and Arduino products

E-Textiles

Visit www.rapidonline.com
to see our range of textiles products



- ✓ Batik
- ✓ E-Textiles
- ✓ Fabrics
- ✓ Haberdashery
- ✓ Fabric Paints, Crayons & Dyes
- ✓ Textiles Tools