



Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 24

Pattex Repair Xtreme

SDS No. : 583429

V008.0

Revision: 18.03.2024

printing date: 10.08.2025

Replaces version from: 22.02.2023

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Pattex Repair Xtreme

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

1-Component reaction adhesive (except super glue)

1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Adhesives

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

SDSinfo.Adhesive@henkel.com

For Safety Data Sheet updates please visit our website <https://mysds.henkel.com/index.html#/appSelection> or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 0 8701 906777 - For further general health & safety, technical and practical advice on this product, please call +44 (0) 1606 593933 or write to: Technical Services; Henkel Limited; Road 5; Winsford Industrial Estate; Winsford; Cheshire; CW7 3QY- Email: technical.services@henkel.co.uk

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin sensitizer

Category 1

H317 May cause an allergic skin reaction.

2.2. Label elements

Label elements (CLP):

Hazard pictogram:



Contains

Trimethoxyvinylsilane

N-(3-(Trimethoxysilyl)propyl)ethylenediamine

Signal word: Warning

Hazard statement: H317 May cause an allergic skin reaction.

Precautionary statement: P102 Keep out of reach of children.
P101 If medical advice is needed, have product container or label at hand.
P261 Avoid breathing mist/vapours.
P280 Wear protective gloves.

Precautionary statement: P302+P352 IF ON SKIN: Wash with plenty of soap and water.
Response

Precautionary statement: P501 Dispose of contents/container in accordance with national regulation.
Disposal

2.3. Other hazards

Evolves methanol during cure.

Following substances are present in a concentration \geq the concentration limit for depiction in Section 3 and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

This mixture does not contain any substances in a concentration \geq the concentration limit for depiction in Section 3 that are assessed to be a PBT, vPvB or ED.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No. EC Number REACH-Reg No.	Concentration	Classification	Specific Conc. Limits, M-factors and ATEs	Add. Information
Siloxanes and Silicones, methoxy vinyl 131298-48-1	5- < 10 %	Eye Irrit. 2, H319		
N-(3-(Trimethoxysilyl)propyl)ethylene diamine 1760-24-3 217-164-6 01-2119970215-39	0,1- < 1 %	Skin Sens. 1A, H317 Eye Dam. 1, H318 Acute Tox. 4, Inhalation, H332 STOT RE 2, Inhalation, H373	inhalation:ATE = 1,49 mg/l;dust/mist	
Trimethoxyvinylsilane 2768-02-7 220-449-8 01-2119513215-52	0,1- < 1 %	Flam. Liq. 3, H226 Acute Tox. 4, Inhalation, H332 Skin Sens. 1B, H317		
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9 258-207-9 01-2119537297-32	0,1- < 1 %	Repr. 2, H361f Eye Dam. 1, H318 Aquatic Chronic 2, H411 Aquatic Acute 1, H400	M acute = 1	
methanol 67-56-1 200-659-6 01-2119433307-44	0,1- < 1 %	Flam. Liq. 2, H225 Acute Tox. 3, Inhalation, H331 Acute Tox. 3, Dermal, H311 Acute Tox. 3, Oral, H301 STOT SE 1, H370	STOT SE 1; H370; C >= 10 % STOT SE 2; H371; C 3 - < 10 % ===== dermal:ATE = 300 mg/kg oral:ATE = 300 mg/kg	EU OEL
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2 229-713-7 01-2119977097-24	0,1- < 1 %	Acute Tox. 3, Oral, H301 Skin Corr. 1B, H314 Eye Dam. 1, H318 Met. Corr. 1, H290	oral:ATE = 215 mg/kg	

If no ATE values are displayed, please refer to LD/LC50 values in Section 11.

For full text of the H - statements and other abbreviations see section 16 "Other information".

SECTION 4: First aid measures**4.1. Description of first aid measures**

General information:

In case of adverse health effects seek medical advice.

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing. If necessary, see a dermatologist.

Eye contact:

Immediately flush eyes with soft jet of water or eye rinse solution for at least 5 minutes. If pains remain (intensive smarting, sensitivity to light, visual disturbance) continue flushing and contact/seek doctor or hospital.

Ingestion:

Rinse mouth and throat. Drink 1-2 glasses of water. Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

May cause an allergic skin reaction.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

carbon dioxide, foam, powder, water spray jet, fine water spray

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Wear protective equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

Avoid contact with skin and eyes.

Ensure adequate ventilation.

Danger of slipping on spilled product.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Remove with liquid-absorbing material (sand, peat, sawdust).

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Ensure that workrooms are adequately ventilated.

Avoid skin and eye contact.

Hygiene measures:

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

Store in sealed original container.

Recommended storage temperature 5 to 35°C at 50 % relative humidity.

Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

7.3. Specific end use(s)

1-Component reaction adhesive (except super glue)

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, INHALABLE DUST]		6	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [Dust, respirable dust]		4	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [Dust, inhalable dust]		10	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, INHALABLE DUST]		6	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [Dust, respirable dust]		4	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [Dust, inhalable dust]		10	Time Weighted Average (TWA):		EH40 WEL
methanol 67-56-1 [METHANOL]			Skin designation:	Can be absorbed through the skin.	EH40 WEL
methanol 67-56-1 [METHANOL]	200	266	Time Weighted Average (TWA):		EH40 WEL
methanol 67-56-1 [METHANOL]	250	333	Short Term Exposure Limit (STEL):	15 minutes	EH40 WEL
methanol 67-56-1 [Methanol]	200	260	Time Weighted Average (TWA):	Indicative	ECTLV
methanol 67-56-1 [Methanol]			Skin designation:	Can be absorbed through the skin.	ECTLV

Occupational Exposure LimitsValid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS]		6	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS]		2,4	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 112945-52-5		10	Time Weighted Average (TWA):		IR_OEL

[DUSTS NON-SPECIFIC]					
Silicon dioxide 112945-52-5 [DUSTS NON-SPECIFIC]		4	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS]		6	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS]		2,4	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 112945-52-5 [DUSTS NON-SPECIFIC]		10	Time Weighted Average (TWA):		IR_OEL
Silicon dioxide 112945-52-5 [DUSTS NON-SPECIFIC]		4	Time Weighted Average (TWA):		IR_OEL
methanol 67-56-1 [Methanol]	200	260	Time Weighted Average (TWA):	Indicative OELV	IR_OEL
methanol 67-56-1 [Methanol]	200	260	Time Weighted Average (TWA):	Indicative	ECTLV
methanol 67-56-1 [Methanol]			Skin designation:	Can be absorbed through the skin.	IR_OEL
methanol 67-56-1 [Methanol]			Skin designation:	Can be absorbed through the skin.	ECTLV

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	aqua (freshwater)		0,05 mg/l				
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	aqua (marine water)		0,005 mg/l				
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	Freshwater - intermittent		0,072 mg/l				
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	sediment (freshwater)				0,181 mg/kg		
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	sediment (marine water)				0,018 mg/kg		
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	Soil				0,007 mg/kg		
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	sewage treatment plant (STP)		20 mg/l				
Trimethoxyvinylsilane 2768-02-7	aqua (freshwater)		0,4 mg/l				
Trimethoxyvinylsilane 2768-02-7	aqua (marine water)		0,04 mg/l				
Trimethoxyvinylsilane 2768-02-7	Freshwater - intermittent		1,21 mg/l				
Trimethoxyvinylsilane 2768-02-7	sediment (freshwater)				1,5 mg/kg		
Trimethoxyvinylsilane 2768-02-7	sediment (marine water)				0,15 mg/kg		
Trimethoxyvinylsilane 2768-02-7	Soil				0,06 mg/kg		
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	aqua (freshwater)		0,004 mg/l				
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	aqua (marine water)		0,00038 mg/l				
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	Freshwater - intermittent		0,007 mg/l				
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	sediment (freshwater)				5,9 mg/kg		
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	sediment (marine water)				0,59 mg/kg		
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	Soil				1,18 mg/kg		
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	sewage treatment plant (STP)		1 mg/l				
methanol 67-56-1	aqua (freshwater)						no hazard identified
methanol 67-56-1	sediment (freshwater)						no hazard identified
methanol 67-56-1	aqua (marine water)						no hazard identified
methanol 67-56-1	Soil						no hazard identified
methanol 67-56-1	sewage treatment plant (STP)						no hazard identified
methanol 67-56-1	aqua (intermittent releases)						no hazard identified
methanol 67-56-1	sediment (marine water)						no hazard identified
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	aqua (freshwater)		0,24 mg/l				

1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	aqua (marine water)		0,024 mg/l				
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	aqua (intermittent releases)		0,5 mg/l				
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	sewage treatment plant (STP)		13 mg/l				
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	sediment (freshwater)				1,46 mg/kg		
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	sediment (marine water)				0,146 mg/kg		
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	Soil				0,152 mg/kg		

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	Workers	inhalation	Long term exposure - systemic effects		130 mg/m3	
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	Workers	inhalation	Acute/short term exposure - local effects		5,36 mg/m3	
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	General population	inhalation	Long term exposure - systemic effects		26 mg/m3	
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	General population	oral	Long term exposure - systemic effects		4 mg/kg	
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	General population	inhalation	Acute/short term exposure - local effects		4 mg/m3	
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	Workers	inhalation	Long term exposure - local effects		0,6 mg/m3	
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	General population	inhalation	Long term exposure - local effects		0,1 mg/m3	
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	General population	inhalation	Acute/short term exposure - systemic effects		26400 mg/m3	
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	Workers	dermal	Long term exposure - local effects			
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	Workers	dermal	Acute/short term exposure - local effects			
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	General population	dermal	Long term exposure - local effects			
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	General population	dermal	Acute/short term exposure - local effects			
Trimethoxyvinylsilane 2768-02-7	Workers	dermal	Long term exposure - systemic effects		0,91 mg/kg	
Trimethoxyvinylsilane 2768-02-7	Workers	inhalation	Long term exposure - systemic effects		27,6 mg/m3	
Trimethoxyvinylsilane 2768-02-7	General population	dermal	Long term exposure - systemic effects		0,63 mg/kg	
Trimethoxyvinylsilane 2768-02-7	General population	inhalation	Long term exposure - systemic effects		6,8 mg/m3	
Trimethoxyvinylsilane 2768-02-7	General population	oral	Long term exposure - systemic effects		0,63 mg/kg	
Trimethoxyvinylsilane 2768-02-7	Workers	inhalation	Acute/short term exposure - systemic effects		73,6 mg/m3	
Trimethoxyvinylsilane 2768-02-7	General population	inhalation	Acute/short term exposure - systemic effects		54,4 mg/m3	
Trimethoxyvinylsilane 2768-02-7	Workers	dermal	Long term exposure - local effects			
Trimethoxyvinylsilane 2768-02-7	Workers	dermal	Acute/short term exposure - local effects			
Trimethoxyvinylsilane 2768-02-7	General population	dermal	Long term exposure - local effects			
Trimethoxyvinylsilane 2768-02-7	General population	dermal	Acute/short term exposure - local effects			

			effects			
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	Workers	dermal	Long term exposure - systemic effects		1,8 mg/kg	
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	Workers	Inhalation	Long term exposure - systemic effects		1,27 mg/m3	
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	General population	Inhalation	Long term exposure - systemic effects		0,31 mg/m3	
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	General population	dermal	Long term exposure - systemic effects		0,9 mg/kg	
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	General population	oral	Long term exposure - systemic effects		0,18 mg/kg	
methanol 67-56-1	Workers	inhalation	Long term exposure - systemic effects		260 mg/m3	no hazard identified
methanol 67-56-1	Workers	inhalation	Acute/short term exposure - systemic effects		260 mg/m3	no hazard identified
methanol 67-56-1	Workers	inhalation	Long term exposure - local effects		260 mg/m3	no hazard identified
methanol 67-56-1	Workers	inhalation	Acute/short term exposure - local effects		260 mg/m3	no hazard identified
methanol 67-56-1	Workers	dermal	Long term exposure - systemic effects		40 mg/kg	no hazard identified
methanol 67-56-1	Workers	dermal	Acute/short term exposure - systemic effects		40 mg/kg	no hazard identified
methanol 67-56-1	General population	inhalation	Long term exposure - systemic effects		50 mg/m3	no hazard identified
methanol 67-56-1	General population	inhalation	Acute/short term exposure - systemic effects		50 mg/m3	no hazard identified
methanol 67-56-1	General population	inhalation	Long term exposure - local effects		50 mg/m3	no hazard identified
methanol 67-56-1	General population	inhalation	Acute/short term exposure - local effects		50 mg/m3	no hazard identified
methanol 67-56-1	General population	dermal	Long term exposure - systemic effects		8 mg/kg	no hazard identified
methanol 67-56-1	General population	dermal	Acute/short term exposure - systemic effects		8 mg/kg	no hazard identified
methanol 67-56-1	General population	oral	Long term exposure - systemic effects		8 mg/kg	no hazard identified
methanol 67-56-1	General population	oral	Acute/short term exposure - systemic effects		8 mg/kg	no hazard identified
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	Workers	inhalation	Long term exposure - systemic effects		10,6 mg/m3	
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	Workers	dermal	Long term exposure - systemic effects		3 mg/kg	
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	General population	inhalation	Long term exposure - systemic effects		2,6 mg/m3	
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	General population	dermal	Long term exposure - systemic effects		1,5 mg/kg	
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	General population	oral	Long term exposure - systemic effects		1,5 mg/kg	

1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	Workers	inhalation	Acute/short term exposure - systemic effects			
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	Workers	inhalation	Long term exposure - local effects			
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	Workers	inhalation	Acute/short term exposure - local effects			
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	Workers	dermal	Long term exposure - local effects			
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	Workers	dermal	Acute/short term exposure - local effects			
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	General population	inhalation	Acute/short term exposure - systemic effects			
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	General population	inhalation	Long term exposure - local effects			
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	General population	inhalation	Acute/short term exposure - local effects			
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	General population	dermal	Long term exposure - local effects			
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	General population	dermal	Acute/short term exposure - local effects			
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	General population	oral	Acute/short term exposure - systemic effects			

Biological Exposure Indices:

None

8.2. Exposure controls:**Respiratory protection:**

Suitable breathing mask when there is inadequate ventilation.

Filter : AX (EN 14387)

This recommendation should be matched to local conditions.

Hand protection:

Recommended are gloves made from Nitril rubber (Material thickness >0,1 mm, Perforation time < 30s).Gloves should be replaced after each short time contact or contamination. Available at laboratory specialized trade or at pharmacies / chemist's shops.

In the case of longer contact protective gloves made from nitrile rubber are recommended according to EN 374.

material thickness > 0.4 mm

Perforation time > 30 minutes

In the case of longer and repeated contact please note that in practice the penetration times may be considerably shorter than those determined according to EN 374. The protective gloves must always be checked for their suitability for use at the specific workplace (e.g. mechanical and thermal stress, product compatibility, antistatic effects, etc.). The gloves must be replaced immediately at the first signs of wear and tear. The information provided by the manufacturers and given in the relevant trade association regulations for industrial safety must always be observed. We recommend that a hand care plan is drawn up in cooperation with a glove manufacturer and the trade association in accordance with the local operating conditions.

Eye protection:

Goggles which can be tightly sealed.

Protective eye equipment should conform to EN166.

Skin protection:

Suitable protective clothing

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Delivery form	gel
Colour	transparent, colourless
Odor	minty
Physical state	liquid
Melting point	Not applicable, Product is a liquid
Solidification temperature	< -50 °C (< -58 °F)
Initial boiling point	220 °C (428 °F)
Flammability	The product is not flammable.
Explosive limits	
lower	0,16 %(V);
Flash point	68 - 72 °C (154.4 - 161.6 °F)
Auto-ignition temperature	> 300 °C (> 572 °F)
Decomposition temperature	Not applicable, Substance/mixture is not self-reactive, no organic peroxide and does not decompose under foreseen conditions of use
pH	Not applicable, Product is non-soluble (in water).
Viscosity (kinematic) (20 °C (68 °F);)	68.000 mm ² /s
Viscosity, dynamic (Brookfield; 40 °C (104 °F); speed of rotation: 20 min-1; Spindle No: 7)	150.000 - 200.000 mPa.s no method / method unknown
Solubility (qualitative) (23 °C (73.4 °F); Solvent: Water)	Partially soluble
Partition coefficient: n-octanol/water	Not applicable
Vapour pressure (20 °C (68 °F))	Mixture 0,14 hPa
Density (20 °C (68 °F))	1,0 - 1,1 g/cm ³ no method / method unknown
Relative vapour density: (20 °C)	Heavier than air
Particle characteristics	Not applicable Product is a liquid

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity

10.1. Reactivity

None if used for intended purpose.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

None if used properly.

10.6. Hazardous decomposition products

Evolves methanol during cure.

SECTION 11: Toxicological information**General toxicological information:**

Cross-reactions with other amine compounds are possible.

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008**Acute oral toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	LD50	2.295 mg/kg	rat	EPA OPPTS 870.1100 (Acute Oral Toxicity)
Trimethoxyvinylsilane 2768-02-7	LD50	6.899 mg/kg	rat	equivalent or similar to OECD Guideline 401 (Acute Oral Toxicity)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	LD50	3.700 mg/kg	rat	OECD Guideline 423 (Acute Oral toxicity)
methanol 67-56-1	Acute toxicity estimate (ATE)	300 mg/kg		Expert judgement
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	Acute toxicity estimate (ATE)	215 mg/kg		Expert judgement

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	LD50	> 2.000 mg/kg	rat	EPA OPPTS 870.1200 (Acute Dermal Toxicity)
Trimethoxyvinylsilane 2768-02-7	LD50	3.158 mg/kg	rabbit	equivalent or similar to OECD Guideline 402 (Acute Dermal Toxicity)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	LD50	> 3.170 mg/kg	rat	OECD Guideline 402 (Acute Dermal Toxicity)
methanol 67-56-1	Acute toxicity estimate (ATE)	300 mg/kg		Expert judgement

Acute inhalative toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Test atmosphere	Exposure time	Species	Method
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	LC50	1,49 - 2,44 mg/l	dust/mist	4 h	rat	EPA OPPTS 870.1300 (Acute inhalation toxicity)
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	Acute toxicity estimate (ATE)	1,49 mg/l	dust/mist			Expert judgement
Trimethoxyvinylsilane 2768-02-7	LC50	16,8 mg/l	vapour	4 h	rat	equivalent or similar to OECD Guideline 403 (Acute Inhalation Toxicity)

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	mildly irritating	4 h	rabbit	EPA OPPTS 870.2500 (Acute Dermal Irritation)
Trimethoxyvinylsilane 2768-02-7	not irritating		rabbit	other guideline:
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	not irritating	24 h	rabbit	EPA OPP 81-5 (Acute Dermal Irritation)
methanol 67-56-1	not irritating	20 h	rabbit	BASF Test

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	highly irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Trimethoxyvinylsilane 2768-02-7	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	corrosive	24 h	rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
methanol 67-56-1	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	Sub-Category 1A (sensitising)	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)
Trimethoxyvinylsilane 2768-02-7	sensitising	Buehler test	guinea pig	OECD Guideline 406 (Skin Sensitisation)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)
methanol 67-56-1	not sensitising	Guinea pig maximisation test	guinea pig	equivalent or similar to OECD Guideline 406 (Skin Sensitisation)

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Trimethoxyvinylsilane 2768-02-7	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Trimethoxyvinylsilane 2768-02-7	positive	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Trimethoxyvinylsilane 2768-02-7	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
methanol 67-56-1	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
methanol 67-56-1	negative	in vitro mammalian cell micronucleus test	without		not specified
methanol 67-56-1	negative	mammalian cell gene mutation assay	with and without		equivalent or similar to OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)

Carcinogenicity

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Sex	Method
methanol 67-56-1	not carcinogenic	inhalation: vapour	18 m 19 h/d	mouse	male/female	equivalent or similar OECD Guideline 453 (Combined Chronic Toxicity / Carcinogenicity Studies)

Reproductive toxicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
Trimethoxyvinylsilane 2768-02-7	NOAEL P 250 mg/kg	one- generation study	oral: gavage	rat	OECD Combined Repeated Dose and Reproductive / Developmental Toxicity Screening Test (Precursor Protocol of GL 422)
Trimethoxyvinylsilane 2768-02-7	NOAEL P 1.000 mg/kg	one- generation study	oral: gavage	rat	OECD Combined Repeated Dose and Reproductive / Developmental Toxicity Screening Test (Precursor Protocol of GL 422)
Trimethoxyvinylsilane 2768-02-7	NOAEL F1 1.000 mg/kg	one- generation study	oral: gavage	rat	OECD Combined Repeated Dose and Reproductive / Developmental Toxicity Screening Test (Precursor Protocol of GL 422)
Bis(2,2,6,6-tetramethyl-4- piperidyl) sebacate 52829-07-9	NOAEL P 109 mg/kg NOAEL F1 121 mg/kg	two- generation study	oral: feed	rat	OECD Guideline 443 (Extended One-Generation Reproductive Toxicity Study)
methanol 67-56-1	NOAEL P 1,3 mg/l NOAEL F1 0,13 mg/l NOAEL F2 0,13 mg/l	Two generation study	inhalation	rat	equivalent or similar to OECD Guideline 416 (Two- Generation Reproduction Toxicity Study)

STOT-single exposure:

No data available.

STOT-repeated exposure:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
Trimethoxyvinylsilane 2768-02-7	NOAEL 62,5 mg/kg	oral: gavage	42d daily	rat	OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)
Trimethoxyvinylsilane 2768-02-7	NOAEL 0,605 mg/l	inhalation: vapour	5 days/week for 14 weeks 6 hours/day	rat	not specified
Trimethoxyvinylsilane 2768-02-7	NOAEL 50 mg/kg	oral: gavage	28 d daily	rat	OECD Guideline 407 (Repeated Dose 28-Day Oral Toxicity in Rodents)
Bis(2,2,6,6-tetramethyl-4- piperidyl) sebacate 52829-07-9	NOAEL 36 mg/kg	oral: feed	daily	rat	other guideline:
methanol 67-56-1	NOAEL 6,63 mg/l	inhalation: vapour	4 weeks 6 h/d, 5 d/w	rat	equivalent or similar to OECD Guideline 412 (Repeated Dose Inhalation Toxicity: 28/14-Day)
methanol 67-56-1	NOAEL 0,13 mg/l	inhalation: vapour	12 m 20 h/d	rat	equivalent or similar to OECD Guideline 453 (Combined Chronic Toxicity / Carcinogenicity Studies)

Aspiration hazard:

No data available.

11.2 Information on other hazards

not applicable

SECTION 12: Ecological information**General ecological information:**

Do not empty into drains, soil or bodies of water.

12.1. Toxicity**Toxicity (Fish):**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	LC50	168 mg/l	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
Trimethoxyvinylsilane 2768-02-7	LC50	191 mg/l	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	LC50	4,4 mg/l	96 h	Lepomis macrochirus	OECD Guideline 203 (Fish, Acute Toxicity Test)
methanol 67-56-1	LC50	15.400 mg/l	96 h	Lepomis macrochirus	EPA-660 (Methods for Acute Toxicity Tests with Fish, Macroinvertebrates and Amphibians)
methanol 67-56-1	NOEC	7.900 mg/l	200 h	Oryzias latipes	OECD Guideline 210 (fish early life stage toxicity test)
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	LC50	> 100 - 220 mg/l	96 h	Leuciscus idus	DIN 38412-15

Toxicity (aquatic invertebrates):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	EC50	87,4 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Trimethoxyvinylsilane 2768-02-7	EC50	168,7 mg/l	48 h	Daphnia magna	EU Method C.2 (Acute Toxicity for Daphnia)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	EC50	8,58 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
methanol 67-56-1	EC50	18.260 mg/l	96 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	EC50	50 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

Chronic toxicity (aquatic invertebrates):

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
N-(3-(Trimethoxysilyl)propyl)ethylenediamine	NOEC	> 1 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

1760-24-3					
Trimethoxyvinylsilane 2768-02-7	NOEC	28,1 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	NOEC	0,23 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	NOEC	> 12 mg/l	21 day	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
N-(3-(Trimethoxysilyl)propyl)ethyl enediamine 1760-24-3	EC50	8,8 mg/l	96 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
N-(3-(Trimethoxysilyl)propyl)ethyl enediamine 1760-24-3	NOEC	3,1 mg/l	96 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
Trimethoxyvinylsilane 2768-02-7	EC50	> 957 mg/l	72 h	Desmodesmus subspicatus	EU Method C.3 (Algal Inhibition test)
Trimethoxyvinylsilane 2768-02-7	NOEC	957 mg/l	72 h	Desmodesmus subspicatus	EU Method C.3 (Algal Inhibition test)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	EC50	0,705 mg/l	72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	EC10	0,188 mg/l	72 h	Pseudokirchneriella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
methanol 67-56-1	EC50	22.000 mg/l	96 h	Selenastrum capricornutum (new name: Pseudokirchneriella subcapitata)	OECD Guideline 201 (Alga, Growth Inhibition Test)
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	EC50	> 100 mg/l	72 h	Desmodesmus subspicatus (reported as Scenedesmus subspicatus)	EU Method C.3 (Algal Inhibition test)
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	NOEC	> 100 mg/l	72 h	Desmodesmus subspicatus (reported as Scenedesmus subspicatus)	EU Method C.3 (Algal Inhibition test)

Toxicity (microorganisms):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
N-(3-(Trimethoxysilyl)propyl)ethyl enediamine 1760-24-3	EC 50	435 mg/l	3 h		OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)
Trimethoxyvinylsilane 2768-02-7	EC50	> 100 mg/l	3 h	activated sludge of a predominantly domestic sewage	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	EC50	> 100 mg/l	3 h	activated sludge, domestic	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)
methanol 67-56-1	EC50	> 1.000 mg/l	3 h	activated sludge of a predominantly domestic sewage	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	EC 50	330 mg/l	17 h		not specified

12.2. Persistence and degradability

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3		aerobic	50 %		OECD Guideline 301 A (new version) (Ready Biodegradability: DOC Die Away Test)
Trimethoxyvinylsilane 2768-02-7	not readily biodegradable.	aerobic	51 %	28 d	OECD Guideline 301 F (Ready Biodegradability: Manometric Respirometry Test)
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	not readily biodegradable.	aerobic	24 %	28 d	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test)
methanol 67-56-1	readily biodegradable	aerobic	82 - 92 %	30 d	EU Method C.4-E (Determination of the "Ready" Biodegradability Closed Bottle Test)
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	not inherently biodegradable	aerobic	< 20 %	28 day	OECD Guideline 302 B (Inherent biodegradability: Zahn-Wellens/EMPA Test)
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	not readily biodegradable.	aerobic	< 20 %	28 day	OECD Guideline 301 A (new version) (Ready Biodegradability: DOC Die Away Test)

12.3. Bioaccumulative potential

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Bioconcentration factor (BCF)	Exposure time	Temperature	Species	Method
methanol 67-56-1	< 10	72 h		Leuciscus idus melanotus	not specified
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	< 0,4	42 day		Cyprinus carpio	OECD Guideline 305 C (Bioaccumulation: Test for the Degree of Bioconcentration in Fish)

12.4. Mobility in soil

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	LogPow	Temperature	Method
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	-1,67		not specified
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	0,35	25 °C	OECD Guideline 107 (Partition Coefficient (n-octanol / water), Shake Flask Method)
methanol 67-56-1	-0,77		other guideline:

12.5. Results of PBT and vPvB assessment

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	PBT / vPvB
N-(3-(Trimethoxysilyl)propyl)ethylenediamine 1760-24-3	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Trimethoxyvinylsilane 2768-02-7	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
Bis(2,2,6,6-tetramethyl-4-piperidyl) sebacate 52829-07-9	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
methanol 67-56-1	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
1,8-Diazabicyclo[5.4.0]undec-7-ene 6674-22-2	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Endocrine disrupting properties

not applicable

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Dispose of waste and residues in accordance with local authority requirements.

Disposal of uncleaned packages:

Use packages for recycling only when totally empty.

Waste code

080409

SECTION 14: Transport information

14.1. UN number or ID number

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

14.2. UN proper shipping name

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

14.3. Transport hazard class(es)

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

14.4. Packing group

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.7. Maritime transport in bulk according to IMO instruments

not applicable

SECTION 15: Regulatory information

No information available:

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Ozone Depleting Substance (ODS) (Regulation (EC) No 1005/2009):	Not applicable
Prior Informed Consent (PIC) (Regulation (EU) No 649/2012):	Not applicable
Persistent organic pollutants (Regulation (EU) 2019/1021):	Not applicable

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H225 Highly flammable liquid and vapour.
H226 Flammable liquid and vapour.
H290 May be corrosive to metals.
H301 Toxic if swallowed.
H311 Toxic in contact with skin.
H314 Causes severe skin burns and eye damage.
H317 May cause an allergic skin reaction.
H318 Causes serious eye damage.
H319 Causes serious eye irritation.
H331 Toxic if inhaled.
H332 Harmful if inhaled.
H361f Suspected of damaging fertility.
H370 Causes damage to organs.
H373 May cause damage to organs through prolonged or repeated exposure if inhaled.
H400 Very toxic to aquatic life.
H411 Toxic to aquatic life with long lasting effects.

ED:	Substance identified as having endocrine disrupting properties
EU OEL:	Substance with a Union workplace exposure limit
EU EXPLD 1:	Substance listed in Annex I, Reg (EC) No. 2019/1148
EU EXPLD 2	Substance listed in Annex II, Reg (EC) No. 2019/1148
SVHC:	Substance of very high concern (REACH Candidate List)
PBT:	Substance fulfilling persistent, bioaccumulative and toxic criteria
PBT/vPvB:	Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very bioaccumulative criteria
vPvB:	Substance fulfilling very persistent and very bioaccumulative criteria

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (SDSinfo.Adhesive@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,
Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.