

Item No.: 1848642

Type: SDDC 1,5/ 2-PV-3,5

PCB direct plug, Push-in spring connection



The figure shows a 2-pos. version with 4 contacts

1 Main features



- | | | | |
|---------------------------|---------------------------|------------------------|---------------------|
| • No. of pos. | 2 | • Nominal current | 8 A |
| • Conductor cross section | 1.5 mm ² | • Nominal voltage | 160 V |
| • Color | green (6021) | • Connection direction | 90 ° |
| • Pitch | 3.5 mm | • Type of packaging | packed in cardboard |
| • Connection method | Push-in spring connection | | |

2 Your advantages

- ✓ SKEDD direct plug-in technology enables flexible positioning on the PCB
- ✓ Reduced component and process costs: simple insertion by hand and vibration-resistant connection
- ✓ Contacts arranged in a double row enable high packing density in a compact area
- ✓ Wide range of applications, thanks to suitability for PCBs with chemically tin-plated or Hot Air Leveling (HAL) surface
- ✓ Time saving push-in connection, tools not required
- ✓ Intuitive use through colour coded actuation lever
- ✓ Quick and convenient testing using integrated test option



Make sure you always use the latest documentation.
It can be downloaded at: phoenixcontact.net/product/1848642

3 Table of contents

1	Main features.....	1
2	Your advantages	1
3	Table of contents	2
4	3D model in PDF can be activated (Acrobat Reader only)	3
5	General Technical Data	4
6	Mounting.....	5
7	Conductor connection	6
8	Material properties.....	7
9	Dimensions.....	8
10	Series drawing.....	9
11	Product notes	10
12	Packaging information	10
13	Application.....	10
14	General tests	11
15	Mechanical tests.....	11
16	Insertion and withdrawal forces	13
17	Electrical tests	14
18	Current carrying capacity/derating curves	15
19	Environmental and durability tests	16
20	Type approval and special tests	17
21	Classification for connectors.....	17
22	Approvals / Certificates.....	18
23	Commercial Data.....	19
24	Accessories	19
25	Combination tests.....	20

1848642 SDDC 1,5/ 2-PV-3,5

4 3D model in PDF can be activated (Acrobat Reader only)



1848642 SDDC 1,5/ 2-PV-3,5**5 General Technical Data****5.1 item properties**

Item no.	1848642
Type	SDDC 1,5/ 2-PV-3,5
Connector system	SKEDD
Product type	PCB direct plug
Range of articles	SDDC 1,5/..-PV
Pitch	3.5 mm
Number of positions	2
Number of rows	2
Number of connections	4
Number of potentials	4
Connection method	Push-in spring connection
Connection direction of the connector to the PCB	90 °
Connection direction of the conductor to plug-in direction	90 °
Pin layout	Linear double pinning
Solder pins per potential	1

1848642 SDDC 1,5/ 2-PV-3,5**6 Mounting****6.1 Flange mounting**

Type of locking

Snap-in locking

Mounting flange

Self-locking flange

1848642 SDDC 1,5/ 2-PV-3,5**7 Conductor connection****7.1 Connection capacity**

Nominal cross section	1.5 mm ²
Conductor cross section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve	0.2 mm ² ... 1.5 mm ²
Conductor cross section flexible, with ferrule with plastic sleeve	0.2 mm ² ... 1 mm ²
Cylindrical gauge a x b / diameter	2.4 mm x 1.5 mm / 1.6 mm
Stripping length	8 mm

7.2 Connection capacity AWG

Conductor cross section AWG	24 ... 16
-----------------------------	-----------

1848642 SDDC 1,5/ 2-PV-3,5**8 Material properties****8.1 Material of metal parts**

Note	WEEE/RoHS-compliant, whisker-free acc. to IEC 60068-2-82/JEDEC JESD 201
Contact material	Cu alloy
Terminal point surface	Tin (4 - 8 µm Sn)
Surface contact area	Tin (4 - 8 µm Sn)
Surface characteristics	hot-dip tin-plated


8.2 Material of plastic parts

	Housing	Actuation element
Color	green (6021)	
Insulating material	PA	PBT
Insulating material group	I	I
CTI according to IEC 60112	600	600
Flammability rating according to UL 94	V0	V0
Glow wire flammability index GWFI according to EN 60695-2-12	850	
Glow wire ignition temperature GWIT according to EN 60695-2-13	775	
Temperature for the ball pressure test according to EN 60695-10-2	125 °C	

1848642 SDDC 1,5/ 2-PV-3,5**9 Dimensions****9.1 Dimensions for the product**

Length	13.5 mm
Width	14.3 mm
Installed height	14 mm
Total height	17.6 mm

10 Series drawing



1848642 SDDC 1,5/ 2-PV-3,5**11 Product notes****11.1 General information**

Notes on operation

In accordance with IEC 61984, COMBICON connectors have no switching power (COC). During designated use, they must not be plugged in or disconnected when carrying voltage or under load.

12 Packaging information

Type of packaging

packed in cardboard

Pieces per package

250

13 Application

Ferrules without insulating collar, according to DIN 46228-1

Recommended crimping pliers

1212034 CRIMPFOX 6

Ferrules without insulating collar, according to DIN 46228-1

Cross section: 0.5 mm²; Length: 8 mm ... 10 mm
 Cross section: 0.75 mm²; Length: 8 mm ... 10 mm
 Cross section: 1 mm²; Length: 8 mm ... 10 mm
 Cross section: 1.5 mm²; Length: 8 mm

Ferrules with insulating collar, according to DIN 46228-4

Recommended crimping pliers

1212034 CRIMPFOX 6

Ferrules with insulating collar, according to DIN 46228-4

Cross section: 0.25 mm²; Length: 8 mm ... 10 mm
 Cross section: 0.5 mm²; Length: 8 mm ... 10 mm
 Cross section: 0.75 mm²; Length: 10 mm
 Cross section: 1 mm²; Length: 10 mm

13.1 Temperature limit values

Ambient temperature (storage/transport)

-40 °C ... 70 °C

Relative humidity (storage/transport)

30 % ... 70 %

Ambient temperature (assembly)

-5 °C ... 100 °C

Ambient temperature (operation)

-40 °C ... 100 °C (dependent on the derating curve)

1848642 SDDC 1,5/ 2-PV-3,5**14 General tests****14.1 Specification**

Specification	IEC 61984
Specification	IEC 60999-1
Brief description	Printed-circuit board connector

15 Mechanical tests**15.1 Check for damage to conductor or loosening**

Result	Test passed
Specification	IEC 60999-1:1999-11

15.2 Pull-out test

Specification	IEC 60999-1:1999-11
Result	Test passed
Conductor cross section/conductor type/tractive force actual value	0.2 mm ² / solid / > 10 N
Conductor cross section/conductor type/tractive force actual value	0.2 mm ² / flexible / > 10 N
Conductor cross section/conductor type/tractive force actual value	1.5 mm ² / solid / > 40 N
Conductor cross section/conductor type/tractive force actual value	1.5 mm ² / flexible / > 40 N

15.3 Repeated connection and disconnection

Specification	IEC 60999-1:1999-11
Result	Test passed

15.4 Conductor connection

Specification	IEC 60999-1:1999-11
Result	Test passed

15.5 Visual examination

Specification	IEC 61984:2008-10
Visual examination	Test passed
Specification	IEC 60512-1-1:2002-02

15.6 Dimensional test

Dimensional test	Test passed
Specification	IEC 60512-1-2:2002-02

15.7 Resistance of marking

1848642 SDDC 1,5/ 2-PV-3,5

Resistance of marking

Test passed

Specification

IEC 60068-2-70:1995-12

15.8 Polarization and codingPolarization when inserted
Requirement >20 N

Test passed

Specification

IEC 60512-13-5:2006-02

1848642 SDDC 1,5/ 2-PV-3,5**16 Insertion and withdrawal forces**

Insertion and withdrawal force	Test passed
Specification	IEC 60512-13-2:2006-02
No. of cycles	25
Insertion strength per pos. approx.	8 N
Withdraw strength per pos. approx.	6 N

1848642 SDDC 1,5/ 2-PV-3,5**17 Electrical tests**

Rated current / conductor cross section	8 A / 1.5 mm ²
Rated insulation voltage (III/2)	160 V
Rated surge voltage (III/2)	2.5 kV
Contact resistance	1.4 mΩ
Degree of pollution	2

17.1 Air and creepage distances

Component	PCB direct plug		
Specification	IEC 60664-1:2007-04		
Mains type	unearthed mains		
Insulating material group	I		
Comparative tracking index (IEC 60112)	CTI 600		
Rated insulation voltage	160 V	160 V	400 V
Rated surge voltage	2.5 kV	2.5 kV	2.5 kV
Degree of pollution	3	2	2
Overvoltage category	III	III	II
Minimum clearance case A (inhomogeneous field)	1.5 mm	1.5 mm	1.5 mm
Minimum value of the creepage path requirement in acc. with table	2 mm	1.5 mm	2 mm

17.2 Electrical function

Specification	IEC 60999-1:1999-11
Result	Test passed
Voltage drop	Voltage drop (U) after the load ≤ 15 mV
Test current (minimum cross section)	4 A AC
Test current (maximum cross section)	8 A AC
Conductor cross section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross section, rigid	0.2 mm ² ... 1.5 mm ²

17.3 Temperature cycles

Specification	IEC 60999-1:1999-11
Result	Test passed
Voltage drop	Voltage drop (U) after the load ≤ 22.5 mV or $1.5 \times U_{\text{after 24 h}}$ The small value is to be used.
Test current (minimum cross section)	4 A DC
Test current (maximum cross section)	8 A DC
Temperature cycles	192
Conductor cross section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross section, rigid	0.2 mm ² ... 1.5 mm ²

1848642 SDDC 1,5/ 2-PV-3,5**18 Current carrying capacity/derating curves**

Specification

IEC 61984:2008-10

Note

Representation based on IEC 60512-5-2:2002-02


Note

For number of positions, see diagram

Reduction factor

0.8

Conductor cross section

1.5 mm²**Type: SDDC 1,5/...-PV-3,5**

1848642 SDDC 1,5/ 2-PV-3,5**19 Environmental and durability tests****19.1 Vibration test**

Specification	IEC 60068-2-6:2007-12
Result	Test passed
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm (10 - 60.1 Hz)
Acceleration	5g (60.1 - 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis
Note	The connecting cables must be strain relieved.

19.2 Railway application, vibration test

Specification	IEC 61373:2010-05
Result	Test passed
Testing	Vibration, broadband noise
Frequency	5 - 150 Hz
Test directions	X-, Y- and Z-axis (pos. and neg.)
Spectrum	Service life test category 1, class B, body mounted

19.3 Insulation resistance

Specification	IEC 60512-3-1:2002-02
Result	Test passed
Insulation resistance, neighboring positions	> 5 MΩ

19.4 Insulation resistance

Specification	IEC 60512-3-1:2002-02
Result	Test passed
Requirements, insulation resistance	> 5 MΩ
Insulation resistance, neighboring positions	> 5 MΩ

1848642 SDDC 1,5/ 2-PV-3,5**20 Type approval and special tests****21 Classification for connectors**

Specification	IEC 61984:2008-10
Main features	Connectors without switching capacity (COC)
Construction form	Fixed connectors
Strain relief elements	without strain relief
Connection method	Can be reconnected
Protection against electric shock	Not encapsulated - touch-proof when inserted
Protective conductor	without PE
Locking	no
Connection method	Screwless terminal points

1848642 SDDC 1,5/ 2-PV-3,5

22 Approvals / Certificates

IECEE CB Scheme 				
cULus Recognized 	Voltage [V]	Current [A]	Cross section [AWG]	Cross section [mm ²]
Usegroup B				
	300 V	8 A	24 - 16	-
Usegroup D				
	300 V	8 A	24 - 16	-
EAC 				
VDE Zeichengenehmigung 	Voltage [V]	Current [A]	Cross section [AWG]	Cross section [mm ²]
	160 V	8 A	-	0.2 - 1.5
UL Recognized 	Voltage [V]	Current [A]	Cross section [AWG]	Cross section [mm ²]
Usegroup F				
	250 V	8 A	24 - 16	-

1848642 SDDC 1,5/ 2-PV-3,5**23 Commercial Data**

Item no.	1848642
Type	SDDC 1,5/ 2-PV-3,5
Pieces per package	250
Net weight	2.4 g
GTIN	4055626307114
	Information that applies locally, see link on page 1

24 Accessories

Description	Item No.	Type
Coding profile, inserted into the hole on the plug, made from red insulating material, diameter: 1.35 mm	1985564	CP-PT 1,5
	0804073	SK 3,5/2,8:FORTL.ZAHLEN
	0825121	SK 2,8 REEL P3,5 WH CUS
	0803883	SK U/2,8 WH:UNBEDRUCKT
	0805205	SK 2,8 WH:REEL
Test plug, consisting of 1.0 mm Ø test pin and 2.0 mm Ø socket	1944372	MPS-MT 1-S
	1982800	MPS-MT 1-S4-B RD
Crimping pliers, for ferrules without insulating collar according to DIN 46228 Part 1 and ferrules with insulating collar according to DIN 46228 Part 4, 0.25 mm ² ... 6.0 mm ² , lateral entry, trapezoidal crimp	1212034	CRIMPFOX 6
	3203037	Al 0,25- 8 YE
	3200014	Al 0,5 - 8 WH
	3200881	Al 0,5 - 8 WH -1000
	3201288	Al 0,75-10 GY
	3200182	Al 1 -10 RD
Ferrules, 1.0 mm ² , taped, sleeve length: 8 mm, with plastic collar, galvanically tin-plated, color: red, color range according to DIN 46228-4, CSA-certified	3201385	Al 1 - 8 RD-B
	3202481	A 0,5 - 8
	3202504	A 0,75- 8
	3200234	A 0,75-10
	3202517	A 1 - 8
	3200250	A 1 -10
	3200276	A 1,5 -10

1848642 SDDC 1,5/ 2-PV-3,5**25 Combination tests****SDDC 1,5/..-PV**

IEC 61984	IEC 61984			
Mechanical tests (A)				
Insertion/withdrawal force per position	approx. 8 N / 6 N			
Polarization when inserted Requirement >20 N	Test passed			
Contact holder in insert Requirements >20 N	Test passed			
Durability tests (B)				
Contact resistance R ₁ 1st level	1.4 mΩ			
Contact resistance R ₁ 2nd level				
Insertion/withdrawal cycles	25			
Contact resistance R ₂	1.5 mΩ			
Rated impulse voltage at sea level Voltage waveform ≥ (1.2/50 μs)	2.95 kV			
Power-frequency withstand voltage Voltage waveform ≥ (50/60 Hz)	1.39 kV			
Insulation resistance Requirements > 5 MΩ	> 5 MΩ			
Thermal tests (C)				
Tested number of positions	16			
Tested conductor cross section	1.5 mm ²			
Test current	8 A			
Upper limiting temperature Requirements < 100°C	Test passed			
Climatic tests (D)				
Test sequence 1: low temperature storage	-40 °C/2 h			
Test sequence 2: heat storage	100 °C/168 h			
Test sequence 3: noxious gas storage (ISO 6988)	0.2 dm ³ SO ₂ on 300 dm ³ / 40 °C/1 cycle			
Rated impulse voltage at sea level Voltage waveform ≥ (1.2/50 μs)	2.95 kV			
Power-frequency withstand voltage Voltage waveform ≥ (50/60 Hz)	1.39 kV			
Environmental and endurance tests (E)				
Specification	IEC 61984:2008-10			
Degree of protection	Finger safety above the PCB.			