



Safety Data Sheet

Copyright, 2019, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilising 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document group:	34-3734-0	Version number:	3.00
Revision date:	30/08/2019	Supersedes date:	22/10/2018
Transportation version number:	6.00 (02/09/2019)		

This Safety Data Sheet has been prepared in accordance with the REACH Regulation (EC) 1907/2006 and its modifications.

IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green

Product Identification Numbers

62-2854-1446-2 62-2854-3631-7

7100075409 7100097574

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses

Adhesive

1.3. Details of the supplier of the safety data sheet

Address: 3M United Kingdom PLC, 3M Centre, Cain Road, Bracknell, Berkshire, RG12 8HT.
Telephone: +44 (0)1344 858 000
E Mail: tox.uk@mmm.com
Website: www.3M.com/uk

1.4. Emergency telephone number

+44 (0)1344 858 000

This product is a kit or a multipart product which consists of multiple, independently packaged components. A Safety Data Sheet for each of these components is included. Please do not separate the component Safety Data Sheets from this cover page. The document numbers of the MSDSs for components of this product are:

34-3732-4, 34-3730-8

TRANSPORTATION INFORMATION

62-2854-1446-2, 62-2854-3631-7

Not hazardous for transportation

KIT LABEL

2.1. Classification of the substance or mixture

CLP REGULATION (EC) No 1272/2008

CLASSIFICATION:

Serious Eye Damage/Eye Irritation, Category 2 - Eye Irrit. 2; H319

Skin Corrosion/Irritation, Category 2 - Skin Irrit. 2; H315

Skin Sensitization, Category 1 - Skin Sens. 1; H317

Reproductive Toxicity, Category 1B - Repr. 1B; H360

Hazardous to the Aquatic Environment (Chronic), Category 2 - Aquatic Chronic 2; H411

For full text of H phrases, see Section 16.

2.2. Label elements

CLP REGULATION (EC) No 1272/2008

SIGNAL WORD

DANGER.

Symbols:

GHS07 (Exclamation mark) | GHS08 (Health Hazard) | GHS09 (Environment) |

Pictograms



Contains:

Tert-butyl 3,5,5-trimethylperoxyhexanoate; Tetrahydrofurfuryl methacrylate; 2-hydroxyethyl methacrylate

HAZARD STATEMENTS:

H319 Causes serious eye irritation.
H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H360D May damage the unborn child.

H411 Toxic to aquatic life with long lasting effects.

PRECAUTIONARY STATEMENTS

Prevention:

P201 Obtain special instructions before use.
P280E Wear protective gloves.

Response:

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P333 + P313 If skin irritation or rash occurs: Get medical advice/attention.
P308 + P313 If exposed or concerned: Get medical advice/attention.

Disposal:

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green
--

P501 Dispose of contents/container in accordance with applicable local/regional/national/international regulations.

For containers not exceeding 125 ml the following Hazard and Precautionary statements may be used:

<=125 ml Hazard statements

H317 May cause an allergic skin reaction.
H360D May damage the unborn child.

<=125 ml Precautionary statements

Prevention:

P201 Obtain special instructions before use.
P280E Wear protective gloves.

Response:

P333 + P313 If skin irritation or rash occurs: Get medical advice/attention.
P308 + P313 IF exposed or concerned: Get medical advice/attention.

SUPPLEMENTAL INFORMATION:

Supplemental Precautionary Statements:

Restricted to professional users.

Refer to Safety Data Sheet for component % unknown values (www.3M.com/msds).

Notes on labelling

The organic peroxide classification from CAS# 13122-18-4 does not apply to the material. The calculated available oxygen content is less than 1%.

Revision information:

Kit: Component document group number(s) information was modified.
Label: CLP Classification information was modified.
Label: CLP Environmental Hazard Statements information was modified.



Safety Data Sheet

Copyright, 2018, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilising 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document group:	34-3732-4	Version number:	2.02
Revision date:	11/10/2018	Supersedes date:	10/09/2018
Transportation version number: 1.00 (28/09/2016)			

This Safety Data Sheet has been prepared in accordance with the REACH Regulation (EC) 1907/2006 and its modifications.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green, Part A

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses

Adhesive

1.3. Details of the supplier of the safety data sheet

Address: 3M United Kingdom PLC, 3M Centre, Cain Road, Bracknell, Berkshire, RG12 8HT.
Telephone: +44 (0)1344 858 000
E Mail: tox.uk@mmm.com
Website: www.3M.com/uk

1.4. Emergency telephone number

+44 (0)1344 858 000

SECTION 2: Hazard identification

2.1. Classification of the substance or mixture

CLP REGULATION (EC) No 1272/2008

CLASSIFICATION:

Skin Sensitization, Category 1B - Skin Sens. 1B; H317

Hazardous to the Aquatic Environment (Chronic), Category 2 - Aquatic Chronic 2; H411

For full text of H phrases, see Section 16.

2.2. Label elements

CLP REGULATION (EC) No 1272/2008

SIGNAL WORD

WARNING.

Symbols:

GHS07 (Exclamation mark) | GHS09 (Environment) |

Pictograms



Ingredients:

Ingredient	CAS Nbr	EC No.	% by Wt
Tert-butyl 3,5,5-trimethylperoxyhexanoate	13122-18-4	236-050-7	1 - 10

HAZARD STATEMENTS:

H317	May cause an allergic skin reaction.
H411	Toxic to aquatic life with long lasting effects.

PRECAUTIONARY STATEMENTS

Prevention:

P280E	Wear protective gloves.
P273	Avoid release to the environment.

Response:

P333 + P313	If skin irritation or rash occurs: Get medical advice/attention.
-------------	--

Disposal:

P501	Dispose of contents/container in accordance with applicable local/regional/national/international regulations.
------	--

For containers not exceeding 125 ml the following Hazard and Precautionary statements may be used:

<=125 ml Hazard statements

H317	May cause an allergic skin reaction.
------	--------------------------------------

<=125 ml Precautionary statements

Prevention:

P280E	Wear protective gloves.
-------	-------------------------

Response:

P333 + P313	If skin irritation or rash occurs: Get medical advice/attention.
-------------	--

Contains 34% of components with unknown hazards to the aquatic environment.

Notes on labelling

The organic peroxide classification from CAS# 13122-18-4 does not apply to the material. The calculated available oxygen content is less than 1%.

2.3. Other hazards

None known.

SECTION 3: Composition/information on ingredients

Ingredient	CAS Nbr	EC No.	REACH Registration No.	% by Wt	Classification
Oxydipropyl dibenzoate	27138-31-4	248-258-5		50 - 80	Aquatic Chronic 3, H412
Styrene, polymer with 1,3-Butadiene, butylacrylate and methyl methacrylate	25101-28-4			5 - 30	Substance not classified as hazardous
Catalyst (NJTS Reg. No. 04499600-6922)	Trade Secret			1 - 20	Substance not classified as hazardous
Tert-butyl 3,5,5-trimethylperoxyhexanoate	13122-18-4	236-050-7		1 - 10	Org. Perox. CD, H242; Aquatic Acute 1, H400,M=1; Aquatic Chronic 1, H410,M=1 Skin Sens. 1B, H317

Please see section 16 for the full text of any H statements referred to in this section

For information on ingredient occupational exposure limits or PBT or vPvB status, see sections 8 and 12 of this SDS

SECTION 4: First aid measures**4.1. Description of first aid measures****Inhalation**

Remove person to fresh air. If you feel unwell, get medical attention.

Skin contact

Immediately wash with soap and water. Remove contaminated clothing and wash before reuse. If signs/symptoms develop, get medical attention.

Eye contact

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

If swallowed

Rinse mouth. If you feel unwell, get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1 Information on toxicological effects

4.3. Indication of any immediate medical attention and special treatment required

Not applicable

SECTION 5: Fire-fighting measures**5.1. Extinguishing media**

In case of fire: Use a fire fighting agent suitable for ordinary combustible material such as water or foam to extinguish.

5.2. Special hazards arising from the substance or mixture

None inherent in this product.

Hazardous Decomposition or By-Products

Substance

Hydrocarbons.
Carbon monoxide.
Carbon dioxide.

Condition

During combustion.
During combustion.
During combustion.

5.3. Advice for fire-fighters

Wear full protective clothing, including helmet, self-contained, positive pressure or pressure demand breathing apparatus, bunker coat and pants, bands around arms, waist and legs, face mask, and protective covering for exposed areas of the head.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate area. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapours, in accordance with good industrial hygiene practice. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Contain spill. Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Remember, adding an absorbent material does not remove a physical, health, or environmental hazard. Collect as much of the spilled material as possible. Place in a closed container approved for transportation by appropriate authorities. Clean up residue with an appropriate solvent selected by a qualified and authorised person. Ventilate the area with fresh air. Read and follow safety precautions on the solvent label and Safety Data Sheet. Seal the container. Dispose of collected material as soon as possible.

6.4. Reference to other sections

Refer to Section 8 and Section 13 for more information

SECTION 7: Handling and storage

7.1. Precautions for safe handling

For industrial/occupational use only. Not for consumer sale or use. Avoid breathing dust/fume/gas/mist/vapours/spray. Do not get in eyes, on skin, or on clothing. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Avoid release to the environment. Wash contaminated clothing before reuse. Avoid contact with oxidising agents (eg. chlorine, chromic acid etc.)

7.2. Conditions for safe storage including any incompatibilities

Store away from heat. Store away from acids. Store away from strong bases. Store away from oxidising agents. Store away from amines.

7.3. Specific end use(s)

See information in Section 7.1 and 7.2 for handling and storage recommendations. See Section 8 for exposure controls and personal protection recommendations.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational exposure limits

No occupational exposure limit values exist for any of the components listed in Section 3 of this Safety Data Sheet.

Biological limit values

No biological limit values exist for any of the components listed in Section 3 of this safety data sheet.

8.2. Exposure controls**8.2.1. Engineering controls**

Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapours/spray. If ventilation is not adequate, use respiratory protection equipment.

8.2.2. Personal protective equipment (PPE)**Eye/face protection**

Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:

Safety glasses with side shields.

Applicable Norms/Standards

Use eye protection conforming to EN 166

Skin/hand protection

Select and use gloves and/or protective clothing approved to relevant local standards to prevent skin contact based on the results of an exposure assessment. Selection should be based on use factors such as exposure levels, concentration of the substance or mixture, frequency and duration, physical challenges such as temperature extremes, and other use conditions. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible gloves/protective clothing. When only incidental contact is anticipated, alternative glove material(s) may be used. If contact with the glove does occur, remove immediately and replace with a set of new gloves. For incidental contact, gloves made of nitrile rubber are recommended. Note: Nitrile gloves may be worn over polymer laminate gloves to improve dexterity.

Gloves made from the following material(s) are recommended:

Material	Thickness (mm)	Breakthrough Time
Polymer laminate	No data available	No data available

Applicable Norms/Standards

Use gloves tested to EN 374

Respiratory protection

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for organic vapours and particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

Applicable Norms/Standards

Use a respirator conforming to EN 140 or EN 136: filter types A & P

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Physical state	Liquid.
Specific Physical Form:	Paste
Appearance/Odour	Blue, hydrocarbon odour
Odour threshold	No data available.

pH	<i>Not applicable.</i>
Boiling point/boiling range	≥ 65.6 °C
Melting point	<i>Not applicable.</i>
Flammability (solid, gas)	Not applicable.
Explosive properties	Not classified
Oxidising properties	Not classified
Flash point	> 93.3 °C [Test Method: Closed Cup]
Autoignition temperature	<i>No data available.</i>
Flammable Limits(LEL)	<i>No data available.</i>
Flammable Limits(UEL)	<i>No data available.</i>
Vapour pressure	<i>No data available.</i>
Relative density	1.08 [Ref Std: WATER=1]
Water solubility	Nil
Solubility- non-water	<i>No data available.</i>
Partition coefficient: n-octanol/water	<i>No data available.</i>
Evaporation rate	<i>No data available.</i>
Vapour density	<i>No data available.</i>
Decomposition temperature	<i>No data available.</i>
Viscosity	20,000 mPa-s
Density	1.08 g/ml

9.2. Other information

EU Volatile Organic Compounds	<i>No data available.</i>
Molecular weight	<i>Not applicable.</i>
Percent volatile	<i>No data available.</i>

SECTION 10: Stability and reactivity**10.1 Reactivity**

This material may be reactive with certain agents under certain conditions - see the remaining headings in this section

10.2 Chemical stability

Stable.

10.3 Possibility of hazardous reactions

Hazardous polymerisation will not occur.

10.4 Conditions to avoid

Heat.

Sparks and/or flames.

10.5 Incompatible materials

Amines.

Strong acids.

Strong bases.

Strong oxidising agents.

10.6 Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
None known.	

Refer to section 5.2 for hazardous decomposition products during combustion.

SECTION 11: Toxicological information

The information below may not agree with the EU material classification in Section 2 and/or the ingredient classifications in Section 3 if specific ingredient classifications are mandated by a competent authority. In addition, statements and data presented in Section 11 are based on UN GHS calculation rules and classifications derived from 3M assessments.

11.1 Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation

This product may have a characteristic odour; however, no adverse health effects are anticipated.

Skin contact

Contact with the skin during product use is not expected to result in significant irritation. Allergic skin reaction (non-photo induced): Signs/symptoms may include redness, swelling, blistering, and itching.

Eye contact

Contact with the eyes during product use is not expected to result in significant irritation.

Ingestion

May be harmful if swallowed.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
Overall product	Dermal		No data available; calculated ATE >5,000 mg/kg
Overall product	Ingestion		No data available; calculated ATE 2,000 - 5,000 mg/kg
Oxydipropyl dibenzoate	Dermal	Rat	LD50 > 2,000 mg/kg
Oxydipropyl dibenzoate	Inhalation-Dust/Mist (4 hours)	Rat	LC50 > 200 mg/l
Oxydipropyl dibenzoate	Ingestion	Rat	LD50 3,295 mg/kg
Styrene, polymer with 1,3-Butadiene, butylacrylate and methyl methacrylate	Dermal		LD50 estimated to be > 5,000 mg/kg
Styrene, polymer with 1,3-Butadiene, butylacrylate and methyl methacrylate	Ingestion	Rat	LD50 > 5,000 mg/kg
Catalyst (NJTS Reg. No. 04499600-6922)	Dermal	Professional judgement	LD50 estimated to be 2,000 - 5,000 mg/kg
Catalyst (NJTS Reg. No. 04499600-6922)	Ingestion	Rat	LD50 > 2,000 mg/kg
Tert-butyl 3,5,5-trimethylperoxyhexanoate	Dermal	Rat	LD50 > 2,000 mg/kg
Tert-butyl 3,5,5-trimethylperoxyhexanoate	Inhalation-Dust/Mist (4 hours)	Rat	LC50 > 0.8 mg/l
Tert-butyl 3,5,5-trimethylperoxyhexanoate	Ingestion	Rat	LD50 12,905 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
------	---------	-------

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green, Part A

Oxydipropyl dibenzoate	Rabbit	No significant irritation
Tert-butyl 3,5,5-trimethylperoxyhexanoate	Rabbit	No significant irritation

Serious Eye Damage/Irritation

Name	Species	Value
Oxydipropyl dibenzoate	Rabbit	No significant irritation
Tert-butyl 3,5,5-trimethylperoxyhexanoate	Rabbit	No significant irritation

Skin Sensitisation

Name	Species	Value
Oxydipropyl dibenzoate	Guinea pig	Not classified
Catalyst (NJTS Reg. No. 04499600-6922)	Mouse	Not classified
Tert-butyl 3,5,5-trimethylperoxyhexanoate	Guinea pig	Sensitising

Respiratory Sensitisation

For the component/components, either no data is currently available or the data is not sufficient for classification.

Germ Cell Mutagenicity

Name	Route	Value
Oxydipropyl dibenzoate	In Vitro	Not mutagenic
Catalyst (NJTS Reg. No. 04499600-6922)	In Vitro	Not mutagenic

Carcinogenicity

For the component/components, either no data is currently available or the data is not sufficient for classification.

Reproductive Toxicity**Reproductive and/or Developmental Effects**

Name	Route	Value	Species	Test result	Exposure Duration
Oxydipropyl dibenzoate	Ingestion	Not classified for female reproduction	Rat	NOAEL 500 mg/kg/day	2 generation
Oxydipropyl dibenzoate	Ingestion	Not classified for male reproduction	Rat	NOAEL 400 mg/kg/day	2 generation
Oxydipropyl dibenzoate	Ingestion	Not classified for development	Rat	NOAEL 1,000 mg/kg/day	during gestation

Target Organ(s)**Specific Target Organ Toxicity - single exposure**

Name	Route	Target Organ(s)	Value	Species	Test result	Exposure Duration
Catalyst (NJTS Reg. No. 04499600-6922)	Ingestion	nervous system	Not classified	Rat	NOAEL 2,000 mg/kg	

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test result	Exposure Duration
Oxydipropyl dibenzoate	Ingestion	hematopoietic system liver	Not classified	Rat	NOAEL 2,500 mg/kg/day	90 days

Aspiration Hazard

For the component/components, either no data is currently available or the data is not sufficient for classification.

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green, Part A

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information

The information below may not agree with the EU material classification in Section 2 and/or the ingredient classifications in Section 3 if specific ingredient classifications are mandated by a competent authority. In addition, statements and data presented in Section 12 are based on UN GHS calculation rules and classifications derived from 3M assessments.

12.1. Toxicity

No product test data available.

Material	CAS #	Organism	Type	Exposure	Test endpoint	Test result
Oxydipropyl dibenzoate	27138-31-4	Fathead minnow	Experimental	96 hours	LC50	3.7 mg/l
Oxydipropyl dibenzoate	27138-31-4	Green Algae	Experimental	72 hours	Effect Level 50%	4.9 mg/l
Oxydipropyl dibenzoate	27138-31-4	Water flea	Experimental	48 hours	Effect Level 50%	19.31 mg/l
Oxydipropyl dibenzoate	27138-31-4	Green Algae	Experimental	72 hours	Effect Concentration 10%	0.89 mg/l
Styrene, polymer with 1,3-Butadiene, butylacrylate and methyl methacrylate	25101-28-4		Data not available or insufficient for classification			
Catalyst (NJTS Reg. No. 04499600-6922)	Trade Secret		Data not available or insufficient for classification			
Tert-butyl 3,5,5-trimethylperoxyhexanoate	13122-18-4	Green Algae	Experimental		EC50	0.51 mg/l
Tert-butyl 3,5,5-trimethylperoxyhexanoate	13122-18-4	Rainbow trout	Experimental		LC50	7 mg/l
Tert-butyl 3,5,5-trimethylperoxyhexanoate	13122-18-4	Water flea	Experimental		EC50	>100 mg/l
Tert-butyl 3,5,5-trimethylperoxyhexanoate	13122-18-4	Green Algae	Experimental		NOEC	0.125 mg/l

12.2. Persistence and degradability

Material	CAS Nbr	Test type	Duration	Study Type	Test result	Protocol
Oxydipropyl dibenzoate	27138-31-4	Experimental Biodegradation	28 days	CO2 evolution	85 % weight	OECD 301B - Modified sturm or CO2
Styrene, polymer with 1,3-Butadiene, butylacrylate and methyl methacrylate	25101-28-4	Data not availbl-insufficient			N/A	
Catalyst (NJTS Reg. No. 04499600-6922)	Trade Secret	Data not availbl-insufficient			N/A	
Tert-butyl 3,5,5-trimethylperoxyhexanoate	13122-18-4	Estimated Biodegradation	28	BOD	14 % BOD/ThBOD	OECD 301C - MITI test (I)

12.3 : Bioaccumulative potential

Material	Cas No.	Test type	Duration	Study Type	Test result	Protocol
Oxydipropyl dibenzoate	27138-31-4	Estimated Bioconcentration		Bioaccumulation factor	8	Estimated: Bioconcentration factor

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green, Part A

Styrene, polymer with 1,3-Butadiene, butylacrylate and methyl methacrylate	25101-28-4	Data not available or insufficient for classification	N/A	N/A	N/A	N/A
Catalyst (NJTS Reg. No. 04499600-6922)	Trade Secret	Estimated Bioconcentration		Bioaccumulation factor	4.8	Estimated: Bioconcentration factor
Tert-butyl 3,5,5-trimethylperoxyhexanoate	13122-18-4	Estimated Bioconcentration		Bioaccumulation factor	363	Estimated: Bioconcentration factor

12.4. Mobility in soil

Please contact manufacturer for more details

12.5. Results of the PBT and vPvB assessment

This material does not contain any substances that are assessed to be a PBT or vPvB

12.6. Other adverse effects

No information available.

SECTION 13: Disposal considerations**13.1 Waste treatment methods**

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Dispose of completely cured (or polymerized) material in a permitted industrial waste facility. As a disposal alternative, incinerate uncured product in a permitted waste incineration facility. Proper destruction may require the use of additional fuel during incineration processes. Empty drums/barrels/containers used for transporting and handling hazardous chemicals (chemical substances/mixtures/preparations classified as Hazardous as per applicable regulations) shall be considered, stored, treated & disposed of as hazardous wastes unless otherwise defined by applicable waste regulations. Consult with the respective regulating authorities to determine the available treatment and disposal facilities.

The coding of a waste stream is based on the application of the product by the consumer. Since this is out of the control of 3M, no waste code(s) for products after use will be provided. Please refer to the European Waste Code (EWC - 2000/532/EC and amendments) to assign the correct waste code to your waste stream. Ensure national and/or regional regulations are complied with and always use a licensed waste contractor.

EU waste code (product as sold)

08 04 09* Waste adhesives and sealants containing organic solvents or other dangerous substances
20 01 27* Paint, inks, adhesives and resins containing dangerous substances

SECTION 14: Transportation information

ADR/IATA/IMDG: Not restricted for transport.

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture****Global inventory status**

Contact 3M for more information. The components of this product are in compliance with the new substance notification requirements of CEPA. The components of this product are in compliance with the chemical notification requirements of TSCA.

15.2. Chemical Safety Assessment

A chemical safety assessment has not been carried out for this substance/mixture in accordance with Regulation (EC) No 1907/2006, as amended.

SECTION 16: Other information

List of relevant H statements

H242	Heating may cause a fire.
H317	May cause an allergic skin reaction.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

Revision information:

Section 7: Precautions safe handling information information was modified.

Section 14: Transportation classification information was modified.

DISCLAIMER: The information on this Safety Data Sheet is based on our experience and is correct to the best of our knowledge at the date of publication, but we do not accept any liability for any loss, damage or injury resulting from its use (except as required by law). The information may not be valid for any use not referred to in this Data Sheet or use of the product in combination with other materials. For these reasons, it is important that customers carry out their own test to satisfy themselves as to the suitability of the product for their own intended applications.

3M United Kingdom MSDSs are available at www.3M.com/uk



Safety Data Sheet

Copyright, 2019, 3M Company All rights reserved. Copying and/or downloading of this information for the purpose of properly utilising 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document group:	34-3730-8	Version number:	4.00
Revision date:	03/09/2019	Supersedes date:	30/08/2019
Transportation version number: 5.00 (02/09/2019)			

This Safety Data Sheet has been prepared in accordance with the REACH Regulation (EC) 1907/2006 and its modifications.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green and Low Odor Acrylic Adhesive 8810NS Green, Part B

Product Identification Numbers

62-2854-9531-3

7100097626

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses

Adhesive

1.3. Details of the supplier of the safety data sheet

Address:	3M United Kingdom PLC, 3M Centre, Cain Road, Bracknell, Berkshire, RG12 8HT.
Telephone:	+44 (0)1344 858 000
E Mail:	tox.uk@mmm.com
Website:	www.3M.com/uk

1.4. Emergency telephone number

+44 (0)1344 858 000

SECTION 2: Hazard identification

2.1. Classification of the substance or mixture

CLP REGULATION (EC) No 1272/2008

CLASSIFICATION:

Serious Eye Damage/Eye Irritation, Category 2 - Eye Irrit. 2; H319

Skin Corrosion/Irritation, Category 2 - Skin Irrit. 2; H315

Skin Sensitization, Category 1 - Skin Sens. 1; H317

Reproductive Toxicity, Category 1B - Repr. 1B; H360

Hazardous to the Aquatic Environment (Chronic), Category 3 - Aquatic Chronic 3; H412

For full text of H phrases, see Section 16.

2.2. Label elements

CLP REGULATION (EC) No 1272/2008

SIGNAL WORD

DANGER.

Symbols:

GHS07 (Exclamation mark) | GHS08 (Health Hazard) |

Pictograms



Ingredients:

Ingredient	CAS Nbr	EC No.	% by Wt
Tetrahydrofurfuryl methacrylate	2455-24-5	219-529-5	30 - 45
2-Hydroxyethyl methacrylate	868-77-9	212-782-2	10 - 20

HAZARD STATEMENTS:

H319	Causes serious eye irritation.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H360D	May damage the unborn child.
H412	Harmful to aquatic life with long lasting effects.

PRECAUTIONARY STATEMENTS

Prevention:

P201	Obtain special instructions before use.
P280E	Wear protective gloves.

Response:

P305 + P351 + P338	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P333 + P313	If skin irritation or rash occurs: Get medical advice/attention.
P308 + P313	IF exposed or concerned: Get medical advice/attention.

Disposal:

P501	Dispose of contents/container in accordance with applicable local/regional/national/international regulations.
------	--

For containers not exceeding 125 ml the following Hazard and Precautionary statements may be used:

<=125 ml Hazard statements

H317	May cause an allergic skin reaction.
H360D	May damage the unborn child.

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green and Low Odor Acrylic Adhesive 8810NS Green, Part B

H412 Harmful to aquatic life with long lasting effects.

<=125 ml Precautionary statements**Prevention:**

P201 Obtain special instructions before use.
P280E Wear protective gloves.

Response:

P333 + P313 If skin irritation or rash occurs: Get medical advice/attention.
P308 + P313 IF exposed or concerned: Get medical advice/attention.

SUPPLEMENTAL INFORMATION:**Supplemental Precautionary Statements:**

Restricted to professional users.

2% of the mixture consists of components of unknown acute oral toxicity.

Contains 6% of components with unknown hazards to the aquatic environment.

2.3. Other hazards

None known.

SECTION 3: Composition/information on ingredients

Ingredient	CAS Nbr	EC No.	REACH Registration No.	% by Wt	Classification
Tetrahydrofurfuryl methacrylate	2455-24-5	219-529-5		30 - 45	Skin Sens. 1, H317; Repr. 1B, H360D; Aquatic Chronic 3, H412
Acrylonitrile - butadiene polymer	9003-18-3			10 - 20	Substance not classified as hazardous
2-Hydroxyethyl methacrylate	868-77-9	212-782-2		10 - 20	Skin Irrit. 2, H315; Eye Irrit. 2, H319; Skin Sens. 1, H317 - Nota D
Exo-1,7,7-trimethylbicyclo[2.2.1]hept-2-yl methacrylate	7534-94-3	231-403-1		10 - 15	Aquatic Chronic 3, H412
Fillers (NJTS Reg. No. 04499600-6923)	Trade Secret			5 - 10	Substance with a Community level exposure limit in the workplace
BIS-MEPP (polymer)	41637-38-1			1 - 7	Substance not classified as hazardous
Poly[oxy(methyl-1,2-ethanediyl)], .a.-(2-methyl-1-oxo-2-propenyl)-.w.-(phosphonoxy)-	95175-93-2			< 3	Skin Irrit. 2, H315; Eye Dam. 1, H318
Tetrahydrofurfuryl alcohol	97-99-4	202-625-6		< 1	Eye Irrit. 2, H319; Repr. 1B, H360Df
Naphthenic acids, copper salts	1338-02-9	215-657-0		< 0.1	Flam. Liq. 3, H226; Acute Tox. 4, H302; Aquatic Acute 1, H400,M=10; Aquatic Chronic 1, H410,M=1

Please see section 16 for the full text of any H statements referred to in this section

For information on ingredient occupational exposure limits or PBT or vPvB status, see sections 8 and 12 of this SDS

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation

Remove person to fresh air. If you feel unwell, get medical attention.

Skin contact

Immediately wash with soap and water. Remove contaminated clothing and wash before reuse. If signs/symptoms develop, get medical attention.

Eye contact

Immediately flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. Get medical attention.

If swallowed

Rinse mouth. If you feel unwell, get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1 Information on toxicological effects

4.3. Indication of any immediate medical attention and special treatment required

Not applicable

SECTION 5: Fire-fighting measures

5.1. Extinguishing media

In case of fire: Use a fire fighting agent suitable for ordinary combustible material such as water or foam to extinguish.

5.2. Special hazards arising from the substance or mixture

None inherent in this product.

Hazardous Decomposition or By-Products

Substance

Carbon monoxide.
Carbon dioxide.
Hydrogen Chloride
Oxides of nitrogen.

Condition

During combustion.
During combustion.
During combustion.
During combustion.

5.3. Advice for fire-fighters

Wear full protective clothing, including helmet, self-contained, positive pressure or pressure demand breathing apparatus, bunker coat and pants, bands around arms, waist and legs, face mask, and protective covering for exposed areas of the head.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Evacuate area. Ventilate the area with fresh air. For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapours, in accordance with good industrial hygiene practice. Refer to other sections of this SDS for information regarding physical and health hazards, respiratory protection, ventilation, and personal protective equipment.

6.2. Environmental precautions

Avoid release to the environment. For larger spills, cover drains and build dykes to prevent entry into sewer systems or bodies of water.

6.3. Methods and material for containment and cleaning up

Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Remember, adding an absorbent material does not remove a physical, health, or environmental hazard. Collect as much of the spilled material as possible. Place in a closed container approved for transportation by appropriate authorities. Clean up residue with an appropriate solvent selected by a qualified and authorised person. Ventilate the area with fresh air. Read and follow safety precautions on the solvent label and Safety Data Sheet. Seal the container. Dispose of collected material as soon as possible.

6.4. Reference to other sections

Refer to Section 8 and Section 13 for more information

SECTION 7: Handling and storage

7.1. Precautions for safe handling

For industrial/occupational use only. Not for consumer sale or use. Do not handle until all safety precautions have been read and understood. Do not breathe dust/fume/gas/mist/vapours/spray. Do not get in eyes, on skin, or on clothing. Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Contaminated work clothing should not be allowed out of the workplace. Avoid release to the environment. Wash contaminated clothing before reuse. Avoid contact with oxidising agents (eg. chlorine, chromic acid etc.) Use personal protective equipment (eg. gloves, respirators...) as required.

7.2. Conditions for safe storage including any incompatibilities

Store away from heat. Store away from acids. Store away from strong bases. Store away from oxidising agents. Store away from amines.

7.3. Specific end use(s)

See information in Section 7.1 and 7.2 for handling and storage recommendations. See Section 8 for exposure controls and personal protection recommendations.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational exposure limits

If a component is disclosed in section 3 but does not appear in the table below, an occupational exposure limit is not available for the component.

Ingredient	CAS Nbr	Agency	Limit type	Additional comments
Fillers (NJTS Reg. No. 04499600-6923)	Trade Secret	UK HSC	TWA(as inhalable dust):10 mg/m ³ ;TWA(as respirable dust):2 mg/m ³	

UK HSC : UK Health and Safety Commission

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit

CEIL: Ceiling

Biological limit values

No biological limit values exist for any of the components listed in Section 3 of this safety data sheet.

Recommended monitoring procedures:Information on recommended monitoring procedures can be obtained from UK HSC

8.2. Exposure controls

8.2.1. Engineering controls

Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapours/spray. If ventilation is not adequate, use respiratory protection equipment.

8.2.2. Personal protective equipment (PPE)

Eye/face protection

Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:

Indirect vented goggles.

Applicable Norms/Standards

Use eye protection conforming to EN 166

Skin/hand protection

Select and use gloves and/or protective clothing approved to relevant local standards to prevent skin contact based on the results of an exposure assessment. Selection should be based on use factors such as exposure levels, concentration of the substance or mixture, frequency and duration, physical challenges such as temperature extremes, and other use conditions. Consult with your glove and/or protective clothing manufacturer for selection of appropriate compatible gloves/protective clothing. Note: Nitrile gloves may be worn over polymer laminate gloves to improve dexterity.

Gloves made from the following material(s) are recommended:

Material	Thickness (mm)	Breakthrough Time
Polymer laminate	No data available	No data available

When only incidental contact is anticipated, alternative glove material(s) may be used. If contact with the glove does occur, remove immediately and replace with a set of new gloves. For incidental contact, gloves made of the following material(s) may be used: Nitrile rubber.

Applicable Norms/Standards

Use gloves tested to EN 374

Respiratory protection

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for organic vapours and particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

Applicable Norms/Standards

Use a respirator conforming to EN 140 or EN 136: filter types A & P

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Physical state

Liquid.

Colour

White

Specific Physical Form:

Paste

Odor	Acrylate
Odour threshold	<i>No data available.</i>
pH	<i>Not applicable.</i>
Boiling point/boiling range	$\geq 37.8\text{ }^{\circ}\text{C}$
Melting point	<i>Not applicable.</i>
Flammability (solid, gas)	Not applicable.
Explosive properties	Not classified
Oxidising properties	Not classified
Flash point	$> 93.3\text{ }^{\circ}\text{C}$ [Test Method: Closed Cup]
Autoignition temperature	<i>No data available.</i>
Flammable Limits(LEL)	<i>No data available.</i>
Flammable Limits(UEL)	<i>No data available.</i>
Vapour pressure	<i>No data available.</i>
Relative density	1.13 [Ref Std: WATER=1]
Water solubility	Nil
Solubility- non-water	<i>No data available.</i>
Partition coefficient: n-octanol/water	<i>No data available.</i>
Evaporation rate	<i>No data available.</i>
Vapour density	<i>No data available.</i>
Decomposition temperature	<i>No data available.</i>
Viscosity	100,000 - 125,000 mPa-s
Density	1.13 g/ml

9.2. Other information

EU Volatile Organic Compounds

No data available.

Molecular weight

Not applicable.

SECTION 10: Stability and reactivity

10.1 Reactivity

This material may be reactive with certain agents under certain conditions - see the remaining headings in this section

10.2 Chemical stability

Stable.

10.3 Possibility of hazardous reactions

Hazardous polymerisation will not occur.

10.4 Conditions to avoid

Heat.

Sparks and/or flames.

10.5 Incompatible materials

Amines.

Strong acids.

Strong bases.

Strong oxidising agents.

10.6 Hazardous decomposition products

Substance

Condition

None known.

Refer to section 5.2 for hazardous decomposition products during combustion.

SECTION 11: Toxicological information

The information below may not agree with the EU material classification in Section 2 and/or the ingredient classifications in Section 3 if specific ingredient classifications are mandated by a competent authority. In addition, statements and data presented in Section 11 are based on UN GHS calculation rules and classifications derived from 3M assessments.

11.1 Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation

Respiratory tract irritation: Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain. May cause additional health effects (see below).

Skin contact

Mild Skin Irritation: Signs/symptoms may include localised redness, swelling, itching, and dryness. Allergic skin reaction (non-photo induced): Signs/symptoms may include redness, swelling, blistering, and itching. May cause additional health effects (see below).

Eye contact

Severe eye irritation: Signs/symptoms may include significant redness, swelling, pain, tearing, cloudy appearance of the cornea, and impaired vision.

Ingestion

Gastrointestinal irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhoea. May cause additional health effects (see below).

Additional Health Effects:

Reproductive/Developmental Toxicity:

Contains a chemical or chemicals which can cause birth defects or other reproductive harm.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
Overall product	Dermal		No data available; calculated ATE >5,000 mg/kg
Overall product	Ingestion		No data available; calculated ATE >5,000 mg/kg
Tetrahydrofurfuryl methacrylate	Ingestion	Rat	LD50 4,000 mg/kg
Tetrahydrofurfuryl methacrylate	Dermal	similar health hazards	LD50 estimated to be 2,000 - 5,000 mg/kg
2-Hydroxyethyl methacrylate	Dermal	Rabbit	LD50 > 5,000 mg/kg
2-Hydroxyethyl methacrylate	Ingestion	Rat	LD50 5,564 mg/kg
Acrylonitrile - butadiene polymer	Dermal	Rabbit	LD50 > 15,000 mg/kg
Acrylonitrile - butadiene polymer	Ingestion	Rat	LD50 > 30,000 mg/kg
Exo-1,7,7-trimethylbicyclo[2.2.1]hept-2-yl methacrylate	Dermal	Rabbit	LD50 > 3,000 mg/kg
Exo-1,7,7-trimethylbicyclo[2.2.1]hept-2-yl methacrylate	Ingestion	Rat	LD50 > 2,000 mg/kg
Fillers (NJTS Reg. No. 04499600-6923)	Dermal		LD50 estimated to be > 5,000 mg/kg
Fillers (NJTS Reg. No. 04499600-6923)	Ingestion	Human	LD50 > 15,000 mg/kg
BIS-MEPP (polymer)	Dermal	Rat	LD50 > 2,000 mg/kg
BIS-MEPP (polymer)	Ingestion	Rat	LD50 > 35,000 mg/kg

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green and Low Odor Acrylic Adhesive 8810NS Green, Part B

Poly[oxy(methyl-1,2-ethanediyl)], .a.-(2-methyl-1-oxo-2-propenyl)-.w.-(phosphonooxy)-	Ingestion	Rat	LD50 > 5,000 mg/kg
Poly[oxy(methyl-1,2-ethanediyl)], .a.-(2-methyl-1-oxo-2-propenyl)-.w.-(phosphonooxy)-	Dermal	similar health hazards	LD50 estimated to be > 5,000 mg/kg
Tetrahydrofurfuryl alcohol	Dermal	Professional judgement	LD50 estimated to be 2,000 - 5,000 mg/kg
Tetrahydrofurfuryl alcohol	Inhalation-Vapour (4 hours)	Rat	LC50 > 3.1 mg/l
Tetrahydrofurfuryl alcohol	Ingestion	Rat	LD50 > 2,000 mg/kg
Naphthenic acids, copper salts	Dermal	similar compounds	LD50 > 2,000 mg/kg
Naphthenic acids, copper salts	Ingestion	similar compounds	LD50 > 300, < 2,000 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
Tetrahydrofurfuryl methacrylate	Rabbit	No significant irritation
2-Hydroxyethyl methacrylate	Rabbit	Minimal irritation
Acrylonitrile - butadiene polymer	Professional judgement	No significant irritation
Exo-1,7,7-trimethylbicyclo[2.2.1]hept-2-yl methacrylate	Rabbit	Mild irritant
Fillers (NJTS Reg. No. 04499600-6923)	Professional judgement	No significant irritation
BIS-MEPP (polymer)	Rabbit	Minimal irritation
Poly[oxy(methyl-1,2-ethanediyl)], .a.-(2-methyl-1-oxo-2-propenyl)-.w.-(phosphonooxy)-	Not available	Irritant
Tetrahydrofurfuryl alcohol	Rabbit	No significant irritation
Naphthenic acids, copper salts	Rabbit	No significant irritation

Serious Eye Damage/Irritation

Name	Species	Value
Tetrahydrofurfuryl methacrylate	Rabbit	No significant irritation
2-Hydroxyethyl methacrylate	Rabbit	Moderate irritant
Acrylonitrile - butadiene polymer	Professional judgement	No significant irritation
Exo-1,7,7-trimethylbicyclo[2.2.1]hept-2-yl methacrylate	Rabbit	Mild irritant
Fillers (NJTS Reg. No. 04499600-6923)	Professional judgement	No significant irritation
BIS-MEPP (polymer)	Rabbit	No significant irritation
Poly[oxy(methyl-1,2-ethanediyl)], .a.-(2-methyl-1-oxo-2-propenyl)-.w.-(phosphonooxy)-	Not available	Corrosive
Tetrahydrofurfuryl alcohol	Rabbit	Severe irritant
Naphthenic acids, copper salts	In vitro data	No significant irritation

Skin Sensitisation

Name	Species	Value
------	---------	-------

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green and Low Odor Acrylic Adhesive 8810NS Green, Part B

Tetrahydrofurfuryl methacrylate	In vitro data	Sensitising
2-Hydroxyethyl methacrylate	Human and animal	Sensitising
Exo-1,7,7-trimethylbicyclo[2.2.1]hept-2-yl methacrylate	Guinea pig	Not classified
BIS-MEPP (polymer)	Guinea pig	Not classified
Tetrahydrofurfuryl alcohol	Mouse	Not classified
Naphthenic acids, copper salts	Guinea pig	Not classified

Respiratory Sensitisation

For the component/components, either no data is currently available or the data is not sufficient for classification.

Germ Cell Mutagenicity

Name	Route	Value
Tetrahydrofurfuryl methacrylate	In Vitro	Not mutagenic
2-Hydroxyethyl methacrylate	In vivo	Not mutagenic
2-Hydroxyethyl methacrylate	In Vitro	Some positive data exist, but the data are not sufficient for classification
BIS-MEPP (polymer)	In Vitro	Not mutagenic
Tetrahydrofurfuryl alcohol	In Vitro	Not mutagenic

Carcinogenicity

Name	Route	Species	Value
Fillers (NJTS Reg. No. 04499600-6923)	Inhalation	Multiple animal species	Not carcinogenic

Reproductive Toxicity
Reproductive and/or Developmental Effects

Name	Route	Value	Species	Test result	Exposure Duration
Tetrahydrofurfuryl methacrylate	Ingestion	Not classified for male reproduction	Rat	NOAEL 300 mg/kg/day	29 days
Tetrahydrofurfuryl methacrylate	Ingestion	Toxic to female reproduction	Rat	NOAEL 120 mg/kg/day	premating into lactation
Tetrahydrofurfuryl methacrylate	Ingestion	Toxic to development	Rat	NOAEL 120 mg/kg/day	premating into lactation
2-Hydroxyethyl methacrylate	Ingestion	Not classified for female reproduction	Rat	NOAEL 1,000 mg/kg/day	premating & during gestation
2-Hydroxyethyl methacrylate	Ingestion	Not classified for male reproduction	Rat	NOAEL 1,000 mg/kg/day	49 days
2-Hydroxyethyl methacrylate	Ingestion	Not classified for development	Rat	NOAEL 1,000 mg/kg/day	premating & during gestation
Tetrahydrofurfuryl alcohol	Ingestion	Toxic to female reproduction	Rat	NOAEL 50 mg/kg/day	premating into lactation
Tetrahydrofurfuryl alcohol	Dermal	Toxic to male reproduction	Rat	NOAEL 100 mg/kg/day	13 weeks
Tetrahydrofurfuryl alcohol	Ingestion	Toxic to male reproduction	Rat	NOAEL 150 mg/kg/day	47 days
Tetrahydrofurfuryl alcohol	Inhalation	Toxic to male reproduction	Rat	NOAEL 0.6 mg/l	90 days
Tetrahydrofurfuryl alcohol	Ingestion	Toxic to development	Rat	NOAEL 50 mg/kg/day	premating into lactation

Target Organ(s)

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green and Low Odor Acrylic Adhesive 8810NS Green, Part B**Specific Target Organ Toxicity - single exposure**

Name	Route	Target Organ(s)	Value	Species	Test result	Exposure Duration
Poly[oxy(methyl-1,2-ethanediyl)], .a.-(2-methyl-1-oxo-2-propenyl)-.w.-(phosphonoxy)-	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification	similar health hazards	NOAEL Not available	
Tetrahydrofurfuryl alcohol	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification	similar health hazards	NOAEL Not available	

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test result	Exposure Duration
Tetrahydrofurfuryl methacrylate	Ingestion	hematopoietic system nervous system	Not classified	Rat	NOAEL 300 mg/kg/day	29 days
Fillers (NJTS Reg. No. 04499600-6923)	Inhalation	pneumoconiosis	Causes damage to organs through prolonged or repeated exposure	Human	NOAEL NA	occupational exposure
Fillers (NJTS Reg. No. 04499600-6923)	Inhalation	pulmonary fibrosis	Not classified	Rat	NOAEL Not available	
Tetrahydrofurfuryl alcohol	Inhalation	nervous system	Causes damage to organs through prolonged or repeated exposure	Rat	LOAEL 0.2 mg/l	90 days
Tetrahydrofurfuryl alcohol	Inhalation	hematopoietic system	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 0.6 mg/l	90 days
Tetrahydrofurfuryl alcohol	Inhalation	eyes	Not classified	Rat	NOAEL 2.1 mg/l	90 days
Tetrahydrofurfuryl alcohol	Ingestion	hematopoietic system	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 69 mg/kg/day	91 days
Tetrahydrofurfuryl alcohol	Ingestion	immune system	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 150 mg/kg/day	28 days
Tetrahydrofurfuryl alcohol	Ingestion	endocrine system kidney and/or bladder	Not classified	Rat	NOAEL 600 mg/kg/day	28 days
Tetrahydrofurfuryl alcohol	Ingestion	liver eyes	Not classified	Rat	NOAEL 781 mg/kg/day	91 days
Tetrahydrofurfuryl alcohol	Ingestion	heart nervous system	Not classified	Rat	NOAEL 600 mg/kg/day	28 days

Aspiration Hazard

For the component/components, either no data is currently available or the data is not sufficient for classification.

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information

The information below may not agree with the EU material classification in Section 2 and/or the ingredient classifications in Section 3 if specific ingredient classifications are mandated by a competent authority. In addition, statements and data presented in Section 12 are based on UN GHS calculation rules and classifications derived from 3M assessments.

12.1. Toxicity

No product test data available.

Material	CAS #	Organism	Type	Exposure	Test endpoint	Test result
----------	-------	----------	------	----------	---------------	-------------

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green and Low Odor Acrylic Adhesive 8810NS Green, Part B

Tetrahydrofurfuryl methacrylate	2455-24-5	Fathead minnow	Experimental	96 hours	LC50	34.7 mg/l
Tetrahydrofurfuryl methacrylate	2455-24-5	Green algae	Experimental	72 hours	EC50	>100 mg/l
Tetrahydrofurfuryl methacrylate	2455-24-5	Green algae	Experimental	72 hours	Effect Concentration 10%	>100 mg/l
Tetrahydrofurfuryl methacrylate	2455-24-5	Water flea	Experimental	21 days	NOEC	37.2 mg/l
Acrylonitrile - butadiene polymer	9003-18-3		Data not available or insufficient for classification			
2-Hydroxyethyl methacrylate	868-77-9	Fathead minnow	Experimental	96 hours	LC50	227 mg/l
2-Hydroxyethyl methacrylate	868-77-9	Green algae	Experimental	72 hours	EC50	710 mg/l
2-Hydroxyethyl methacrylate	868-77-9	Water flea	Experimental	48 hours	EC50	380 mg/l
2-Hydroxyethyl methacrylate	868-77-9	Green Algae	Experimental	72 hours	NOEC	160 mg/l
2-Hydroxyethyl methacrylate	868-77-9	Water flea	Experimental	21 days	NOEC	24.1 mg/l
Exo-1,7,7-trimethylbicyclo[2.2.1] hept-2-yl methacrylate	7534-94-3	Green Algae	Experimental	72 hours	EC50	2.3 mg/l
Exo-1,7,7-trimethylbicyclo[2.2.1] hept-2-yl methacrylate	7534-94-3	Water flea	Experimental	48 hours	EC50	1.1 mg/l
Exo-1,7,7-trimethylbicyclo[2.2.1] hept-2-yl methacrylate	7534-94-3	Zebra Fish	Experimental	96 hours	LC50	1.8 mg/l
Exo-1,7,7-trimethylbicyclo[2.2.1] hept-2-yl methacrylate	7534-94-3	Green Algae	Experimental	72 hours	Effect Concentration 10%	0.751 mg/l
Exo-1,7,7-trimethylbicyclo[2.2.1] hept-2-yl methacrylate	7534-94-3	Water flea	Experimental	21 days	NOEC	0.233 mg/l
Fillers (NJTS Reg. No. 04499600-6923)	Trade Secret	Water flea	Experimental	48 hours	LC50	>1,100 mg/l
BIS-MEPP (polymer)	41637-38-1	Green Algae	Estimated	72 hours	Effect Level 50%	>100 mg/l
BIS-MEPP (polymer)	41637-38-1	Water flea	Estimated	48 hours	Effect Level 50%	>100 mg/l
BIS-MEPP (polymer)	41637-38-1	Zebra Fish	Estimated	96 hours	Lethal Level 50%	>100 mg/l
Poly[oxy(methyl-1,2-ethanediyl)], .a.-(2-methyl-1-oxo-2-propenyl)-.w.-(phosphonooxy)-	95175-93-2		Data not available or insufficient for classification			
Tetrahydrofurfuryl alcohol	97-99-4	Green Algae	Experimental	72 hours	EC50	>100 mg/l
Tetrahydrofurfuryl alcohol	97-99-4	Ricefish	Experimental	96 hours	LC50	>100 mg/l
Tetrahydrofurfuryl alcohol	97-99-4	Water flea	Experimental	48 hours	EC50	>100 mg/l
Tetrahydrofurfuryl alcohol	97-99-4	Green Algae	Experimental	72 hours	NOEC	>100 mg/l
Tetrahydrofurfuryl alcohol	97-99-4	Water flea	Experimental	21 days	NOEC	>100 mg/l
Naphthenic acids, copper salts	1338-02-9	Green Algae	Estimated	72 hours	EC50	0.629 mg/l
Naphthenic acids, copper salts	1338-02-9	Water flea	Estimated	48 hours	EC50	0.0756 mg/l
Naphthenic acids, copper salts	1338-02-9	Zebra Fish	Estimated	96 hours	LC50	0.0702 mg/l
Naphthenic acids, copper salts	1338-02-9	Algae or other aquatic plants	Estimated	hours	NOEC	0.132 mg/l

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green and Low Odor Acrylic Adhesive 8810NS Green, Part B

Naphthenic acids, copper salts	1338-02-9	Fathead minnow	Estimated	32 days	Effect Concentration 10%	0.0354 mg/l
Naphthenic acids, copper salts	1338-02-9	Water flea	Estimated	21 days	NOEC	0.0756 mg/l

12.2. Persistence and degradability

Material	CAS Nbr	Test type	Duration	Study Type	Test result	Protocol
Tetrahydrofurfuryl methacrylate	2455-24-5	Experimental Biodegradation	28 days	BOD	75 % BOD/ThBOD	OECD 301F - Manometric respirometry
Acrylonitrile - butadiene polymer	9003-18-3	Data not available - insufficient			N/A	
2-Hydroxyethyl methacrylate	868-77-9	Experimental Biodegradation	14 days	BOD	95 % BOD/ThBOD	OECD 301C - MITI test (I)
Exo-1,7,7-trimethylbicyclo[2.2.1]hept-2-yl methacrylate	7534-94-3	Estimated Photolysis		Photolytic half-life (in air)	1.12 days (t 1/2)	Other methods
Exo-1,7,7-trimethylbicyclo[2.2.1]hept-2-yl methacrylate	7534-94-3	Experimental Biodegradation	28 days	CO2 evolution	70 % weight	OECD 310 CO2 Headspace
Fillers (NJTS Reg. No. 04499600-6923)	Trade Secret	Data not available - insufficient			N/A	
BIS-MEPP (polymer)	41637-38-1	Experimental Biodegradation	28 days	Percent degraded	24 % degraded	Other methods
Poly[oxy(methyl-1,2-ethanediyl)], .a.-(2-methyl-1-oxo-2-propenyl)-.w.-(phosphonoxy)-	95175-93-2	Data not available - insufficient			N/A	
Tetrahydrofurfuryl alcohol	97-99-4	Experimental Biodegradation	28 days	BOD	92 % weight	OECD 301C - MITI test (I)
Naphthenic acids, copper salts	1338-02-9	Data not available - insufficient			N/A	

12.3 : Bioaccumulative potential

Material	Cas No.	Test type	Duration	Study Type	Test result	Protocol
Tetrahydrofurfuryl methacrylate	2455-24-5	Estimated Bioconcentration		Bioaccumulation factor	3.42	Estimated: Bioconcentration factor
Acrylonitrile - butadiene polymer	9003-18-3	Data not available or insufficient for classification	N/A	N/A	N/A	N/A
2-Hydroxyethyl methacrylate	868-77-9	Experimental Bioconcentration		Log Kow	0.42	Other methods
Exo-1,7,7-trimethylbicyclo[2.2.1]hept-2-yl methacrylate	7534-94-3	Estimated Bioconcentration		Bioaccumulation factor	39	Estimated: Bioconcentration factor
Fillers (NJTS Reg. No. 04499600-6923)	Trade Secret	Data not available or insufficient for classification	N/A	N/A	N/A	N/A
BIS-MEPP (polymer)	41637-38-1	Estimated Bioconcentration		Bioaccumulation factor	6.6	Other methods
Poly[oxy(methyl-1,2-ethanediyl)], .a.-(2-methyl-1-oxo-2-propenyl)-.w.-(phosphonoxy)-	95175-93-2	Data not available or insufficient for classification	N/A	N/A	N/A	N/A
Tetrahydrofurfuryl alcohol	97-99-4	Experimental Bioconcentration		Log Kow	-0.11	Other methods
Naphthenic acids, copper salts	1338-02-9	Estimated BCF-Carp	42 days	Bioaccumulation factor	≤27	OECD 305E - Bioaccumulation flow-through fish test

12.4. Mobility in soil

Please contact manufacturer for more details

12.5. Results of the PBT and vPvB assessment

This material does not contain any substances that are assessed to be a PBT or vPvB

12.6. Other adverse effects

No information available.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Dispose of completely cured (or polymerized) material in a permitted industrial waste facility. As a disposal alternative, incinerate uncured product in a permitted waste incineration facility. Proper destruction may require the use of additional fuel during incineration processes. Combustion products will include halogen acid (HCl/HF/HBr). Facility must be capable of handling halogenated materials. Empty drums/barrels/containers used for transporting and handling hazardous chemicals (chemical substances/mixtures/preparations classified as Hazardous as per applicable regulations) shall be considered, stored, treated & disposed of as hazardous wastes unless otherwise defined by applicable waste regulations. Consult with the respective regulating authorities to determine the available treatment and disposal facilities.

The coding of a waste stream is based on the application of the product by the consumer. Since this is out of the control of 3M, no waste code(s) for products after use will be provided. Please refer to the European Waste Code (EWC - 2000/532/EC and amendments) to assign the correct waste code to your waste stream. Ensure national and/or regional regulations are complied with and always use a licensed waste contractor.

EU waste code (product as sold)

08 04 09*	Waste adhesives and sealants containing organic solvents or other dangerous substances
20 01 27*	Paint, inks, adhesives and resins containing dangerous substances

SECTION 14: Transportation information

62-2854-9531-3

Not hazardous for transportation

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

A chemical safety assessment has not been carried out for this substance/mixture in accordance with Regulation (EC) No 1907/2006, as amended.

SECTION 16: Other information

List of relevant H statements

H226	Flammable liquid and vapour.
H302	Harmful if swallowed.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.

3M(TM) Scotch-Weld(TM) Low Odor Acrylic Adhesive DP8810NS Green and Low Odor Acrylic Adhesive 8810NS Green, Part B

H318	Causes serious eye damage.
H319	Causes serious eye irritation.
H360D	May damage the unborn child.
H360Df	May damage the unborn child. Suspected of damaging fertility.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.

Revision information:

No revision information

DISCLAIMER: The information on this Safety Data Sheet is based on our experience and is correct to the best of our knowledge at the date of publication, but we do not accept any liability for any loss, damage or injury resulting from its use (except as required by law). The information may not be valid for any use not referred to in this Data Sheet or use of the product in combination with other materials. For these reasons, it is important that customers carry out their own test to satisfy themselves as to the suitability of the product for their own intended applications.

3M United Kingdom MSDSs are available at www.3M.com/uk