350 PH Screwdriver for Phillips screws, PH 1 x 300 mm

Screwdrivers Kraftform Plus - Series 300







EAN/GTIN: Part no.: Article no.: 4013288003621 05008715001 350 PH Dimension: Weight: Country of origin: Customs tariff number:

398x33x33 mm 80 g CZ 82054000







- Screwdriver for cross-recess screws, Phillips
- Smooth hard zones for high speed turning, soft grip zones for high torque transfer
- "Take it easy" Tool Finder: colour coding according to profile and size
- · Hexagonal anti-roll feature against rolling away
- Lasertip tips for more secure fit in the screw head

High quality Kraftform Plus screwdriver. Multi-component Kraftform Plus handle for pleasant, ergonomic working that makes blisters and calluses a thing of the past. Hard gripping zones for high working speeds whereas soft zones ensure high torque transfer. "Take it easy" tool finder with colour coding according to profiles and size stamp – for simple and rapid accessing of the required tool. The hexagonal non-roll feature prevents any rolling away at the workplace.

Screwdrivers Kraftform Plus - Series 300



Lasertip prevents slipping out

Lasertip

Reduced contact pressure



Kraftform Plus screwdrivers – ergonomics you can grasp. They relieve the entire hand-arm system even when used intensively. Along with other technical and product advantages such as the Lasertip for a secure fit in the screw head, Kraftform screwdrivers are the ideal choice whenever manual screwdriving jobs are concerned.



It happens time and time again that the tip slips out of the screw head when screwdriving, sometimes damaging valuable surfaces or even causing injury. The tips of the Wera Lasertip screwdrivers are microscopically roughened by means of a laser. This rough surface literally "bites" itself firmly into the screw head. Slipping out becomes a thing of the past.



A precisely-focused laser creates a sharp-edged surface structure. This laser treatment results in an edge hardness of up to 1000 HV 0.3. Wera Lasertip "bites" itself into the screw head and prevents any slips out of the recess. It is available for screwdrivers for slotted, Phillips and Pozidriv screws.

Wera Lasertip reduces the contact pressure required and enhances force transfer – meaning less screwdriving effort is required. Screwdriving becomes safer and easier. Screwdrivers Kraftform Plus - Series 300



Kraftform

Large contact area



The basic idea for the prototype of the Kraftform handle - that the hand should dictate the design has, right through to today, proved to be correct. In cooperation with the internationally recognised Fraunhofer IAO Institute, Wera developed a screwdriver handle designed to match the shape of the human hand as long ago as 1960s. After a long the development phase, the Wera Kraftform handle was launched to the market in 1968. It has been optimised through the years with new technologies, but has kept its proven shape. After all, the human hand has not changed either.



The large contact area – with particularly high friction to the soft zones – results in high torque transfer without any bruising from the edges.

Rapid hand repositioning

Non-roll feature



The hard materials used for the handle ensure rapid hand repositioning without any danger of the skin "sticking" to the handle. The surrounding hard zones with large diameters glide like wheels across the hand.



The hexagonal non-roll feature prevents any rolling away at the workplace.

Screwdrivers Kraftform Plus – Series 300



More variants of this product family:

| | \mathbf{O} | ∏ ↓ wm | ∭ v wm | Mm | |
|---------------------------|--------------|-----------|-----------|------|-------|
| | | | | | |
| 05008705001 ¹⁾ | PH 0 | 60 | 81 | 3.0 | 2 3/8 |
| 050087060011) | PH 0 | 100 | 81 | 3.0 | 4 |
| 05008710001 | PH 1 | 80 | 98 | 4.5 | 3 1/8 |
| 05008712001 | PH 1 | 200 | 98 | 4.5 | 8 |
| 05008715001 ¹⁾ | PH 1 | 300 | 98 | 4.5 | 12 |
| 05008720001 | PH 2 | 100 | 105 | 6.0 | 4 |
| 05008723001 | PH 2 | 150 | 105 | 6.0 | 6 |
| 05008725001 | PH 2 | 200 | 105 | 6.0 | 8 |
| 050087300011) | PH 2 | 300 | 105 | 6.0 | 12 |
| 05008735001 | PH 3 | 150 | 112 | 8.0 | 6 |
| 050087400011) | PH 4 | 200 | 112 | 10.0 | 8 |

1) without Lasertip